



Price List Cooking

September 2024

Table of Contents

Ranges	03
Range Product Highlights	03
Ranges	04
Rangetops	18
Rangetops Product Highlights	18
Rangetops	19
Convection Ovens	24
Convection Ovens Product Highlights	24
Convection Ovens	25
Speed, Combi-Steam & Microwave Ovens	38
Speed, Combi-Steam & Microwave Ovens Product Highlights	38
Speed, Combi-Steam & Microwave Ovens	39
Combi-Steam Ovens Optional Accessories	51
Handle Options	70
Gas Cooktops	71
Gas Cooktops Product Highlights	71
Gas Cooktops	72
Electric & Induction Cooktops	80
Electric & Induction Cooktops Product Highlights	80
Electric & Induction Cooktops	81
Ventilation Hoods	91
Ventilation Hoods Product Highlights	91
Ventilation Hoods	92

Warming Drawers & Vacuum Sealing Drawers 114

 Warming Drawers & Vacuum Sealing Drawers Product Highlights 114

 Warming Drawers & Vacuum Sealing Drawers 115

CVA Built-In Coffee 127

 CVA Built-In Coffee Product Highlights 127

 CVA Built-In Coffee 128

CM Countertop Coffee 134

 CM Countertop Coffee Product Highlights 134

 CM Countertop Coffee 135

Accessories & Consumables 140

Product Highlights

Ranges

*See specific models for details

FEATURE	DESCRIPTION
Wireless Precision Probe	Precise temperature control, with 4 points of temperature monitoring and wireless connection.
Moisture Plus	Adds a burst of steam for extraordinary roasting and baking results.
M Touch Controls with MotionReact	Operate your appliance quickly and intuitively by tapping and swiping the touch display. MotionReact turns on the light when it detects movement near the oven.
Automatic Programs	Miele guides you through hundreds of easy-to-use cooking programs.
M Pro Griddle	The infrared griddle delivers even heat distribution. Perfect for eggs, pancakes, fish or steak.
Backlit Precision Knobs	This elegant feature let's you know at a glance whether your burners are on or off.
Miele@home	Interact with your Miele appliances from your mobile device with Miele@home.

Note: Ranges are not convertible, choose the correct fuel for the application when selecting a range

30" All Gas Range



MODEL	MATERIAL	UMRP/RETAIL
HR 1124-3 AG	11791360	\$6,799 / \$7,299
HR 1124-3 AG LP	11791390	\$6,799 / \$7,299

SPECIFICATIONS

Burners	3 x 19,500 BTU 1 x 12,500 BTU
Width	29 ^{15/16} in (760 mm)
Height	35 ^{1/5} - 37 in (902 - 940 mm)
Depth	27 ^{1/2} in (698 mm)
Shipping Weight	337.3 lbs (153 kg)

FEATURES

- EasyControl - Easy to Read and Control
- Four Powerful Burners - Plenty of Cooking Space
- Self Clean Oven - For Easy Cleaning
- TwinPower Fans - Convection Oven for more even Baking and Better Roasting

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL	INCLUDED
PerfectClean Universal Tray	9811950	\$180 / \$180	1
30 in Wire rack with PyroFit	9811970	\$185 / \$185	1
30 in Telescopic Rack w/ PyroFit	12072650	\$325 / \$325	1

OPTIONAL ACCESSORIES

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Backsplash 30 in width	9908930	\$259 / \$259
Backguard 12 in/30 in width	9908710	\$349 / \$349
Backguard 20 in/30 in width	9908740	\$389 / \$389
WokRing	9974600	\$95 / \$95
PerfectClean Grilling and Roasting Insert	9520630	\$125 / \$125
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75

30" Dual Fuel Range



MODEL	MATERIAL	UMRP/RETAIL
HR 1724-3 DF	11791530	\$7,399 / \$7,899
HR 1724-3 DF LP	11791540	\$7,399 / \$7,899

SPECIFICATIONS	
Burners	3 x 19,500 BTU 1 x 12,500 BTU
Width	29 ^{15/16} in (760 mm)
Height	35 ^{1/5} - 37 in (902 - 940 mm)
Depth	27 ^{1/2} in (698 mm)
Shipping Weight	337.3 lbs (153 kg)

- FEATURES**
- EasyControl - Easy to Read and Control
 - Four Powerful Burners - Plenty of Cooking Space
 - Self Clean Oven - For Easy Cleaning
 - TwinPower Fans - Convection Oven for More even Baking and Better Roasting
 - Dual Fuel - Superior Control of Oven Temperatures

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL	INCLUDED
PerfectClean Universal Tray	9811950	\$180 / \$180	1
30 in Wire rack with PyroFit	9811970	\$185 / \$185	1
30 in Telescopic Rack w/ PyroFit	12072650	\$325 / \$325	1

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Backsplash 30 in width	9908930	\$259 / \$259
Backguard DF 12 in/30 in width	9908760	\$349 / \$349
Backguard DF 20 in/30 in width	9908860	\$389 / \$389
WokRing	9974600	\$95 / \$95
PerfectClean Grilling and Roasting Insert	9520630	\$125 / \$125
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75

30" Dual Fuel Range



MODEL	MATERIAL	UMRP/RETAIL
HR 1924-3 DF	11791550	\$8,599 / \$8,899
HR 1924-3 DF LP	11791560	\$8,599 / \$8,899

SPECIFICATIONS

Burners	3 x 19,500 BTU 1 x 12,500 BTU
Width	29 ^{15/16} in (760 mm)
Height	38 ^{5/8} in (980 mm)
Depth	27 ^{1/2} in (698 mm)
Shipping Weight	337.3 lbs (153 kg)

FEATURES

- Automatic Programs - Easily Master New Recipes
- M Touch Display - Simple to use Touch Controls
- Moisture Plus - For Perfect Baking and Roasting Results
- Wireless Precision Probe - Simple to Monitor Food Temperature
- Miele@home - Monitor Appliances from your Mobile Device
- MotionReact - Appliance Reacts to you when Approached

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL	INCLUDED
PerfectClean Universal Tray	9811950	\$180 / \$180	1
30 in Wire rack with PyroFit	9811970	\$185 / \$185	2
30 in Telescopic Rack w/ PyroFit	12072650	\$325 / \$325	1
PerfectClean Grilling and Roasting Insert	9520630	\$125 / \$125	1
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110	1

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Backsplash 30 in width	9908930	\$259 / \$259
Backguard DF 12 in/30 in width	9908760	\$349 / \$349
Backguard DF 20 in/30 in width	9908860	\$389 / \$389
WokRing	9974600	\$95 / \$95
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75

30" Induction Range



MODEL	MATERIAL	UMRP/RETAIL
HR 1422-3 i	12298850	\$6,999 / \$7,499
SPECIFICATIONS		
Burners	4-6 ¹ / ₄ in diameter 1,250-2,000W (208V) 1,450-2,300W (240V)	
	5 ¹ / ₂ -7 ³ / ₄ in diameter 1,700-2,700W (208V) 1,950-3,100W (240V)	
	6 ¹ / ₄ -9 in diameter 2,100-3,500W (208V) 2,400-3,850W (240V)	
	7-11 in diameter 2,300-3,350W (208V) 2,700-3,850W (240V)	
	Total Power Output 6,700W (208V) 7,700W (240V)	
Width	29 ¹⁵ / ₁₆ in (760 mm)	
Height	35 ¹ / ₅ - 37 in (902 - 940 mm)	
Depth	27 ¹ / ₂ in (698 mm)	
Shipping Weight	337.3 lbs (153 kg)	

FEATURES

- Twin Power - Fast and Even Heating Time
- Self Cleaning - Minimal Cleaning Effort
- State of the Art Cooking Technology
- Easy Opening and Closing and - Noise and Vibration Absorbers
- MotionReact - Appliance Reacts to you when Approached
- 4 Zone Induction Cooktop - Precise Temperature Control

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL	INCLUDED
PerfectClean Universal Tray	9811950	\$180 / \$180	1
30 in Wire rack with PyroFit	9811970	\$185 / \$185	2
30 in Telescopic Rack w/ PyroFit	12072650	\$325 / \$325	1
PerfectClean Grilling and Roasting Insert	9520630	\$125 / \$125	1
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110	1

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Backsplash 30 in width	9908930	\$259 / \$259
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75

30" Induction Range



MODEL	MATERIAL	UMRP/RETAIL
HR 1622-3 i	11791520	\$9,299 / \$9,799
SPECIFICATIONS		
Burners	4-6 ¹ / ₄ in diameter 1,250-2,000W (208V) 1,450-2,300W (240V)	
	5 ¹ / ₂ -7 ³ / ₄ in diameter 1,700-2,700W (208V) 1,950-3,100W (240V)	
	6 ¹ / ₄ -9 in diameter 2,100-3,500W (208V) 2,400-3,850W (240V)	
	7-11 in diameter 2,300-3,350W (208V) 2,700-3,850W (240V)	
	Total Power Output 6,700W (208V) 7,700W (240V)	
Width	29 ¹⁵ / ₁₆ in (760 mm)	
Height	35 ¹ / ₅ - 37 in (902 - 940 mm)	
Depth	27 ¹ / ₂ in (698 mm)	
Shipping Weight	337.3 lbs (153 kg)	

FEATURES

- Automatic Programs - Easily Master New Recipes
- M Touch Display - Simple to use Touch Controls
- Moisture Plus - For Perfect Baking and Roasting Results
- Wireless Precision Probe - Simple to Monitor Food Temperature
- Miele@home - Monitor Appliances from your Mobile Device
- MotionReact - Appliance Reacts to you when Approached
- 4 Zone Induction Cooktop - Precise Temperature Control

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL	INCLUDED
PerfectClean Universal Tray	9811950	\$180 / \$180	1
30 in Wire rack with PyroFit	9811970	\$185 / \$185	2
30 in Telescopic Rack w/ PyroFit	12072650	\$325 / \$325	1
PerfectClean Grilling and Roasting Insert	9520630	\$125 / \$125	1
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110	1

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Backsplash 30 in width	9908930	\$259 / \$259
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75

36" All Gas Range



MODEL	MATERIAL	UMRP/RETAIL
HR 1134-3 AG	11791410	\$8,199 / \$8,699
HR 1134-3 AG LP	11791430	\$8,199 / \$8,699

SPECIFICATIONS	
Burners	3 x 19,500 BTU 2 x 9,000 BTU 1 x 8,000 BTU
Width	35 ¹⁵ / ₁₆ in (915 mm)
Height	35 ¹ / ₅ - 37 in (902 - 940 mm)
Depth	27 ¹ / ₂ in (698 mm)
Shipping Weight	448.6 lbs (203.5 kg)

- FEATURES**
- EasyControl - Easy to Read and Control
 - Six Powerful Burners - Plenty of Cooking Space
 - Self Clean Oven - For Easy Cleaning
 - TwinPower Fans - Convection Oven for More Even Baking and Better Roasting

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL	INCLUDED
PerfectClean Universal Tray	9811950	\$180 / \$180	1
36 in Wire Rack w/ PyroFit	9858830	\$225 / \$225	1
36 in Telescopic Rack w/ PyroFit	12072710	\$345 / \$345	1

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Backsplash - 36 in width	9909090	\$289 / \$289
Backguard 12 in / 36 in width	9908730	\$375 / \$375
Backguard 20 in / 36 in width	9908750	\$409 / \$409
WokRing	9974600	\$95 / \$95
PerfectClean Grilling and Roasting Insert	9520630	\$125 / \$125
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75

36" Dual Fuel Range



MODEL	MATERIAL	UMRP/RETAIL
HR 1934-3 DF	11791570	\$12,199 / \$12,499
HR 1934-3 DF LP	11791590	\$12,199 / \$12,499

SPECIFICATIONS

Burners	3 x 19,500 BTU 2 x 9,000 BTU 1 x 8,000 BTU
Width	35 ¹⁵ / ₁₆ in (915 mm)
Height	35 ¹ / ₅ - 37 in (902 - 940 mm)
Depth	27 ¹ / ₂ in (698 mm)
Shipping Weight	448.6 lbs (203.5 kg)

FEATURES

- Automatic Programs - Easily Master New Recipes
- M Touch Display - Simple to Use Touch Controls
- Moisture Plus - For Perfect Baking and Roasting Results
- Wireless Precision Probe - Simple to Monitor Food Temperature
- Miele@home - Monitor your Appliances from your Mobile Device
- MotionReact - Appliance Reacts to you when Approached

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL	INCLUDED
PerfectClean Universal Tray	9811950	\$180 / \$180	1
36 in Wire Rack w/ PyroFit	9858830	\$225 / \$225	2
36 in Telescopic Rack w/ PyroFit	12072710	\$345 / \$345	1
PerfectClean Grilling and Roasting Insert	9520630	\$125 / \$125	1
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110	1

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Backsplash - 36 in width	9909090	\$289 / \$289
Backguard DF 12 in / 36 in width	9908770	\$375 / \$375
Backguard DF 20 in / 36 in width	9908900	\$409 / \$409
WokRing	9974600	\$95 / \$95
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75

36" All Gas Range With M Pro Infrared Grill



MODEL	MATERIAL	UMRP/RETAIL
HR 1135-3 AG GR	11791450	\$9,199 / \$9,699

SPECIFICATIONS

Burners	2 x 19,500 BTU 1 x 9,000 BTU 1 x 8,000 BTU
Width	35 ^{15/16} in (915 mm)
Height	35 ^{1/5} - 37 in (902 - 940 mm)
Depth	27 ^{1/2} in (698 mm)
Shipping Weight	448.6 lbs (203.5 kg)

FEATURES

- EasyControl - Easy to Read and Control
- Four Powerful Burners - Versatile Cooking Space
- Self Clean Oven - For Easy Cleaning
- TwinPower Fans - Convection Oven for More Even Baking and Better Roasting
- M Pro Grill - A Powerful Grill on your Cooktop

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL	INCLUDED
PerfectClean Universal Tray	9811950	\$180 / \$180	1
36 in Wire Rack w/ PyroFit	9858830	\$225 / \$225	1
36 in Telescopic Rack w/ PyroFit	12072710	\$345 / \$345	1
Grill / Griddle Cover	9974610	\$250 / \$250	1

OPTIONAL ACCESSORIES

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Backsplash - 36 in width	9909090	\$289 / \$289
Backguard 12 in / 36 in width	9908730	\$375 / \$375
Backguard 20 in / 36 in width	9908750	\$409 / \$409
WokRing	9974600	\$95 / \$95
PerfectClean Grilling and Roasting Insert	9520630	\$125 / \$125
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75

36" All Gas Range With M Pro Infrared Griddle



MODEL	MATERIAL	UMRP/RETAIL
HR 1136-3 AG GD	11791500	\$9,199 / \$9,699
HR 1136-3 AG GD LP	11791510	\$9,199 / \$9,699

SPECIFICATIONS

Burners	2 x 19,500 BTU 1 x 9,000 BTU 1 x 8,000 BTU
Width	35 ^{15/16} in (915 mm)
Height	35 ^{1/5} - 37 in (902 - 940 mm)
Depth	27 ^{1/2} in (698 mm)
Shipping Weight	448.6 lbs (203.5 kg)

FEATURES

- EasyControl - Easy to Read and Control
- Four Powerful Burners - Plenty of Cooking Space
- Self Clean Oven - For Easy Cleaning
- TwinPower Fans - Convection Oven for More Even Baking and Better Roasting
- M Pro Infrared Griddle - Great Results for Everything from Pancakes to Hamburgers

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL	INCLUDED
PerfectClean Universal Tray	9811950	\$180 / \$180	1
36 in Wire Rack w/ PyroFit	9858830	\$225 / \$225	1
36 in Telescopic Rack w/ PyroFit	12072710	\$345 / \$345	1
Grill / Griddle Cover	9974610	\$250 / \$250	1

OPTIONAL ACCESSORIES

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Backsplash - 36 in width	9909090	\$289 / \$289
Backguard 12 in / 36 in width	9908730	\$375 / \$375
Backguard 20 in / 36 in width	9908750	\$409 / \$409
WokRing	9974600	\$95 / \$95
PerfectClean Grilling and Roasting Insert	9520630	\$125 / \$125
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75

36" Dual Fuel Range With M Pro Infrared Grill



MODEL	MATERIAL	UMRP/RETAIL
HR 1935-3 DF GR	11791600	\$13,199 / \$13,699

SPECIFICATIONS

Burners	2 x 19,500 BTU 1 x 9,000 BTU 1 x 8,000 BTU
Width	35 ¹⁵ / ₁₆ in (915 mm)
Height	35 ¹ / ₅ - 37 in (902 - 940 mm)
Depth	27 ¹ / ₂ in (698 mm)
Shipping Weight	448.6 lbs (203.5 kg)

FEATURES

- Automatic Programs - Easily Master New Recipes
- M Touch Display - Simple to use Touch Controls
- Moisture Plus - For Perfect Baking and Roasting Results
- Wireless Precision Probe - Simple to Monitor Food Temperature
- Miele@home - Monitor your Appliances from your Mobile Device
- MotionReact - Appliance Reacts to you when Approached
- M Pro Grill - A Powerful Grill on your Cooktop

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL	INCLUDED
PerfectClean Universal Tray	9811950	\$180 / \$180	1
36 in Wire Rack w/ PyroFit	9858830	\$225 / \$225	2
36 in Telescopic Rack w/ PyroFit	12072710	\$345 / \$345	1
PerfectClean Grilling and Roasting Insert	9520630	\$125 / \$125	1
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110	1
Grill / Griddle Cover	9974610	\$250 / \$250	1

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Backsplash - 36 in width	9909090	\$289 / \$289
Backguard DF 12 in / 36 in width	9908770	\$375 / \$375
Backguard DF 20 in / 36 in width	9908900	\$409 / \$409
WokRing	9974600	\$95 / \$95
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75

36" Dual Fuel Range With M Pro Infrared Griddle



MODEL	MATERIAL	UMRP/RETAIL
HR 1936-3 DF GD	11791610	\$13,199 / \$13,699
HR 1936-3 DF GD LP	11791630	\$13,199 / \$13,699

SPECIFICATIONS

Burners	2 x 19,500 BTU 1 x 9,000 BTU 1 x 8,000 BTU
Width	35 ¹⁵ / ₁₆ in (915 mm)
Height	35 ¹ / ₅ - 37 in (902 - 940 mm)
Depth	27 ¹ / ₂ in (698 mm)
Shipping Weight	448.6 lbs (203.5 kg)

FEATURES

- Automatic Programs - Easily Master New Recipes
- M Touch Display - Simple to use Touch Controls
- Moisture Plus - For Perfect Baking and Roasting Results
- Wireless Precision Probe - Simple to Monitor Food Temperature
- Miele@home - Monitor your Appliances from your Mobile Device
- MotionReact - Appliance Reacts to you when Approached
- M Pro Infrared Griddle - Great Results for Everything from Pancakes to Hamburgers

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL	INCLUDED
PerfectClean Universal Tray	9811950	\$180 / \$180	1
36 in Wire Rack w/ PyroFit	9858830	\$225 / \$225	2
36 in Telescopic Rack w/ PyroFit	12072710	\$345 / \$345	1
PerfectClean Grilling and Roasting Insert	9520630	\$125 / \$125	1
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110	1
Grill / Griddle Cover	9974610	\$250 / \$250	1

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Backsplash - 36 in width	9909090	\$289 / \$289
Backguard DF 12 in / 36 in width	9908770	\$375 / \$375
Backguard DF 20 in / 36 in width	9908900	\$409 / \$409
WokRing	9974600	\$95 / \$95
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75

48" Dual Fuel Range



MODEL	MATERIAL	UMRP/RETAIL
HR 1954-3 DF	11791670	\$16,399 / \$16,899
HR 1954-3 DF LP	11791680	\$16,399 / \$16,899

SPECIFICATIONS

Burners	4 x 19,500 BTU (G/LP) 2 x 13,600 BTU (G) and 13,000 BTU (LP) 2 x 10,000 BTU (G/LP)
Width	47 ^{15/16} in (1,220 mm)
Height	35 ^{1/5} - 37 in (902 - 940 mm)
Depth	27 ^{1/2} in (698 mm)
Shipping Weight	637 lbs (289 kg)

FEATURES

- Automatic Programs - Easily Master New Recipes
- M Touch Display - Simple to use Touch Controls
- Moisture Plus - For Perfect Baking and Roasting Results
- Wireless Precision Probe - Simple to Monitor Food Temperature
- Miele@home - Monitor your Appliances from your Mobile Device
- Speed Oven - Maximum Versatility in One Appliance

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL	INCLUDED
PerfectClean Universal Tray	9811950	\$180 / \$180	1
48 in Wire Rack w/ PyroFit	9858840	\$189 / \$189	3
FlexiClips w/ PyroFit	9520710	\$225 / \$225	2
PerfectClean Grilling and Roasting Insert	9520630	\$125 / \$125	1
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110	1
Glass Tray 455x353mm	10141820	\$149 / \$149	2

OPTIONAL ACCESSORIES

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Backsplash - 48 in width	9909100	\$359 / \$359
Backguard 12 in / 48 in width	9908790	\$459 / \$459
Backguard 20 in / 48 in width	9908910	\$499 / \$499
WokRing	9974600	\$95 / \$95
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75

48" Dual Fuel Range With M Pro Infrared Grill



MODEL	MATERIAL	UMRP/RETAIL
HR 1955-3 DF GR	11791690	\$17,599 / \$18,099

SPECIFICATIONS

Burners	3 x 19,500 BTU (G) 1 x 13,600 BTU (G) 2 x 10,000 BTU (G)
Width	47 ^{15/16} in (1,220 mm)
Height	35 ^{1/5} - 37 in (902 - 940 mm)
Depth	27 ^{1/2} in (698 mm)
Shipping Weight	637 lbs (289 kg)

FEATURES

- Automatic Programs - Easily Master New Recipes
- M Touch Display - Simple to use Touch Controls
- Moisture Plus - For Perfect Baking and Roasting Results
- Wireless Precision Probe - Simple to Monitor Food Temperature
- Miele@home - Monitor your Appliances from your Mobile Device
- Speed Oven - Maximum Versatility in One Appliance
- M Pro Grill - A powerful Grill on your Cooktop

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL	INCLUDED
PerfectClean Universal Tray	9811950	\$180 / \$180	1
48 in Wire Rack w/ PyroFit	9858840	\$189 / \$189	3
FlexiClips w/ PyroFit	9520710	\$225 / \$225	2
PerfectClean Grilling and Roasting Insert	9520630	\$125 / \$125	1
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110	1
Glass Tray 455x353mm	10141820	\$149 / \$149	2
Grill / Griddle Cover	9974610	\$250 / \$250	1

OPTIONAL ACCESSORIES

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Backsplash - 48 in width	9909100	\$359 / \$359
Backguard 12 in / 48 in width	9908790	\$459 / \$459
Backguard 20 in / 48 in width	9908910	\$499 / \$499
WokRing	9974600	\$95 / \$95
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75

48" Dual Fuel Range With M Pro Infrared Griddle



MODEL	MATERIAL	UMRP/RETAIL
HR 1956-3 DF GD	11791700	\$17,599 / \$18,099
HR 1956-3 DF GD LP	11791750	\$17,599 / \$18,099

SPECIFICATIONS

Burners	3 x 19,500 BTU (G) 1 x 13,600 BTU (G) 2 x 10,000 BTU (G)
Width	47 ^{15/16} in (1,220 mm)
Height	35 ^{1/5} - 37 in (902 - 940 mm)
Depth	27 ^{1/2} in (698 mm)
Shipping Weight	637 lbs (289 kg)

FEATURES

- Automatic Programs - Easily Master New Recipes
- M Touch Display - Simple to use Touch Controls
- Moisture Plus - For Perfect Baking and Roasting Results
- Wireless Precision Probe - Simple to Monitor Food Temperature
- Miele@home - Monitor your Appliances from your Mobile Device
- Speed Oven - Maximum Versatility in One Appliance
- M Pro Infrared Griddle - Great Results for Everything from Pancakes to Hamburgers

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL	INCLUDED
PerfectClean Universal Tray	9811950	\$180 / \$180	1
48 in Wire Rack w/ PyroFit	9858840	\$189 / \$189	3
FlexiClips w/ PyroFit	9520710	\$225 / \$225	2
PerfectClean Grilling and Roasting Insert	9520630	\$125 / \$125	1
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110	1
Glass Tray 455x353mm	10141820	\$149 / \$149	2
Grill / Griddle Cover	9974610	\$250 / \$250	1

OPTIONAL ACCESSORIES

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Backsplash - 48 in width	9909100	\$359 / \$359
Backguard 12 in / 48 in width	9908790	\$459 / \$459
Backguard 20 in / 48 in width	9908910	\$499 / \$499
WokRing	9974600	\$95 / \$95
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75

Product Highlights

RangeTops

*See specific models for details

FEATURE	DESCRIPTION
TrueSimmer Function	Achieve the perfect temperature and even heat for simmering.
M Pro Griddle	The infrared griddle delivers even heat distribution. Perfect for eggs, pancakes, fish or steak.
Backlit Precision Knobs	This elegant feature let's you know at a glance whether your burners are on or off.
Convenient and Safe	Automatic re-ignition for all burners.
Easy Cleaning	ComfortClean dishwasher safe grates. Clean Touch Steel™ finish which resists fingerprints, scratches and smudges for a clean looking exterior.

30" All Gas RangeTop



MODEL	MATERIAL	UMRP/RETAIL
KMR 1124-3 G 30" All Gas RangeTop	11852270	\$3,899 / \$4,099

SPECIFICATIONS

Width	29 ^{15/16} in (762 mm)
Height	7 ^{1/2} in (191 mm)
Depth	26 ^{1/2} in (673 mm)
Shipping Weight	110.3 lbs (50 kg)

FEATURES

- Direct Control
- ComfortClean Gates
- Clean Touch Steel™ finish
- 4 Powerful Burners
- 1 Continuous Simmer Burner

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Backsplash - 30 in width	9908930	\$259 / \$259
Backguard - 12 in / 30 in width	9908760	\$349 / \$349
Backguard - 20 in / 30 in width	9908900	\$389 / \$389
Wok Ring	9974600	\$95 / \$95

MODEL	MATERIAL	UMRP/RETAIL
KMR 1124-3 LP 30" All Gas RangeTop	11852330	\$3,899 / \$4,099

SPECIFICATIONS

Width	29 ^{15/16} in (762 mm)
Height	7 ^{1/2} in (191 mm)
Depth	26 ^{1/2} in (673 mm)
Shipping Weight	110.3 lbs (50 kg)

FEATURES

- Direct Control
- ComfortClean Gates
- Clean Touch Steel™ Finish
- 4 Powerful Burners
- 1 Continuous Simmer Burner

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Backsplash - 30 in width	9908930	\$259 / \$259
Backguard - 12 in / 30 in width	9908760	\$349 / \$349
Backguard - 20 in / 30 in width	9908900	\$389 / \$389
Wok Ring	9974600	\$95 / \$95

36" All Gas RangeTop



MODEL	MATERIAL	UMRP/RETAIL
KMR 1134-3 G 36" All Gas RangeTop	11852340	\$4,699 / \$4,899

KMR 1134-3 LP 36" All Gas RangeTop	11852370	\$4,699 / \$4,899
---------------------------------------	----------	-------------------

SPECIFICATIONS

Width	35 ^{15/16} in (915 mm)
Height	7 ^{1/2} in (191 mm)
Depth	26 ^{1/2} in (673 mm)
Shipping Weight	134.5 lbs (61 kg)

FEATURES

- Direct Control
- ComfortClean gates
- Clean Touch Steel™ Finish
- 1 Continuous Simmer Burner
- 6 Powerful Burners

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Wok Ring	9974600	\$95 / \$95
Backsplash - 36 in width	9909090	\$289 / \$289
Backguard - 12 in / 36 in width	9908770	\$375 / \$375
Backguard - 20 in / 36 in width	9908900	\$409 / \$409

MODEL	MATERIAL	UMRP/RETAIL
KMR 1135-3 G GR 36" All Gas RangeTop with Grill	11852380	\$5,599 / \$5,799

SPECIFICATIONS

Width	35 ^{15/16} in (915 mm)
Height	7 ^{1/2} in (191 mm)
Depth	26 ^{1/2} in (673 mm)
Shipping Weight	145.5 lbs (66 kg)

FEATURES

- Direct Control
- ComfortClean Gates
- Clean Touch Steel™ Finish
- 4 Powerful Burners
- 1 Continuous Simmer Burner
- M Pro Grill

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
Grill / Griddle Cover	9974610	\$250 / \$250

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Wok Ring	9974600	\$95 / \$95
Backsplash - 36 in width	9909090	\$289 / \$289
Backguard - 12 in / 36 in width	9908770	\$375 / \$375
Backguard - 20 in / 36 in width	9908900	\$409 / \$409

36" All Gas RangeTop



MODEL	MATERIAL	UMRP/RETAIL
KMR 1136-3 G GD 36" All Gas RangeTop with Griddle	11852460	\$5,599 / \$5,799

SPECIFICATIONS

Width	35 ¹⁵ / ₁₆ in (915 mm)
Height	7 ¹ / ₂ in (191 mm)
Depth	26 ¹ / ₂ in (673 mm)
Shipping Weight	164.3 lbs (74.5 kg)

FEATURES

- Direct Control
- ComfortClean Gates
- Clean Touch Steel™ Finish
- 4 Powerful Burners
- 1 Continuous Simmer Burner
- M Pro Infrared Griddle

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
Grill / Griddle Cover	9974610	\$250 / \$250

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Wok Ring	9974600	\$95 / \$95
Backsplash - 36 in width	9909090	\$289 / \$289
Backguard - 12 in / 36 in width	9908770	\$375 / \$375
Backguard - 20 in / 36 in width	9908900	\$409 / \$409

MODEL	MATERIAL	UMRP/RETAIL
KMR 1136-3 LP GD 36" All Gas RangeTop with Griddle	11852550	\$5,599 / \$5,799

SPECIFICATIONS

Width	35 ¹⁵ / ₁₆ in (915 mm)
Height	7 ¹ / ₂ in (191 mm)
Depth	26 ¹ / ₂ in (673 mm)
Shipping Weight	164.3 lbs (74.5 kg)

FEATURES

- Direct Control
- ComfortClean Gates
- Clean Touch Steel™ Finish
- 4 Powerful Burners
- 1 Continuous Simmer Burner
- M Pro Infrared Griddle

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
Grill / Griddle Cover	9974610	\$250 / \$250

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Wok Ring	9974600	\$95 / \$95
Backsplash - 36 in width	9909090	\$289 / \$289
Backguard - 12 in / 36 in width	9908770	\$375 / \$375
Backguard - 20 in / 36 in width	9908900	\$409 / \$409

48" All Gas RangeTop



MODEL	MATERIAL	UMRP/RETAIL
KMR 1354-3 LP 48" All Gas RangeTop	11852570	\$5,899 / \$6,099

KMR 1354-3 G 48" All Gas RangeTop	11852560	\$5,899 / \$6,099
--------------------------------------	----------	-------------------

SPECIFICATIONS

Width	47 ¹⁵ / ₁₆ in (1220 mm)
Height	7 ¹ / ₂ in (191 mm)
Depth	26 ¹ / ₂ in (673 mm)
Shipping Weight	165.3 lbs (75 kg)

FEATURES

- Direct Control
- Clean Touch Steel™ Finish
- ComfortClean Gates
- 2 Continuous Simmer Burners

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Wok Ring	9974600	\$95 / \$95
Backsplash - 48 in width	9909100	\$359 / \$359
Backguard - 12 in / 48 in width	9908790	\$459 / \$459
Backguard - 20 in / 48 in width	9908910	\$499 / \$499

MODEL	MATERIAL	UMRP/RETAIL
KMR 1355-3 G GR 48" All Gas RangeTop with Grill	11852600	\$6,299 / \$6,499

SPECIFICATIONS

Width	47 ¹⁵ / ₁₆ in (1220 mm)
Height	7 ¹ / ₂ in (191 mm)
Depth	26 ¹ / ₂ in (673 mm)
Shipping Weight	174 lbs (79 kg)

FEATURES

- Direct Control
- ComfortClean Gates
- Clean Touch Steel™ Finish
- M Pro Grill
- 2 Continuous Simmer Burners

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
Grill / Griddle Cover	9974610	\$250 / \$250

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Wok Ring	9974600	\$95 / \$95
Backsplash - 48 in width	9909100	\$359 / \$359
Backguard - 12 in / 48 in width	9908790	\$459 / \$459
Backguard - 20 in / 48 in width	9908910	\$499 / \$499

48" All Gas RangeTop



MODEL	MATERIAL	UMRP/RETAIL
KMR 1356-3 G GD 48" All Gas RangeTop with Griddle	11852640	\$6,299 / \$6,499
KMR 1356-3 LP GD 48" All Gas RangeTop with Griddle	11852660	\$6,299 / \$6,499

SPECIFICATIONS

Width	47 ^{15/16} in (1220 mm)
Height	7 ^{1/2} in (191 mm)
Depth	26 ^{1/2} in (673 mm)
Shipping Weight	187.4 lbs (85 kg)

FEATURES

- Direct Control
- ComfortClean Gates
- Clean Touch Steel™ Finish
- M Pro Infrared Griddle
- 2 Continuous Simmer Burners

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
Grill / Griddle Cover	9974610	\$250 / \$250

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Wok Ring	9974600	\$95 / \$95
Backsplash - 48 in width	9909100	\$359 / \$359
Backguard - 12 in / 48 in width	9908790	\$459 / \$459
Backguard - 20 in / 48 in width	9908910	\$499 / \$499

Product Highlights

Convection Ovens

*See specific models for details

FEATURE	DESCRIPTION
FoodView	See the progress of your cooking on your mobile device with the in-oven camera.
Wireless Precision Probe	Precise temperature control, with 4 points of temperature monitoring and wireless connection.
M Touch Controls with MotionReact	Operate your appliance quickly and intuitively by tapping and swiping the touch display. Motion React turns on the light when it detects movement near the oven.
Moisture Plus	Adds a burst of steam for extraordinary roasting and baking results.
Automatic Programs	Miele guides you through hundreds of easy-to-use cooking programs.
Taste Control	Oven rapidly cools when cooking time is up to ensure that your meals are never overcooked.
Miele@home	Interact with your Miele appliances from your mobile device with Miele@home.

30" Convection Oven



MODEL	MATERIAL	UMRP/RETAIL
H 7780 BP 30" Convection Oven	11805560	\$8,199 / \$8,399

DESIGN LINE

ContourLine

SPECIFICATIONS

Width	29 ^{13/16} in (757 mm)
Height	28 ^{5/8} in (727 mm)
Depth	23 ^{3/4} in (603 mm)
Shipping Weight	215 lbs (98 kg)

FEATURES

- FoodView - In Oven Camera
- Wireless Precision Probe
- M Touch Controls with MotionReact
- Moisture Plus
- TasteControl
- Miele@home
- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray (1)	9811950	\$180 / \$180
30" Wire Rack w/ PyroFit (2)	9811970	\$185 / \$185
30" Telescopic Rack w/ PyroFit (1)	12072650	\$325 / \$325
PerfectClean Grilling and Roasting Insert (1)	9520630	\$125 / \$125
PerfectClean Perforated Baking Tray (1)	9520620	\$110 / \$110

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139

MODEL	MATERIAL	UMRP/RETAIL
H 7880 BP 30" Convection Oven	11805590	\$8,199 / \$8,399

DESIGN LINE

PureLine

SPECIFICATIONS

Width	29 ^{13/16} in (757 mm)
Height	28 ^{5/8} in (727 mm)
Depth	23 ^{3/4} in (603 mm)
Shipping Weight	215 lbs (98 kg)

FEATURES

- FoodView - In Oven Camera
- Wireless Precision Probe
- M Touch Controls with MotionReact
- Moisture Plus
- TasteControl
- Miele@home
- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray (1)	9811950	\$180 / \$180
30" Wire Rack w/ PyroFit (2)	9811970	\$185 / \$185
30" Telescopic Rack w/ PyroFit (1)	12072650	\$325 / \$325
PerfectClean Grilling and Roasting Insert (1)	9520630	\$125 / \$125
PerfectClean Perforated Baking Tray (1)	9520620	\$110 / \$110

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139

30" Convection Oven



MODEL	MATERIAL	UMRP/RETAIL
H 7880 BP 30" Convection Oven	11805610	\$8,199 / \$8,399

DESIGN LINE	FINISH
VitroLine	Obsidian black

SPECIFICATIONS

Width	29 ^{13/16} in (757 mm)
Height	28 ^{5/8} in (727 mm)
Depth	23 ^{3/4} in (603 mm)
Shipping Weight	215 lbs (98 kg)

FEATURES

- FoodView - In Oven Camera
- Wireless Precision Probe
- M Touch Controls with MotionReact
- Moisture Plus
- TasteControl
- Miele@home
- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray (1)	9811950	\$180 / \$180
30" Wire Rack w/ PyroFit (2)	9811970	\$185 / \$185
30" Telescopic Rack w/ PyroFit (1)	12072650	\$325 / \$325
PerfectClean Grilling and Roasting Insert (1)	9520630	\$125 / \$125
PerfectClean Perforated Baking Tray (1)	9520620	\$110 / \$110

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139

MODEL	MATERIAL	UMRP/RETAIL
H 7880 BP 30" Convection Oven	11805580	\$8,199 / \$8,399

DESIGN LINE	FINISH
VitroLine	Brilliant white

SPECIFICATIONS

Width	29 ^{13/16} in (757 mm)
Height	28 ^{5/8} in (727 mm)
Depth	23 ^{3/4} in (603 mm)
Shipping Weight	215 lbs (98 kg)

FEATURES

- FoodView - In Oven Camera
- Wireless Precision Probe
- M Touch Controls with MotionReact
- Moisture Plus
- TasteControl
- Miele@home
- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray (1)	9811950	\$180 / \$180
30" Wire Rack w/ PyroFit (2)	9811970	\$185 / \$185
30" Telescopic Rack w/ PyroFit (1)	12072650	\$325 / \$325
PerfectClean Grilling and Roasting Insert (1)	9520630	\$125 / \$125
PerfectClean Perforated Baking Tray (1)	9520620	\$110 / \$110

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139

30" Convection Oven



MODEL	MATERIAL	UMRP/RETAIL
H 7880 BP 30" Convection Oven	11805600	\$8,199 / \$8,399

DESIGN LINE	FINISH
VitroLine	Graphite grey

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	28 ^{5/8} in (727 mm)
Depth	23 ^{3/4} in (603 mm)
Shipping Weight	215 lbs (98 kg)

FEATURES	
- FoodView	- TasteControl
- Wireless Precision Probe	- Miele@home
- M Touch Controls with MotionReact	- Automatic Programs
- Moisture Plus	

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray (1)	9811950	\$180 / \$180
30" Wire Rack w/ PyroFit (2)	9811970	\$185 / \$185
30" Telescopic Rack w/ PyroFit (1)	12072650	\$325 / \$325
PerfectClean Grilling and Roasting Insert (1)	9520630	\$125 / \$125
PerfectClean Perforated Baking Tray (1)	9520620	\$110 / \$110

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139

MODEL	MATERIAL	UMRP/RETAIL
H 7880 BPX 30" Convection Oven	11805630	\$8,399 / \$8,599

DESIGN LINE	FINISH
ArtLine	Graphite grey

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	28 ^{5/8} in (727 mm)
Depth	23 ^{3/4} in (603 mm)
Shipping Weight	215 lbs (98 kg)

FEATURES	
- FoodView	- TasteControl
- Wireless Precision Probe	- Miele@home
- M Touch Controls with MotionReact	- Automatic Programs
- Moisture Plus	

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray (1)	9811950	\$180 / \$180
30" Wire Rack w/ PyroFit (2)	9811970	\$185 / \$185
30" Telescopic Rack w/ PyroFit (1)	12072650	\$325 / \$325
PerfectClean Grilling and Roasting Insert (1)	9520630	\$125 / \$125
PerfectClean Perforated Baking Tray (1)	9520620	\$110 / \$110

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139

30" Convection Oven



MODEL	MATERIAL	UMRP/RETAIL
H 7880 BPX 30" Convection Oven	12397540	\$8,199 / \$8,399

DESIGN LINE	FINISH
Artline	Obsidian Black matte

SPECIFICATIONS

Width	29 ^{13/16} in (757 mm)
Height	28 ^{5/8} in (727 mm)
Depth	23 ^{3/4} in (603 mm)
Shipping Weight	215 lbs (98 kg)

FEATURES

- FoodView
- TasteControl
- Wireless Precision Probe
- Miele@home
- M Touch Controls with MotionReact
- Automatic Programs
- Moisture Plus

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray (1)	9811950	\$180 / \$180
30" Wire Rack w/ PyroFit (2)	9811970	\$185 / \$185
30" Telescopic Rack w/ PyroFit (1)	12072650	\$325 / \$325
PerfectClean Grilling and Roasting Insert (1)	9520630	\$125 / \$125
PerfectClean Perforated Baking Tray (1)	9520620	\$110 / \$110

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139

30" Convection Oven



MODEL	MATERIAL	UMRP/RETAIL
H 7580 BP 30" Convection Oven	11805540	\$6,999 / \$7,199

DESIGN LINE

ContourLine

SPECIFICATIONS

Width	29 ^{13/16} in (757 mm)
Height	28 ^{5/8} in (727 mm)
Depth	23 ^{3/4} in (603 mm)
Shipping Weight	215 lbs (98 kg)

FEATURES

- Moisture Plus
- TasteControl
- Miele@home
- Wired Food Probe
- M Touch S Controls with MotionReact
- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray (1)	9811950	\$180 / \$180
30" Wire Rack w/ PyroFit (2)	9811970	\$185 / \$185
30" Telescopic Rack w/ PyroFit (1)	12072650	\$325 / \$325
PerfectClean Grilling and Roasting Insert (1)	9520630	\$125 / \$125

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110

MODEL	MATERIAL	UMRP/RETAIL
H 7680 BP 30" Convection Oven	11805550	\$6,999 / \$7,199

DESIGN LINE

PureLine

SPECIFICATIONS

Width	29 ^{13/16} in (757 mm)
Height	28 ^{5/8} in (727 mm)
Depth	23 ^{3/4} in (603 mm)
Shipping Weight	215 lbs (98 kg)

FEATURES

- Moisture Plus
- TasteControl
- Miele@home
- Wired Food Probe
- M Touch S Controls with MotionReact
- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray (1)	9811950	\$180 / \$180
30" Wire Rack w/ PyroFit (2)	9811970	\$185 / \$185
30" Telescopic Rack w/ PyroFit (1)	12072650	\$325 / \$325
PerfectClean Grilling and Roasting Insert (1)	9520630	\$125 / \$125

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110

30" Convection Oven



MODEL	MATERIAL	UMRP/RETAIL
H 7180 BP 30" Convection Oven	11805340	\$5,399 / \$5,599

DESIGN LINE

ContourLine

SPECIFICATIONS

Width	29 ^{13/16} in (757 mm)
Height	28 ^{5/8} in (727 mm)
Depth	23 ^{3/4} in (603 mm)
Shipping Weight	215 lbs (98 kg)

FEATURES

- Miele@home
- DirectSensor S Controls
- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray (1)	9811950	\$180 / \$180
30" Wire Rack w/ PyroFit (1)	9811970	\$185 / \$185
30" Telescopic Rack w/ PyroFit (1)	12072650	\$325 / \$325

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Grilling and Roasting Insert	9520630	\$125 / \$125

MODEL	MATERIAL	UMRP/RETAIL
H 7280 BP 30" Convection Oven	11805500	\$5,399 / \$5,599

DESIGN LINE

PureLine

SPECIFICATIONS

Width	29 ^{13/16} in (757 mm)
Height	28 ^{5/8} in (727 mm)
Depth	23 ^{3/4} in (603 mm)
Shipping Weight	215 lbs (98 kg)


FEATURES

- Miele@home
- DirectSensor S Controls
- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray (1)	9811950	\$180 / \$180
30" Wire Rack w/ PyroFit (1)	9811970	\$185 / \$185
30" Telescopic Rack w/ PyroFit (1)	12072650	\$325 / \$325

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Grilling and Roasting Insert	9520630	\$125 / \$125

30" Convection Oven



MODEL	MATERIAL	UMRP/RETAIL
H 7280 BP 30" Convection Oven	11805350	\$5,399 / \$5,599

DESIGN LINE	FINISH
VitroLine	Brilliant white

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	28 ^{5/8} in (727 mm)
Depth	23 ^{3/4} in (603 mm)
Shipping Weight	215 lbs (98 kg)

FEATURES
<ul style="list-style-type: none"> - Miele@home - DirectSensor S Controls - Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray (1)	9811950	\$180 / \$180
30" Wire Rack w/ PyroFit (1)	9811970	\$185 / \$185
30" Telescopic Rack w/ PyroFit (1)	12072650	\$325 / \$325

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Grilling and Roasting Insert	9520630	\$125 / \$125

MODEL	MATERIAL	UMRP/RETAIL
H 7280 BP 30" Convection Oven	11805520	\$5,399 / \$5,599

DESIGN LINE	FINISH
VitroLine	Graphite grey

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	28 ^{5/8} in (727 mm)
Depth	23 ^{3/4} in (603 mm)
Shipping Weight	215 lbs (98 kg)

FEATURES
<ul style="list-style-type: none"> - Miele@home - DirectSensor S Controls - Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray (1)	9811950	\$180 / \$180
30" Wire Rack w/ PyroFit (1)	9811970	\$185 / \$185
30" Telescopic Rack w/ PyroFit (1)	12072650	\$325 / \$325

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Grilling and Roasting Insert	9520630	\$125 / \$125

30" Convection Oven



MODEL	MATERIAL	UMRP/RETAIL
H 2780 BP 30" Convection Oven	11805320	\$4,699 / \$4,899

DESIGN LINE

ContourLine

SPECIFICATIONS

Width	29 ^{13/16} in (757 mm)
Height	28 ^{5/8} in (727 mm)
Depth	23 ^{3/4} in (603 mm)
Shipping Weight	215 lbs (98 kg)

FEATURES

- Easy Control

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray (1)	9811950	\$180 / \$180
Baking and Roasting Rack (1)	9811970	\$185 / \$185

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Grilling and Roasting Insert	9520630	\$125 / \$125
30" Rack w/ PyroFit	9811970	\$185 / \$185
30" Telescopic Rack w/ PyroFit	12072650	\$325 / \$325

MODEL	MATERIAL	UMRP/RETAIL
H 2880 BP 30" Convection Oven	11805330	\$4,699 / \$4,899

DESIGN LINE

PureLine

SPECIFICATIONS

Width	29 ^{13/16} in (757 mm)
Height	28 ^{5/8} in (727 mm)
Depth	23 ^{3/4} in (603 mm)
Shipping Weight	215 lbs (98 kg)

FEATURES

- Easy Control

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray (1)	9811950	\$180 / \$180
Baking and Roasting Rack (1)	9811970	\$185 / \$185

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Grilling and Roasting Insert	9520630	\$125 / \$125
30" Rack w/ PyroFit	9811970	\$185 / \$185
30" Telescopic Rack w/ PyroFit	12072650	\$325 / \$325

30" Double Oven



MODEL	MATERIAL	UMRP/RETAIL
H 7780 BP2 30" Double Oven	11805570	\$10,299 / \$10,499

DESIGN LINE

Contour Line

SPECIFICATIONS

Width	29 ^{13/16} in (757 mm)
Height	50 ^{7/8} in (1290 mm)
Depth	23 ^{5/8} in (597 mm)
Shipping Weight	344 lbs (156 kg)

FEATURES

- M Touch Controls with Motion React
- Moisture Plus
- Wireless Precision Probe
- Miele@home
- Automatic Programs

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ logo	9520730	\$75 / \$75
Perforated round Baking Tray	10116800	\$69 / \$69
Wooden cutting board	9120970	\$139 / \$139

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL	INCLUDED
Perfect Clean Universal Tray	9811950	\$180 / \$180	2
30" Wire Rack w/ PyroFit	9811970	\$185 / \$185	4
30" Telescopic Rack w/ PyroFit	12072650	\$325 / \$325	2
Perfect Clean Grilling and Roasting Insert	9520630	\$125 / \$125	1
Perfect Clean Perforated Baking Tray	9520620	\$110 / \$110	1

24" Convection Oven



MODEL	MATERIAL	UMRP/RETAIL
H 7660 BP 24" Convection Oven	11804810	\$4,499 / \$4,699

DESIGN LINE
PureLine

SPECIFICATIONS	
Width	23 ^{7/16} in (595 mm)
Height	23 ^{7/16} in (596 mm)
Depth	21 ^{1/2} in (546 mm)
Shipping Weight	119 lbs (54 kg)

FEATURES	
- M Touch S Controls with MotionReact	- Miele@home
- Moisture Plus	- Wired Food Probe
- TasteControl	- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready (2)	9520640	\$119 / \$119
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean Grill Insert 24" Oven (1)	9520630	\$125 / \$125

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Baking Tray	9519820	\$105 / \$105
PerfectClean Grill Insert 24" Oven	9520630	\$125 / \$125
Shelf Trim for 24" - Black	5165170	\$59 / \$59
Shelf Trim for 24" - Stainless	7114780	\$59 / \$59
Trim Kit: PureLine	11515790	\$449 / \$449



MODEL	MATERIAL	UMRP/RETAIL
H 7660 BP 24" Convection Oven	11804860	\$4,499 / \$4,699

DESIGN LINE	FINISH
VitroLine	Obsidian black

SPECIFICATIONS	
Width	23 ^{7/16} in (595 mm)
Height	23 ^{7/16} in (596 mm)
Depth	21 ^{1/2} in (546 mm)
Shipping Weight	119 lbs (54 kg)

FEATURES	
- M Touch S Controls with MotionReact	- Miele@home
- Moisture Plus	- Wired Food Probe
- TasteControl	- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready (2)	9520640	\$119 / \$119
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean Grill Insert 24" Oven (1)	9520630	\$125 / \$125

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Baking Tray	9519820	\$105 / \$105
PerfectClean Grill Insert 24" Oven	9520630	\$125 / \$125
Shelf Trim for 24" - Black	5165170	\$59 / \$59
Shelf Trim for 24" - Stainless	7114780	\$59 / \$59
Trim Kit: Obsidian black	11515800	\$449 / \$449

24" Convection Oven



MODEL	MATERIAL	UMRP/RETAIL
H 7660 BP 24" Convection Oven	11804800	\$4,499 / \$4,699

DESIGN LINE	FINISH
VitroLine	Brilliant white

SPECIFICATIONS	
Width	23 ^{7/16} in (595 mm)
Height	23 ^{7/16} in (596 mm)
Depth	21 ^{1/2} in (546 mm)
Shipping Weight	119 lbs (54 kg)

FEATURES	
- M Touch S Controls with MotionReact	- Miele@home
- Moisture Plus	- Wired Food Probe
- TasteControl	- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready (2)	9520640	\$119 / \$119
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean Grill Insert 24" Oven (1)	9520630	\$125 / \$125

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Baking Tray	9519820	\$105 / \$105
PerfectClean Grill Insert 24" Oven	9520630	\$125 / \$125
Shelf Trim for 24" - Black	5165170	\$59 / \$59
Shelf Trim for 24" - Stainless	7114780	\$59 / \$59
Trim Kit: Brilliant white	11515810	\$449 / \$449

MODEL	MATERIAL	UMRP/RETAIL
H 7660 BP 24" Convection Oven	11804840	\$4,499 / \$4,699

DESIGN LINE	FINISH
VitroLine	Graphite grey

SPECIFICATIONS	
Width	23 ^{7/16} in (595 mm)
Height	23 ^{7/16} in (596 mm)
Depth	21 ^{1/2} in (546 mm)
Shipping Weight	119 lbs (54 kg)

FEATURES	
- M Touch S Controls with MotionReact	- Miele@home
- Moisture Plus	- Wired Food Probe
- TasteControl	- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready (2)	9520640	\$119 / \$119
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean Grill Insert 24" Oven (1)	9520630	\$125 / \$125

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Baking Tray	9519820	\$105 / \$105
PerfectClean Grill Insert 24" Oven	9520630	\$125 / \$125
Shelf Trim for 24" - Black	5165170	\$59 / \$59
Shelf Trim for 24" - Stainless	7114780	\$59 / \$59
Trim Kit: Graphite grey	11515820	\$449 / \$449

24" Convection Oven



MODEL	MATERIAL	UMRP/RETAIL
H 7263 BP 24" Convection Oven	11804760	\$2,999 / \$3,199

DESIGN LINE
PureLine

SPECIFICATIONS	
Width	23 ^{7/16} in (595 mm)
Height	23 ^{7/16} in (596 mm)
Depth	21 ^{1/2} in (546 mm)
Shipping Weight	119 lbs (54 kg)

FEATURES
<ul style="list-style-type: none"> - Miele@home - DirectSensor S Controls - Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119
PerfectClean Universal Tray 24" Oven	9519840	\$150 / \$150

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Baking Tray	9519820	\$105 / \$105
PerfectClean Grill Insert 24" Oven	9520630	\$125 / \$125
PerfectClean FlexiClips	9520660	\$185 / \$185
Shelf Trim for 24" - Black	5165170	\$59 / \$59
Shelf Trim for 24" - Stainless	7114780	\$59 / \$59
Trim Kit: Pureline	11515790	\$449 / \$449

MODEL	MATERIAL	UMRP/RETAIL
H 7263 BP 24" Convection Oven	11804750	\$2,999 / \$3,199

DESIGN LINE	FINISH
VitroLine	Brilliant white

SPECIFICATIONS	
Width	23 ^{7/16} in (595 mm)
Height	23 ^{7/16} in (596 mm)
Depth	21 ^{1/2} in (546 mm)
Shipping Weight	119 lbs (54 kg)

FEATURES
<ul style="list-style-type: none"> - Miele@home - DirectSensor S Controls - Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119
PerfectClean Universal Tray 24" Oven	9519840	\$150 / \$150

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Baking Tray	9519820	\$105 / \$105
PerfectClean Grill Insert 24" Oven	9520630	\$125 / \$125
PerfectClean FlexiClips	9520660	\$185 / \$185
Shelf Trim for 24" - Black	5165170	\$59 / \$59
Shelf Trim for 24" - Stainless	7114780	\$59 / \$59
Trim Kit: Brilliant white	11515810	\$449 / \$449

24" Convection Oven



MODEL	MATERIAL	UMRP/RETAIL
H 7263 BP 24" Convection Oven	11804780	\$2,999 / \$3,199

DESIGN LINE	FINISH
VitroLine	Graphite grey

SPECIFICATIONS

Width	23 ^{7/16} in (595 mm)
Height	23 ^{7/16} in (596 mm)
Depth	21 ^{1/2} in (546 mm)
Shipping Weight	119 lbs (54 kg)

FEATURES

- Miele@home
- Automatic Programs
- DirectSensor S Controls

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119
PerfectClean Universal Tray 24" Oven	9519840	\$150 / \$150

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Baking Tray	9519820	\$105 / \$105
PerfectClean Grill Insert 24" Oven	9520630	\$125 / \$125
PerfectClean FlexiClips	9520660	\$185 / \$185
Shelf Trim for 24" - Black	5165170	\$59 / \$59
Shelf Trim for 24" - Stainless	7114780	\$59 / \$59
Trim Kit: Graphite grey	11515820	\$449 / \$449

Product Highlights

Speed Ovens, Combi-Steam Ovens and Microwave Ovens

*See specific models for details

FEATURE	DESCRIPTION
New Inverter Technology	True variable power levels cook food faster and more evenly than conventional microwaves.
Easy Maintenance	The stainless steel interior cavity makes for easy wipe down and clean-up.
Automatic Programs	Miele guides you through hundreds of easy-to-use cooking programs.
Combination Microwave/Convection Mode	Speed ovens can reduce cook time up to 30% in combining microwave technology with conventional heat.
Dual Steam	Redesigned steam entry ports allow steam to circulate and cook faster and more completely than ever before.
Mix & Match	Use your Miele app to select ingredients you already have to quickly cook a perfect meal in your Combi-Steam oven.
Popcorn and Beverage Function	With Miele microwave ovens, reheat beverages or make popcorn with one touch of a button.

30" Speed Oven



MODEL	MATERIAL	UMRP/RETAIL
H 7770 BM 30" Speed Oven	11804620	\$5,099 / \$5,299

DESIGN LINE

ContourLine

SPECIFICATIONS

Width	29 ^{13/16} in (757 mm)
Height	18 ^{7/8} in (479 mm)
Depth	21 ^{11/16} in (551 mm)
Shipping Weight	128 lbs (58 kg)

FEATURES

- M Touch Controls with MotionReact
- Miele@home
- Wired Food Probe
- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
HGS100 Glass Bowl (2)	10141820	N/A
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Baking Tray	9519820	\$105 / \$105
PerfectClean Grill Insert 24" Oven	9520630	\$125 / \$125

MODEL	MATERIAL	UMRP/RETAIL
H 7870 BM 30" Speed Oven	11804680	\$5,099 / \$5,299

DESIGN LINE

PureLine

SPECIFICATIONS

Width	29 ^{13/16} in (757 mm)
Height	18 ^{7/8} in (479 mm)
Depth	21 ^{11/16} in (551 mm)
Shipping Weight	128 lbs (58 kg)

FEATURES

- M Touch Controls with MotionReact
- Miele@home
- Wired Food Probe
- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
HGS100 Glass Bowl (2)	10141820	N/A
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Baking Tray	9519820	\$105 / \$105
PerfectClean Grill Insert 24" Oven	9520630	\$125 / \$125

NOTE: Metal trays not for use in microwave modes

30" Speed Oven



MODEL	MATERIAL	UMRP/RETAIL
H 7870 BM 30" Speed Oven	11804700	\$5,099 / \$5,299

DESIGN LINE	FINISH
VitroLine	Obsidian black

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	18 ^{7/8} in (479 mm)
Depth	21 ^{11/16} in (551 mm)
Shipping Weight	128 lbs (58 kg)

FEATURES	
- M Touch Controls with MotionReact	- Wired Food Probe
- Miele@home	- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
HGS100 Glass Bowl (2)	10141820	N/A
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Baking Tray	9519820	\$105 / \$105
PerfectClean Grill Insert 24" Oven	9520630	\$125 / \$125

MODEL	MATERIAL	UMRP/RETAIL
H 7870 BM 30" Speed Oven	11804670	\$5,099 / \$5,299

DESIGN LINE	FINISH
VitroLine	Brilliant white

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	18 ^{7/8} in (479 mm)
Depth	21 ^{11/16} in (551 mm)
Shipping Weight	128 lbs (58 kg)

FEATURES	
-M Touch Controls with MotionReact	- Wired Food Probe
- Miele@home	- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
HGS100 Glass Bowl (2)	10141820	N/A
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Baking Tray	9519820	\$105 / \$105
PerfectClean Grill Insert 24" Oven	9520630	\$125 / \$125

NOTE: Metal trays not for use in microwave modes

30" Speed Oven



MODEL	MATERIAL	UMRP/RETAIL
H 7870 BM 30" Speed Oven	11804690	\$5,099 / \$5,299

DESIGN LINE	FINISH
VitroLine	Graphite grey

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	18 ^{7/8} in (479 mm)
Depth	21 ^{11/16} in (551 mm)
Shipping Weight	128 lbs (58 kg)

FEATURES	
- M Touch Controls with MotionReact	- Automatic Programs
- Miele@home	- DirectSensor Controls

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
HGS100 Glass Bowl (2)	10141820	N/A
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Baking Tray	9519820	\$105 / \$105
PerfectClean Grill Insert 24" Oven	9520630	\$125 / \$125

MODEL	MATERIAL	UMRP/RETAIL
H 7870 BMX 30" Speed Oven	11804710	\$5,299 / \$5,499

DESIGN LINE	FINISH
ArtLine	Graphite grey

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	18 ^{7/8} in (479 mm)
Depth	21 ^{11/16} in (551 mm)
Shipping Weight	128 lbs (58 kg)

FEATURES	
- M Touch Controls with MotionReact	- Automatic Programs
- Miele@home	- DirectSensor Controls

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
HGS100 Glass Bowl (2)	10141820	N/A
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Baking Tray	9519820	\$105 / \$105
PerfectClean Grill Insert 24" Oven	9520630	\$125 / \$125

NOTE: Metal trays not for use in microwave modes

30" Speed Oven



MODEL	MATERIAL	UMRP/RETAIL
H 7870 BMX 30" Speed Oven	12397570	\$5,099 / \$5,299

DESIGN LINE	FINISH
ArtLine	Obsidian Black matte

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	18 ^{7/8} in (479 mm)
Depth	21 ^{11/16} in (551 mm)
Shipping Weight	128 lbs (58 kg)

FEATURES	
- M Touch Controls with MotionReact	- Automatic Programs
- Miele@home	- DirectSensor Controls

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
HGS100 Glass Bowl (2)	10141820	N/A
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Baking Tray	9519820	\$105 / \$105
PerfectClean Grill Insert 24" Oven	9520630	\$125 / \$125

30" Speed Oven



MODEL	MATERIAL	UMRP/RETAIL
H 7570 BM 30" Speed Oven	11804590	\$4,599 / \$4,799

DESIGN LINE

ContourLine

SPECIFICATIONS

Width	29 ^{13/16} in (757 mm)
Height	18 ^{7/8} in (479 mm)
Depth	21 ^{11/16} in (551 mm)
Shipping Weight	128 lbs (58 kg)

FEATURES

- M Touch S Controls with MotionReact
- Miele@home
- Automatic Programs
- DirectSensor Controls

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
HGS100 Glass Bowl (1)	10141820	N/A
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Baking Tray	9519820	\$105 / \$105
PerfectClean Grill Insert 24" Oven	9520630	\$125 / \$125

MODEL	MATERIAL	UMRP/RETAIL
H 7670 BM 30" Speed Oven	11804610	\$4,599 / \$4,799

DESIGN LINE

PureLine

SPECIFICATIONS

Width	29 ^{13/16} in (757 mm)
Height	18 ^{7/8} in (479 mm)
Depth	21 ^{11/16} in (551 mm)
Shipping Weight	128 lbs (58 kg)

FEATURES

- M Touch S Controls with MotionReact
- Miele@home
- Automatic Programs
- DirectSensor Controls

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
HGS100 Glass Bowl (1)	10141820	N/A
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Baking Tray	9519820	\$105 / \$105
PerfectClean Grill Insert 24" Oven	9520630	\$125 / \$125

NOTE: Metal trays not for use in microwave modes

30" Speed Oven



MODEL	MATERIAL	UMRP/RETAIL
H 7170 BM 30" Speed Oven	11804470	\$3,299 / \$3,499

DESIGN LINE

ContourLine

SPECIFICATIONS

Width	29 ^{13/16} in (757 mm)
Height	18 ^{7/8} in (479 mm)
Depth	21 ^{11/16} in (551 mm)
Shipping Weight	128 lbs (58 kg)

FEATURES

- Miele@home
- DirectSensor S Controls

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
HGS100 Glass Bowl (1)	10141820	N/A
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Baking Tray	9519820	\$105 / \$105
PerfectClean Grill Insert 24" Oven	9520630	\$125 / \$125

MODEL	MATERIAL	UMRP/RETAIL
H 7270 BM 30" Speed Oven	11804570	\$3,299 / \$3,499

DESIGN LINE

PureLine

SPECIFICATIONS

Width	29 ^{13/16} in (757 mm)
Height	18 ^{7/8} in (479 mm)
Depth	21 ^{11/16} in (551 mm)
Shipping Weight	128 lbs (58 kg)

FEATURES

- Miele@home
- DirectSensor S Controls

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
HGS100 Glass Bowl (1)	10141820	N/A
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Baking Tray	9519820	\$105 / \$105
PerfectClean Grill Insert 24" Oven	9520630	\$125 / \$125

NOTE: Metal trays not for use in microwave modes

30" Speed Oven



MODEL	MATERIAL	UMRP/RETAIL
H 7270 BM 30" Speed Oven	11804530	\$3,299 / \$3,499

DESIGN LINE	FINISH
VitroLine	Brilliant white

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	18 ^{7/8} in (479 mm)
Depth	21 ^{11/16} in (551 mm)
Shipping Weight	128 lbs (58 kg)

FEATURES	
- Miele@home	- DirectSensor S Controls

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
HGS100 Glass Bowl (1)	10141820	N/A
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Baking Tray	9519820	\$105 / \$105
PerfectClean Grill Insert 24" Oven	9520630	\$125 / \$125

MODEL	MATERIAL	UMRP/RETAIL
H 7270 BM 30" Speed Oven	11804580	\$3,299 / \$3,499

DESIGN LINE	FINISH
VitroLine	Graphite grey

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	18 ^{7/8} in (479 mm)
Depth	21 ^{11/16} in (551 mm)
Shipping Weight	128 lbs (58 kg)

FEATURES	
- Miele@home	- DirectSensor S Controls

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
HGS100 Glass Bowl (1)	10141820	N/A
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Baking Tray	9519820	\$105 / \$105
PerfectClean Grill Insert 24" Oven	9520630	\$125 / \$125

NOTE: Metal trays not for use in microwave modes

24" Speed Oven



MODEL	MATERIAL	UMRP/RETAIL
H 7840 BM 24" Speed Oven	11804640	\$4,599 / \$4,799

DESIGN LINE
PureLine

SPECIFICATIONS	
Width	23 ^{7/16} in (595 mm)
Height	17 ^{15/16} in (455.5 mm)
Depth	21 ^{5/8} in (549 mm)
Shipping Weight	101 lbs (46 kg)

FEATURES
<ul style="list-style-type: none"> - M Touch Controls with MotionReact - Miele@home - Wired Food Probe - Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
HGS100 Glass Bowl (2)	10141820	N/A
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Universal Tray 24" Oven	9519840	\$150 / \$150
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Baking Tray	9519820	\$105 / \$105
PerfectClean Grill Insert 24" Oven	9520630	\$125 / \$125
Shelf Trim for 24" - Black	5165170	\$59 / \$59
Shelf Trim for 24" - Stainless	7114780	\$59 / \$59
Trim Kit: PureLine	11410740	\$449 / \$449

NOTE: Metal trays not for use in microwave modes

MODEL	MATERIAL	UMRP/RETAIL
H 7840 BM 24" Speed Oven	11804660	\$4,599 / \$4,799

DESIGN LINE	FINISH
VitroLine	Obsidian black


SPECIFICATIONS	
Width	23 ^{7/16} in (595 mm)
Height	17 ^{15/16} in (455.5 mm)
Depth	21 ^{5/8} in (549 mm)
Shipping Weight	101 lbs (46 kg)

FEATURES
<ul style="list-style-type: none"> - M Touch Controls with MotionReact - Miele@home - Wired Food Probe - Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
HGS100 Glass Bowl (2)	10141820	N/A
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Universal Tray 24" Oven	9519840	\$150 / \$150
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Baking Tray	9519820	\$105 / \$105
PerfectClean Grill Insert 24" Oven	9520630	\$125 / \$125
Shelf Trim for 24" - Black	5165170	\$59 / \$59
Shelf Trim for 24" - Stainless	7114780	\$59 / \$59
Trim Kit: Obsidian black	11410770	\$449 / \$449

24" Speed Oven



MODEL	MATERIAL	UMRP/RETAIL
H 7840 BM 24" Speed Oven	11804630	\$4,599 / \$4,799

DESIGN LINE	FINISH
VitroLine	Brilliant white

SPECIFICATIONS	
Width	23 ^{7/16} in (595 mm)
Height	17 ^{15/16} in (455.5 mm)
Depth	21 ^{5/8} in (549 mm)
Shipping Weight	101 lbs (46 kg)

FEATURES	
- M Touch Controls with MotionReact	- Wired Food Probe
- Miele@home	- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
HGS100 Glass Bowl (1)	10141820	N/A
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Universal Tray 24" Oven	9519840	\$150 / \$150
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Baking Tray	9519820	\$105 / \$105
PerfectClean Grill Insert 24" Oven	9520630	\$125 / \$125
Shelf Trim for 24" - Black	5165170	\$59 / \$59
Shelf Trim for 24" - Stainless	7114780	\$59 / \$59
Trim Kit: Brilliant white	11410790	\$449 / \$449

MODEL	MATERIAL	UMRP/RETAIL
H 7840 BM 24" Speed Oven	11804650	\$4,599 / \$4,799

DESIGN LINE	FINISH
VitroLine	Graphite grey

SPECIFICATIONS	
Width	23 ^{7/16} in (595 mm)
Height	17 ^{15/16} in (455.5 mm)
Depth	21 ^{5/8} in (549 mm)
Shipping Weight	101 lbs (46 kg)

FEATURES	
- M Touch Controls with MotionReact	- Wired Food Probe
- Miele@home	- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
HGS100 Glass Bowl (1)	10141820	N/A
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Universal Tray 24" Oven	9519840	\$150 / \$150
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Baking Tray	9519820	\$105 / \$105
PerfectClean Grill Insert 24" Oven	9520630	\$125 / \$125
Shelf Trim for 24" - Black	5165170	\$59 / \$59
Shelf Trim for 24" - Stainless	7114780	\$59 / \$59
Trim Kit: Graphite grey	11410800	\$449 / \$449

NOTE: Metal trays not for use in microwave modes

24" Speed Oven



MODEL	MATERIAL	UMRP/RETAIL
H 7640 BM 24" Speed Oven	11804600	\$3,899 / \$4,099

DESIGN LINE

PureLine

SPECIFICATIONS

Width	23 ^{7/16} in (595 mm)
Height	17 ^{15/16} in (455.5 mm)
Depth	21 ^{5/8} in (549 mm)
Shipping Weight	101 lbs (46 kg)

FEATURES

- M Touch S Controls with MotionReact
- Miele@home
- Wired Food Probe
- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
HGS100 Glass Bowl (1)	10141820	N/A
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Universal Tray 24" Oven	9519840	\$150 / \$150
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Baking Tray	9519820	\$105 / \$105
PerfectClean Grill Insert 24" Oven	9520630	\$125 / \$125
Shelf Trim for 24" - Black	5165170	\$59 / \$59
Shelf Trim for 24" - Stainless	7114780	\$59 / \$59
Trim Kit: PureLine	11410740	\$449 / \$449

MODEL	MATERIAL	UMRP/RETAIL
H 7240 BM 24" Speed Oven	11804510	\$2,999 / \$3,199

DESIGN LINE

PureLine

SPECIFICATIONS

Width	23 ^{7/16} in (595 mm)
Height	17 ^{15/16} in (455.5 mm)
Depth	21 ^{5/8} in (549 mm)
Shipping Weight	101 lbs (46 kg)

FEATURES



- Miele@home
- DirectSensor S Controls

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
HGS100 Glass Bowl (1)	10141820	N/A
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Universal Tray 24" Oven	9519840	\$150 / \$150
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Baking Tray	9519820	\$105 / \$105
PerfectClean Grill Insert 24" Oven	9520630	\$125 / \$125
Shelf Trim for 24" - Black	5165170	\$59 / \$59
Shelf Trim for 24" - Stainless	7114780	\$59 / \$59
Trim Kit: PureLine	11410740	\$449 / \$449

NOTE: Metal trays not for use in microwave modes

24" Speed Oven



MODEL	MATERIAL	UMRP/RETAIL
H 7240 BM 24" Speed Oven	11804480	\$2,999 / \$3,199
DESIGN LINE	FINISH	
PureLine	Brilliant white	
SPECIFICATIONS		
Width	23 ^{7/16} in (595 mm)	
Height	17 ^{15/16} in (455.5 mm)	
Depth	21 ^{5/8} in (549 mm)	
Shipping Weight	101 lbs (46 kg)	

FEATURES		
- Miele@home	- DirectSensor S Controls	

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
HGS100 Glass Bowl (1)	10141820	N/A
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Universal Tray 24" Oven	9519840	\$150 / \$150
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Baking Tray	9519820	\$105 / \$105
PerfectClean Grill Insert 24" Oven	9520630	\$125 / \$125
Shelf Trim for 24" - Black	5165170	\$59 / \$59
Shelf Trim for 24" - Stainless	7114780	\$59 / \$59
Trim Kit: Brilliant white	11410790	\$449 / \$449

MODEL	MATERIAL	UMRP/RETAIL
H 7240 BM 24" Speed Oven	11804520	\$2,999 / \$3,199
DESIGN LINE	FINISH	
PureLine	Graphite grey	
SPECIFICATIONS		
Width	23 ^{7/16} in (595 mm)	
Height	17 ^{15/16} in (455.5 mm)	
Depth	21 ^{5/8} in (549 mm)	
Shipping Weight	101 lbs (46 kg)	

FEATURES		
- Miele@home	- DirectSensor S Controls	

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
HGS100 Glass Bowl (1)	10141820	N/A
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Universal Tray 24" Oven	9519840	\$150 / \$150
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Baking Tray	9519820	\$105 / \$105
PerfectClean Grill Insert 24" Oven	9520630	\$125 / \$125
Shelf Trim for 24" - Black	5165170	\$59 / \$59
Shelf Trim for 24" - Stainless	7114780	\$59 / \$59
Trim Kit: Graphite grey	11410800	\$449

NOTE: Metal trays not for use in microwave modes

24" Microwave



MODEL	MATERIAL	UMRP/RETAIL
M 2241 SC 24" Microwave	11845640	\$1,899 / \$2,099

DESIGN LINE

Obsidian Black

SPECIFICATIONS

Width	23 ^{7/16} in (595 mm)
Height	17 ^{15/16} in (455.5 mm)
Depth	15 ^{1/4} in (387 mm)
Shipping Weight	48.5 lbs (22 kg)

FEATURES

- 7-segment display with sensor controls – EasySensor
- Perfect defrosting and cooking – Automatic Programs
- Food remains at serving temperature – keep warm function
- Compact 0.92 cu. ft. oven capacity
- Popcorn and drinks at the touch of a button

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Trim Kit Contourline	11909130	\$449 / \$449
Trim Kit Obsidian Black	11768890	\$449 / \$449

MODEL	MATERIAL	UMRP/RETAIL
M 7240 TC 24" Microwave	11845600	\$2,399 / \$2,599

DESIGN LINE

PureLine

SPECIFICATIONS

Width	23 ^{7/16} in (595 mm)
Height	17 ^{15/16} in (455.5 mm)
Depth	16 ^{5/16} in (490 mm)
Shipping Weight	70.5 lbs (32 kg)

FEATURES

- Clear text display with sensor controls – Direct-Sensor S
- Perfect defrosting and cooking – Automatic Programs
- Plenty of space – 1.62 cu. ft. oven capacity & 15 3/4" turntable
- Very powerful microwave – 900 W
- What you want at the touch of a button – Popcorn button

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Trim Kit: PureLine	11410740	\$449 / \$449

NOTE: Metal trays not for use in microwave modes

30" Combi-Steam XL



MODEL	MATERIAL	UMRP/RETAIL
DGC 7775 30" Combi-Steam XL	11875760	\$7,499 / \$7,699

DESIGN LINE	TYPE
ContourLine	Plumbed

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	18 ^{7/8} in (479 mm)
Depth	23 ^{1/8} in (587 mm)
Shipping Weight	143 lbs (65 kg)

FEATURES	
- M Touch Controls with MotionReact	- Wired Food Probe
- Miele@home with Miele Mix & Match	- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$65 / \$65
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

MODEL	MATERIAL	UMRP/RETAIL
DGC 7770 30" Combi-Steam XL	11875780	\$6,999 / \$7,199

DESIGN LINE	TYPE
ContourLine	Non-plumbed

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	18 ^{7/8} in (479 mm)
Depth	23 ^{1/8} in (587 mm)
Shipping Weight	143 lbs (65 kg)

FEATURES	
- M Touch Controls with MotionReact	- Wired Food Probe
- Miele@home with Miele Mix & Match	- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$65 / \$65
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

30" Combi-Steam XL



MODEL	MATERIAL	UMRP/RETAIL
DGC 7875 30" Combi-Steam XL	11876050	\$7,699 / \$7,899
DESIGN LINE	TYPE	
PureLine	Plumbed	

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	18 ^{7/8} in (479 mm)
Depth	23 ^{1/8} in (587 mm)
Shipping Weight	143 lbs (65 kg)

FEATURES	
- M Touch Controls with MotionReact	- Wired Food Probe
- Miele@home with Miele Mix & Match	- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$65 / \$65
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

MODEL	MATERIAL	UMRP/RETAIL
DGC 7870 30" Combi-Steam XL	11876080	\$6,999 / \$7,199
DESIGN LINE	TYPE	
PureLine	Non-plumbed	

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	18 ^{7/8} in (479 mm)
Depth	23 ^{1/8} in (587 mm)
Shipping Weight	143 lbs (65 kg)

FEATURES	
- M Touch Controls with MotionReact	- Wired Food Probe
- Miele@home with Miele Mix & Match	- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$65 / \$65
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

30" Combi-Steam XL



MODEL	MATERIAL	UMRP/RETAIL
DGC 7870 30" Combi-Steam XL	11876190	\$6,999 / \$7,199
DESIGN LINE	FINISH	TYPE
VitroLine	Obsidian black	Non-plumbed

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	18 ^{7/8} in (479 mm)
Depth	23 ^{1/8} in (587 mm)
Shipping Weight	143 lbs (65 kg)

FEATURES	
- M Touch Controls with MotionReact	- Wired Food Probe
- Miele@home with Miele Mix & Match	- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$65 / \$65
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

MODEL	MATERIAL	UMRP/RETAIL
DGC 7870 30" Combi-Steam XL	11876200	\$6,999 / \$7,199
DESIGN LINE	FINISH	TYPE
VitroLine	Brilliant white	Non-plumbed

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	18 ^{7/8} in (479 mm)
Depth	23 ^{1/8} in (587 mm)
Shipping Weight	143 lbs (65 kg)

FEATURES	
- M Touch Controls with MotionReact	- Wired Food Probe
- Miele@home with Miele Mix & Match	- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$65 / \$65
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

30" Combi-Steam XL



MODEL	MATERIAL	UMRP/RETAIL
DGC 7870 30" Combi-Steam XL	11876180	\$6,999 / \$7,199
DESIGN LINE	FINISH	TYPE
VitroLine	Graphite grey	Non-plumbed

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	18 ^{7/8} in (479 mm)
Depth	23 ^{1/8} in (587 mm)
Shipping Weight	143 lbs (65 kg)

FEATURES	
- M Touch Controls with MotionReact	- Wired Food Probe
- Miele@home with Miele Mix & Match	- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$65 / \$65
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

MODEL	MATERIAL	UMRP/RETAIL
DGC 7870 X 30" Combi-Steam XL	11877030	\$7,199 / \$7,399
DESIGN LINE	FINISH	TYPE
ArtLine	Graphite grey	Non-plumbed

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	18 ^{7/8} in (479 mm)
Depth	23 ^{1/8} in (587 mm)
Shipping Weight	143 lbs (65 kg)

FEATURES	
- M Touch Controls with MotionReact	- Wired Food Probe
- Miele@home with Miele Mix & Match	- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$65 / \$65
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

30" Combi-Steam XL



MODEL	MATERIAL	UMRP/RETAIL
DGC 7870 X 30" Combi-Steam XL	12423580	\$6,999 / \$7,199

DESIGN LINE	FINISH	TYPE
ArtLine	Obsidian Black matte	Non-plumbed

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	18 ^{7/8} in (479 mm)
Depth	23 ^{1/8} in (587 mm)
Shipping Weight	143 lbs (65 kg)

FEATURES	
- M Touch Controls with MotionReact	- Wired Food Probe
- Miele@home with Miele Mix & Match	- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$65 / \$65
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

30" Combi-Steam XL



MODEL	MATERIAL	UMRP/RETAIL
DGC 7570 30" Combi-Steam XL	11875790	\$6,499 / \$6,699
DESIGN LINE	TYPE	
ContourLine	Non-plumbed	
SPECIFICATIONS		
Width	29 ^{13/16} in (757 mm)	
Height	18 ^{7/8} in (479 mm)	
Depth	23 ^{1/8} in (587 mm)	
Shipping Weight	143 lbs (65 kg)	
FEATURES		
<ul style="list-style-type: none"> - M Touch S Controls with MotionReact - Miele@home with Miele Mix & Match 	<ul style="list-style-type: none"> - Wired Food Probe - Automatic Programs 	
STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

MODEL	MATERIAL	UMRP/RETAIL
DGC 7670 30" Combi-Steam XL	11876210	\$6,499 / \$6,699
DESIGN LINE	TYPE	
PureLine	Non-plumbed	
SPECIFICATIONS		
Width	29 ^{13/16} in (757 mm)	
Height	18 ^{7/8} in (479 mm)	
Depth	23 ^{1/8} in (587 mm)	
Shipping Weight	143 lbs (65 kg)	
FEATURES		
<ul style="list-style-type: none"> - M Touch S Controls with MotionReact - Miele@home with Miele Mix & Match 	<ul style="list-style-type: none"> - Wired Food Probe - Automatic Programs 	
STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

30" Combi-Steam XL



MODEL	MATERIAL	UMRP/RETAIL
DGC 7370 30" Combi-Steam XL	11875800	\$4,899 / \$5,099
DESIGN LINE	TYPE	
ContourLine	Non-plumbed	
SPECIFICATIONS		
Width	29 ^{13/16} in (757 mm)	
Height	18 ^{7/8} in (479 mm)	
Depth	23 ^{1/8} in (587 mm)	
Shipping Weight	143 lbs (65 kg)	

FEATURES

- Miele@home with Miele Mix & Match
- DirectSensor Controls

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

MODEL	MATERIAL	UMRP/RETAIL
DGC 7470 30" Combi-Steam XL	11876230	\$4,899 / \$5,099
DESIGN LINE	TYPE	
PureLine	Non-plumbed	
SPECIFICATIONS		
Width	29 ^{13/16} in (757 mm)	
Height	18 ^{7/8} in (479 mm)	
Depth	23 ^{1/8} in (587 mm)	
Shipping Weight	143 lbs (65 kg)	

FEATURES

- Miele@home with Miele Mix & Match
- DirectSensor Controls

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

30" Combi-Steam XL



MODEL	MATERIAL	UMRP/RETAIL
DGC 7470 30" Combi-Steam XL	11876270	\$4,899 / \$5,099

DESIGN LINE	FINISH	TYPE
VitroLine	Brilliant white	Non-plumbed

SPECIFICATIONS

Width	29 ^{13/16} in (757 mm)
Height	18 ^{7/8} in (479 mm)
Depth	23 ^{1/8} in (587 mm)
Shipping Weight	143 lbs (65 kg)

FEATURES

- Miele@home with Miele Mix & Match
- DirectSensor Controls

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

MODEL	MATERIAL	UMRP/RETAIL
DGC 7470 30" Combi-Steam XL	11876250	\$4,899 / \$5,099

DESIGN LINE	FINISH	TYPE
VitroLine	Graphite grey	Non-plumbed

SPECIFICATIONS

Width	29 ^{13/16} in (757 mm)
Height	18 ^{7/8} in (479 mm)
Depth	23 ^{1/8} in (587 mm)
Shipping Weight	143 lbs (65 kg)

FEATURES

- Miele@home with Miele Mix & Match
- DirectSensor Controls

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

30" Combi-Steam XXL



MODEL	MATERIAL	UMRP/RETAIL
DGC 7785 30" Combi-Steam XXL	11875810	\$8,299 / \$8,499

DESIGN LINE	TYPE
ContourLine	Plumbed

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	24 ^{3/8} in (619.5 mm)
Depth	23 ^{1/8} in (587 mm)
Shipping Weight	159 lbs (72 kg)

FEATURES	
- M Touch Controls with MotionReact	- Wired Food Probe
- Miele@home with Miele Mix & Match	- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready	9520640	\$119 / \$119
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$65 / \$65
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

MODEL	MATERIAL	UMRP/RETAIL
DGC 7780 30" Combi-Steam XXL	11875830	\$7,799 / \$7,999

DESIGN LINE	TYPE
ContourLine	Non-plumbed

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	24 ^{3/8} in (619.5 mm)
Depth	23 ^{1/8} in (587 mm)
Shipping Weight	159 lbs (72 kg)

FEATURES	
- M Touch Controls with MotionReact	- Wired Food Probe
- Miele@home with Miele Mix & Match	- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready	9520640	\$119 / \$119
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$65 / \$65
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

30" Combi-Steam XXL



MODEL	MATERIAL	UMRP/RETAIL
DGC 7885 30" Combi-Steam XXL	11876310	\$8,299 / \$8,499

DESIGN LINE	TYPE
PureLine	Plumbed

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	24 ^{3/8} in (619.5 mm)
Depth	23 ^{1/8} in (587 mm)
Shipping Weight	159 lbs (72 kg)

FEATURES	
- M Touch Controls with MotionReact	- Wired Food Probe
- Miele@home with Miele Mix & Match	- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready	9520640	\$119 / \$119
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$65 / \$65
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

MODEL	MATERIAL	UMRP/RETAIL
DGC 7880 30" Combi-Steam XXL	11876350	\$7,799 / \$7,999

DESIGN LINE	TYPE
PureLine	Non-plumbed

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	24 ^{3/8} in (619.5 mm)
Depth	23 ^{1/8} in (587 mm)
Shipping Weight	159 lbs (72 kg)

FEATURES	
- M Touch Controls with MotionReact	- Wired Food Probe
- Miele@home with Miele Mix & Match	- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready	9520640	\$119 / \$119
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$65 / \$65
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

30" Combi-Steam XXL



29^{13/16}"



29^{13/16}"

MODEL	MATERIAL	UMRP/RETAIL
DGC 7880 30" Combi-Steam XXL	11876420	\$7,799 / \$7,999
DESIGN LINE	FINISH	TYPE
VitroLine	Obsidian black	Non-plumbed

SPECIFICATIONS

Width	29 ^{13/16} in (757 mm)
Height	24 ^{3/8} in (619.5 mm)
Depth	23 ^{1/8} in (587 mm)
Shipping Weight	159 lbs (72 kg)

FEATURES

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready	9520640	\$119 / \$119
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$65 / \$65
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

MODEL	MATERIAL	UMRP/RETAIL
DGC 7880 30" Combi-Steam XXL	11876440	\$7,799 / \$7,999
DESIGN LINE	FINISH	TYPE
VitroLine	Brilliant white	Non-plumbed

SPECIFICATIONS

Width	29 ^{13/16} in (757 mm)
Height	24 ^{3/8} in (619.5 mm)
Depth	23 ^{1/8} in (587 mm)
Shipping Weight	159 lbs (72 kg)

FEATURES

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready	9520640	\$119 / \$119
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$65 / \$65
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

30" Combi-Steam XXL



24^{3/8"}

29^{13/16"}



24^{3/8"}

29^{13/16"}

MODEL	MATERIAL	UMRP/RETAIL
DGC 7880 30" Combi-Steam XXL	11876370	\$7,799 / \$7,999
DESIGN LINE	FINISH	TYPE
VitroLine	Graphite grey	Non-plumbed

SPECIFICATIONS

Width	29 ^{13/16} in (757 mm)
Height	24 ^{3/8} in (619.5 mm)
Depth	23 ^{1/8} in (587 mm)
Shipping Weight	159 lbs (72 kg)

FEATURES

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready	9520640	\$119 / \$119
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$65 / \$65
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

MODEL	MATERIAL	UMRP/RETAIL
DGC 7880 X 30" Combi-Steam XXL	11877040	\$7,999 / \$8,199
DESIGN LINE	FINISH	TYPE
ArtLineLine	Graphite grey	Non-plumbed

SPECIFICATIONS

Width	29 ^{13/16} in (757 mm)
Height	24 ^{3/8} in (619.5 mm)
Depth	23 ^{1/8} in (587 mm)
Shipping Weight	159 lbs (72 kg)

FEATURES

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready	9520640	\$119 / \$119
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$65 / \$65
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

30" Combi-Steam XXL



MODEL	MATERIAL	UMRP/RETAIL
DGC 7880 X 30" Combi-Steam XXL	12423590	\$7,299 / \$8,199

DESIGN LINE	FINISH	TYPE
ArtLineLine	Obsidian Black matte	Non-plumbed

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	24 ^{3/8} in (619.5 mm)
Depth	23 ^{1/8} in (587 mm)
Shipping Weight	159 lbs (72 kg)

FEATURES	
- M Touch Controls with MotionReact	- Wired Food Probe
- Miele@home with Miele Mix & Match	- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready	9520640	\$119 / \$119
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$65 / \$65
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

30" Combi-Steam XXL



MODEL	MATERIAL	UMRP/RETAIL
DGC 7680 30" Combi-Steam XXL	11876470	\$7,199 / \$7,399

DESIGN LINE	TYPE
PureLine	Non-plumbed

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	24 ^{3/8} in (619.5 mm)
Depth	23 ^{1/8} in (587 mm)
Shipping Weight	159 lbs (72 kg)

FEATURES	
- M Touch S Controls with MotionReact	- Wired Food Probe
- Miele@home with Miele Mix & Match	- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready	9520640	\$119 / \$119
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

MODEL	MATERIAL	UMRP/RETAIL
DGC 7685 30" Combi-Steam XXL	11876450	\$7,699 / \$7,899

DESIGN LINE	TYPE
PureLine	Plumbed

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	24 ^{3/8} in (619.5 mm)
Depth	23 ^{1/8} in (587 mm)
Shipping Weight	159 lbs (72 kg)

FEATURES	
- M Touch S Controls with MotionReact	- Wired Food Probe
- Miele@home with Miele Mix & Match	- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready	9520640	\$119 / \$119
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

30" Combi-Steam XXL



MODEL	MATERIAL	UMRP/RETAIL
-------	----------	-------------

DGC 7580 30" Combi-Steam XXL	11876020	\$7,199 / \$7,399
---------------------------------	----------	-------------------

DESIGN LINE	TYPE
-------------	------

ContourLine	Non-plumbed
-------------	-------------

SPECIFICATIONS

Width	29 ^{13/16} in (757 mm)
Height	24 ^{3/8} in (619.5 mm)
Depth	23 ^{1/8} in (587 mm)
Shipping Weight	159 lbs (72 kg)

FEATURES

- M Touch S Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
----------------------	----------	-------------

PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready	9520640	\$119 / \$119
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

MODEL	MATERIAL	UMRP/RETAIL
-------	----------	-------------

DGC 7585 30" Combi-Steam XXL	11875850	\$7,699 / \$7,899
---------------------------------	----------	-------------------

DESIGN LINE	TYPE
-------------	------

ContourLine	Plumbed
-------------	---------

SPECIFICATIONS

Width	29 ^{13/16} in (757 mm)
Height	24 ^{3/8} in (619.5 mm)
Depth	23 ^{1/8} in (587 mm)
Shipping Weight	159 lbs (72 kg)

FEATURES

- M Touch S Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
----------------------	----------	-------------

PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready	9520640	\$119 / \$119
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

24" Combi-Steam XL



23^{7/16}"



23^{7/16}"

MODEL	MATERIAL	UMRP/RETAIL
DGC 7845 24" Combi-Steam XL	11876580	\$6,499 / \$6,699

DESIGN LINE	TYPE
PureLine	Plumbed

SPECIFICATIONS

Width	23 ^{7/16} in (595 mm)
Height	17 ^{15/16} in (455.5 mm)
Depth	23 ^{1/4} in (590 mm)
Shipping Weight	128 lbs (58 kg)

FEATURES

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$65 / \$65
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

MODEL	MATERIAL	UMRP/RETAIL
DGC 7840 24" Combi-Steam XL	11876590	\$5,999 / \$6,199

DESIGN LINE	TYPE
PureLine	Non-plumbed

SPECIFICATIONS

Width	23 ^{7/16} in (595 mm)
Height	17 ^{15/16} in (455.5 mm)
Depth	23 ^{1/4} in (590 mm)
Shipping Weight	128 lbs (58 kg)

FEATURES

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$65 / \$65
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

24" Combi-Steam XL



23^{7/16}"



23^{7/16}"

MODEL	MATERIAL	UMRP/RETAIL
DGC 7840 24" Combi-Steam XL	11876610	\$5,999 / \$6,199

DESIGN LINE	FINISH	TYPE
VitroLine	Obsidian black	Non-plumbed

SPECIFICATIONS

Width	23 ^{7/16} in (595 mm)
Height	17 ^{15/16} in (455.5 mm)
Depth	23 ^{1/4} in (590 mm)
Shipping Weight	128 lbs (58 kg)

FEATURES

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$65 / \$65
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

MODEL	MATERIAL	UMRP/RETAIL
DGC 7840 24" Combi-Steam XL	11876630	\$5,999 / \$6,199

DESIGN LINE	FINISH	TYPE
VitroLine	Brilliant white	Non-plumbed

SPECIFICATIONS

Width	23 ^{7/16} in (595 mm)
Height	17 ^{15/16} in (455.5 mm)
Depth	23 ^{1/4} in (590 mm)
Shipping Weight	128 lbs (58 kg)

FEATURES

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$65 / \$65
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

24" Combi-Steam XL



23^{7/16}"



23^{7/16}"

MODEL	MATERIAL	UMRP/RETAIL
DGC 7840 24" Combi-Steam XL	11876600	\$5,999 / \$6,199

DESIGN LINE	FINISH	TYPE
VitroLine	Graphite grey	Non-plumbed

SPECIFICATIONS

Width	23 ^{7/16} in (595 mm)
Height	17 ^{15/16} in (455.5 mm)
Depth	23 ^{1/4} in (590 mm)
Shipping Weight	128 lbs (58 kg)

FEATURES

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$65 / \$65
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

MODEL	MATERIAL	UMRP/RETAIL
DGC 7640 24" Combi-Steam XL	11876660	\$5,399 / \$5,599

DESIGN LINE	TYPE
PureLine	Non-plumbed

SPECIFICATIONS

Width	23 ^{7/16} in (595 mm)
Height	17 ^{15/16} in (455.5 mm)
Depth	23 ^{1/4} in (590 mm)
Shipping Weight	128 lbs (58 kg)

FEATURES

- M Touch S Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

24" Combi-Steam XL



23^{7/16}"



23^{7/16}"

MODEL	MATERIAL	UMRP/RETAIL
DGC 7440 24" Combi-Steam XL	11876950	\$3,999 / \$4,199

DESIGN LINE	TYPE
PureLine	Non-plumbed

SPECIFICATIONS	
Width	23 ^{7/16} in (595 mm)
Height	17 ^{15/16} in (455.5 mm)
Depth	23 ^{1/4} in (590 mm)
Shipping Weight	128 lbs (58 kg)

FEATURES	
- Miele@home with Miele Mix & Match	- DirectSensor Controls

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

MODEL	MATERIAL	UMRP/RETAIL
DGC 7440 24" Combi-Steam XL	11876970	\$3,999 / \$4,199

DESIGN LINE	FINISH	TYPE
VitroLine	Brilliant white	Non-plumbed

SPECIFICATIONS	
Width	23 ^{7/16} in (595 mm)
Height	17 ^{15/16} in (455.5 mm)
Depth	23 ^{1/4} in (590 mm)
Shipping Weight	128 lbs (58 kg)

FEATURES	
- Miele@home with Miele Mix & Match	- DirectSensor Controls

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

24" Combi-Steam XL



MODEL	MATERIAL	UMRP/RETAIL
DGC 7440 24" Combi-Steam XL	11876960	\$3,999 / \$4,199

DESIGN LINE	FINISH	TYPE
VitroLine	Graphite grey	Non-plumbed

SPECIFICATIONS

Width	23 ^{7/16} in (595 mm)
Height	17 ^{15/16} in (455.5 mm)
Depth	23 ^{1/4} in (590 mm)
Shipping Weight	128 lbs (58 kg)

FEATURES

- Miele@home with Miele Mix & Match
- DirectSensor Controls

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
Wire Rack - Self Clean Ready (1)	9520640	\$119 / \$119
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

24" Combi-Steam XXL



MODEL	MATERIAL	UMRP/RETAIL
DGC 7865 24" Combi-Steam XXL	11877020	\$7,299 / \$7,499

DESIGN LINE	TYPE
PureLine	Plumbed

SPECIFICATIONS	
Width	23 ^{7/16} in (595 mm)
Height	23 ^{7/16} in (596 mm)
Depth	23 ^{1/4} in (590 mm)
Shipping Weight	140 lbs (63.6 kg)

- | FEATURES | |
|-------------------------------------|----------------------|
| - M Touch Controls with MotionReact | - Wired Food Probe |
| - Miele@home with Miele Mix & Match | - Automatic Programs |

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready	9520640	\$119 / \$119
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$65 / \$65
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

MODEL	MATERIAL	UMRP/RETAIL
DGC 7860 24" Combi-Steam XXL	11876980	\$6,799 / \$6,999


DESIGN LINE	TYPE
PureLine	Non-plumbed

SPECIFICATIONS	
Width	23 ^{7/16} in (595 mm)
Height	23 ^{7/16} in (596 mm)
Depth	23 ^{1/4} in (590 mm)
Shipping Weight	140 lbs (63.6 kg)

- | FEATURES | |
|-------------------------------------|----------------------|
| - M Touch Controls with MotionReact | - Wired Food Probe |
| - Miele@home with Miele Mix & Match | - Automatic Programs |

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready	9520640	\$119 / \$119
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$65 / \$65
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

24" Combi-Steam XXL



MODEL	MATERIAL	UMRP/RETAIL
DGC 7860 24" Combi-Steam XXL	11877010	\$6,799 / \$6,999
DESIGN LINE	FINISH	TYPE
VitroLine	Brilliant white	Non-plumbed

SPECIFICATIONS

Width	23 ^{7/16} in (595 mm)
Height	23 ^{7/16} in (596 mm)
Depth	23 ^{1/4} in (590 mm)
Shipping Weight	140 lbs (63.6 kg)

FEATURES

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready	9520640	\$119 / \$119
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$65 / \$65
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

MODEL	MATERIAL	UMRP/RETAIL
DGC 7860 24" Combi-Steam XXL	11877000	\$6,799 / \$6,999
DESIGN LINE	FINISH	TYPE
VitroLine	Obsidian black	Non-plumbed

SPECIFICATIONS

Width	23 ^{7/16} in (595 mm)
Height	23 ^{7/16} in (596 mm)
Depth	23 ^{1/4} in (590 mm)
Shipping Weight	140 lbs (63.6 kg)

FEATURES

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready	9520640	\$119 / \$119
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$65 / \$65
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

24" Combi-Steam XXL



MODEL	MATERIAL	UMRP/RETAIL
DGC 7860 24" Combi-Steam XXL	11876990	\$6,799 / \$6,999

DESIGN LINE	FINISH	TYPE
VitroLine	Graphite grey	Non-plumbed

SPECIFICATIONS

Width	23 ^{7/16} in (595 mm)
Height	23 ^{7/16} in (596 mm)
Depth	23 ^{1/4} in (590 mm)
Shipping Weight	140 lbs (63.6 kg)

FEATURES

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs












STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
PerfectClean Universal Tray 24" Oven (1)	9519840	\$150 / \$150
PerfectClean FlexiClips (1)	9520660	\$185 / \$185
Wire Rack - Self Clean Ready	9520640	\$119 / \$119
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$65 / \$65
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$49 / \$49
DGG 20 Solid Cooking Pan (1)	8246340	\$49 / \$49

Optional Accessories

Combi-Steam Ovens

PRODUCT	MATERIAL	UMRP/RETAIL
Round Baking Tray	9520720	\$65 / \$65
Round Baking Tray w/ Logo	9520730	\$75 / \$75
Perforated Round Baking Tray	10116800	\$69 / \$69
Wooden Cutting Board	9120970	\$139 / \$139
PerfectClean Perforated Baking Tray	9520620	\$110 / \$110
PerfectClean Baking Tray	9519820	\$105 / \$105
PerfectClean Grill Insert (24" Oven)	9811960	\$125 / \$125
Side Runner for Holding Pans	8249560	\$49 / \$49
DGGL 12 Perforated Stainless Cooking Pan Large	8249430	\$65 / \$65
DGGL1 Small Perforated SS Pan	5001370	\$49 / \$49
DGG2 Small, Deep Solid Pan	5001390	\$49 / \$49
DGG3 Large, Deep Solid Pan	5001400	\$59 / \$59
DGG7 Small, Deepest Solid Pan	8019361	\$49 / \$49
DGGL4 Large, Deep Perforated Pan	5379570	\$59 / \$59
DGGL8 Large, Shallow Perforated Dish	8227240	\$59 / \$59
DGSE1 Porcelan Serving Dish	9438520	\$180 / \$180
EBA 7848 USA EDST/CLST Trim Kit: PureLine XL	11410740	\$449 / \$449
EBA 7848 USA OBSW Trim Kit: Obsidian black XL	11410770	\$449 / \$449
EBA 7848 USA BRWS Trim Kit: Brilliant white XL	11410790	\$449 / \$449
EBA 7848 USA GRGR Trim Kit: Graphite grey XL	11410800	\$449 / \$449
EBA 7868 USA EDST/CLST Trim Kit: PureLine XXL	11515790	\$449 / \$449
EBA 7868 USA OBSW Trim Kit: Obsidian black XXL	11515800	\$449 / \$449
EBA 7868 USA BRWS Trim Kit: Brilliant white XXL	11515810	\$449 / \$449
EBA 7868 USA GRGR Trim Kit: Graphite grey XXL	11515820	\$449 / \$449

Handle Options

GEN 7	MODEL	MATERIAL	TRIM / COLOR	HANDLE WIDTH	COOKING	VI DISHWASHER	SF DISHWASHER	VI COOLING	SF MASTERCOOL	UMRP/RETAIL
	DS 7000	11345890	PureLine Stainless steel ¹	15 ^{3/4} in	x	x		x		\$149 / \$149
	DS 7000	11345930	VitroLine Obsidian black ¹	15 ^{3/4} in	x	x		x		\$309 / \$309
	DS 7000	11345940	VitroLine Brilliant white ¹	15 ^{3/4} in	x	x		x		\$309 / \$309
	DS 7000	11345950	VitroLine Graphite grey ¹	15 ^{3/4} in	x	x		x		\$309 / \$309
	DS 7308	12047020	ContourLine Stainless steel standard handle	21 ^{1/8} in	x	x		x	x	\$169 / \$169
	DS 7708	12047000	ContourLine Stainless steel swiveling handle	21 ^{1/8} in	x	x		x	x	\$209 / \$209
	DS 7808	12047030	VitroLine Obsidian black	19 ^{11/16} in	x	x		x		\$349 / \$349
	DS 7808	12047050	VitroLine Graphite grey	19 ^{11/16} in	x	x		x		\$349 / \$349
	DS 7808	12047060	VitroLine Brilliant white	19 ^{11/16} in	x	x		x		\$349 / \$349
	DS 7808	12046910	PureLine Stainless steel	19 ^{11/16} in	x	x		x		\$169 / \$169
GEN 6	MODEL	MATERIAL	TRIM / COLOR	HANDLE WIDTH	COOKING	VI DISHWASHER	SF DISHWASHER	VI COOLING	SF MASTERCOOL	UMRP/RETAIL
	DS 6000	10490600	GEN6000 PureLine handle ²	22 ^{1/6} in			x (G 5000 SF)			\$169 / \$169
	DS 6000	9824160	GEN6000 ContourLine handle ²	22 ^{1/6} in			x (G 7000 SF)			\$169 / \$169

Fits Slimline VI Dishwashers¹
Dishwasher Replacement Handles²


Product Highlights

Gas Cooktops

*See specific models for details

FEATURE	DESCRIPTION
ComfortClean Grates	Enjoy the convenience of removable, dishwasher safe grates.
Powerful Burners	Option of natural gas or liquid propane.
Wok Burners	Single or dual-wok burner for uniform and/or separate power regulation of both flame rings.
Simple controls	Single-handed operation via rotary dial control.
Installation and Design Options	Choose a flush mounted cooktop for a more seamless look, or a proud installation including a lip of stainless steel above your countertop. Choose from stainless steel or elegant ceramic glass to suit your design needs.

Gas Cooktop



MODEL	MATERIAL	UMRP/RETAIL
KM 3010 G 24" Gas on Glass Cooktop	9272050	\$1,799 / \$1,899

SPECIFICATIONS

Width	24 ³ / ₄ in (626 mm)
Height	2 ¹ / ₄ in (54 mm)
Depth	20 ³ / ₄ in (526 mm)
Shipping Weight	37 lbs (17 kg)
Number of Burners	4
Burner Output in BTU	9300
Burner Output in BTU	5800
Burner Output in BTU	5800
Burner Output in BTU	3700

MODEL	MATERIAL	UMRP/RETAIL
KM 2012 G 24" Gas Cooktop	11471350	\$1,499 / \$1,599

SPECIFICATIONS

Width	25 ⁹ / ₁₆ in (650 mm)
Height	3 ⁵ / ₈ in (90 mm)
Depth	20 ¹ / ₂ in (520 mm)
Shipping Weight	36 lbs (16 kg)
Number of Burners	4
Burner Output in BTU	11300
Burner Output in BTU	5500
Burner Output in BTU	5500
Burner Output in BTU	3800

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
RWR1000 Wok Ring	9974600	\$95 / \$95

Gas Cooktop



MODEL	MATERIAL	UMRP/RETAIL
KM 3464 G 30" Gas Cooktop	6792680	\$2,399 / \$2,499

SPECIFICATIONS

Width	30 in (762 mm)
Height	3 1/4 in (83 mm)
Depth	21 3/8 in (542 mm)
Shipping Weight	50 lbs (22.7 kg)
Number of Burners	4
Burner Output in BTU	15300
Burner Output in BTU	12000
Burner Output in BTU	9000
Burner Output in BTU	9000

FEATURES

- Wok Burner

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
RWR1000 Wok Ring	9974600	\$95 / \$95

MODEL	MATERIAL	UMRP/RETAIL
KM 3465 G 30" Gas Cooktop	6792700	\$2,399 / \$2,499

SPECIFICATIONS

Width	30 in (762 mm)
Height	3 1/4 in (83 mm)
Depth	21 3/8 in (542 mm)
Shipping Weight	50 lbs (22.7 kg)
Number of Burners	4
Burner Output in BTU	15300
Burner Output in BTU	12000
Burner Output in BTU	9000
Burner Output in BTU	9000

FEATURES

- Wok Burner

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
RWR1000 Wok Ring	9974600	\$95 / \$95

Gas Cooktop



MODEL	MATERIAL	UMRP/RETAIL
KM 3465 LP 30" Gas Cooktop	6792730	\$2,399 / \$2,499

SPECIFICATIONS

Width	30 in (762 mm)
Height	3 ¹ / ₄ in (83 mm)
Depth	21 ³ / ₈ in (542 mm)
Shipping Weight	50 lbs (22.7 kg)
Number of Burners	4
Burner Output in BTU	15300
Burner Output in BTU	12000
Burner Output in BTU	9000
Burner Output in BTU	9000

FEATURES

- Wok Burner

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
RWR1000 Wok Ring	9974600	\$95 / \$95

MODEL	MATERIAL	UMRP/RETAIL
KM 2032 G 30" Gas Cooktop	10735660	\$1,499 / \$1,599

SPECIFICATIONS

Width	29 ¹ / ₂ in (750 mm)
Height	2 ¹ / ₈ in (54 mm)
Depth	20 ¹ / ₂ in (520 mm)
Shipping Weight	40 lbs (19 kg)
Number of Burners	5
Burner Output in BTU	11300
Burner Output in BTU	8600
Burner Output in BTU	5500
Burner Output in BTU	5500
Burner Output in BTU	3800

FEATURES

- Wok Burner

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
RWR1000 Wok Ring	9974600	\$95 / \$95

Gas Cooktop



MODEL	MATERIAL	UMRP/RETAIL
KM 3474 36" Gas Cooktop Hexa G	6792760	\$2,699 / \$2,799
KM 3474 36" Gas Cooktop Hexa LP	6792800	\$2,699 / \$2,799

SPECIFICATIONS

Width	36 in (914 mm)
Height	3 3/8 in (86 mm)
Depth	21 3/8 in (542 mm)
Shipping Weight	64 lbs (29 kg)
Number of Burners	5
Burner Output in BTU	15300
Burner Output in BTU	15300
Burner Output in BTU	1200
Burner Output in BTU	9000
Burner Output in BTU	9000

FEATURES

- Two Wok Burners

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
RWR1000 Wok Ring	9974600	\$95 / \$95

MODEL	MATERIAL	UMRP/RETAIL
KM 3475 36" Gas Cooktop Linear G	6792770	\$2,699 / \$2,799
KM 3475 G 36" Gas Cooktop Linear LP	6792810	\$2,699 / \$2,799

SPECIFICATIONS



Width	36 in (914 mm)
Height	3 3/8 in (86 mm)
Depth	21 3/8 in (542 mm)
Shipping Weight	64 lbs (29 kg)
Number of Burners	5
Burner Output in BTU	15300
Burner Output in BTU	15300
Burner Output in BTU	12000
Burner Output in BTU	9000
Burner Output in BTU	9000

FEATURES

- Two Wok Burners

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
RWR1000 Wok Ring	9974600	\$95 / \$95

Gas Cooktop



MODEL	MATERIAL	UMRP/RETAIL
KM 2355 G 36" Flush Gas Cooktop G	9450190	\$2,799 / \$2,899

SPECIFICATIONS

Width	35 ^{1/8} in (892 mm)
Height	4 ^{1/16} in (102 mm)
Depth	20 ^{3/16} in (512 mm)
Shipping Weight	51.8 lbs (23.5 kg)
Number of Burners	5
Burner Output in BTU	15000
Burner Output in BTU	9800
Burner Output in BTU	5900
Burner Output in BTU	5900
Burner Output in BTU	3900

FEATURES

- Wok Burner

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
RWR1000 Wok Ring	9974600	\$95 / \$95

MODEL	MATERIAL	UMRP/RETAIL
KM 2355 LP 36" Flush Gas Cooktop LP	9456920	\$2,799 / \$2,899

SPECIFICATIONS


Width	35 ^{1/8} in (892 mm)
Height	4 ^{1/16} in (102 mm)
Depth	20 ^{3/16} in (512 mm)
Shipping Weight	51.8 lbs (23.5 kg)
Number of Burners	5
Burner Output in BTU	15000
Burner Output in BTU	9800
Burner Output in BTU	5900
Burner Output in BTU	5900
Burner Output in BTU	3900

FEATURES

- Wok Burner

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
RWR1000 Wok Ring	9974600	\$95 / \$95

Gas Cooktop



MODEL	MATERIAL	UMRP/RETAIL
KM 3054-1G 36" Gas on Glass Cooktop G	11766750	\$2,799 / \$2,899

SPECIFICATIONS

Width	37 ¹ / ₈ in (942 mm)
Height	21 ³ / ₁₆ in (71 mm)
Depth	20 ³ / ₄ in (526 mm)
Shipping Weight	54 lbs (24.5 kg)
Number of Burners	5
Burner Output in BTU	16500
Burner Output in BTU	9300
Burner Output in BTU	5800
Burner Output in BTU	5800
Burner Output in BTU	3750

FEATURES

- Wok Burner

MODEL	MATERIAL	UMRP/RETAIL
KM 3484 G 42" Gas Cooktop Hexa G	6792840	\$2,899 / \$2,999



SPECIFICATIONS

Width	42 ¹ / ₂ in (1079 mm)
Height	3 ¹ / ₄ in (83 mm)
Depth	21 ³ / ₈ in (542 mm)
Shipping Weight	75 lbs (34 kg)
Number of Burners	6
Burner Output in BTU	15300
Burner Output in BTU	15300
Burner Output in BTU	12000
Burner Output in BTU	12000
Burner Output in BTU	9000
Burner Output in BTU	9000

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
RWR1000 Wok Ring	9974600	\$95 / \$95

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
RWR1000 Wok Ring	9974600	\$95 / \$95

Gas Cooktop



MODEL	MATERIAL	UMRP/RETAIL
KM 3485 G 42" Gas Cooktop Linear G	6792850	\$2,899 / \$2,999

SPECIFICATIONS

Width	42 ^{1/2} in (1079 mm)
Height	3 ^{1/4} in (83 mm)
Depth	21 ^{3/8} in (542 mm)
Shipping Weight	75 lbs (34 kg)
Number of Burners	6
Burner Output in BTU	15300
Burner Output in BTU	15300
Burner Output in BTU	12000
Burner Output in BTU	12000
Burner Output in BTU	9000
Burner Output in BTU	9000

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
RWR1000 Wok Ring	9974600	\$95 / \$95

MODEL	MATERIAL	UMRP/RETAIL
KM 3485 LP 42" Gas Cooktop Linear LP	6792870	\$2,899 / \$2,999

SPECIFICATIONS

Width	42 ^{1/2} in (1079 mm)
Height	3 ^{1/4} in (83 mm)
Depth	21 ^{3/8} in (542 mm)
Shipping Weight	75 lbs (34 kg)
Number of Burners	6
Burner Output in BTU	15300
Burner Output in BTU	15300
Burner Output in BTU	12000
Burner Output in BTU	12000
Burner Output in BTU	9000
Burner Output in BTU	9000

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
RWR1000 Wok Ring	9974600	\$95 / \$95



Product Highlights

Electric Cooktops and Induction Cooktops

*See specific models for details

FEATURE	DESCRIPTION
Auto Heat-Up	Provides an initial power boost before reducing the power level for continued cooking.
Keep Warm Function	The temperature is controlled to keep food at serving temperature, while also preventing the food from burning.
Timer	Set a duration for cook time with automatic alert once complete.
TwinBoost	Booster function for the shortest boiling times.
Flex Zones	Accommodates many sizes and shapes of cooking.
Efficient Induction	Most energy efficient cooking method Miele offers.
Stylish Glass	Black glass surface adds a clean look to any kitchen.

Electric Cooktop



MODEL	MATERIAL	UMRP/RETAIL
KM 5621 240v Electric Cooktop	7821660	\$1,899 / \$1,999

SPECIFICATIONS

Width	24 ^{3/4} in (626 mm)
Height	21 ^{7/16} in (68 mm)
Depth	21 ^{7/16} in (544 mm)
Shipping Weight	39 lbs (17.7 kg)
Number of Burners	3 (2 variable)
Burner Output in Watts	1100-2150-3100
Burner Output in Watts	700-1800
Burner Output in Watts	1200

FEATURES

- Residual Heat Indicators for Each Zone
- Easy to use Direct Control

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
HUB62-22 16" x 10" Casserole Dish	10314280	\$249 / \$249
HUB62-35 16" x 15" Casserole Dish	10314300	\$319 / \$319
HUB5000-XL 17.6" x 15" x 2" Casserole Dish	10314310	\$319 / \$319
Scraper Razor Blade Glass Scraper	1065471	\$18 / \$18
Glass Cooktop Cleaner	10173130	\$13.99 / \$13.99

MODEL	MATERIAL	UMRP/RETAIL
KM 5621 208v Electric Cooktop	7821670	\$1,899 / \$1,999

SPECIFICATIONS



Width	24 ^{3/4} in (626 mm)
Height	21 ^{7/16} in (68 mm)
Depth	21 ^{7/16} in (544 mm)
Shipping Weight	39 lbs (17.7 kg)
Number of Burners	3 (2 variable)
Burner Output in Watts	1100-2150-3100
Burner Output in Watts	700-1800
Burner Output in Watts	1200

FEATURES

- Residual Heat Indicators for Each Zone
- Easy to use Direct Control

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
HUB62-22 16" x 10" Casserole Dish	10314280	\$249 / \$249
HUB62-35 16" x 15" Casserole Dish	10314300	\$319 / \$319
HUB5000-XL 17.6" x 15" x 2" Casserole Dish	10314310	\$319 / \$319
Razor Blade Glass Scraper	1065471	\$18 / \$18
Glass Cooktop Cleaner	10173130	\$13.99 / \$13.99

Electric Cooktop



MODEL	MATERIAL	UMRP/RETAIL
KM 5820 240v Electric Cooktop	7821720	\$1,999 / \$2,099

SPECIFICATIONS

Width	24 ^{3/4} in (626 mm)
Height	2 ^{11/16} in (68 mm)
Depth	20 ^{3/4} in (526 mm)
Shipping Weight	39 lbs (17.7 kg)
Number of Burners	3 (2 variable)
Burner Output in Watts	1100-2150-3100
Burner Output in Watts	700-1800
Burner Output in Watts	1200

FEATURES

- Residual Heat Indicators for Each Zone
- Easy to use Direct Control Plus

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
HUB62-22 16" x 10" Casserole Dish	10314280	\$249 / \$249
HUB62-35 16" x 15" Casserole Dish	10314300	\$319 / \$319
HUB5000-XL 17.6" x 15" x 2" Casserole Dish	10314310	\$319 / \$319
Razor Blade Glass Scraper	1065471	\$18 / \$18
Glass Cooktop Cleaner	10173130	\$13.99 / \$13.99

MODEL	MATERIAL	UMRP/RETAIL
KM 5624 240v Electric Cooktop	7821680	\$2,099 / \$2,199

SPECIFICATIONS


Width	30 ^{1/2} in (775 mm)
Height	2 ^{15/16} in (75 mm)
Depth	21 ^{7/16} in (544 mm)
Shipping Weight	41 lbs (18.8 kg)
Number of Burners	4 (3 variable)
Burner Output in Watts	1600-2500
Burner Output in Watts	700-1800
Burner Output in Watts	1200

FEATURES

- Residual Heat Indicators for Each Zone
- Easy to use Direct Control


OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
HUB62-22 16" x 10" Casserole Dish	10314280	\$249 / \$249
HUB62-35 16" x 15" Casserole Dish	10314300	\$319 / \$319
HUB5000-XL 17.6" x 15" x 2" Casserole Dish	10314310	\$319 / \$319
Razor Blade Glass Scraper	1065471	\$18 / \$18
Glass Cooktop Cleaner	10173130	\$13.99 / \$13.99

Electric Cooktop



21 ⁷/₁₆"

30 ¹/₂"



21 ⁷/₁₆"

36"

MODEL	MATERIAL	UMRP/RETAIL
KM 5840 240v Electric Cooktop	7821740	\$2,299 / \$2,399

SPECIFICATIONS

Width	30 ¹ / ₂ in (775 mm)
Height	2 ¹¹ / ₁₆ in (68 mm)
Depth	21 ⁷ / ₁₆ in (544 mm)
Shipping Weight	41 lbs (18.5 kg)
Number of Burners	4 (3 variable)
Burner Output in Watts	1600-2500
Burner Output in Watts	1600-2500
Burner Output in Watts	700-1800
Burner Output in Watts	1200

FEATURES

- Residual Heat Indicators for Each Zone
- Easy to use Direct Control Plus

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
HUB62-22 16" x 10" Casserole Dish	10314280	\$249 / \$249
HUB62-35 16" x 15" Casserole Dish	10314300	\$319 / \$319
HUB5000-XL 17.6" x 15" x 2" Casserole Dish	10314310	\$319 / \$319
Razor Blade Glass Scraper	1065471	\$18 / \$18
Glass Cooktop Cleaner	10173130	\$13.99 / \$13.99

MODEL	MATERIAL	UMRP/RETAIL
KM 5627 240v Electric Cooktop	7821700	\$2,299 / \$2,399

SPECIFICATIONS



Width	36 in (915 mm)
Height	2 ¹⁵ / ₁₆ in (75 mm)
Depth	21 ⁷ / ₁₆ in (544 mm)
Shipping Weight	50 lbs (22.7 kg)
Number of Burners	5 (4 variable)
Burner Output in Watts	2000-2700
Burner Output in Watts	1600-2500
Burner Output in Watts	700-1800
Burner Output in Watts	700-1800
Burner Output in Watts	1200

FEATURES

- Residual Heat Indicators for Each Zone
- Easy to use Direct Control

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
HUB62-22 16" x 10" Casserole Dish	10314280	\$249 / \$249
HUB62-35 16" x 15" Casserole Dish	10314300	\$319 / \$319
HUB5000-XL 17.6" x 15" x 2" Casserole Dish	10314310	\$319 / \$319
Razor Blade Glass Scraper	1065471	\$18 / \$18
Glass Cooktop Cleaner	10173130	\$13.99 / \$13.99

Electric Cooktop



MODEL	MATERIAL	UMRP/RETAIL
KM 5627 208v Electric Cooktop	7821710	\$2,299 / \$2,399

SPECIFICATIONS

Width	36 in (915 mm)
Height	2 ¹⁵ / ₁₆ in (75 mm)
Depth	21 ⁷ / ₁₆ in (544 mm)
Shipping Weight	50 lbs (22.7 kg)
Number of Burners	5 (4 variable)
Burner Output in Watts	2000-3100
Burner Output in Watts	1600-2500
Burner Output in Watts	700-1800
Burner Output in Watts	700-1800
Burner Output in Watts	1200

FEATURES

- Residual Heat Indicators for Each Zone
- Easy to use Direct Control

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
HUB62-22 16" x 10" Casserole Dish	10314280	\$249 / \$249
HUB62-35 16" x 15" Casserole Dish	10314300	\$319 / \$319
HUB5000-XL 17.6" x 15" x 2" Casserole Dish	10314310	\$319 / \$319
Razor Blade Glass Scraper	1065471	\$18 / \$18
Glass Cooktop Cleaner	10173130	\$13.99 / \$13.99

MODEL	MATERIAL	UMRP/RETAIL
KM 5860 240v Electric Cooktop	7821760	\$2,599 / \$2,699

SPECIFICATIONS


Width	36 in (915 mm)
Height	2 ¹¹ / ₁₆ in (68 mm)
Depth	21 ⁷ / ₁₆ in (544 mm)
Shipping Weight	48.5 lbs (22 kg)
Number of Burners	5 (4 variable)
Burner Output in Watts	1100-2150-3100
Burner Output in Watts	1600-2500
Burner Output in Watts	700-1800
Burner Output in Watts	700-1800
Burner Output in Watts	1200

FEATURES

- Residual Heat Indicators for Each Zone
- Easy to use Direct Control Plus

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
HUB62-22 16" x 10" Casserole Dish	10314280	\$249 / \$249
HUB62-35 16" x 15" Casserole Dish	10314300	\$319 / \$319
HUB5000-XL 17.6" x 15" x 2" Casserole Dish	10314310	\$319 / \$319
Razor Blade Glass Scraper	1065471	\$18 / \$18
Glass Cooktop Cleaner	10173130	\$13.99 / \$13.99

Electric Cooktop



MODEL	MATERIAL	UMRP/RETAIL
KM 5880 240v Electric Cooktop	7821780	\$2,899 / \$2,999

SPECIFICATIONS

Width	42 ^{1/2} in (915 mm)
Height	2 ^{11/16} in (75 mm)
Depth	21 ^{7/16} in (544 mm)
Shipping Weight	55 lbs (25 kg)
Number of Burners	5 (4 variable)
Burner Output in Watts	1100-2150-3100
Burner Output in Watts	1600-2500
Burner Output in Watts	700-1800
Burner Output in Watts	700-1800
Burner Output in Watts	1200

FEATURES

- Residual Heat Indicators for Each Zone
- Easy to use Direct Control Plus

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
HUB62-22 16" x 10" Casserole Dish	10314280	\$249 / \$249
HUB62-35 16" x 15" Casserole Dish	10314300	\$319 / \$319
HUB5000-XL 17.6" x 15" x 2" Casserole Dish	10314310	\$319 / \$319
Razor Blade Glass Scraper	1065471	\$18 / \$18
Glass Cooktop Cleaner	10173130	\$13.99 / \$13.99

Induction Cooktop



MODEL	MATERIAL	UMRP/RETAIL
KM 7720 Induction Cooktop	12074190	\$1,999 / \$2,099

SPECIFICATIONS

Width	24 ^{5/8} in (626 mm)
Height	3 ^{1/8} in (78 mm)
Depth	21 ^{7/16} in (544 mm)
Shipping Weight	35.6 lbs (17.5 kg)
Number of Burners	3 (1)
Burner Output in Watts: (208v - 240v)	2400-2750-3350 / 2600-3000-3700
Burner Output in Watts: (208v - 240v)	1700-2300-2750 / 1850-2500-3000
Burner Output in Watts: (208v - 240v)	1300-1550-2000 / 1850-2500-3000

FEATURES

- SmartSelect controls with yellow display
- Boost function up to 3700W
- 3 powerful cooking zones
- Stainless Steel Frame for surface mounting

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Razor Blade Glass Scraper	1065471	\$18 / \$18
Glass Cooktop Cleaner	10173130	\$13.99 / \$13.99

MODEL	MATERIAL	UMRP/RETAIL
KM 7730 FR Induction Cooktop	12074200	\$2,499 / \$2,599

SPECIFICATIONS

Width	30 ^{1/2} in (775 mm)
Height	3 ^{1/8} in (78 mm)
Depth	21 ^{7/16} in (544 mm)
Shipping Weight	44 lbs (20 kg)
Number of Burners	4 (1)
Burner Output in Watts: (208v - 240v)	2400-2750-3350 / 2600-3000-3700
Burner Output in Watts: (208v - 240v)	1300-1550-2000 / 1400-1700-2200
Burner Output in Watts: (208v - 240v)	1700-2300-1750 / 1850-2300-3300
Burner Output in Watts: (208v - 240v)	1700-2300-2750 / 1850-2500-3000

FEATURES

- SmartSelect controls with yellow display
- Boost function up to 3700W
- 4 powerful cooking zones
- Stainless Steel Frame for surface mounting

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Razor Blade Glass Scraper	1065471	\$18 / \$18
Glass Cooktop Cleaner	10173130	\$13.99 / \$13.99

Induction Cooktop



MODEL	MATERIAL	UMRP/RETAIL
KM 7735 FL Induction Cooktop	12074210	\$2,999 / \$3,099

SPECIFICATIONS

Width	30 ³ / ₈ in (769 mm)
Height	3 ⁷ / ₈ in (98 mm)
Depth	21 ¹ / ₄ in (538 mm)
Shipping Weight	44.6 lbs (21.23 kg)
Number of Burners	4 (1)
Burner Output in Watts: Max. Rating Max. Booster power rating Max. TwinBooster power rating (208v - 240v)	2600-3000-3700
Burner Output in Watts: Max. Rating Max. Booster power rating Max. TwinBooster power rating (208v - 240v)	1400-1700-2200
Burner Output in Watts: Max. Rating Max. Booster power rating Max. TwinBooster power rating (208v - 240v)	3400-4800-7400

FEATURES

- SmartSelect controls with yellow display
- Boost function up to 4800W
- 4 powerful cooking zones
- Stainless Steel Frame for surface mounting

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Razor Blade Glass Scraper	1065471	\$18 / \$18
Glass Cooktop Cleaner	10173130	\$13.99 / \$13.99

MODEL	MATERIAL	UMRP/RETAIL
KM 7740 36" Induction Cooktop with Frame	12074220	\$2,899 / \$2,999

SPECIFICATIONS

Width	36 in (915 mm)
Height	3 ¹ / ₈ in (78 mm)
Depth	21 ¹ / ₂ in (544 mm)
Shipping Weight	55 lbs (25 kg)
Number of Burners	5
Burner Output in Watts: (208v - 240v)	1300-1550-2000 / 1400-1700-2200
Burner Output in Watts: (208v - 240v)	2100-2750-3350 / 2300-3000-3700
Burner Output in Watts: (208v - 240v)	2400-2750-3350 / 2600-3000-3700
Burner Output in Watts: (208v - 240v)	1700-2300-2750 / 1850-2500-3000
Burner Output in Watts: (208v - 240v)	1700-2300-2750 / 1850-2500-3000

FEATURES

- SmartSelect controls with yellow display
- Boost function up to 3700W
- 5 powerful cooking zones
- Stainless Steel Frame for surface mounting

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Razor Blade Glass Scraper	1065471	\$18 / \$18
Glass Cooktop Cleaner	10173130	\$13.99 / \$13.99

Induction Cooktop



MODEL	MATERIAL	UMRP/RETAIL
KM 7745 FL 36" Induction Cooktop with Frame	12074230	\$3,499 / \$3,599

SPECIFICATIONS

Width	35 7/8 in (909 mm)
Height	4 1/8 in (103 mm)
Depth	21 1/4 in (578 mm)
Shipping Weight	68.34 lbs (31 kg)
Number of Burners	6
Burner Output in Watts: Max. Rating Max. Booster power rating Max. TwinBooster power rating (208v - 240v)	3100-3400-3700
Burner Output in Watts: Max. Rating Max. Booster power rating Max. TwinBooster power rating (208v - 240v)	3400-4800-7400
Burner Output in Watts: Max. Rating Max. Booster power rating Max. TwinBooster power rating (208v - 240v)	3400-4800-7400

FEATURES

- SmartSelect controls with yellow display
- Boost function up to 4800W
- 5 powerful cooking zones
- Stainless Steel Frame for surface mounting

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Razor Blade Glass Scraper	1065471	\$18 / \$18
Glass Cooktop Cleaner	10173130	\$13.99 / \$13.99

MODEL	MATERIAL	UMRP/RETAIL
KM 7755 FL 42" Induction Cooktop with Frame	12074240	\$4,499 / \$4,599

SPECIFICATIONS

Width	42 3/8 in (1074 mm)
Height	35 7/8 in (909 mm)
Depth	21 1/4 in (538 mm)
Shipping Weight	72.3 lbs (32.8 kg)
Number of Burners	5
Burner Output in Watts: Max. Rating Max. Booster power rating Max. TwinBooster power rating (208v - 240v)	3400-4800-7400
Burner Output in Watts: Max. Rating Max. Booster power rating Max. TwinBooster power rating (208v - 240v)	2600-3000-3700
Burner Output in Watts: Max. Rating Max. Booster power rating Max. TwinBooster power rating (208v - 240v)	3400-4800-7400

FEATURES

- SmartSelect controls with yellow display
- Boost function up to 4800W
- 5 powerful cooking zones
- Stainless Steel Frame for surface mounting

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Razor Blade Glass Scraper	1065471	\$18 / \$18
Glass Cooktop Cleaner	10173130	\$13.99 / \$13.99

CombiSets



MODEL	MATERIAL	UMRP/RETAIL
CS1011-1 G 12" Wok Gas Burner G	11763790	\$1,499 / \$1,599

SPECIFICATIONS

Width	11 ^{5/16} in (288 mm)
Height	2 ^{1/4} in (57 mm)
Depth	20 ^{1/2} in (520 mm)
Shipping Weight	21 lbs (9.5 kg)
Number of Burners	1
Burner Output in BTU	680-17500

MODEL	MATERIAL	UMRP/RETAIL
CS1012-2 G 12" Double Gas Burner G	11763800	\$1,499 / \$1,599

SPECIFICATIONS

Width	11 ^{5/16} in (288 mm)
Height	2 ^{1/4} in (57 mm)
Depth	20 ^{1/2} in (520 mm)
Shipping Weight	21 lbs (9.5 kg)
Number of Burners	2
Burner Output in BTU	1550-10600
Burner Output in BTU	775-5700

CombiSets



MODEL	MATERIAL	UMRP/RETAIL
CS1012-2 LP 12" Double Gas Burner LP	11763810	\$1,499 / \$1,599

SPECIFICATIONS

Width	11 ⁵ / ₁₆ in (288 mm)
Height	2 ¹ / ₄ in (57 mm)
Depth	20 ¹ / ₂ in (520 mm)
Shipping Weight	21 lbs (9.5 kg)
Number of Burners	2
Burner Output in BTU	1550-10600
Burner Output in BTU	775-5700

MODEL	MATERIAL	UMRP/RETAIL
CS 1112 E 240v 12" Electric Double Burner 240V	7141710	\$1,499 / \$1,599

SPECIFICATIONS

Width	11 ⁵ / ₁₆ in (288 mm)
Height	2 ¹ / ₄ in (57 mm)
Depth	20 ¹ / ₂ in (520 mm)
Shipping Weight	18 lbs (8.1 kg)
Number of Burners	2
Burner Output in Watts	700-1800
Burner Output in Watts	1200

CombiSets



MODEL	MATERIAL	UMRP/RETAIL
CS 1327 Y 15" Tepan Yaki	7890140	\$2,599 / \$2,699

SPECIFICATIONS

Width	14 ^{15/16} in (288 mm)
Height	2 ^{5/8} in (68 mm)
Depth	20 ^{1/2} in (520 mm)
Shipping Weight	34 lbs (15.4 kg)
Number of Burners	1
Burner Output in Watts	1200

MODEL	MATERIAL	UMRP/RETAIL
CS 1411 F Electric Boiler/Fryer	7141820	\$2,099 / \$2,199

SPECIFICATIONS

Width	11 ^{5/16} in (288 mm)
Height	9 ^{1/16} in (100 mm)
Depth	20 ^{1/2} in (520 mm)
Shipping Weight	23 lbs (10.4 kg)
Number of Burners	1
Burner Output in Watts	2400

Product Highlights

Ventilation Hoods

*See specific models for details

FEATURE	DESCRIPTION
LED Lighting	Shines a bright, more natural light and is energy efficient and long-lasting.
Miele@home	Control the airflow or turn your hood on/off by interacting with your appliance via the Miele@home app.
Delayed Shutdown	After cooking, program the hood to turn off automatically once the air is clear.
Stainless Steel Mesh Filters	Efficiently and effectively filter steam, odors and grease from your kitchen. Dishwasher safe and extremely durable.
Miele CleanCover	Smooth liner inside the canopy preventing exposure to live components, cables and sharp edges.
Odor Free Charcoal Filter with Recirculation Option	Works to neutralize any unpleasant odors.

Range Hood



MODEL	MATERIAL	UMRP/RETAIL
DAR1220-3 30" Wall Range Hood	11898130	\$2,299 / \$2,399

SPECIFICATIONS

Width	29 ^{15/16} in (760 mm)
Height	18 in (457 mm)
Depth	24 ^{1/16} in (611 mm)
Shipping Weight	90.4 lbs. (41 kg)

FEATURES

- LED ClearView Lighting
- Vented or Recirculating Option
- Recessed Knob Controls

BLOWERS (ONE IS REQUIRED)	MATERIAL	UMRP/RETAIL
700 CFM Internal Blower DRIB XL	9764830	\$699 / \$699
700 CFM External Blower DREB XL	9764930	\$949 / \$949

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
30" Recirculating Kit DRUU 30	9764700	\$489 / \$489
6" x 30" DuctCover DRDC 3006		\$369 / \$369
12" x 30" DuctCover DRDC 3012	9764560	\$389 / \$389
18" x 30" DuctCover DRDC 3018	9764570	\$409 / \$409
24" x 30" DuctCover DRDC 3024	9764590	\$459 / \$459
DKF23-1 Charcoal Filter 2 pcs.	9812040	\$119 / \$119

MODEL	MATERIAL	UMRP/RETAIL
DAR1230-3 36" Wall Range Hood	11898170	\$2,399 / \$2,499

SPECIFICATIONS

Width	35 ^{15/16} in (913 mm)
Height	18 in (457 mm)
Depth	24 ^{1/16} in (611 mm)
Shipping Weight	103.6 lbs. (47 kg)

FEATURES

- LED ClearView Lighting
- Vented or Recirculating Option
- Recessed Knob Controls

BLOWERS (ONE IS REQUIRED)	MATERIAL	UMRP/RETAIL
700 CFM Internal Blower DRIB XL	9764830	\$699 / \$699
1100 CFM Internal Blower DRIB XXL	9764910	\$749 / \$749
700 CFM External Blower DREB XL	9764930	\$949 / \$949
1100 CFM External Blower DREB XXL	9764940	\$1,049 / \$1,049

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
36" Recirculating Kit DRUU 36	9764750	\$529 / \$529
6" x 36" DuctCover DRDC 3606	9764610	\$369 / \$369
12" x 36" DuctCover DRDC 3612	9764630	\$389 / \$389
18" x 36" DuctCover DRDC 3618	9764640	\$409 / \$409
24" x 36" DuctCover DRDC 3624	9764660	\$459 / \$459
DKF24-1 Charcoal Filter 3 pcs.	9812050	\$149 / \$149

Range Hood



MODEL	MATERIAL	UMRP/RETAIL
DAR1250-3 48" Wall Range Hood	11898190	\$2,599 / \$2,699

SPECIFICATIONS

Width	47 ^{15/16} in (1218 mm)
Height	18 in (457 mm)
Depth	24 ^{1/16} in (611 mm)
Shipping Weight	125.7 lbs. (57 kg)

FEATURES

- LED ClearView Lighting
- Recessed Knob Controls

BLOWERS (ONE IS REQUIRED)	MATERIAL	UMRP/RETAIL
1100 CFM Internal Blower DRIB XXL	9764910	\$749 / \$749
1100 CFM External Blower DREB XXL	9764940	\$1,049 / \$1,049

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
6" x 48" DuctCover DRDC 4806	9764650	\$369 / \$369
12" x 48" DuctCover DRDC 4812	9764670	\$389 / \$389
18" x 48" DuctCover DRDC 4818	9764680	\$409 / \$409
24" x 48" DuctCover DRDC 4824	9764690	\$459 / \$459

MODEL	MATERIAL	UMRP/RETAIL
DAR 1130 36" Insert Hood	9753480	\$1,799 / \$1,899

SPECIFICATIONS

Width	33 ^{7/16} in (850 mm)
Height	17 ^{5/8} in (448 mm)
Depth	22 ^{13/16} in (579 mm)
Shipping Weight	77.2 lbs. (35 kg)

FEATURES

- LED ClearView Lighting
- Vented or Recirculating Option
- Recessed Knob Controls

BLOWERS (ONE IS REQUIRED)	MATERIAL	UMRP/RETAIL
700 CFM Internal Blower DRIB XL	9764830	\$699 / \$699
1100 CFM Internal Blower DRIB XXL	9764910	\$749 / \$749
700 CFM External Blower DREB XL	9764930	\$949 / \$949
1100 CFM External Blower DREB XXL	9764940	\$1,049 / \$1,049

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
36" Recirculating Kit DRUU 36	9764750	\$529 / \$529
6" x 36" DuctCover DRDC 3606	9764610	\$369 / \$369
12" x 36" DuctCover DRDC 3612	9764630	\$389 / \$389
18" x 36" DuctCover DRDC 3618	9764640	\$409 / \$409
24" x 36" DuctCover DRDC 3624	9764660	\$459 / \$459
DKF24-1 Charcoal Filter 3 pcs.	9812050	\$149 / \$149

Range Hood



MODEL	MATERIAL	UMRP/RETAIL
DAR 1150 48" Insert Hood	9753510	\$1,999 / \$2,099



SPECIFICATIONS	
Width	45 ^{1/2} in (1155 mm)
Height	17 ^{5/8} in (448 mm)
Depth	22 ^{13/16} in (579 mm)
Shipping Weight	92.6 lbs. (42 kg)

FEATURES
<ul style="list-style-type: none"> - LED ClearView lighting - Recessed Knob Controls

BLOWERS (ONE IS REQUIRED)	MATERIAL	UMRP/RETAIL
1100 CFM Internal Blower DRIB XXL	9764910	\$749 / \$749
1100 CFM External Blower DREB XXL	9764940	\$1,049 / \$1,049

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
6" x 48" DuctCover DRDC 4806	9764650	\$369 / \$369
12" x 48" DuctCover DRDC 4812	9764670	\$389 / \$389
18" x 48" DuctCover DRDC 4818	9764680	\$409 / \$409
24" x 48" DuctCover DRDC 4824	9764690	\$459 / \$459

Wall Hood



MODEL	MATERIAL	UMRP/RETAIL
DA398-7 30" Wall Hood	10558810	\$2,499 / \$2,599

SPECIFICATIONS

Width	29 ^{7/16} in (748 mm)
Height	4 ^{3/4} in (120mm)
Overall Height Vented	27 ^{3/8} - 40 in (695-1015 mm)
Overall Height Recirculation	32 ^{1/2} - 45 ^{1/16} in (825-1145 mm)
Depth	20 ^{1/2} " (520 mm)
Shipping Weight	55.3 lbs (25.1 kg)

FEATURES

- Vented or Recirculating

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Recirculating Kit DUW20	6264790	\$109 / \$109
Charcoal Filter DKF12-900	10363780	\$139 / \$139
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66
Chimney Extension DATK1-760	6847210	\$259 / \$259
Chimney Extension DATK2-1000	6847220	\$329 / \$329

MODEL	MATERIAL	UMRP/RETAIL
DA399-7 36" Wall Hood	10558800	\$2,499 / \$2,599

SPECIFICATIONS

Width	35 ^{1/4} in (898 mm)
Height	4 ^{3/4} in (120 mm)
Overall Height Vented	27 ^{3/8} - 40 in (695-1015 mm)
Overall Height Recirculation	32 ^{1/2} - 45 ^{1/16} in (825-1145 mm)
Depth	20 ^{1/2} in (520 mm)
Shipping Weight	55.3 lbs (25.1 kg)

FEATURES

- Vented or Recirculating

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Recirculating Kit DUW20	6264790	\$109 / \$109
Charcoal Filter DKF12-900	10363780	\$139 / \$139
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66
Chimney Extension DATK1-760	6847210	\$259 / \$259
Chimney Extension DATK2-1000	6847220	\$329 / \$329

Wall Hood



MODEL	MATERIAL	UMRP/RETAIL
DA5428W 48" Wall Hood w/Wifi	10934860	\$3,199 / \$3,299

SPECIFICATIONS

Width	47 ^{3/16} in (1198 mm)
Height	4 ^{3/4} in (120 mm)
Overall Height Vented	29 ^{5/16} - 41 ^{9/16} in (745 - 1005 mm)
Overall Height Recirculation	34 ^{7/16} - 46 ^{11/16} in (875 - 1185 mm)
Depth	20 ^{1/2} in (520 mm)
Shipping Weight	114 lbs (52 kg)

FEATURES

- Con@ctivity
- Vented or Recirculating

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Recirculating Kit DUW20	6264790	\$109 / \$109
Charcoal Filter DKF12-900	10363780	\$139 / \$139
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66

MODEL	MATERIAL	UMRP/RETAIL
DA6596 W 36" Incognito Wall Hood	9762220	\$2,899 / \$2,999

SPECIFICATIONS

Width	35 ^{1/4} in (898 mm)
Height	2 ^{7/8} in (70 mm)
Overall Height Vented	27 ^{1/4} - 39 ^{3/4} in (693-1010 mm)
Overall Height Recirculation	32 ^{1/4} - 45 in (820-1143 mm)
Depth	19 ^{1/16} in (500 mm)
Shipping Weight	55 lbs (25 kg)

FEATURES

- Vented or Recirculating
- Variable - Swappable Glass or Steel Panels

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Recirculating Kit DUW20	6264790	\$109 / \$109
Charcoal Filter DKF12-900	10363780	\$139 / \$139
Glass Panels (3) DRP6590W Glass	9047920	\$120 / \$120
Stainless Steel Panels (3)DRP6590W SS	9047970	\$120 / \$120
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66
Chimney Extension DATK1-760	6847210	\$259 / \$259
Chimney Extension DATK2-1000	6847220	\$329 / \$329

Wall Hood



MODEL	MATERIAL	UMRP/RETAIL
DA6698 W 36" Puristic Edition 6000 Wall Hood w/Wifi	10877010	\$3,399 / \$3,499

SPECIFICATIONS

Width	35 ^{3/8} in (898 mm)
Height	3 ^{3/8} in (85 mm)
Overall Height Vented	28 - 40 ^{9/16} in (710 -1030 mm)
Overall Height Recirculation	33 ^{1/16} - 45 ^{11/16} in (840 -1160 mm)
Depth	19 ^{11/16} in (500 mm)
Shipping Weight	57.2 lbs (26 kg)

FEATURES

- Con@ctivity
- Vented or Recirculating

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Recirculating Kit DUW20	6264790	\$109 / \$109
Charcoal Filter DKF12-900	10363780	\$139 / \$139
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66
Chimney Extension DATK1-760	6847210	\$259 / \$259
Chimney Extension DATK2-1000	6847220	\$329 / \$329

MODEL	MATERIAL	UMRP/RETAIL
DA6698 W 36" Puristic Edition 6000 Wall Hood BRWS w/Wifi	10877030	\$3,399 / \$3,499

SPECIFICATIONS


Width	35 ^{3/8} in (898 mm)
Height	3 ^{3/8} in (85 mm)
Overall Height Vented	28 - 40 ^{9/16} in (710 -1030 mm)
Overall Height Recirculation	33 ^{1/16} - 45 ^{11/16} in (840 -1160 mm)
Depth	19 ^{11/16} in (500 mm)
Shipping Weight	57.2 lbs (26 kg)

FEATURES

- Con@ctivity
- Vented or Recirculating

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Recirculating Kit DUW20	6264790	\$109 / \$109
Charcoal Filter DKF12-900	10363780	\$139 / \$139
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66

Wall Hood



MODEL	MATERIAL	UMRP/RETAIL
DA6698 W 36" Puristic Edition 6000 Wall Hood OBSW w/Wifi	10877060	\$3,399 / \$3,499

SPECIFICATIONS

Width	35 ^{3/8} in (898 mm)
Height	3 ^{3/8} in (85 mm)
Overall Height Vented	28 - 40 ^{9/16} in (710 -1030 mm)
Overall Height Recirculation	33 ^{1/16} - 45 ^{11/16} in (840 -1160 mm)
Depth	19 ^{11/16} in (500 mm)
Shipping Weight	57.2 lbs (26 kg)

FEATURES

- Con@ctivity
- Vented or Recirculating

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Recirculating Kit DUW20	6264790	\$109 / \$109
Charcoal Filter DKF12-900	10363780	\$139 / \$139
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66

MODEL	MATERIAL	UMRP/RETAIL
DA6798 36" Shape Wall Hood w/Wifi	10876860	\$2,799 / \$2,899

SPECIFICATIONS



Width	35 ^{3/8} in (898 mm)
Height	22 ^{3/8} in (568 mm)
Depth	19 ^{7/16} in (493 mm)
Shipping Weight	103.5 lbs (47 kg)

FEATURES

- Con@ctivity

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
OdorFree Charcoal Filter DKF 25-900	10515270	\$108 / \$108
Chimney DADC 6000	9947450	\$215 / \$215
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66

Wall Hood



MODEL	MATERIAL	UMRP/RETAIL
PUR88 W 30" PUR Wall Hood	10743170	\$1,399 / \$1,499

SPECIFICATIONS

Width	29 ^{7/16} in (748 mm)
Height	2 ^{1/2} in (62 mm)
Overall Height Vented	26 ^{15/16} in (685 mm) - 39 ^{9/16} in (1005 mm)
Overall Height Recirculation	32 ^{1/16} in (815 mm) - 44 ^{11/16} in (1135 mm)
Depth	19 ^{11/16} in (500 mm)
Shipping Weight	62 lbs (28 kg)

FEATURES

- Vented or Recirculating

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Recirculating Kit DUW20	6264790	\$109 / \$109
Charcoal Filter DKF12-900	10363780	\$139 / \$139
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66
Chimney Extension DATK1-760	6847210	\$259 / \$259
Chimney Extension DATK2-1000	6847220	\$329 / \$329

MODEL	MATERIAL	UMRP/RETAIL
PUR98 W 36" PUR Wall Hood	10743150	\$1,499 / \$1,599

SPECIFICATIONS

Width	35 ^{3/8} in (898 mm)
Height	2 ^{1/2} in (62mm)
Overall Height Vented	26 ^{15/16} in (685 mm) - 39 ^{9/16} in (1005 mm)
Overall Height Recirculation	32 ^{1/16} in (815 mm) - 44 ^{11/16} in (1135 mm)
Depth	19 ^{11/16} in (500 mm)
Shipping Weight	62 lbs (28 kg)

FEATURES

- Vented or Recirculating

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Recirculating Kit DUW20	6264790	\$109 / \$109
Charcoal Filter DKF12-900	10363780	\$139 / \$139
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66
Chimney Extension DATK1-760	6847210	\$259 / \$259
Chimney Extension DATK2-1000	6847220	\$329 / \$329

Wall Hood



MODEL	MATERIAL	UMRP/RETAIL
DA 6498 36" Pure Wall Hood GRGR	10811940	\$2,599 / \$2,699

SPECIFICATIONS

Width	35 ^{3/8} in (898 mm)
Height	21 ^{5/8} in (550 mm)
Depth	20 ^{9/16} in (522 mm)
Shipping Weight	93 lbs (47 kg)

FEATURES

- Con@ctivity
- Vented or Recirculating

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
DADC 6000 GRGR	11900540	\$199 / \$199

Island Hood



MODEL	MATERIAL	UMRP/RETAIL
DA4248 V D 48" Puristic Varia Island Hood w/Wifi	10877250	\$5,299 / \$5,399

SPECIFICATIONS

Width	47 ^{3/16} in (1198 mm)
Height	2 ^{3/4} in (70 mm)
Overall Height Vented	29 ^{3/4} in (755 mm) - 41 ^{7/16} in (1045 mm)
Depth	27 ^{1/8} in (698 mm)
Shipping Weight	107.8 lbs (49 kg)

FEATURES

- Con@ctivity

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66

MODEL	MATERIAL	UMRP/RETAIL
DA6596 D 36" Incognitio Island Hood	9762240	\$3,799 / \$3,899

SPECIFICATIONS

Width	35 ^{3/8} in (898 mm)
Height	2 ^{3/4} in (70 mm)
Overall Height Vented	27 ^{3/16} - 39 in (690-990 mm)
Overall Height Recirculation	29 ^{1/2} - 41 ^{3/4} in (750-1060 mm)
Depth	23 ^{9/16} in (598 mm)
Shipping Weight	74.8 lbs (34kg)

FEATURES

- Con@ctivity
- Vented or Recirculating
- Variable - Swappable Glass or Steel Panels

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Recirc. Kit for Island Hoods DUI32	9561760	\$109 / \$109
Charcoal Filter DKF12-900	10363780	\$139 / \$139
Glass Panels (3) DRP6590 D Glass	9048010	\$115 / \$115
Stainless Steel Panels (3)DRP6590 D SS	9048020	\$115 / \$115
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66

Island Hood



MODEL	MATERIAL	UMRP/RETAIL
DA6698 D 36" Puristic Edition 6000 Island Hood w/Wifi	10877210	\$4,599 / \$4,699

SPECIFICATIONS

Width	35 ^{3/8} in (898mm)
Height	3 ^{3/8} in (85mm)
Overall Height Vented	27 ^{3/4} - 39 ^{9/16} in (705 -1005 mm)
Overall Height Recirculation	30 ^{1/8} - 43 ^{5/16} in (765 -1075 mm)
Depth	23 ^{9/16} in (598 mm)
Shipping Weight	74.8 lbs (34 kg)

FEATURES

- Con@ctivity
- Vented or Recirculating

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Recirc. Kit for Island Hoods DUI32	9561760	\$109 / \$109
Charcoal Filter DKF12-900	10363780	\$139 / \$139
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66

MODEL	MATERIAL	UMRP/RETAIL
DA6698 D 36" Puristic Edition 6000 Island Hood BRWS w/Wifi	10877230	\$4,599 / \$4,699

SPECIFICATIONS


Width	35 ^{3/8} in (898 mm)
Height	3 ^{3/8} in (85 mm)
Overall Height Vented	27 ^{3/4} - 39 ^{9/16} in (705 -1005 mm)
Overall Height Recirculation	30 ^{1/8} - 43 ^{5/16} in (765 -1075 mm)
Depth	23 ^{9/16} in (598 mm)
Shipping Weight	74.8 lbs (34 kg)

FEATURES

- Con@ctivity
- Vented or Recirculating

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Recirc. Kit for Island Hoods DUI32	9561760	\$109 / \$109
Charcoal Filter DKF12-900	10363780	\$139 / \$139
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66

Island Hood



MODEL	MATERIAL	UMRP/RETAIL
DA6698 D 36" Puristic Edition 6000 Island Hood OBSW w/Wifi	10877240	\$4,599 / \$4,699

SPECIFICATIONS	
Width	35 ^{3/8} in (898 mm)
Height	3 ^{3/8} in (85 mm)
Overall Height Vented	27 ^{3/4} - 39 ^{9/16} in (705 -1005 mm)
Overall Height Recirculation	30 ^{1/8} - 43 ^{5/16} in (765 -1075 mm)
Depth	23 ^{9/16} in (598 mm)
Shipping Weight	74.8 lbs (34 kg)

FEATURES
<ul style="list-style-type: none"> - Con@ctivity - Vented or Recirculating

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Recirc. Kit for Island Hoods DUI32	9561760	\$109 / \$109
Charcoal Filter DKF12-900	10363780	\$139 / \$139
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66


MODEL	MATERIAL	UMRP/RETAIL
PUR98 D 36" PUR Island Hood	10743130	\$2,299 / \$2,399

SPECIFICATIONS	
Width	35 ^{3/8} in (898 mm)
Height	2 ^{3/4} in (70 mm)
Overall Height Vented	27 ^{3/16} - 39 in (690-990 mm)
Overall Height Recirculation	29 ^{1/2} - 41 ^{3/4} in (750-1060 mm)
Depth	23 ^{9/16} in (598 mm)
Shipping Weight	74.8 lbs (34 kg)

FEATURES
<ul style="list-style-type: none"> - Vented or recirculating

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Recirc. Kit for Island Hoods DUI32	9561760	\$109 / \$109
Charcoal Filter DKF12-900	10363780	\$139 / \$139
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66

Built In Hood



MODEL	MATERIAL	UMRP/RETAIL
DA2518 44" Built In Hood w/Wifi	10876740	\$1,999 / \$2,099

SPECIFICATIONS	
Width	43 ^{3/4} in (1102 mm)
Height	12 ^{7/8} in (326 mm)
Depth	15 ^{13/16} in (402 mm)
Shipping Weight	40.4 lbs (18.3 kg)

- FEATURES**
- Con@ctivity
 - Vented or Recirculating

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66
Recirculating Kit DUU150	5696270	\$115 / \$115
Recirculating Kit DUU151	7294230	\$115 / \$115
OdorFree Charcoal Filter DKF 15-900	10363800	\$139 / \$139

MODEL	MATERIAL	UMRP/RETAIL
DA2588 32" Built In Hood w/Wifi	10876770	\$1,799 / \$1,899

SPECIFICATIONS	
Width	31 ^{9/16} in (802 mm)
Height	12 ^{7/8} in (326 mm)
Depth	15 ^{13/16} in (402 mm)
Shipping Weight	40.4 lbs (18.3 kg)

- FEATURES**
- Con@ctivity
 - Vented or Recirculating

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66
Recirculating Kit DUU150	5696270	\$115 / \$115
Recirculating Kit DUU151	7294230	\$115 / \$115
OdorFree Charcoal Filter DKF 15-900	10363800	\$139 / \$139

Built In Hood



MODEL	MATERIAL	UMRP/RETAIL
DAS2620 24" Built In Hood	11878490	\$1,199 / \$1,299

SPECIFICATIONS

Width	23 ^{1/2} in (596 mm)
Height	1 ^{1/2} in (36 mm)
Depth	10 ^{3/4} in (273 mm)
Shipping Weight	31 lbs (14.0 kg)

FEATURES

- LED Strip lighting

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66
Recirculating Kit DUU150	5696270	\$109 / \$109
Recirculating Kit DUU151	7294230	\$115 / \$115
OdorFree Charcoal Filter DKF 31-900 P	12123400	See mieleusa.com
Mounting Kit DML 400	9232000	\$90 / \$90

MODEL	MATERIAL	UMRP/RETAIL
DAS4720 30" Built In Hood	11878520	\$1,499 / \$1,599

SPECIFICATIONS

Width	30 in (762 mm)
Height	1 ^{1/2} in (36mm)
Depth	10 ^{3/4} in (273mm)
Shipping Weight	36 lbs (16 kg)

FEATURES

- LED Strip lighting, WiFi Enabled

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66
Recirculating Kit DUU150	5696270	\$115 / \$115
Recirculating Kit DUU151	7294230	\$115 / \$115
OdorFree Charcoal Filter DKF 31-900 P	12123400	See mieleusa.com
Brackets for DAS hoods DML 2000	11839970	\$49 / \$49

Built In Hood



MODEL	MATERIAL	UMRP/RETAIL
DAS4940 34" Built In Hood	11878570	\$1,699 / \$1,799

SPECIFICATIONS

Width	34 in (861 mm)
Height	2 ³ / ₄ in (68 mm)
Depth	12 ¹ / ₈ in (307 mm)
Shipping Weight	38 lbs (17.0 kg)

FEATURES

- LED Strip lighting, WiFi Enabled

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66
Recirculating Kit DUU150	5696270	\$115 / \$115
Recirculating Kit DUU151	7294230	\$115 / \$115
OdorFree Charcoal Filter DKF 31-900 P	12123400	See mieleusa.com

MODEL	MATERIAL	UMRP/RETAIL
DAS8930 34" Built In Hood w/Wifi	11878590	\$2,099 / \$2,199

SPECIFICATIONS

Width	34 in (861 mm)
Height	2 ³ / ₈ in (60 mm)
Depth	12 ¹ / ₈ in (307 mm)
Shipping Weight	42 lbs (19.0 kg)

FEATURES

- LED Strip lighting, WiFi Enabled

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66
Recirculating Kit DUU150	5696270	\$115 / \$115
Recirculating Kit DUU151	7294230	\$115 / \$115
OdorFree Charcoal Filter DKF 31-900 P	12123400	See mieleusa.com

Built In Hood



MODEL	MATERIAL	UMRP/RETAIL
DAS 2920 36" Built In Hood	11878500	\$1,299 / \$1,399

SPECIFICATIONS	
Width	35 ^{3/8} in (896 mm)
Height	1 ^{1/2} in (36 mm)
Depth	10 ^{3/4} in (273 mm)
Shipping Weight	36 lbs (16.0 kg)

FEATURES
- LED Strip lighting

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66
Recirculating Kit DUU150	5696270	\$115 / \$115
Recirculating Kit DUU151	7294230	\$115 / \$115
OdorFree Charcoal Filter DKF 31-900 P	12123400	See mieleusa.com
Brackets for DAS hoods DML 2000	11839970	\$49 / \$49


MODEL	MATERIAL	UMRP/RETAIL
DAS4930 36" Built In Hood w/Wifi	11878550	\$1,599 / \$1,699

SPECIFICATIONS	
Width	35 ^{3/8} in (896 mm)
Height	1 ^{1/2} in (36 mm)
Depth	10 ^{3/4} in (273 mm)
Shipping Weight	36 lbs (16.0 kg)

FEATURES
- LED Strip lighting, WiFi Enabled

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66
Recirculating Kit DUU150	5696270	\$115 / \$115
Recirculating Kit DUU151	7294230	\$115 / \$115
OdorFree Charcoal Filter DKF 31-900 P	12123400	See mieleusa.com

Built In Hood



MODEL	MATERIAL	UMRP/RETAIL
DA 2698 SS 35" Extra Slim Insert ss w/Wifi	10876810	\$2,399 / \$2,499

SPECIFICATIONS

Width	34 ^{5/8} in (880 mm)
Height	13 ^{1/2} in (342 mm)
Depth	11 ^{1/2} in (293 mm)
Shipping Weight	35.5 lbs (16.1 kg)

FEATURES

- Con@ctivity
- Vented or Recirculating

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66
Recirculating Kit DUU150	5696270	\$115 / \$115
Recirculating Kit DUU151	7294230	\$115 / \$115
OdorFree Charcoal Filter DKF 19-900	10794600	\$125 / \$125
6" Adapter DAA6	10811120	\$89 / \$89
Recirculating Kit DUU 2900-900	11131670	\$499 / \$499

MODEL	MATERIAL	UMRP/RETAIL
DA 2698 BRWS 35" Extra Slim Insert BRWS w/Wifi	10876830	\$2,399 / \$2,499

SPECIFICATIONS

Width	34 ^{5/8} in (880 mm)
Height	13 ^{1/2} in (342 mm)
Depth	11 ^{1/2} in (293 mm)
Shipping Weight	35.5 lbs (16.1 kg)

FEATURES

- Con@ctivity
- Vented or Recirculating

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66
Recirculating Kit DUU150	5696270	\$115 / \$115
Recirculating Kit DUU151	7294230	\$115 / \$115
OdorFree Charcoal Filter DKF 19-900	10794600	\$125 / \$125
6" Adapter DAA6	10811120	\$89 / \$89
Recirculating Kit DUU 2900-900	11131670	\$499 / \$499

Built In Hood



MODEL	MATERIAL	UMRP/RETAIL
DA 2628 44" Extra Slim Insert ss w/Wifi	10876800	\$2,699 / \$2,799

SPECIFICATIONS

Width	46 ^{7/16} in (1180 mm)
Height	13 ^{1/2} in (342 mm)
Depth	11 ^{1/2} in (293 mm)
Shipping Weight	33 lbs (15 kg)

FEATURES

- Con@ctivity

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
6" Adapter DAA6	10811120	\$89 / \$89

MODEL	MATERIAL	UMRP/RETAIL
DA 2360 24" Extra Slim Insert	10765130	\$1,199 / \$1,299

SPECIFICATIONS


Width	23 in (584 mm)
Height	13 ^{5/16} in (338 mm)
Depth	11 ^{11/16} in (297 mm)
Shipping Weight	24 lbs (11 lbs)

FEATURES

- Vented or Recirculating

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66
Recirculating Kit DUU150	5696270	\$115 / \$115
Recirculating Kit DUU151	7294230	\$115 / \$115
OdorFree Charcoal Filter DKF 19-900	10794600	\$125 / \$125
6" Adapter DAA6	10811120	\$89 / \$89

Built In Hood



MODEL	MATERIAL	UMRP/RETAIL
DA 2390 36" Extra Slim Insert Insert	10743660	\$1,599 / \$1,699

SPECIFICATIONS

Width	34 ^{11/16} in (884 mm)
Height	13 ^{5/16} in (338 mm)
Depth	11 ^{11/16} in (297 mm)
Shipping Weight	24 lbs (11 lbs)

FEATURES

- Vented or Recirculating

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66
Recirculating Kit DUU150	5696270	\$115 / \$115
Recirculating Kit DUU151	7294230	\$115 / \$115
OdorFree Charcoal Filter DKF 19-900	10794600	\$125 / \$125
6" Adapter DAA6	10811120	\$89 / \$89

Built Under Hood



MODEL	MATERIAL	UMRP/RETAIL
DA1260 24" Built-Under Hood	10662780	\$899 / \$999

SPECIFICATIONS	
Width	23 ^{9/16} in (598 mm)
Height	5 in (125 mm)
Depth	19 ^{11/16} in (500 mm)
Shipping Weight	30.5 lbs (14 kg)


OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66
OdorFree Charcoal Filter DKF 18-900	10363830	\$110 / \$110

MODEL	MATERIAL	UMRP/RETAIL
DA1280 30" Built-Under Hood	10451490	\$999 / \$1,099

SPECIFICATIONS	
Width	29 ^{15/16} in (760 mm)
Height	5 in (125 mm)
Depth	19 ^{11/16} in (500 mm)
Shipping Weight	35 lbs (16 kg)

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66
OdorFree Charcoal Filter DKF 18-900	10363830	\$110 / \$110

Downdraft Extractor



MODEL	MATERIAL	UMRP/RETAIL
DA6881 30" Downdraft chassis Requires One Blower - choose from below	10595900	\$2,750 / \$2,850
DA6881 30" Downdraft w/DAG1000 Requires One Blower - choose from below	94001370	\$3,399 / \$3,499

SPECIFICATIONS

Width	30 in (762 mm)
Height	25 ^{11/16} in (652 mm)
Depth	4 ^{3/4} in (120 mm)
Shipping Weight	63 lbs (28.6 kg)

FEATURES

- Vented or Recirculating

BLOWERS (ONE IS REQUIRED)	MATERIAL	UMRP/RETAIL
DAG 600 Internal Blower	10596850	\$249 / \$249
DAG 1000 External Blower	7832530	\$649 / \$649

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66
Recirculating Kit DUU 2900-900	11131670	\$499 / \$499
OdorFree Charcoal Filter DKF 18-900	10363830	\$99.95 / \$99.95

MODEL	MATERIAL	UMRP/RETAIL
DA6891 36" Downdraft chassis Requires One Blower - choose from below	10595910	\$2,950 / \$3,050
DA6891 36" Downdraft w/DAG1000 Requires One Blower - choose from below	94001390	\$3,599 / \$3,699

SPECIFICATIONS

Width	36 in (915 mm)
Height	25 ^{11/16} in (652 mm)
Depth	4 ^{3/4} in (120 mm)
Shipping Weight	74 lbs (33.6 kg)

FEATURES

- Vented or Recirculating

BLOWERS (ONE IS REQUIRED)	MATERIAL	UMRP/RETAIL
DAG 600 Internal Blower	10596850	\$249 / \$249
DAG 1000 External Blower	7832530	\$649 / \$649

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66
Recirculating Kit DUU 2900-900	11131670	\$499 / \$499
OdorFree Charcoal Filter DKF 18-900	10363830	\$110 / \$110

Ceiling Extractor



MODEL	MATERIAL	UMRP/RETAIL
DA 2818 Ceiling Extractor	9762150	\$3,099 / \$3,199

SPECIFICATIONS

Width	43 ⁵ / ₁₆ in (1100 mm)
Height	12 ¹ / ₈ in (308 mm)
Depth	27 ⁹ / ₁₆ in (700 mm)
Shipping Weight	71 lbs (32.2 kg)

FEATURES

- Con@ctivity
- Vented or Recirculating


OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Reducing Collar DRC 2000	12140450	\$127.66 / \$127.66
Remote Control DARC6	9812060	\$99 / \$99
Recirculating Kit DUU 2900-900	11131670	\$499 / \$499
OdorFree Charcoal Filter DKF 18-900	w	

Product Highlights

Warming Drawers and Vacuum Sealing Drawers

FEATURE	DESCRIPTION
Touch Controls	Program selection at the touch of a button via a flush touch control panel.
Push2Open Mechanism	Opening the drawer requires the lightest touch.
Four Operating Modes for Warming Drawers	Warm cups and plates or keep food at serving temperature with temperature settings from 104 - 185° F.
Fully Telescopic Runners	Drawers can be pulled out completely for easy loading and unloading.
Three Vacuum Settings	Choose from three vacuum settings - level 3 for meat, level 1 for fruit.
Sous-Vide Cooking Preparation	Thanks to the vacuum drawer, you can optimally prepare all different types of food for Sous-Vide cooking.

24" Handleless Warming Drawer



MODEL	MATERIAL	UMRP/RETAIL
ESW 7010 24" Handleless Warming Drawer	11794720	\$1,599 / \$1,699

DESIGN LINE	FINISH
VitroLine	Obsidian black

SPECIFICATIONS

Width	23 ^{7/16} in (595 mm)
Height	5 ^{9/16} in (141 mm)
Depth	22 ^{1/2} in (587 mm)
Shipping Weight	45 lbs (20.3 kg)

FEATURES

- Keep Food or Plates and Cups Warm
- Fits 6 Place Settings
- Non-Slip Liner
- Control Panel with Sensor Controls
- Miele@home Connected

MODEL	MATERIAL	UMRP/RETAIL
ESW 7010 24" Handleless Warming Drawer	11794730	\$1,599 / \$1,699

DESIGN LINE	FINISH
VitroLine	Brilliant white


SPECIFICATIONS

Width	23 ^{7/16} in (595 mm)
Height	5 ^{9/16} in (141 mm)
Depth	22 ^{1/2} in (587 mm)
Shipping Weight	45 lbs (20.3 kg)

FEATURES

- Keep Food or Plates and Cups Warm
- Fits 6 Place Settings
- Non-Slip Liner
- Control Panel with Sensor Controls
- Miele@home Connected

24" Handleless Warming Drawer



MODEL	MATERIAL	UMRP/RETAIL
ESW 7010 24" Handleless Warming Drawer	11794740	\$1,599 / \$1,699

DESIGN LINE	FINISH
VitroLine	Graphite grey

SPECIFICATIONS

Width	23 ^{7/16} in (595 mm)
Height	5 ^{9/16} in (141 mm)
Depth	22 ^{1/2} in (587 mm)
Shipping Weight	45 lbs (20.3 kg)

FEATURES

- Keep Food or Plates and Cups Warm
- Fits 6 Place Settings
- Non-Slip Liner
- Control Panel with Sensor Controls
- Miele@home Connected

30" Handleless Warming Drawer



MODEL	MATERIAL	UMRP/RETAIL
ESW 7570 30" Handleless Warming Drawer	11794790	\$2,499 / \$2,599

DESIGN LINE

ContourLine

SPECIFICATIONS

Width	29 ^{13/16} in (757 mm)
Height	9 ^{13/16} in (250 mm)
Depth	21 ^{3/4} in (542 mm)
Shipping Weight	70.5 lbs (32 kg)

FEATURES

- Keep Food or Plates and Cups Warm
- Fits 12 Place Settings
- Non-Slip Liner
- Control Panel with Sensor Controls
- Miele@home Connected

*Can have DGC, CVA or BM sit directly on top of drawer.

MODEL	MATERIAL	UMRP/RETAIL
ESW 7580 30" Handleless Warming Drawer	11794800	\$2,599 / \$2,699

DESIGN LINE

ContourLine

SPECIFICATIONS


Width	29 ^{13/16} in (757 mm)
Height	10 ^{13/16} in (275 mm)
Depth	23 ^{7/8} in (608 mm)
Shipping Weight	74.3 lbs (33.7 kg)

FEATURES

- Keep Food or Plates and Cups Warm
- Fits 12 Place Settings
- Non-Slip Liner
- Control Panel with Sensor Controls
- Miele@home Connected

*Requires shelf above drawer.

30" Handleless Warming Drawer



MODEL	MATERIAL	UMRP/RETAIL
ESW 7670 30" Handleless Warming Drawer	11794810	\$2,499 / \$2,599

DESIGN LINE
PureLine

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	9 ^{13/16} in (250 mm)
Depth	21 ^{3/4} in (542 mm)
Shipping Weight	70.5 lbs (32 kg)

FEATURES	
- Keep Food or Plates and Cups Warm	- Control Panel with Sensor Controls
- Fits 12 Place Settings	- Miele@home Connected
- Non-Slip Liner	

*Can have DGC, CVA or BM sit directly on top of drawer.

MODEL	MATERIAL	UMRP/RETAIL
ESW 7670 30" Handleless Warming Drawer	11794840	\$2,499 / \$2,599


DESIGN LINE	FINISH
VitroLine	Obsidian black

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	9 ^{13/16} in (250 mm)
Depth	21 ^{3/4} in (542 mm)
Shipping Weight	70.5 lbs (32 kg)

FEATURES	
- Keep Food or Plates and Cups Warm	- Control Panel with Sensor Controls
- Fits 12 Place Settings	- Miele@home Connected
- Non-Slip Liner	

*Can have DGC, CVA or BM sit directly on top of drawer.

30" Handleless Warming Drawer



MODEL	MATERIAL	UMRP/RETAIL
ESW 7670 30" Handleless Warming Drawer	11794850	\$2,499 / \$2,599

DESIGN LINE	FINISH
VitroLine	Brilliant white

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	9 ^{13/16} in (250 mm)
Depth	21 ^{3/4} in (542 mm)
Shipping Weight	70.5 lbs (32 kg)

FEATURES	
- Keep Food or Plates and Cups Warm	- Control Panel with Sensor Controls
- Fits 12 Place Settings	- Miele@home Connected

*Can have DGC, CVA or BM sit directly on top of drawer.

MODEL	MATERIAL	UMRP/RETAIL
ESW 7670 30" Handleless Warming Drawer	11794820	\$2,499 / \$2,599

DESIGN LINE	FINISH
VitroLine	Graphite grey

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	9 ^{13/16} in (250 mm)
Depth	21 ^{3/4} in (542 mm)
Shipping Weight	70.5 lbs (32 kg)

FEATURES	
- Keep Food or Plates and Cups Warm	- Control Panel with Sensor Controls
- Fits 12 Place Settings	- Miele@home Connected

*Can have DGC, CVA or BM sit directly on top of drawer.

30" Handleless Warming Drawer



MODEL	MATERIAL	UMRP/RETAIL
ESW 7670 30" Handleless Warming Drawer	12423660	\$2,499 / \$2,599


DESIGN LINE	FINISH
ArtLine	Obsidian Black matte

SPECIFICATIONS	
Width	29 13/16 in (757 mm)
Height	9 13/16 in (250 mm)
Depth	21 3/4 in (542 mm)
Shipping Weight	70.5 lbs (32 kg)

FEATURES	
- Keep Food or Plates and Cups Warm	- Control Panel with Sensor Controls
- Fits 12 Place Settings	- Miele@home Connected

*Can have DGC, CVA or BM sit directly on top of drawer.

30" Handleless Warming Drawer



MODEL	MATERIAL	UMRP/RETAIL
ESW 7680 30" Handleless Warming Drawer	11794860	\$2,599 / \$2,699

DESIGN LINE
PureLine

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	10 ^{13/16} in (275 mm)
Depth	23 ^{7/8} in (608 mm)
Shipping Weight	74.3 lbs (33.7 kg)

FEATURES	
- Keep Food or Plates and Cups Warm	- Control Panel with Sensor Controls
- Fits 12 Place Settings	- Miele@home Connected

*Requires shelf above drawer.

MODEL	MATERIAL	UMRP/RETAIL
ESW 7680 30" Handleless Warming Drawer	11794880	\$2,599 / \$2,699

DESIGN LINE	FINISH
VitroLine	Obsidian black

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	10 ^{13/16} in (275 mm)
Depth	23 ^{7/8} in (608 mm)
Shipping Weight	74.3 lbs (33.7 kg)

FEATURES	
- Keep Food or Plates and Cups Warm	- Control Panel with Sensor Controls
- Fits 12 Place Settings	- Miele@home Connected

*Requires shelf above drawer.

30" Handleless Warming Drawer



MODEL	MATERIAL	UMRP/RETAIL
ESW 7680 30" Handleless Warming Drawer	11794890	\$2,599 / \$2,699

DESIGN LINE	FINISH
VitroLine	Brilliant white

SPECIFICATIONS

Width	29 ^{13/16} in (757 mm)
Height	10 ^{13/16} in (275 mm)
Depth	23 ^{7/8} in (608 mm)
Shipping Weight	74.3 lbs (33.7 kg)

FEATURES

- Keep Food or Plates and Cups Warm
- Fits 12 Place Settings
- Control Panel with Sensor Controls
- Miele@home Connected

*Requires shelf above drawer.

MODEL	MATERIAL	UMRP/RETAIL
ESW 7680 30" Handleless Warming Drawer	11794870	\$2,599 / \$2,699

DESIGN LINE	FINISH
ArtLine	Graphite grey

SPECIFICATIONS

Width	29 ^{13/16} in (757 mm)
Height	10 ^{13/16} in (275 mm)
Depth	23 ^{7/8} in (608 mm)
Shipping Weight	74.3 lbs (33.7 kg)

FEATURES

- Keep Food or Plates and Cups Warm
- Fits 12 Place Settings
- Control Panel with Sensor Controls
- Miele@home Connected

*Requires shelf above drawer.

30" Handleless Warming Drawer



MODEL	MATERIAL	UMRP/RETAIL
ESW 7680	12424280	\$2,599 / \$2,699

DESIGN LINE	FINISH
ArtLine	Obsidian Black matte

SPECIFICATIONS	
Width	29 ^{13/16} in (757 mm)
Height	10 ^{13/16} in (275 mm)
Depth	23 ^{7/8} in (608 mm)
Shipping Weight	74.3 lbs (33.7 kg)

FEATURES	
- Keep Food or Plates and Cups Warm	- Control Panel with Sensor Controls
- Fits 12 Place Settings	- Miele@home Connected

*Requires shelf above drawer.

30" Handleless Warming Drawer



MODEL	MATERIAL	UMRP/RETAIL
-------	----------	-------------

ESW 6380 FB 30" Warming Drawer - Panel Ready	9685060	\$2,499 / \$2,599
---	---------	-------------------

DESIGN LINE

Fully Integrated

SPECIFICATIONS



Width	29 ^{13/16} in (757 mm)
Height	10 ^{13/16} in (275 mm)
Depth	24 ^{3/4} in (629 mm)
Shipping Weight	70 lbs (31.7 kg)

FEATURES

- Keep Food or Plates and Cups Warm
- Fits 12 Place Settings
- Control Panel with Sensor Controls
- Miele@home

*Requires shelf above drawer.

Vacuum Sealing Drawers



MODEL	MATERIAL	UMRP/RETAIL
EVS 7010 24" Vacuum Sealing Drawer	11845430	\$3,399 / \$3,499

SPECIFICATIONS

Width	23 ^{1/2} in (595 mm)
Height	5 ^{5/8} in (141 mm)
Depth	22 ^{1/2} in (570 mm)
Shipping Weight	77 lbs (35 kg)

FEATURES

- Three Vacuum Settings
- Push2Open
- Preperation for Sous-Vide Cooking
- Large Usable Space

MODEL	MATERIAL	UMRP/RETAIL
EVS 7670 30" Vacuum Sealing Drawer	11845480	\$4,299 / \$4,399


SPECIFICATIONS

Width	29 ^{7/8} in (757 mm)
Height	9 ^{7/8} in (248 mm)
Depth	22 ^{1/2} in (570 mm)
Shipping Weight	114.5 lbs (52 kg)

FEATURES

- Three Vacuum Settings
- Push2Open
- Preperation for Sous-Vide Cooking
- Large Usable Space

Vacuum Sealing Drawers



MODEL	MATERIAL	UMRP/RETAIL
EVS 7670 (ArtLine Obsidian Black matte) 30" Vacuum Sealing Drawer	12423610	\$4,299 / \$4,399

SPECIFICATIONS

Width	29 7/8 in (757 mm)
Height	9 7/8 in (248 mm)
Depth	22 1/2 in (570 mm)
Shipping Weight	114.5 lbs (52 kg)

FEATURES

- Three Vacuum Settings
- Push2Open
- Preperation for Sous-Vide Cooking
- Large Usable Space

Product Highlights

Built-In Coffee Machines

FEATURE	DESCRIPTION
Quality	Miele products are designed to last. Our machines are tested to a service life of 20 years.
AromaticSystemFresh	Intensive coffee aroma submerges the home with this intelligent technology.
OneTouch for Two	The OneTouch for Two function allows two glasses of latte macchiato, cappuccino, coffee or espresso to be made at the same time.
M Touch	Large touch display with MotionReact movement sensor.
Removable Brew Unit	Easy to remove and clean, your machine guarantees impeccable hygiene, long service life and perfect coffee enjoyment.
Miele@home	Convenient and time-saving, control your machine right from your mobile device.
AutoDescal & AutoClean	No manual descaling or cleaning: select CVA models clean fully-automatically.
CoffeeSelect	Featured on select CVA 7000 machines, enjoy 3 bean containers where your coffee specialty is always prepared with the right coffee bean.

Built-In Coffee System



18 7/8"

29 13/16"



17 15/16"

23 7/16"



MODEL	MATERIAL	UMRP/RETAIL
CVA 7370 Built-In Coffee System	11733830	\$5,499 / \$5,699

FINISH	DESIGN LINE	TYPE
Clean Touch Steel™	ContourLine	Non-plumbed

SPECIFICATIONS

Width	29 13/16 in
Height	18 7/8 in
Depth	18 5/8 in
Shipping Weight	81 lbs

FEATURES

- DirectSensor Touch Display
- AromaticSystemFresh
- Miele@home
- 26 Coffee & Tea Specialty Drinks
- Coffee Pot / Teapot / DoubleShot
- OneTouch for Two
- EasyClick Milk System
- Programmable Beverage Parameters
- Maximum Spout Height: 6.5"
- 10 Programmable User Profiles
- BrilliantLight
- CupSensor
- Removable Brew Unit / ComfortClean

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
EasyClick Milk System	11234120	\$155 / \$155
Descaling Tablets	11201170	\$21.99 / \$21.99
Cleaning Tablets	11201250	\$21.99 / \$21.99
Milk Pipework Cleaner	10182210	\$42.99 / \$42.99

MODEL	MATERIAL	UMRP/RETAIL
CVA 7440 Built-In Coffee System	11733860	\$4,699 / \$4,899

FINISH	DESIGN LINE	TYPE
Clean Touch Steel™	PureLine	Non-plumbed

SPECIFICATIONS

Width	23 7/16 in
Height	17 15/16 in
Depth	17 3/4 in
Shipping Weight	63.5 lbs

FEATURES

- DirectSensor Touch Display
- AromaticSystemFresh
- Miele@home
- 26 Coffee & Tea Specialty Drinks
- Coffee Pot / Teapot / DoubleShot
- OneTouch for Two
- EasyClick Milk System
- Programmable Beverage Parameters
- Maximum Spout Height: 6.5"
- 10 Programmable User Profiles
- BrilliantLight
- CupSensor
- Removable Brew Unit / ComfortClean

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
EasyClick Milk System	11234120	\$155 / \$155
Descaling Tablets	11201170	\$21.99 / \$21.99
Cleaning Tablets	11201250	\$21.99 / \$21.99
Milk Pipework Cleaner	10182210	\$42.99 / \$42.99

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
EBA 7848 USA EDST/CLST	11410740	\$449 / \$449

NOTE: Trim kit not applicable on this model

Built-In Coffee System



23^{7/16}"



23^{7/16}"

MODEL	MATERIAL	UMRP/RETAIL
CVA 7440 Built-In Coffee System	11754290	\$4,699 / \$4,899

FINISH	DESIGN LINE	TYPE
Brilliant white	VitroLine	Non-plumbed

SPECIFICATIONS

Width	23 ^{7/16} in
Height	17 ^{15/16} in
Depth	17 ^{3/4} in
Shipping Weight	63.5 lbs

FEATURES

- DirectSensor Touch Display
- AromaticSystemFresh
- Miele@home
- 26 Coffee & Tea Specialty Drinks
- Coffee Pot / Teapot / DoubleShot
- OneTouch for Two
- EasyClick Milk System
- Programmable Beverage Parameters
- Maximum Spout Height: 6.5"
- 10 Programmable User Profiles
- BrilliantLight
- CupSensor
- Removable Brew Unit / ComfortClean

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
EasyClick Milk System	11234120	\$155 / \$155
Descaling Tablets	11201170	\$21.99 / \$21.99
Cleaning Tablets	11201250	\$21.99 / \$21.99
Milk Pipework Cleaner	10182210	\$42.99 / \$42.99

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
EBA 7848 USA BRWS	11410790	\$449 / \$449

MODEL	MATERIAL	UMRP/RETAIL
CVA 7440 Built-In Coffee System	11754280	\$4,699 / \$4,899

FINISH	DESIGN LINE	TYPE
Graphite grey	VitroLine	Non-plumbed

SPECIFICATIONS

Width	23 ^{7/16} in
Height	17 ^{15/16} in
Depth	17 ^{3/4} in
Shipping Weight	63.5 lbs

FEATURES

- DirectSensor Touch Display
- AromaticSystemFresh
- Miele@home
- 26 Coffee & Tea Specialty Drinks
- Coffee Pot / Teapot / DoubleShot
- OneTouch for Two
- EasyClick Milk System
- Programmable Beverage Parameters
- Maximum Spout Height: 6.5"
- 10 Programmable User Profiles
- BrilliantLight
- CupSensor
- Removable Brew Unit / ComfortClean

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
EasyClick Milk System	11234120	\$155 / \$155
Descaling Tablets	11201170	\$21.99 / \$21.99
Cleaning Tablets	11201250	\$21.99 / \$21.99
Milk Pipework Cleaner	10182210	\$42.99 / \$42.99

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
EBA 7848 USA GRGR	11410800	\$449 / \$449

Built-In Coffee System



MODEL	MATERIAL	UMRP/RETAIL
CVA 7445 Built-In Coffee System	11754300	\$5,199 / \$5,399

FINISH	DESIGN LINE	TYPE
Clean Touch Steel™	PureLine	Plumbed

SPECIFICATIONS

Width	23 ^{7/16} in
Height	17 ^{15/16} in
Depth	19 ^{5/8} in
Shipping Weight	65 lbs

FEATURES

- DirectSensor Touch Display
- AromaticSystemFresh
- Miele@home
- 26 Coffee & Tea Specialty Drinks
- Coffee Pot / Teapot / DoubleShot
- OneTouch for Two
- EasyClick Milk System
- Programmable Beverage Parameters
- Maximum Spout Height: 6.5"
- 10 Programmable User Profiles
- BrilliantLight
- CupSensor
- Removable Brew Unit / ComfortClean

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
EasyClick Milk System	11234120	\$155 / \$155
Descaling Tablets	11201170	\$21.99 / \$21.99
Cleaning Tablets	11201250	\$21.99 / \$21.99
Milk Pipework Cleaner	10182210	\$42.99 / \$42.99

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
EBA 7848 USA EDST/CLST	11410740	\$449 / \$449

MODEL	MATERIAL	UMRP/RETAIL
CVA 7775 Built-In Coffee System	11733820	\$6,499 / \$6,699

FINISH	DESIGN LINE	TYPE
Clean Touch Steel™	ContourLine	Plumbed

SPECIFICATIONS

Width	29 ^{13/16} in
Height	18 ^{7/8} in
Depth	18 ^{5/8} in
Shipping Weight	83.7 lbs

FEATURES

- DirectSensor Touch Display
- AromaticSystemFresh
- CoffeeSelect (3 Bean Containers)
- M Touch display with MotionReact
- Miele@home
- 26 Coffee & Tea Specialty Drinks
- Coffee Pot / Teapot / DoubleShot
- OneTouch for Two
- EasyClick Milk System
- Programmable Beverage Parameters
- Maximum Spout Height: 6.5"
- 10 Programmable User Profiles
- BrilliantLight / Niche Lighting
- CupSensor
- AutoDescal / AutoClean
- Removable Brew Unit / ComfortClean

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
Descaling Cartridge	11202520	\$99.99 / \$99.99
Cleaning Tablets	11201250	\$21.99 / \$21.99
AutoCleaner	10971480	\$99.99 / \$99.99
Milk Pipework Cleaner	10182210	\$42.99 / \$42.99

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
EasyClick Milk System	11234120	\$155 / \$155
Descaling Tablets	11201170	\$21.99 / \$21.99
Cleaning Tablets	11201250	\$21.99 / \$21.99

NOTE: Trim kit not applicable on this model

Built-In Coffee System



MODEL	MATERIAL	UMRP/RETAIL
CVA 7840 Built-In Coffee System	11754270	\$5,599 / \$5,799

FINISH	DESIGN LINE	TYPE
Clean Touch Steel™	PureLine	Non-plumbed

SPECIFICATIONS

Width	23 ^{7/16} in
Height	17 ^{15/16} in
Depth	17 ^{3/4} in
Shipping Weight	63.5 lbs

FEATURES

- AromaticSystemFresh
- CoffeeSelect (3 Bean Containers)
- M Touch display with MotionReact
- Miele@home
- 26 Coffee & Tea Specialty Drinks
- Coffee Pot / Teapot / DoubleShot
- OneTouch for Two
- EasyClick Milk System
- Programmable Beverage Parameters
- Maximum Spout Height: 6.5"
- 10 Programmable User Profiles
- BrilliantLight / Niche Lighting
- CupSensor
- AutoDescalce / AutoClean
- Removable Brew Unit / ComfortClean

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
Descaling Cartridge	11202520	\$99.99 / \$99.99
Cleaning Tablets	11201250	\$21.99 / \$21.99
AutoCleaner	10971480	\$99.99 / \$99.99
Milk Pipework Cleaner	10182210	\$42.99 / \$42.99

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
EasyClick Milk System	11234120	\$155 / \$155
Descaling Tablets	11201170	\$21.99 / \$21.99
Cleaning Tablets	11201250	\$21.99 / \$21.99
Milk Pipework Cleaner	10182210	\$42.99 / \$42.99
EBA 7848 USA EDST/CLST	11410740	\$449 / \$449

MODEL	MATERIAL	UMRP/RETAIL
CVA 7845 Built-In Coffee System	11733840	\$6,099 / \$6,299

FINISH	DESIGN LINE	TYPE
Clean Touch Steel™	PureLine	Plumbed

SPECIFICATIONS

Width	23 ^{7/16} in
Height	17 ^{15/16} in
Depth	19 ^{5/8} in
Shipping Weight	65 lbs

FEATURES

- M Touch Display with MotionReact
- CoffeeSelect (3 Bean Containers)
- AromaticSystemFresh
- Miele@home
- 26 Coffee & Tea Specialty Drinks
- Coffee Pot / Teapot / DoubleShot
- OneTouch for Two
- EasyClick Milk System
- Programmable Beverage Parameters
- Maximum Spout Height: 6.5"
- 10 Programmable User Profiles
- BrilliantLight / Niche Lighting
- CupSensor
- AutoDescalce / AutoClean
- Removable Brew Unit / ComfortClean

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
Descaling Cartridge	11202520	\$99.99 / \$99.99
Cleaning Tablets	11201250	\$21.99 / \$21.99
AutoCleaner	10971480	\$99.99 / \$99.99
Milk Pipework Cleaner	10182210	\$42.99 / \$42.99

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
EasyClick Milk System	11234120	\$155 / \$155
Descaling Tablets	11201170	\$21.99 / \$21.99
Cleaning Tablets	11201250	\$21.99 / \$21.99
Milk Pipework Cleaner	10182210	\$42.99 / \$42.99
EBA 7848 USA EDST/CLST	11410740	\$449 / \$449

Built-In Coffee System



MODEL	MATERIAL	UMRP/RETAIL
CVA 7845 Built-In Coffee System	11754260	\$6,099 / \$6,299

FINISH	DESIGN LINE	TYPE
Brilliant white	VitroLine	Plumbed

SPECIFICATIONS

Width	23 ^{7/16} in
Height	17 ^{15/16} in
Depth	19 ^{5/8} in
Shipping Weight	65 lbs

FEATURES

- DirectSensor Touch Display
- CoffeeSelect (3 Bean Containers)
- AromaticSystemFresh
- M Touch Display with MotionReact
- 26 Coffee & Tea Specialty Drinks
- Coffee Pot / Teapot / DoubleShot / CoffeeSelect
- OneTouch for Two
- EasyClick Milk System
- Programmable Beverage Parameters
- Maximum Spout Height: 6.5"
- 10 Programmable User Profiles
- BrilliantLight / Niche Lighting
- CupSensor
- Removable Brew Unit / ComfortClean

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
Descaling Cartridge	11202520	\$99.99 / \$99.99
Cleaning Tablets	11201250	\$21.99 / \$21.99
AutoCleaner	10971480	\$99.99 / \$99.99
Milk Pipework Cleaner	10182210	\$42.99 / \$42.99

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
EasyClick Milk System	11234120	\$155 / \$155
Descaling Tablets	11201170	\$21.99 / \$21.99
Cleaning Tablets	11201250	\$21.99 / \$21.99
Milk Pipework Cleaner	10182210	\$42.99 / \$42.99
EBA 7848 USA BRWS	11410790	\$449 / \$449

MODEL	MATERIAL	UMRP/RETAIL
CVA 7845 Built-In Coffee System	11733850	\$6,099 / \$6,299

FINISH	DESIGN LINE	TYPE
Graphite grey	VitroLine	Plumbed

SPECIFICATIONS

Width	23 ^{7/16} in
Height	17 ^{15/16} in
Depth	19 ^{5/8} in
Shipping Weight	65 lbs

FEATURES

- DirectSensor Touch Display
- CoffeeSelect (3 Bean Containers)
- AromaticSystemFresh
- M Touch Display with MotionReact
- 26 Coffee & Tea Specialty Drinks
- Coffee Pot / Teapot / DoubleShot / CoffeeSelect
- OneTouch for Two
- EasyClick Milk System
- Programmable Beverage Parameters
- Maximum Spout Height: 6.5"
- 10 Programmable User Profiles
- BrilliantLight / Niche Lighting
- CupSensor
- Removable Brew Unit / ComfortClean

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
Descaling Cartridge	11202520	\$99.99 / \$99.99
Cleaning Tablets	11201250	\$21.99 / \$21.99
AutoCleaner	10971480	\$99.99 / \$99.99
Milk Pipework Cleaner	10182210	\$42.99 / \$42.99

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
EasyClick Milk System	11234120	\$155 / \$155
Descaling Tablets	11201170	\$21.99 / \$21.99
Cleaning Tablets	11201250	\$21.99 / \$21.99
Milk Pipework Cleaner	10182210	\$42.99 / \$42.99
EBA 7848 USA GRGR	11410800	\$449 / \$449

Built-In Coffee System



MODEL	MATERIAL	UMRP/RETAIL
CVA 7845 Built-In Coffee System	11754250	\$6,099 / \$6,299

FINISH	DESIGN LINE	TYPE
Obsidian black	VitroLine	Plumbed

SPECIFICATIONS

Width	23 ^{7/16} in
Height	17 ^{15/16} in
Depth	19 ^{5/8} in
Shipping Weight	65 lbs

FEATURES

- DirectSensor Touch Display
- CoffeeSelect (3 Bean Containers)
- AromaticSystemFresh
- M Touch Display with MotionReact
- 26 Coffee & Tea Specialty Drinks
- Coffee Pot / Teapot / DoubleShot / CoffeeSelect
- OneTouch for Two
- EasyClick Milk System
- Programmable Beverage Parameters
- Maximum Spout Height: 6.5"
- 10 Programmable User Profiles
- BrilliantLight / Niche Lighting
- CupSensor
- Removable Brew Unit / ComfortClean

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
Descaling Cartridge	11202520	\$99.99 / \$99.99
Cleaning Tablets	11201250	\$21.99 / \$21.99
AutoCleaner	10971480	\$99.99 / \$99.99
Milk Pipework Cleaner	10182210	\$42.99 / \$42.99

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
EasyClick Milk System	11234120	\$155 / \$155
Descaling Tablets	11201170	\$21.99 / \$21.99
Cleaning Tablets	11201250	\$21.99 / \$21.99
Milk Pipework Cleaner	10182210	\$42.99 / \$42.99
EBA 7848 USA OBSW	11410770	\$449 / \$449

Product Highlights

Countertop Coffee Machines

FEATURE	DESCRIPTION
AromaticSystem	Intensive coffee aroma submerges the home with this intelligent technology.
OneTouch for Two	The OneTouch for Two function allows two glasses of latte macchiato, cappuccino, coffee or espresso to be made at the same time.
Removable Brew Unit	Easy to remove and clean, your machine guarantees impeccable hygiene, long service life and perfect coffee enjoyment.
Automatic Rinsing	After making special coffee drinks that require milk, the machine is cleaned automatically.
WiFiConn@ct	Convenient and time-saving, control your machine right from your mobile device.
50% Quieter	New grinder motor for a 50% reduction in sound while grinding on all CM5 Silence machines.*
Double Venturi Technology	Featured on all CM6 MilkPerfection units, provides enhanced milk froth quality, temperature and quantity.
CoffeeSelect	Featured on the CM7 machine, enjoy 3 bean containers where your coffee specialty is always prepared with the right coffee bean.

*vs. CM 5300

Countertop Coffee Machine



MODEL	MATERIAL	UMRP/RETAIL
CM 5310 Silence Countertop Coffee Machine	11648150	\$1,799 / \$1,899

FINISH

Obsidian black

SPECIFICATIONS

Width	9 ¹ / ₂ in
Height	14 ¹³ / ₁₆ in
Depth	18 ¹ / ₈ in
Shipping Weight	24.6 lbs (11 kg)

FEATURES

- AromaticSystem
- 50% Quieter Grinding*
- Creamy Milk Froth
- OneTouch for Two
- Coffee Pot Function
- Programmable Beverage Parameters
- 5.3" Maximum Spout Height
- ComfortClean

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
Descaling Tablets	11201170	\$21.99 / \$21.99
Cleaning Tablets	11201250	\$21.99 / \$21.99
Quick Start Guide	N/A	N/A
Cleaning Brush	N/A	N/A

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Glass Milk Container	11574240	\$97.71 / \$97.71

MODEL	MATERIAL	UMRP/RETAIL
CM 5310 Silence Countertop Coffee Machine	11648140	\$1,799 / \$1,899

FINISH

Tayberry red

SPECIFICATIONS

Width	9 ¹ / ₂ in
Height	14 ¹³ / ₁₆ in
Depth	18 ¹ / ₈ in
Shipping Weight	24.6 lbs (11 kg)

FEATURES

- AromaticSystem
- 50% Quieter Grinding*
- Creamy Milk Froth
- OneTouch for Two
- Coffee Pot Function
- Programmable Beverage Parameters
- 5.3" Maximum Spout Height
- ComfortClean

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
Descaling Tablets	11201170	\$21.99 / \$21.99
Cleaning Tablets	11201250	\$21.99 / \$21.99
Quick Start Guide	N/A	N/A
Cleaning Brush	N/A	N/A

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Glass Milk Container	11574240	\$97.71 / \$97.71

Countertop Coffee Machine



MODEL	MATERIAL	UMRP/RETAIL
CM 5510 Silence Countertop Coffee Machine	11648160	\$1,899 / \$1,999

FINISH

Rose Gold PearlFinish

SPECIFICATIONS

Width	9 1/2 in
Height	14 13/16 in
Depth	18 1/8 in
Shipping Weight	24.6 lbs (11 kg)

FEATURES

- AromaticSystem
- 50% Quieter Grinding*
- Creamy Milk Froth
- OneTouch for Two
- Coffee Pot Function
- Programmable Beverage Parameters
- 5.3" Maximum Spout Height
- ComfortClean
- Hot Water Function
- 2 Programmable User Profiles

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
Descaling Tablets	11201170	\$21.99 / \$21.99
Cleaning Tablets	11201250	\$21.99 / \$21.99
Quick Start Guide	N/A	N/A
Cleaning Brush	N/A	N/A

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Glass Milk Container	11574240	\$97.71 / \$97.71

MODEL	MATERIAL	UMRP/RETAIL
CM 5510 Silence Countertop Coffee Machine	11861030	\$1,899 / \$1,999

FINISH

AluSilver Metallic

SPECIFICATIONS

Width	9 1/2 in
Height	14 13/16 in
Depth	18 1/8 in
Shipping Weight	24.6 lbs (11 kg)

FEATURES

- AromaticSystem
- 50% Quieter Grinding*
- Creamy Milk Froth
- OneTouch for Two
- Coffee Pot Function
- Programmable Beverage Parameters
- 5.3" Maximum Spout Height
- ComfortClean
- Hot Water Function
- 2 Programmable User Profiles

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
Descaling Tablets	11201170	\$21.99 / \$21.99
Cleaning Tablets	11201250	\$21.99 / \$21.99
Quick Start Guide	N/A	N/A
Cleaning Brush	N/A	N/A

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
Glass Milk Container	11574240	\$97.71 / \$97.71

Countertop Coffee Machine



MODEL	MATERIAL	UMRP/RETAIL
-------	----------	-------------

CM 6160 MilkPerfection Countertop Coffee Machine	11648170	\$2,299 / \$2,399
--	----------	-------------------

FINISH

Lotus white

SPECIFICATIONS

Width	9 ⁷ / ₈ in
Height	14 ¹ / ₈ in
Depth	16 ³ / ₄ in
Shipping Weight	26 lbs (11.8 kg)

FEATURES

- AromaticSystem
- Creamy Milk Froth
- Double Venturi Milk-Frothing Technology
- OneTouch for Two
- Coffee Pot Function
- Programmable Beverage Parameters
- 5.5" Maximum Spout Height
- ComfortClean
- Hot Water Function
- 4 Programmable User Profiles
- Miele@home
- BrilliantLight

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
----------------------	----------	-------------

Descaling Tablets	11201170	\$21.99 / \$21.99
Cleaning Tablets	11201250	\$21.99 / \$21.99
Quick Start Guide	N/A	N/A
Cleaning Brush	N/A	N/A

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
----------------------	----------	-------------

Glass Milk Container	11574240	\$97.71 / \$97.71
----------------------	----------	-------------------

MODEL	MATERIAL	UMRP/RETAIL
-------	----------	-------------

CM 6160 MilkPerfection Countertop Coffee Machine	11648180	\$2,299 / \$2,399
--	----------	-------------------

FINISH

Obsidian black

SPECIFICATIONS

Width	9 ⁷ / ₈ in
Height	14 ¹ / ₈ in
Depth	16 ³ / ₄ in
Shipping Weight	26 lbs (11.8 kg)

FEATURES

- AromaticSystem
- Creamy Milk Froth
- Double Venturi Milk-Frothing Technology
- OneTouch for Two
- Coffee Pot Function
- Programmable Beverage Parameters
- 5.5" Maximum Spout Height
- ComfortClean
- Hot Water Function
- 4 Programmable User Profiles
- Miele@home
- BrilliantLight

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
----------------------	----------	-------------

Descaling Tablets	11201170	\$21.99 / \$21.99
Cleaning Tablets	11201250	\$21.99 / \$21.99
Quick Start Guide	N/A	N/A
Cleaning Brush	N/A	N/A

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
----------------------	----------	-------------

Glass Milk Container	11574240	\$97.71 / \$97.71
----------------------	----------	-------------------

Countertop Coffee Machine



MODEL	MATERIAL	UMRP/RETAIL
CM 6360 MilkPerfection Countertop Coffee Machine	11648190	\$2,799 / \$2,899

FINISH

Lotus white CleanSteelMetallic

SPECIFICATIONS

Width	9 ^{7/8} in
Height	14 ^{1/8} in
Depth	16 ^{3/4} in
Shipping Weight	27.3 lbs (12.4 kg)

FEATURES

- AromaticSystem
- Creamy Milk Froth
- Double Venturi Milk-Frothing Technology
- OneTouch for Two
- Coffee Pot Function
- Programmable Beverage Parameters
- 5.5" Maximum Spout Height
- ComfortClean
- Hot Water Function
- 8 Programmable User Profiles
- Miele@home
- Glass Milk Container
- BrilliantLight
- Cup Warmer

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
Glass Milk Container	11574240	\$97.71 / \$97.71
Descaling Tablets	11201170	\$21.99 / \$21.99
Cleaning Tablets	11201250	\$21.99 / \$21.99
Quick Start Guide	N/A	N/A
Cleaning Brush	N/A	N/A

MODEL	MATERIAL	UMRP/RETAIL
CM 6360 MilkPerfection Countertop Coffee Machine	11648200	\$2,799 / \$2,899

FINISH

Obsidian black CleanSteelMetallic

SPECIFICATIONS

Width	9 ^{7/8} in
Height	14 ^{1/8} in
Depth	16 ^{3/4} in
Shipping Weight	27.3 lbs (12.4 kg)

FEATURES

- AromaticSystem
- Creamy Milk Froth
- Double Venturi Milk-Frothing Technology
- OneTouch for Two
- Coffee Pot Function
- Programmable Beverage Parameters
- 5.5" Maximum Spout Height
- ComfortClean
- Hot Water Function
- 8 Programmable User Profiles
- Miele@home
- Glass Milk Container
- BrilliantLight
- Cup Warmer

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
Glass Milk Container	11574240	\$97.71 / \$97.71
Descaling Tablets	11201170	\$21.99 / \$21.99
Cleaning Tablets	11201250	\$21.99 / \$21.99
Quick Start Guide	N/A	N/A
Cleaning Brush	N/A	N/A

Countertop Coffee Machine



MODEL	MATERIAL	UMRP/RETAIL
CM 6360 MilkPerfection Countertop Coffee Machine	11648400	\$2,799 / \$2,899

FINISH

Obsidian black BronzePearlFinish

SPECIFICATIONS

Width	9 7/8 in
Height	14 1/8 in
Depth	16 3/4 in
Shipping Weight	27.3 lbs (12.4 kg)

FEATURES

- AromaticSystemFresh
- Creamy Milk Froth
- Double Venturi Milk-Frothing Technology
- OneTouch for Two
- Coffee Pot Function
- Programmable Beverage Parameters
- 5.5" Maximum Spout Height
- ComfortClean
- Hot Water Function
- 8 Programmable User Profiles
- Miele@home
- Glass Milk Container
- BrilliantLight
- Cup Warmer

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
Glass Milk Container	11574240	\$97.71 / \$97.71
Descaling Tablets	11201170	\$21.99 / \$21.99
Cleaning Tablets	11201250	\$21.99 / \$21.99
Quick Start Guide	N/A	N/A
Cleaning Brush	N/A	N/A



MODEL	MATERIAL	UMRP/RETAIL
CM 7750 Coffee Select Countertop Coffee Machine	11106260	\$6,399 / \$6,499

FINISH

Obsidian black

SPECIFICATIONS

Width	12 1/4 in
Height	16 9/16 in
Depth	17 1/2 in
Shipping Weight	39.2 lbs (141 kg)

FEATURES

- AromaticSystemFresh
- CoffeeSelect (3 Bean Containers)
- Creamy Milk Froth
- OneTouch for Two
- Coffee Pot Function
- Programmable Beverage Parameters
- 6.3" Maximum Spout Height
- ComfortClean
- Hot Water Function
- 10 Programmable User Profiles
- Miele@home
- BrilliantLight
- Glass Milk Container
- Cup Warmer
- CupSensor
- AutoDescale

STANDARD ACCESSORIES	MATERIAL	UMRP/RETAIL
Glass Milk Container	11574240	\$97.71 / \$97.71
Descaling Tablets	11201170	\$21.99 / \$21.99
Descaling Cartridge	11202520	\$99.99 / \$99.99
Cleaning Tablets	11201250	\$21.99 / \$21.99
Quick Start Guide	N/A	N/A

Accessories & Consumables

Cooktops

PRODUCT	MATERIAL	UMRP/RETAIL
Razor Blade Glass Scraper	1065471	\$18 / \$18.
Glass Cooktop Cleaner	10173130	\$13.99 / \$13.99

Ovens

PRODUCT	MATERIAL	UMRP/RETAIL
Glass Cooktop Cleaner	10162910	\$13.99 / \$13.99
DG Clean Cleaner	10172760	\$18.99 / \$18.99
Descaling Tablets	11201170	\$21.99 / \$21.99

Coffee Machines

PRODUCT	MATERIAL	UMRP/RETAIL
Descaling Tablets	11201170	\$21.99 / \$21.99
Descaling Cartridge	11202520	\$99.99 / \$99.99
Cleaning Tablets	11201250	\$21.99 / \$21.99
Coffee Machine Milk Pipework Cleaner	10182210	\$42.99 / \$42.99
Coffee Machine Silicone Grease	5132001	\$12.99 / \$12.99
Coffee Beans - One for All (4 x 8.8 oz)	11030100	\$44.99 / \$44.99
Coffee Beans - Café Crema (4 x 8.8 oz)	11029370	\$44.99 / \$44.99
Coffee Beans - Espresso (4 x 8.8 oz)	11029650	\$44.99 / \$44.99
Coffee Beans - Decaf (4 x 8.8 oz)	11029870	\$44.99 / \$44.99

Miele

Miele, Inc.
9 Independence Way
Princeton, NJ 08540

mieleusa.com
800.843.7231

Visit one of Miele's Experience Centers:

Beverly Hills
Boca Raton
Chicago
Coral Gables
Manhattan
Princeton
San Francisco
Scottsdale
Seattle
Tysons Corner

Prices effective September 2024.

Prices subject to change without notice.

Miele reserves the right to accept or deny all orders at its Princeton, NJ offices.

Alteration rights reserved / September 2024