



Price List Cooling

February 2025

Table of Contents

PerfectCool Refrigeration	03
PerfectCool Refrigeration Product Highlights	03
PerfectCool Refrigeration	04
PerfectCool Wine Storage	12
PerfectCool Wine Storage Product Highlights	12
PerfectCool Wine Storage	13
MasterCool Refrigeration	15
MasterCool Refrigeration Product Highlights	15
MasterCool Refrigeration	16
MasterCool Wine Storage	27
MasterCool Wine Storage Product Highlights	27
MasterCool Wine Storage	28

Product Highlights

PerfectCool Refrigeration

*See specific models for details

FEATURE	DESCRIPTION
PerfectFresh Pro	Food stays fresh for up to five times longer. With automatically controlled temperature zones, PerfectFreshPro is Miele's best system for perfect storage conditions of fresh produce.
FlexiLight	Glare-free, LED glass shelf lighting.
ComfortClean	The shelves on the inside of the door are dishwasher-safe for easy cleaning.
DynaCool	With uniform distribution and circulation of temperature, store your food anywhere in the fridge and freezer.
SuperCool	Rapid and gentle freezing of food.
PerfectFresh Active	Perfect humidity at all times: Whenever the door is opened and every 90 minutes, a fine water mist is sprayed into the drawer for a gentle layer of moisture.
FlexiLight 2.0	Individually adjustable glass shelf lighting; illuminated shelves can be custom-positioned and are entirely glare-free.
FlexiTray	Pivot-able glass shelf allows for items to be removed easily, even from a full refrigerator.
Miele@home	Access your appliance from your smart device for maximum convenience. Adjust fridge or freezer temperature, setting it to SuperCool while on the go.

PerfectCool Refrigeration - Columns



MODEL	MATERIAL	UMRP/RETAIL
FNS 37492 iE 24" Freezer Column (Model to be phased out end of Q2)	10093890	\$4,199 / \$4,299

FINISH	HINGE
Custom Panel	Left (convertible)

SPECIFICATIONS	
Width	22 in (559 mm)
Height	69 ^{11/16} in (1770 mm)
Depth	21 ^{1/2} in (545 mm)
Freezer Capacity	7.8 cu.ft. (221 l)
Shipping Weight	50.7 lbs (23 kg)
Annual Energy Usage	439 kWh

FREEZER FEATURES	
- Lighting: LED	- IceMaker w/ Plumbed Water Connection
- TouchControls	- Maximum Storage Capacity and Flexibility: 9 Removable Drawers
- SoftClose Door	- Sabbath Mode
- Temperature Zones: 1	- DynaCool
- Active AirClean Filter	
- SuperCool	
- Acoustic Door and Temperature Alarm	

MODEL	MATERIAL	UMRP/RETAIL
FNS 7794 E 24" Freezer Column (Model to be phased in end of Q2)	11911910	\$4,199 / \$4,299

FINISH	HINGE
Custom Panel	Left (convertible)

SPECIFICATIONS	
Width	22 in (559 mm)
Height	69 ^{11/16} in (1770 mm)
Depth	21 ^{1/2} in (545 mm)
Freezer Capacity	7.5 cu.ft. (213 l)
Shipping Weight	175.5 lbs (79 kg)
Annual Energy Usage	TBD

FRIDGE FEATURES	
- LED lighting	- Sabbath mode
- SoftClose Door	- TouchControls
- SuperFreeze	- Temperature Zones: 1
- Illuminated icemaker w/ plumbed water connection	- Acoustic Door and Temperature Alarm
- Miele@home	

PerfectCool Refrigeration - Columns



MODEL	MATERIAL	UMRP/RETAIL
KS 37472 iD 24" Refrigerator Column (Model to be phased in end of Q2)	10093870	\$3,749 / \$3,849

FINISH	HINGE
Custom Panel	Right (convertible)

SPECIFICATIONS	
Width	22 in (559 mm)
Height	69 ^{11/16} in (1770 mm)
Depth	21 ^{7/16} in (544 mm)
Refrigerator Capacity	10.88 cu.ft. (308 l)
Shipping Weight	166.5 lbs (75.5 kg)
Annual Energy Usage	283 kWh

FRIDGE FEATURES	
- PerfectFresh	- Maximum Storage Capacity and Flexibility: 5 Door Bins, 3 Drawers, 6 Movable Shelves, 1 Bottle Rack
- FlexiLight LED Shelves: 4	- Active AirClean Filter
- ComfortClean Door Shelves	- SuperCool
- TouchControls	- Acoustic Door and Temperature Alarm
- SoftClose Door	
- Temperature Zones: 2	
- DynaCool	
- Sabbath Mode	

MODEL	MATERIAL	UMRP/RETAIL
KS 7793 D 24" Freezer Column (Model to be phased in end of Q2)	11749850	\$3,749 / \$3,849

FINISH	HINGE
Custom Panel	Right (convertible)

SPECIFICATIONS	
Width	22 in (559 mm)
Height	69 ^{11/16} in (1770 mm)
Depth	21 ^{7/16} in (544 mm)
Freezer Capacity	7.5 cu.ft. (213 l)
Shipping Weight	175.5 lbs (79 kg)
Annual Energy Usage	TBD

FRIDGE FEATURES	
- PerfectFresh Active - keeps food up to 5 times longer fresh, small water container inside, releases steam every 90min	- SoftClose Door
- FlexiLight 2.0	- Sabbath, Party & Holiday Mode
- 2 Temperature Zones	- ComfortClean Door Shelves
- FlexiTray - turns the glass shelf into a turntable, can be rotated by 180°	- TouchControls
- DynaCool	- Maximum Storage Capacity and Flexibility: 4 Door Bins, 3 Drawers, 6 Movable Shelves, 1 Bottle Rack
- SuperCool	- Acoustic Door and Temperature Alarm
- CleanSteel back wall	

PerfectCool Refrigeration - Freestanding



MODEL	MATERIAL	UMRP/RETAIL
KFN 13923 DE 24" Freestanding (Model to be phased out end of Q2)	10870510	\$3,599 / \$3,699

FINISH	HINGE
Clean Touch Steel™	Right (convertible)

SPECIFICATIONS	
Width	23 ^{1/2} in (597 mm)
Height	79 ^{1/2} in (2020 mm)
Depth	24 ^{13/16} in (630 mm)
Refrigerator Capacity	9.43 cu.ft. (267 l)
Freezer Capacity	3.32 cu.ft. (94 l)
Shipping Weight	203 lbs (92 kg)
Annual Energy Usage	480 kWh

FRIDGE FEATURES	
- Lighting: LED	- DynaCool
- ComfortClean Door Shelves	- Active AirClean Filter
- TouchControls	- SuperCool
- Temperature Zones: 2	- Acoustic Door and Temperature Alarm
- Maximum Storage Capacity and Flexibility: 5 Door Bins, 2 Drawers, 4 Movable Shelves, 1 Bottle Rack	- Sabbath Mode

FREEZER FEATURES	
- IceMaker w/ Plumbed Water Connection	
- Maximum Storage Capacity and Flexibility: 3 Removable Drawers	
- SuperCool	

MODEL	MATERIAL	UMRP/RETAIL
KFN 4799 DDE 24" Freestanding	11951210	\$3,149 / \$3,249

FINISH	HINGE
Clean Touch Steel™	Right (convertible)

SPECIFICATIONS	
Width	23 ^{1/2} in (597 mm)
Height	79 ^{1/2} in (2020 mm)
Depth	24 ^{13/16} in (630 mm)
Refrigerator Capacity	9.43 cu.ft. (267 l)
Freezer Capacity	3.32 cu.ft. (94 l)
Shipping Weight	203 lbs (92 kg)
Annual Energy Usage	TBD

FRIDGE FEATURES	
- Sabbath, Party & Holiday Mode	- Maximum Storage Capacity and Flexibility: 5 Door Bins, 2 Drawers, 4 Movable Shelves, 1 Bottle Rack
- 2 Temperature Zones	- Acoustic Door and Temperature Alarm
- LED lighting	- DynaCool
- ComfortClean Door Shelves	
- TouchControls	

FREEZER FEATURES	
- Illuminated IceMaker w/ plumbed water connection	
- Maximum Storage Capacity and Flexibility: 3 Removable Drawers	
- SuperCool	

PerfectCool Refrigeration - Freestanding



MODEL	MATERIAL	UMRP/RETAIL
KFN 4776 ED 30" Freestanding	11954030	\$2,799 / \$2,899

FINISH	HINGE
Clean Touch Steel™	Right (convertible)

SPECIFICATIONS

Width	29 ^{1/2} in (750 mm)
Height	73 ^{1/4} in (2020 mm)
Depth	24 ^{13/16} in (630 mm)
Refrigerator Capacity	11.7 cu.ft. (331 l)
Freezer Capacity	4.3 cu.ft. (121 l)
Shipping Weight	261 lbs (118 kg)
Annual Energy Usage	496 kWh

FRIDGE FEATURES

- Lighting: LED
- ComfortClean Door Shelves
- WifiConn@ct
- Daily Fresh
- FlexiBoard Shelves: FlexiBoard is a split glass shelf
- DynaCool
- Active AirClean Filter
- SuperCool
- DuplexCool – separate circuits for fridge and freezer

FREEZER FEATURES

- Maximum Storage Capacity and Flexibility: 4 Removable Drawers
- SuperCool

PerfectCool Refrigeration - Bottom Mount



MODEL	MATERIAL	UMRP/RETAIL
KFN 7795 D 24" Bottom Mount	11749900	\$4,449 / \$4,549

FINISH	HINGE
Custom Panel	Right (convertible)

SPECIFICATIONS

Width	22 in (559 mm)
Height	69 ^{11/16} in (1770 mm)
Depth	21 ^{1/2} in (545 mm)
Refrigerator Capacity	6.2 cu.ft. (175 l)
Freezer Capacity	2.5 cu.ft. (71 l)
Shipping Weight	175.7 lbs (79.7 kg)
Annual Energy Usage	TBD

FRIDGE FEATURES

- PerfectFresh Active
- FlexiLight 2.0 LED Shelves: 2
- FlexiTray
- ComfortClean Door Shelves
- TouchControls
- SoftClose Door
- Temperature Zones: 3
- Sabbath Mode
- Maximum Storage Capacity and Flexibility: 2 Door Bins, 2 Drawers, 3 Movable Shelves
- DynaCool
- SuperCool
- Acoustic Door and Temperature Alarm
- CleanSteel back panel

FREEZER FEATURES

- IceMaker w/ Plumbed Water Connection
- Maximum Storage Capacity and Flexibility: 3 Removable Drawers
- SuperCool

PerfectCool Refrigeration - Bottom Mount



MODEL	HINGE	MATERIAL	UMRP/RETAIL
KFN 9859iDE 30" Bottom Mount Custom Panel	Right	12153750	\$7,349 / \$7,449
KFN 9859iDE 30" Bottom Mount Custom Panel	Left	12153760	\$7,349 / \$7,449

SPECIFICATIONS	
Width	29 ^{7/8} in (759 mm)
Height	79 ^{13/16} in (2027 mm)
Depth	24 in (610 mm)
Refrigerator Capacity	9.8 cu.ft. (277.5 l)
Freezer Capacity	4.3 cu.ft. (127 l)
Shipping Weight	345 lbs (156.6 kg)
Annual Energy Usage	TBD

FRIDGE FEATURES	
- Lighting: LED	- Maximum Storage Capacity and Flexibility: 3 Door Bins, 2 Drawers, 3 Movable Shelves, 1 Bottle Rack
- ComfortClean Door Shelves	- DynaCool
- TouchControls	- SuperCool
- SoftClose Door	- Acoustic Door and Temperature Alarm
- Temperature Zones: 2	
- Sabbath Mode	

FREEZER FEATURES	
- IceMaker w/ Plumbed Water Connection	
- Maximum Storage Capacity and Flexibility: 2 Drawers	
- SuperCool	

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
KFN9855 K Fridge Panel (w/o handle)	9699670	\$569 / \$619
KFN9855 GF Freezer Panels (2 panels required, w/o handles)	9699700	\$519 / \$619

*Handles sold separately. See page 28 for full list of handle options.

PerfectCool Refrigeration - French Door



MODEL	MATERIAL	UMRP/RETAIL
KFNF 9959IDE 36" French Door Custom Panel	12153770	\$8,549 / \$8,649

FREEZER FEATURES
- IceMaker w/ Plumbed Water Connection
- Maximum Storage Capacity and Flexibility: 2 Drawers
- SuperCool

SPECIFICATIONS	
Width	35 ^{13/16} in (910 mm)
Height	79 ^{13/16} in (2027 mm)
Depth	24 in (610 mm)
Refrigerator Capacity	12.9 cu.ft. (365 l)
Freezer Capacity	6.0 cu.ft. (170 l)
Shipping Weight	383.5 lbs (174 kg)
Annual Energy Usage	TBD

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
KEDF9955 K Fridge Panels (2 panels required, w/o handles)	12556510 (10793570)	\$569 / \$619
KEDF9955 GF Freezer Panels (2 panels required, w/o handles)	12556520 (10793580)	\$569 / \$619

FRIDGE FEATURES	
- Lighting: LED	- Maximum Storage Capacity and Flexibility: 6 Door Bins, 2 Drawers, 4 Movable Shelves
- ComfortClean Door Shelves	- DynaCool
- TouchControls	- SuperCool
- SoftClose Door	- Acoustic Door and Temperature Alarm
- Temperature Zones: 3	
- Sabbath Mode	

PerfectCool Refrigeration - Under-Counter



MODEL	MATERIAL	UMRP/RETAIL
K 31222 Ui 24" Under-Counter Refrigerator	10799700	\$1,949 / \$2,049

FINISH	HINGE
Custom Panel	Right (convertible)

SPECIFICATIONS

Width	23 ^{1/2} in (597 mm)
Height	32 ^{5/16} - 34 ^{5/8} in (820 - 880 mm)
Depth	21 ^{5/8} in (550 mm)
Refrigerator Capacity	4.8 cu.ft. (136 l)
Shipping Weight	116.8 lbs (53 kg)
Annual Energy Usage	227 kWh

FRIDGE FEATURES

- Lighting: LED
- ComfortClean Door Shelves
- PicTronic Controls
- SoftClose Door
- Temperature Zones: 1
- Maximum Storage Capacity and Flexibility: 2 Door Bins, 4 Movable Shelves
- SuperCool
- Acoustic Door and Temperature Alarm

*Handles sold separately.
See page 28 for full list of handle options.

Product Highlights

PerfectCool Wine Storage

*See specific models for details

FEATURE	DESCRIPTION
TouchControl Display	Incredibly convenient: a whole range of settings can be controlled easily with the tap of a finger on the touch display.
LED Lighting	Flush lighting strips present your appliance in the perfect light.
Push2Open	For a handleless design, just apply slight pressure to the door to open.
SoftClose	With just a gentle touch, our dynamic doors close on their own. Integrates perfectly within a handleless kitchen.
FlexiFrame Racks	Individual Beechwood slats can be easily moved to make room for larger wine bottles.
SommelierSet	Perfect for wine connoisseurs: prepare cooled wine glasses and wine for decanting. Drink perfectly conditioned wine even from opened bottles.
3D Bottle Presenter Shelf	Place your favorite bottles on display.
Temperature Zones	Precise temperature regulation, ensuring the best storage conditions for different wine types.
NoteBoard	Every bottle rack features a removable magnetic strip for labeling the types of wine bottles on the rack.

PerfectCool Wine Storage



MODEL	MATERIAL	UMRP/RETAIL
KWT 6312 UGS 24" Under-Counter Wine	10028650	\$3,999 / \$4,099

FINISH	HINGE
Black Glass Frame	Right (convertible)

SPECIFICATIONS	
Width	23 ⁷ / ₁₆ in (596 mm)
Height	32 ¹ / ₄ - 34 ¹ / ₄ in (819 - 870 mm)
Depth	22 ¹ / ₂ in (571 mm)
Shipping Weight	110 lbs (50 kg)

WINE FEATURES	
- Lighting: LED	- FlexiFrame Racks: 3, 1 Fixed Shelf
- TouchControls	- 3D Bottle Presenter Shelf
- SoftClose Door	- UV Tinted Glass
- Temperature Zones: 1	- SommelierSet
- Maximum Storage Capacity and Flexibility: 46 x 0.75 l bottles (if no SommelierSet is placed inside)	- NoteBoard
- Active AirClean Filter	- Push2Open Door
- Acoustic Door and Temperature Alarm	

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
KSK 6300 Merging Kit	9799630	\$229 / \$279

MODEL	MATERIAL	UMRP/RETAIL
KWT 6322 UG 24" Under-Counter Wine	10028620	\$3,999 / \$4,099

FINISH	HINGE
Black Glass Frame	Right (convertible)

SPECIFICATIONS	
Width	23 ⁷ / ₁₆ in (596 mm)
Height	32 ¹ / ₄ - 34 ¹ / ₄ in (819 - 870 mm)
Depth	22 ¹ / ₂ in (571 mm)
Shipping Weight	116.8 lbs (53 kg)

WINE FEATURES	
- Lighting: LED	- FlexiFrame Racks: 3, 1 Fixed Shelf
- TouchControls	- UV Tinted Glass
- SoftClose Door	- NoteBoard
- Temperature Zones: 2	- Push2Open Door
- Maximum Storage Capacity and Flexibility: 34 x 0.75 l bottles	
- Active AirClean Filter	
- Acoustic Door and Temperature Alarm	

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
KSK 6300 Merging Kit	9799630	\$229 / \$279

*Custom Toe Kick Needed for Under-Counter Wine.

PerfectCool Wine Storage



MODEL	MATERIAL	UMRP/RETAIL
KWT 6322 UG 24" Under-Counter Wine	11545800	\$4,349 / \$4,449

FINISH	HINGE
Clean Touch Steel™ Frame	Right (convertible)

SPECIFICATIONS	
Width	23 ^{7/16} in (596 mm)
Height	32 ^{1/4} in - 34 ^{1/4} in (819 - 870 mm)
Depth	22 ^{1/2} in (571 mm)
Shipping Weight	116.8 lbs (53 kg)

WINE FEATURES	
- Lighting: LED	- FlexiFrame Racks: 3, 1 fixed shelf
- TouchControls	- UV Tinted Glass
- SoftClose Door	- NoteBoard
- Temperature Zones: 2	- Push2Open Door
- Maximum Storage Capacity and Flexibility: 34 x 0.75 l bottles	
- Active AirClean Filter	
- Acoustic Door and Temperature Alarm	

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
KSK 6300 Merging Kit	9799630	\$229 / \$279

MODEL	MATERIAL	UMRP/RETAIL
KWT 6722 iS 24" Built-in Wine	11329860	\$5,049 / \$5,149

FINISH	HINGE
Custom Panel	Right (convertible)

SPECIFICATIONS	
Width	21 ^{15/16} in (557 mm)
Height	69 ^{11/16} in (1770 mm)
Depth	21 ^{3/4} in (553 mm)
Shipping Weight	223 lbs (101 kg)

WINE FEATURES	
- Lighting: LED	- FlexiFrame Racks: 8
- TouchControls	- 3D Bottle Presenter Shelf: 1
- SoftClose Door	- UV Tinted Glass
- Temperature Zones: 2	- SommelierSet
- Maximum Storage Capacity and Flexibility: 80 x 0.75 l bottles	- NoteBoard
- DynaCool	- CleanSteel Back Wall
- Acoustic Door and Temperature Alarm	

OPTIONAL ACCESSORIES	MATERIAL	UMRP/RETAIL
KFP 6700 Clean Touch Steel™ Panel (w/o handle)	11329620	\$799 / \$849

Product Highlights

MasterCool Refrigeration

*See specific models for details

FEATURE	DESCRIPTION
MasterFresh	Food stays fresh for up to three times longer. Ideal storage temperatures and humidity levels for fruit, vegetables, fish, meat and dairy products.
BrilliantLight	Each area of the unit is perfectly illuminated by many LED light strips strategically placed throughout.
Push2Open	For a handleless design, just apply slight pressure to the door to open.
DuplexCool Pro	The refrigerator and freezer sections have separate cooling circuits, or dual compressors, ensuring an optimum climate with no air exchange between the two areas.
IceMaker & Ice/Water dispenser	With the ice/water dispenser on the front of the unit, treat yourself to ice and cooled water at the touch of a button. The icemaker can produce up to 150 ice cubes per day.
SoftClose	With just a gentle touch, our dynamic doors close on their own. Integrates perfectly within a handleless kitchen.
MasterSensor Controls	Incredibly convenient: a whole range of settings can be controlled easily with the tap of a finger on the color touch display.
Miele@home/Mobile Control	Access your appliance from your smart device for maximum convenience. Adjust fridge or freezer temperature, setting it to SuperCool while on the go.

MasterCool Refrigeration - 24" Columns



MODEL	HINGE	MATERIAL	UMRP/RETAIL
K2602 Vi Custom Panel	Right	11501360	\$8,199 / \$8,699
K2602 SF Clean Touch Steel™ w/ DS6708 ContourLine Handle	Right	11502570	\$8,949 / \$9,449
K 2612 Vi Custom Panel	Left	11502560	\$8,199 / \$8,699

OPTIONAL ACCESSORIES VI	MATERIAL	UMRP/RETAIL
KFP 2405 24 in Clean Touch Steel™ Panel (No Logo, w/o handle)	11499070	\$999 / \$1,049
KTK 2420 SS 24 in Toekick	10984070	\$179 / \$229
KKF-RF AirClean Filter	07236280	\$68 / \$118
KSK2002 Merge Kit	10984130	\$839 / \$889

SPECIFICATIONS	
Width	23 3/4 in (604 mm)
Height	83 3/4 - 85 3/16 in (2127 - 2164 mm)
Depth	24 in (610 mm)
Refrigerator Capacity	12.96 cu.ft. (357 l)
Shipping Weight	346 lbs (157 kg)
Annual Energy Usage	254 kWh

OPTIONAL ACCESSORIES SF	MATERIAL	UMRP/RETAIL
KTF 1042 42 in Top Frame	10984920	\$349 / \$399
KTF 1048 48 in Top Frame	12556870 (7337440)	\$349 / \$399
KTF 1054 54 in Top Frame	12556860 (7337430)	\$349 / \$399
KTF 1060 60 in Top Frame	12556850 (7337420)	\$349 / \$399
KTF 1066 66 in Top Frame	12556810 (7337400)	\$349 / \$399
KTF 1072 72 in Top Frame	12556830 (7337410)	\$349 / \$399
KTK 2420 SS 24 in Toekick	10984070	\$179 / \$229
KKF-RF AirClean Filter	07236280	\$68 / \$118
KSK2002 Merge Kit	10984130	\$839 / \$889

FRIDGE FEATURES	
- Push2Open Door	- DynaCool
- MasterFresh	- MaxLoad Hinge
- BrilliantLight	- Active AirClean Filter
- MasterSensor Controls	- SuperCool
- SoftClose Door	- Acoustic Door and Temperature Alarm
- Temperature Zones: 2	- Sabbath Mode
- Maximum Storage Capacity and Flexibility: 4 Door Bins, 3 Drawers, 2 Movable Shelves	- CleanSteel Back Wall

DS7308 GEN7000 ContourLine Handle (direct replacement for existing handle)	12047020	\$169 / \$169
--	----------	---------------

MasterCool Refrigeration - 30" Columns



MODEL	HINGE	MATERIAL	UMRP/RETAIL
K2802 Vi Custom Panel	Right	11502590	\$8,649 / \$9,149
K2802 SF Clean Touch Steel™ w/ DS6708 ContourLine Handle	Right	11502700	\$9,449 / \$9,949
K2812 Vi Custom Panel	Left	11502640	\$8,649 / \$9,149

OPTIONAL ACCESSORIES VI	MATERIAL	UMRP/RETAIL
KFP 3005 30 in Clean Touch Steel™ Panel (No Logo, w/o handle)	11499080	\$1,049 / \$1,099
KTK 3020 SS 30 in Toekick	10984090	\$179 / \$229
KKF-RF AirClean Filter	07236280	\$68 / \$118
KSK2002 Merge Kit	10984130	\$839 / \$889

SPECIFICATIONS

Width	29 ^{3/4} in (756 mm)
Height	83 ^{3/4} - 85 ^{3/16} in (2127 - 2164 mm)
Depth	24 in (610 mm)
Refrigerator Capacity	16.77 cu.ft. (475 l)
Shipping Weight	395 lbs (179 kg)
Annual Energy Usage	279 kWh

FRIDGE FEATURES

- Push2Open Door
- MasterFresh
- BrilliantLight
- MasterSensor Controls
- SoftClose Door
- Temperature Zones: 2
- Maximum Storage Capacity and Flexibility: 4 Door Bins, 3 Drawers, 2 Movable Shelves
- DynaCool
- MaxLoad Hinge
- Active AirClean Filter
- SuperCool
- Acoustic Door and Temperature Alarm
- Sabbath Mode
- CleanSteel Back Wall

OPTIONAL ACCESSORIES SF	MATERIAL	UMRP/RETAIL
KTF 1048 48 in Top Frame	12556870 (7337440)	\$349 / \$399
KTF 1054 54 in Top Frame	12556860 (7337430)	\$349 / \$399
KTF 1060 60 in Top Frame	12556850 (7337420)	\$349 / \$399
KTF 1066 66 in Top Frame	12556810 (7337400)	\$349 / \$399
KTF 1072 72 in Top Frame	12556830 (7337410)	\$349 / \$399
KTK 3020 SS 30 in Toekick	10984090	\$179 / \$229
KKF-RF AirClean Filter	07236280	\$68 / \$118
KSK2002 Merge Kit	10984130	\$839 / \$889

DS7308 GEN7000 ContourLine Handle (direct replacement for existing handle)	12047020	\$169 / \$169
---	----------	---------------

*Handles sold separately.
See page 28 for full list of handle options.

MasterCool Refrigeration - 36" Columns



MODEL	HINGE	MATERIAL	UMRP/RETAIL
K2902 Vi Custom Panel	Right	11502710	\$8,949 / \$9,449
K2902 SF Clean Touch Steel™ w/ DS6708 ContourLine Handle	Right	11502840	\$9,899 / \$10,399
K2912 Vi Custom Panel	Left	11502720	\$8,949 / \$9,449

OPTIONAL ACCESSORIES VI	MATERIAL	UMRP/RETAIL
KFP 3605 36 in Clean Touch Steel™ Panel (No Logo, w/o handle)	11499100	\$1,159 / \$1,209
KTK 3620 SS 36 in Toekick	10984110	\$179 / \$229
KKF-RF AirClean Filter	07236280	\$68 / \$118
KSK2002 Merge Kit	10984130	\$839 / \$889

SPECIFICATIONS



Width	35 3/4 in (908 mm)
Height	83 3/4 - 85 3/16 in (2127 - 2164 mm)
Depth	24 in (610 mm)
Refrigerator Capacity	20.55 cu.ft. (582 l)
Shipping Weight	435 lbs (197 kg)
Annual Energy Usage	312 kWh

FRIDGE FEATURES

- Push2Open Door
- MasterFresh
- BrilliantLight
- MasterSensor Controls
- SoftClose Door
- Temperature Zones: 2
- Maximum Storage Capacity and Flexibility: 4 Door Bins, 3 Drawers, 2 Movable Shelves
- DynaCool
- MaxLoad Hinge
- Active AirClean Filter
- SuperCool
- Acoustic Door and Temperature Alarm
- Sabbath Mode
- CleanSteel Back Wall

OPTIONAL ACCESSORIES SF	MATERIAL	UMRP/RETAIL
KTF 1054 54 in Top Frame	12556860 (7337430)	\$349 / \$399
KTF 1060 60 in Top Frame	07337420	\$349 / \$399
KTF 1066 66 in Top Frame	12556810 (7337400)	\$349 / \$399
KTF 1072 72 in Top Frame	12556830 (7337410)	\$349 / \$399
KTK 3620 SS 36 in Toekick	10984110	\$179 / \$229
KKF-RF AirClean Filter	07236280	\$68 / \$118
KSK2002 Merge Kit	10984130	\$839 / \$889
DS7308 GEN7000 ContourLine Handle (direct replacement for existing handle)	12047020	\$169 / \$169

MasterCool Freezers - 18" Columns



MODEL	HINGE	MATERIAL	UMRP/RETAIL
F2412 Vi Custom Panel	Left	11503300	\$7,899 / \$8,399
F2412 SF Clean Touch Steel™ w/ DS6708 ContourLine Handle	Left	11503310	\$8,549 / \$9,049

OPTIONAL ACCESSORIES VI	MATERIAL	UMRP/RETAIL
KFP 1805 18 in Clean Touch Steel™ Panel (No Logo, w/o handle)	11499020	\$899 / \$949
KTK 1820 SS 18 in Toekick	10984060	\$179 / \$229
KSK2002 Merge Kit	10984130	\$839 / \$889
KWF2000 Water Filter 2.0 (MC 2xx2)	11480330	\$83 / \$133

SPECIFICATIONS

Width	17 ^{3/4} in (451 mm)
Height	83 ^{3/4} - 85 ^{3/16} in (2127 - 2164 mm)
Depth	24 in (610 mm)
Freezer Capacity	8.55 cu.ft. (242 l)
Shipping Weight	306 lbs (139 kg)
Annual Energy Usage	404 kWh

OPTIONAL ACCESSORIES SF

OPTIONAL ACCESSORIES SF	MATERIAL	UMRP/RETAIL
KTF 1042 42 in Top Frame	10984920	\$349 / \$399
KTF 1048 48 in Top Frame	12556870 (7337440)	\$349 / \$399
KTF 1054 54 in Top Frame	12556860 (7337430)	\$349 / \$399
KTF 1060 60 in Top Frame	12556850 (7337420)	\$349 / \$399
KTF 1066 66 in Top Frame	12556810 (7337400)	\$349 / \$399
KTF 1072 72 in Top Frame	12556830 (7337410)	\$349 / \$399
KTK 1820 SS 18 in Toekick	10984060	\$179 / \$229
KSK2002 Merge Kit	10984130	\$839 / \$889
KWF2000 Water Filter 2.0 (MC 2xx2)	11480330	\$83 / \$133
DS7308 GEN7000 ContourLine Handle (direct replacement for existing handle)	12047020	\$169 / \$169

FREEZER FEATURES

- Push2Open Door
- MasterFresh
- BrilliantLight
- MasterSensor Controls
- SoftClose Door
- Temperature Zones: 1
- MaxLoad Hinge
- Acoustic Door and Temperature Alarm
- IceMaker w/ plumbed water connection
- Maximum Storage Capacity and Flexibility: 3 Shelves, 2 Drawers, 1 small Door basket, 3 large Door baskets
- SuperCool
- Sabbath Mode
- CleanSteel Back Wall

*Handles sold separately.
See page 28 for full list of handle options.

MasterCool Freezers - 18" Columns



MODEL	HINGE	MATERIAL	UMRP/RETAIL
F2462 Vi Custom Panel	Right	11503420	\$8,299 / \$8,799
F2472 Vi Custom Panel	Left	11503430	\$8,299 / \$8,799
F2472 SF Clean Touch Steel™ w/ DS6708 ContourLine Handle	Left	11503530	\$8,949 / \$9,449

OPTIONAL ACCESSORIES VI	MATERIAL	UMRP/RETAIL
KFP 1845 18 in Clean Touch Steel™ Panel (IWD) (No Logo, w/o handle)	11499570	\$909 / \$959
KTK 1820 SS 18 in Toekick	10984060	\$179 / \$229
KSK2002 Merge Kit	10984130	\$839 / \$889
KWF2000 Water Filter 2.0 (MC 2xx2)	11480330	\$83 / \$133

SPECIFICATIONS

Width	17 ^{3/4} in (451 mm)
Height	83 ^{3/4} - 85 ^{3/16} in (2127 - 2164 mm)
Depth	24 in (610 mm)
Freezer Capacity	7.73 cu.ft. (219 l)
Shipping Weight	328 lbs (149 kg)
Annual Energy Usage	428 kWh

FREEZERS FEATURES

- Push2Open Door
- MasterFresh
- BrilliantLight
- MasterSensor Controls
- SoftClose Door
- Temperature Zones: 1
- MaxLoad Hinge
- Acoustic Door and Temperature Alarm
- Ice & Water Dispenser
- Maximum Storage Capacity and Flexibility: 3 Shelves, 2 Drawers, 1 small Door basket, 3 large Door baskets
- SuperCool
- Sabbath Mode
- CleanSteel Back Wall

OPTIONAL ACCESSORIES SF	MATERIAL	UMRP/RETAIL
KTF 1042 42 in Top Frame	10984920	\$349 / \$399
KTF 1048 48 in Top Frame	12556870 (7337440)	\$349 / \$399
KTF 1054 54 in Top Frame	12556860 (7337430)	\$349 / \$399
KTF 1060 60 in Top Frame	12556850 (7337420)	\$349 / \$399
KTF 1066 66 in Top Frame	12556810 (7337400)	\$349 / \$399
KTF 1072 72 in Top Frame	12556830 (7337410)	\$349 / \$399
KTK 1820 SS 18 in Toekick	10984060	\$179 / \$229
KSK2002 Merge Kit	10984130	\$839 / \$889
KWF2000 Water Filter 2.0 (MC 2xx2)	11480330	\$83 / \$133
DS7308 GEN7000 ContourLine Handle (direct replacement for existing handle)	12047020	\$169 / \$169

MasterCool Freezers - 24" Columns



MODEL	HINGE	MATERIAL	UMRP/RETAIL
F2662 Vi Custom Panel	Right	11503540	\$8,849 / \$9,349
F2672 Vi Custom Panel	Right	11503550	\$8,849 / \$9,349
F2672 SF Clean Touch Steel™ w/ DS6708 ContourLine Handle	Left	11503570	\$9,599 / \$10,099

OPTIONAL ACCESSORIES VI	MATERIAL	UMRP/RETAIL
KFP 2445 24 in Clean Touch Steel™ Panel (IWD) (No Logo, w/o handle)	11499620	\$1,049 / \$1,099
KTK 2420 SS 24 in Toekick	10984070	\$179 / \$229
KSK2002 Merge Kit	10984130	\$839 / \$889
KWF2000 Water Filter 2.0 (MC 2xx2)	11480330	\$83 / \$133

SPECIFICATIONS	
Width	23 3/4 in (604 mm)
Height	83 3/4 - 85 3/16 in (2127 - 2164 mm)
Depth	24 in (610 mm)
Freezer Capacity	11.23 cu.ft. (318 l)
Shipping Weight	375 lbs (170 kg)
Annual Energy Usage	454 kWh


OPTIONAL ACCESSORIES SF	MATERIAL	UMRP/RETAIL
KTF 1042 42 in Top Frame	10984920	\$349 / \$399
KTF 1048 48 in Top Frame	12556870 (7337440)	\$349 / \$399
KTF 1054 54 in Top Frame	12556860 (7337430)	\$349 / \$399
KTF 1060 60 in Top Frame	12556850 (7337420)	\$349 / \$399
KTF 1066 66 in Top Frame	12556810 (7337400)	\$349 / \$399
KTF 1072 72 in Top Frame	12556830 (7337410)	\$349 / \$399
KTK 2420 SS 24 in Toekick	10984070	\$179 / \$229
KSK2002 Merge Kit	10984130	\$839 / \$889
KWF2000 Water Filter 2.0 (MC 2xx2)	11480330	\$83 / \$133
DS7308 GEN7000 ContourLine Handle (direct replacement for existing handle)	12047020	\$169 / \$169

FREEZER FEATURES

- Push2Open Door
- MasterFresh
- BrilliantLight
- MasterSensor Controls
- SoftClose Door
- Temperature Zones: 1
- MaxLoad Hinge
- Acoustic Door and Temperature Alarm
- Ice & Water Dispenser
- Maximum Storage Capacity and Flexibility: 3 Shelves, 2 Drawers, 1 small Door basket, 3 large Door baskets
- SuperCool
- Sabbath Mode
- CleanSteel Back Wall

*Handles sold separately.
See page 28 for full list of handle options.

MasterCool Freezers - 30" Columns



MODEL	HINGE	MATERIAL	UMRP/RETAIL
F2802 Vi Custom Panel	Right	11503330	\$9,449 / \$9,949
F2812 Vi Custom Panel	Left	11503340	\$9,449 / \$9,949
F2812 SF Clean Touch Steel™ w/ DS6708 ContourLine Handle	Left	11503350	\$10,099 / \$10,599

OPTIONAL ACCESSORIES VI	MATERIAL	UMRP/RETAIL
KFP 3005 30 in Clean Touch Steel™ Panel (No Logo, w/o handle)	11499080	\$1,049 / \$1,099
KTK 3020 SS 30 in Toekick	10984090	\$179 / \$229
KKF-RF AirClean Filter	07236280	\$68 / \$118
KSK2002 Merge Kit	10984130	\$839 / \$889


SPECIFICATIONS	
Width	29 3/4 in (756 mm)
Height	83 3/4 - 85 3/16 in (2127 - 2164 mm)
Depth	24 in (610 mm)
Freezer Capacity	15.75 cu.ft. (446 l)
Shipping Weight	395 lbs (179 kg)
Annual Energy Usage	479 kWh

OPTIONAL ACCESSORIES SF	MATERIAL	UMRP/RETAIL
KTF 1048 48 in Top Frame	12556870 (7337440)	\$349 / \$399
KTF 1054 54 in Top Frame	12556860 (7337430)	\$349 / \$399
KTF 1060 60 in Top Frame	12556850 (7337420)	\$349 / \$399
KTF 1066 66 in Top Frame	12556810 (7337400)	\$349 / \$399
KTF 1072 72 in Top Frame	12556830 (7337410)	\$349 / \$399
KTK 3020 SS 30 in Toekick	10984090	\$179 / \$229
KSK2002 Merge Kit	10984130	\$839 / \$889
KWF2000 Water Filter 2.0 (MC 2x2)	11480330	\$83 / \$133

FREEZER FEATURES	
- Push2Open Door	- IceMaker w/ plumbed water connection
- MasterFresh	- Maximum Storage Capacity and Flexibility: 3 Shelves, 2 Drawers, 1 small Door basket, 3 large Door baskets
- BrilliantLight	- SuperCool
- MasterSensor Controls	- Sabbath Mode
- SoftClose Door	- CleanSteel Back Wall
- Temperature Zones: 1	
- MaxLoad Hinge	
- Acoustic Door and Temperature Alarm	

DS7308 GEN7000 ContourLine Handle (direct replacement for existing handle)	12047020	\$169 / \$169
--	----------	---------------

MasterCool Freezers - 36" Columns



MODEL	HINGE	MATERIAL	UMRP/RETAIL
F2902 Vi Custom Panel	Right	11503360	\$9,649 / \$10,149
F2912 Vi Custom Panel	Left	11503390	\$9,649 / \$10,149
F2912 SF Clean Touch Steel™ w/ DS6708 ContourLine Handle	Left	11503410	\$10,399 / \$10,899

OPTIONAL ACCESSORIES VI	MATERIAL	UMRP/RETAIL
KFP 3605 36 in Clean Touch Steel™ Panel (No Logo, w/o handle)	11499100	\$1,159 / \$1,209
KTK 3620 SS 36 in Toekick	10984110	\$179 / \$229
KSK2002 Merge Kit	10984130	\$839 / \$889
KWF2000 Water Filter 2.0 (MC 2xx2)	11480330	\$83 / \$133

SPECIFICATIONS	
Width	35 3/4 in (908 mm)
Height	83 3/4 - 85 3/16 in (2127 - 2164 mm)
Depth	24 in (610 mm)
Freezer Capacity	19.39 cu.ft. (549 l)
Shipping Weight	462 lbs (210 kg)
Annual Energy Usage	528 kWh

OPTIONAL ACCESSORIES SF	MATERIAL	UMRP/RETAIL
KTF 1054 54 in Top Frame	12556860 (7337430)	\$349 / \$399
KTF 1060 60 in Top Frame	12556850 (7337420)	\$349 / \$399
KTF 1066 66 in Top Frame	12556810 (7337400)	\$349 / \$399
KTF 1072 72 in Top Frame	12556830 (7337410)	\$349 / \$399
KTK 3620 SS 36 in Toekick	10984110	\$179 / \$229
KSK2002 Merge Kit	10984130	\$839 / \$889
KWF2000 Water Filter 2.0 (MC 2xx2)	11480330	\$83 / \$133
DS7308 GEN7000 ContourLine Handle (direct replacement for existing handle)	12047020	\$169 / \$169

FREEZER FEATURES	
- Push2Open Door	- IceMaker w/ plumbed water connection
- MasterFresh	- Maximum Storage Capacity and Flexibility: 3 Shelves, 2 Drawers, 1 small Door basket, 3 large Door baskets
- BrilliantLight	- SuperCool
- MasterSensor Controls	- Sabbath Mode
- SoftClose Door	- CleanSteel Back Wall
- Temperature Zones: 1	
- MaxLoad Hinge	
- Acoustic Door and Temperature Alarm	

*Handles sold separately.
See page 28 for full list of handle options.

MasterCool - 30" Bottom Mount



MODEL	HINGE	MATERIAL	UMRP/RETAIL
KF2802 Vi Custom Panel	Right	11502850	\$8,999 / \$9,499
KF2802 SF Clean Touch Steel™ w/ DS6708 ContourLine Handle	Right	11502900	\$9,999 / \$10,499
KF2812 Vi Custom Panel	Left	11502870	\$8,999 / \$9,499
KF2812 SF Clean Touch Steel™ w/ DS6708 ContourLine Handle	Left	11502910	\$9,999 / \$10,499

SPECIFICATIONS

Width	29 ^{3/4} in (756 mm)
Height	83 ^{3/4} - 85 ^{3/16} in (2127 - 2164 mm)
Depth	24 in (610 mm)
Refrigerator Capacity	11.16 cu.ft. (316 l)
Freezer Capacity	4.8 cu.ft. (136 l)
Shipping Weight	450 lbs (204 kg)
Annual Energy Usage	470 kWh

FRIDGE FEATURES

- Push2Open Door
- MasterFresh
- BrilliantLight
- MasterSensor Controls
- SoftClose Door
- Temperature Zones: 3
- Maximum Storage Capacity and Flexibility: 2 Movable Shelves, 2 Drawers, 3 Door Bins
- DynaCool
- DuplexCool Pro
- MaxLoad Hinge
- Active AirClean Filter
- SuperCool
- Acoustic Door and Temperature Alarm
- Sabbath Mode
- CleanSteel Back Wall

FREEZER FEATURES

- IceMaker w/ plumbed water connection
- Maximum Storage Capacity and Flexibility: 2 Drawers
- SuperCool

OPTIONAL ACCESSORIES VI

		MATERIAL	UMRP/RETAIL
KFP 3015	30 in Clean Touch Steel™ Panel (BM Fridge) (No Logo, w/o handle)	11499120	\$899 / \$949
KFP 3025	30 in Clean Touch Steel™ Panel (BM Freezer) (No Logo, w/o handle)	11499130	\$579 / \$629
KTK 3020 SS	30 in Toekick	10984090	\$179 / \$229
KKF-RF	AirClean Filter	07236280	\$68 / \$118
KSK2002	Merge Kit	10984130	\$839 / \$889
KWF2000	Water Filter 2.0 (MC 2xx2)	11480330	\$83 / \$133

OPTIONAL ACCESSORIES SF

		MATERIAL	UMRP/RETAIL
KTF 1048	48 in Top Frame	12556870 (7337440)	\$349 / \$399
KTF 1054	54 in Top Frame	12556860 (7337430)	\$349 / \$399
KTF 1060	60 in Top Frame	12556850 (7337420)	\$349 / \$399
KTF 1066	66 in Top Frame	12556810 (7337400)	\$349 / \$399
KTF 1072	72 in Top Frame	12556830 (7337410)	\$349 / \$399
KTK 3020 SS	30 in Toekick	10984090	\$179 / \$229
KKF-RF	AirClean Filter	07236280	\$68 / \$118
KSK2002	Merge Kit	10984130	\$839 / \$889
KWF2000	Water Filter 2.0 (MC 2xx2)	11480330	\$83 / \$133
DS7308	GEN7000 ContourLine Handle (direct replacement for existing handle)	12047020	\$169 / \$169

*Handles sold separately.
See page 28 for full list of handle options.

MasterCool - 36" Bottom Mount



MODEL	HINGE	MATERIAL	UMRP/RETAIL
KF2902 Vi Custom Panel	Right	11502930	\$9,499 / \$9,999
KF2902 SF Clean Touch Steel™ w/ DS6708 ContourLine Handle	Right	11502960	\$10,499 / \$10,999
KF2912 Vi Custom Panel	Left	11502940	\$9,499 / \$9,999
KF2912 SF Clean Touch Steel™ w/ DS6708 ContourLine Handle	Left	11502970	\$10,499 / \$10,999

SPECIFICATIONS

Width	35 ^{3/4} in (908 mm)
Height	83 ^{3/4} - 85 ^{3/16} in (2127 - 2164 mm)
Depth	24 in (610 mm)
Refrigerator Capacity	13.74 cu.ft. (389 l)
Freezer Capacity	5.86 cu.ft. (166 l)
Shipping Weight	507 lbs (230 kg)
Annual Energy Usage	504 kWh

FRIDGE FEATURES

- Push2Open Door
- MasterFresh
- BrilliantLight
- MasterSensor Controls
- SoftClose Door
- Temperature Zones: 3
- Maximum Storage Capacity and Flexibility: 2 Movable Shelves, 2 Drawers, 3 Door Bins
- DynaCool
- DuplexCool Pro
- MaxLoad Hinge
- Active AirClean Filter
- SuperCool
- Acoustic Door and Temperature Alarm
- Sabbath Mode
- CleanSteel Back Wall

FREEZER FEATURES

- IceMaker w/ plumbed water connection
- Maximum Storage Capacity and Flexibility: 2 Drawers
- SuperCool

OPTIONAL ACCESSORIES VI



		MATERIAL	UMRP/RETAIL
KFP 3615	36 in Clean Touch Steel™ Panel (BM Fridge) (No Logo, w/o handle)	11499140	\$899 / \$949
KFP 3625	36 in Clean Touch Steel™ Panel (BM Freezer) (No Logo, w/o handle)	11499130	\$579 / \$629
KTK 3620 SS	36 in Toekick	10984110	\$179 / \$229
KKF-RF	AirClean Filter	07236280	\$68 / \$118
KSK2002	Merge Kit	10984130	\$839 / \$889
KWF2000	Water Filter 2.0 (MC 2xx2)	11480330	\$83 / \$133

OPTIONAL ACCESSORIES SF

		MATERIAL	UMRP/RETAIL
KTF 1048	48 in Top Frame	12556870 (7337440)	\$349 / \$399
KTF 1054	54 in Top Frame	12556860 (7337430)	\$349 / \$399
KTF 1060	60 in Top Frame	12556850 (7337420)	\$349 / \$399
KTF 1066	66 in Top Frame	12556810 (7337400)	\$349 / \$399
KTF 1072	72 in Top Frame	12556830 (7337410)	\$349 / \$399
KTK 3620 SS	36 in Toekick	10984110	\$179 / \$229
KKF-RF	AirClean Filter	07236280	\$68 / \$118
KSK2002	Merge Kit	10984130	\$839 / \$889
KWF2000	Water Filter 2.0 (MC 2xx2)	11480330	\$83 / \$133
DS7308	GEN7000 ContourLine Handle (direct replacement for existing handle)	12047020	\$169 / \$169

*Handles sold separately.
See page 28 for full list of handle options.

MasterCool - 36" French Door



MODEL	MATERIAL	UMRP/RETAIL
KF2982 Vi Custom Panel	11503020	\$9,999 / \$10,499
KF2982 SF Clean Touch Steel™ w/ DS6708 ContourLine Handle	11503040	\$10,999 / \$11,490

SPECIFICATIONS	
Width	35 ^{3/4} in (908 mm)
Height	83 ^{3/4} - 85 ^{3/16} in (2127 - 2164 mm)
Depth	24 in (610 mm)
Refrigerator Capacity	13.63 cu.ft. (386 l)
Freezer Capacity	5.86 cu.ft. (166 l)
Shipping Weight	507 lbs (230 kg)
Annual Energy Usage	579 kWh

FRIDGE FEATURES	
- Push2Open Door	- DynaCool
- MasterFresh	- DuplexCool Pro
- BrilliantLight	- MaxLoad Hinge
- MasterSensor Controls	- Active AirClean Filter
- SoftClose Door	- SuperCool
- Temperature Zones: 3	- Acoustic Door and Temperature Alarm
- Maximum Storage Capacity and Flexibility: 2 Movable Shelves, 2 Drawers, 3 Door Bins	- Sabbath Mode
	- CleanSteel Back Wall

FREEZER FEATURES	
- IceMaker w/ plumbed water connection	
- Maximum Storage Capacity and Flexibility: 2 Drawers	
- SuperCool	

OPTIONAL ACCESSORIES VI	MATERIAL	UMRP/RETAIL
KFP 3635 36 in Clean Touch Steel™ Panels (FD Fridge) (2 panels required, no logo, w/o handles)	11499420	\$689 / \$739
KFP 3625 36 in Clean Touch Steel™ Panel (BM Fridge) (No Logo, w/o handle)	11499150	\$579 / \$629
KTK 3620 SS 36 in Toekick	10984110	\$179 / \$229
KKF-RF AirClean Filter	07236280	\$68 / \$118
KSK2002 Merge Kit	10984130	\$839 / \$889
KWF2000 Water Filter 2.0 (MC 2xx2)	11480330	\$83 / \$133

OPTIONAL ACCESSORIES SF	MATERIAL	UMRP/RETAIL
KTF 1054 54 in Top Frame	12556860 (7337430)	\$349 / \$399
KTF 1060 60 in Top Frame	12556850 (7337420)	\$349 / \$399
KTF 1066 66 in Top Frame	12556810 (7337400)	\$349 / \$399
KTF 1072 72 in Top Frame	12556830 (7337410)	\$349 / \$399
KTK 3620 SS 36 in Toekick	10984110	\$179 / \$229
KKF-RF AirClean Filter	07236280	\$68 / \$118
KSK2002 Merge Kit	10984130	\$839 / \$889
KWF2000 Water Filter 2.0 (MC 2xx2)	11480330	\$83 / \$133
DS7308 GEN7000 ContourLine Handle (direct replacement for existing handle)	12047020	\$169 / \$169


Product Highlights

MasterCool Wine Storage

*See specific models for details

FEATURE	DESCRIPTION
MasterSensor Controls	Incredibly convenient: a whole range of settings can be controlled easily with the tap of a finger on the color touch display.
BrilliantLight	Each area of the unit is perfectly illuminated by many LED light strips strategically placed throughout.
Push2Open	For a handleless design, just apply slight pressure to the door to open.
SoftClose	With just a gentle touch, our dynamic doors close on their own. Integrates perfectly within a handleless kitchen.
Temperature Zones	Store up to three different types of wine with different temperature zones.
FlexiFrame Racks	Individual wooden slats can be easily moved to make room for larger wine bottles.
SommelierSet	Perfect for wine connoisseurs: prepare cooled wine glasses and wine for decanting. Drink perfectly Conditioned wine even from opened bottles.
NoteBoard	Every bottle rack features a removable, magnetic strip for labeling bottles.
Miele@home/Mobile Control	Access your appliance from your smart device for maximum convenience.

MasterCool Wine Storage - 24" Columns



MODEL	HINGE	MATERIAL	UMRP/RETAIL
KWT2602 VI Custom Panel	Right	11503590	\$8,499 / \$8,999
KWT 2602 SF Clean Touch Steel™ w/ DS6708 ContourLine Handle	Right	11503620	\$9,499 / \$9,999
KWT 2612 VI Custom Panel	Left	11503610	\$8,499 / \$8,999
KWT 2612 SF Clean Touch Steel™ w/ DS6708 ContourLine Handle	Left	11503640	\$9,499 / \$9,999

OPTIONAL ACCESSORIES VI	MATERIAL	UMRP/RETAIL
KFP 2455 24 in Clean Touch Steel™ Panel (No Logo, w/o handle)	11499630	\$1,159 / \$1,209
KTK 2420 SS 24 in Toekick	10984070	\$179 / \$229
KSK2002 Merge Kit	10984130	\$839 / \$889

SPECIFICATIONS

Width	23 ^{3/4} in (604 mm)
Height	83 ^{3/4} - 85 ^{3/16} in (2127 - 2164 mm)
Depth	24 in (610 mm)
Shipping Weight	357 lbs (162 kg)
Annual Energy Usage	179 kWh

WINE FEATURES

- Push2Open Door
- MasterFresh
- BrilliantLight
- MasterSensor Controls
- SoftClose Door
- Temperature Zones: 3
- Maximum Storage Capacity and Flexibility: 104 x 0.75 l bottles
- DynaCool
- MaxLoad Hinge
- Acoustic Door and Temperature Alarm
- FlexiFrame Racks: 13
- UV Tinted Glass
- NoteBoard
- Sabbath Mode

OPTIONAL ACCESSORIES SF	MATERIAL	UMRP/RETAIL
KTF 1042 42 in Top Frame	10984920	\$349 / \$399
KTF 1048 48 in Top Frame	12556870 (7337440)	\$349 / \$399
KTF 1054 54 in Top Frame	12556860 (7337430)	\$349 / \$399
KTF 1060 60 in Top Frame	12556850 (7337420)	\$349 / \$399
KTF 1066 66 in Top Frame	12556810 (7337400)	\$349 / \$399
KTF 1072 72 in Top Frame	12556830 (7337410)	\$349 / \$399
KTK 2420 SS 24 in Toekick	10984070	\$179 / \$229
KSK2002 Merge Kit	10984130	\$839 / \$889
DS7308 GEN7000 ContourLine Handle (direct replacement for existing handle)	12047020	\$169 / \$169

MasterCool Wine Storage - 24" Columns w/ SommelierSet



MODEL	HINGE	MATERIAL	UMRP/RETAIL
KWT 2662 ViS Custom Panel	Right	11503650	\$9,499 / \$9,999
KWT 2662 SFS Clean Touch Steel™ w/ DS6708 ContourLine Handle	Right	11503670	\$9,999 / \$10,499
KWT 2672 ViS Custom Panel	Left	11503660	\$9,499 / \$9,999

OPTIONAL ACCESSORIES ViS	MATERIAL	UMRP/RETAIL
KFP 2455 24 in Clean Touch Steel™ Panel (No Logo, w/o handle)	11499630	\$1,159 / \$1,209
KTK 2420 SS 24 in Toekick	10984070	\$179 / \$229
KSK2002 Merge Kit	10984130	\$839 / \$889

SPECIFICATIONS

Width	23 ^{3/4} in (604 mm)
Height	83 ^{3/4} - 85 ^{3/16} in (2127 - 2164 mm)
Depth	24 in (610 mm)
Shipping Weight	357 lbs (162 kg)
Annual Energy Usage	179 kWh

WINE FEATURES













- Push2Open Door
- MasterFresh
- BrilliantLight
- MasterSensor Controls
- SoftClose Door
- Temperature Zones: 3
- Maximum Storage Capacity and Flexibility: 77 x 0.75 l bottles
- DynaCool
- MaxLoad Hinge
- Acoustic Door and Temperature Alarm
- FlexiFrame Racks: 9
- UV Tinted Glass
- SommelierSet
- NoteBoard
- Sabbath Mode

OPTIONAL ACCESSORIES SFS

OPTIONAL ACCESSORIES SFS	MATERIAL	UMRP/RETAIL
KTF 1042 42 in Top Frame	10984920	\$349 / \$399
KTF 1048 48 in Top Frame	12556870 (7337440)	\$349 / \$399
KTF 1054 54 in Top Frame	12556860 (7337430)	\$349 / \$399
KTF 1060 60 in Top Frame	12556850 (7337420)	\$349 / \$399
KTF 1066 66 in Top Frame	12556810 (7337400)	\$349 / \$399
KTF 1072 72 in Top Frame	12556830 (7337410)	\$349 / \$399
KTK 2420 SS 24 in Toekick	10984070	\$179 / \$229
KSK2002 Merge Kit	10984130	\$839 / \$889
DS7308 GEN7000 ContourLine Handle (direct replacement for existing handle)	12047020	\$169 / \$169

*Handles sold separately.
See page 28 for full list of handle options.

Handle Options

GEN 7	MODEL	MATERIAL	TRIM / COLOR	HANDLE WIDTH	COOKING	VI DISHWASHER	SF DISHWASHER	VI COOLING	SF MASTERCOOL	UMRP/RETAIL
	DS 7000	11345890	PureLine Stainless steel ¹	15 ^{3/4} in	x	x		x		\$149 / \$149
	DS 7000	11345930	VitroLine Obsidian black ¹	15 ^{3/4} in	x	x		x		\$309 / \$309
	DS 7000	11345940	VitroLine Brilliant white ¹	15 ^{3/4} in	x	x		x		\$309 / \$309
	DS 7000	11345950	VitroLine Graphite grey ¹	15 ^{3/4} in	x	x		x		\$309 / \$309
	DS 7308	12047020	ContourLine Stainless steel standard handle	21 ^{1/8} in	x	x		x	x	\$169 / \$169
	DS 7708	12047000	ContourLine Stainless steel swiveling handle	21 ^{1/8} in	x	x		x	x	\$209 / \$209
	DS 7808	12047030	VitroLine Obsidian black	19 ^{11/16} in	x	x		x		\$349 / \$349
	DS 7808	12047050	VitroLine Graphite grey	19 ^{11/16} in	x	x		x		\$349 / \$349
	DS 7808	12047060	VitroLine Brilliant white	19 ^{11/16} in	x	x		x		\$349 / \$349
	DS 7808	12046910	PureLine Stainless steel	19 ^{11/16} in	x	x		x		\$169 / \$169
GEN 6	MODEL	MATERIAL	TRIM / COLOR	HANDLE WIDTH	COOKING	VI DISHWASHER	SF DISHWASHER	VI COOLING	SF MASTERCOOL	UMRP/RETAIL
	DS 6000	10490600	GEN6000 PureLine handle ²	22 ^{1/6} in			x (G 5000 SF)			\$169 / \$169
	DS 6000	9824160	GEN6000 ContourLine handle ²	22 ^{1/6} in			x (G 7000 SF)			\$169 / \$169

Fits Slimline VI Dishwashers¹
Dishwasher Replacement Handles²

Miele

Miele, Inc.
9 Independence Way
Princeton, NJ 08540

mieleusa.com
800.843.7231

Visit one of Miele's Experience Centers:

Beverly Hills
Boca Raton
Chicago
Coral Gables
Manhattan
Princeton
San Francisco
Scottsdale
Seattle
Tysons Corner

Prices effective January 2023.

Prices subject to change without notice.

Miele reserves the right to accept or deny all orders at its Princeton, NJ offices.

Alteration rights reserved / January 2023