

A high-quality photograph of a Miele Range Series kitchen unit in a modern dining room. The kitchen unit, featuring a dark grey finish and wood-grain accents, includes a gas cooktop with a white pot, a large oven with a silver handle, and a smaller drawer unit below. The unit is set against a large window with horizontal wooden blinds, offering a view of a coastal town and the sea. In the background, a dining table with wooden chairs and two pendant lights are visible. The floor is made of large, light grey tiles.

Miele

Range Series

Model Comparison Overview 2025

30" Ranges



Models				
HR 1124-3 AG	HR 1724-3 DF	HR 1924-3 DF	HR 1622-3 I	HR 1422-3 I
Gas Material # 11791360 LP Material # 11791390	Gas Material # 11791530 LP Material # 11791540	Gas Material # 11791550 LP Material # 11791560	208/240 V Material # 11791520	208/240 V Material # 12298850



BTU Output: G / LP Watts					
Models	HR 1124-3 AG	HR 1724-3 DF	HR 1924-3 DF	HR 1622-3 I	HR 1422-3 I
Front left	19,500 / 19,500	19,500 / 19,500	19,500 / 19,500	2,700 W – 3,850 W	2,700 W – 3,850 W
Front center	—	—	—	—	—
Front right	19,500 / 19,500	19,500 / 19,500	19,500 / 19,500	1,950 W – 3,100 W	1,950 W – 3,100 W
Back left	12,500 / 12,500	12,500 / 12,500	12,500 / 12,500	1,450 W – 2,300 W	1,450 W – 2,300 W
Back center	—	—	—	—	—
Back right	19,500 / 19,500	19,500 / 19,500	19,500 / 19,500	2,400 W – 3,850 W	2,400 W – 3,850 W
Total	max. 71,000/71,000	max. 71,000 /71,000	max. 71,000 /71,000	8,500 W – 13,100W	8,500 W – 13,100W
Features					
Fuel type	All Gas	Dual Fuel	Dual Fuel	Induction	Induction
Controls	DirectSelect	DirectSelect	M Touch	M Touch	EasyControl
Handle	Comfort handle	Comfort handle	ComfortSwivel handle	ComfortSwivel handle	Comfort handle
WiFi + MotionReact	—	—	•	•	—
Motorised lift-up control panel	—	—	•	•	—
Burners / DW-safe grates	4 / •	4 / •	4 / •	4 / —	4 / —
Automatic programs	— / —	— / —	• / •	• / •	— / —
M Pro griddle / M Pro grill	— / —	— / —	— / —	— / —	— / —
Wireless Precision Probe	—	—	•	•	—
Moisture Plus	—	—	•	•	—

36" Ranges



Models			
HR 1134-3 AG	HR 1135-3 AG GR	HR 1136-3 AG GD	HR 1432-3 I
Gas Material # 11791410 LP Material # 11791430	Gas Material # 11791450	Gas Material # 11791500 LP Material # 11791510	208/240 V Material # 12535250



BTU Output: G / LP				
Models	HR 1124-3 AG	HR 1135-3 AG GR	HR 1136-3 AG GD	HR 1432-3 I
Front left	19,500 / 19,500	19,500	19,500 / 19,500	2,700 W – 3,850 W
Front center	19,500 / 19,500	Grill: 19,000	Griddle: 13,000 / 14,300	—
Front right	19,500 / 19,500	19,500	19,500 / 19,500	1,950 W – 3,100 W
Back left	8,000 / 8,000	8,000	8,000 / 8,000	1,450 W – 2,300 W
Back center	9,000 / 9,000	—	—	—
Back right	9,000 / 9,000	9,000	9,000 / 9,000	2,400 W – 3,850 W
Total	max. 84,500 / 84,500	max. 75,000	max. 69,000 / 70,300	8,500 W – 13,100W
Features				
Fuel type	All Gas	All Gas	All Gas	Induction
Controls	DirectSelect	DirectSelect	M Touch	M Touch
Handle	Comfort handle	Comfort handle	Comfort handle	Comfort handle
WiFi + MotionReact	—	—	—	•
Motorised lift-up control panel	—	—	—	•
Burners / DW-safe grates	6 / •	4 + Grill / •	4 + Griddle / •	4 / —
Automatic programs	— / —	— / —	— / —	• / •
M Pro griddle / M Pro grill	— / —	— / •	• / —	— / —
Wireless Precision Probe	—	—	—	•
Moisture Plus	—	—	—	•

36" Ranges



Models			
HR 1632-3 I	HR 1934-3 DF	HR 1935-3 DF GR	HR 1936-3 DF GD
208/240 V Material # 12535260	Gas Material # 11791570 LP Material # 11791590	Gas Material # 11791600	Gas Material # 11791610 LP Material # 11791630




BTU Output: G / LP				
Models	HR 1632-3 I	HR 1934-3 DF	HR 1935-3 DF GR	HR 1936-3 DF GD
Front left	2,700 W – 3,850 W	19,500 / 19,500	19,500	19,500 / 19,500
Front center	—	19,500 / 19,500	Grill: 19,000	Griddle: 13,000 / 14,300
Front right	1,950 W – 3,100 W	19,500 / 19,500	19,500	19,500 / 19,500
Back left	1,450 W – 2,300 W	12,500 / 12,500	12,500	12,500 / 12,500
Back center	—	13,600 / 13,000	—	—
Back right	2,400 W – 3,850 W	13,600 / 13,000	13,600	13,600 / 13,000
Total	8,500 W – 13,100W	max. 98,200 / 97,000	max. 84,100	max. 78,100 / 78,800
Features				
Fuel type	Induction	Dual Fuel	Dual Fuel	Dual Fuel
Controls	M Touch	M Touch	M Touch	M Touch
Handle	Comfort handle	ComfortSwivel handle	ComfortSwivel handle	ComfortSwivel handle
WiFi + MotionReact	•	•	—	•
Motorised lift-up control panel	•	•	—	•
Burners / DW-safe grates	4 / —	6 / •	4 + Grill / •	4 + Griddle / •
Automatic programs	• / •	• / •	• / •	• / •
M Pro griddle / M Pro grill	— / —	—	— / •	• / —
Wireless Precision Probe	•	•	•	•
Moisture Plus	•	•	•	•

48" Ranges



Models		
HR 1954-3 DF	HR 1955-3 DF GR	HR 1956-3 DF GD
Gas Material # 11791670 LP Material # 11791680	Gas Material # 11791690	Gas Material # 11791700 LP Material # 11791750




BTU Output: G / LP			
Models	HR 1954-3 DF	HR 1955-3 DF GR	HR 1956-3 DF GD
Front left	19,500 / 19,500	19,500	19,500 / 19,500
Front left center	19,500 / 19,500	Grill: 19,000	Griddle: 13,000 / 14,300
Front right center	19,500 / 19,500	19,500	19,500 / 19,500
Front right	19,500 / 19,500	19,500	19,500 / 19,500
Back left	10,000 / 10,000	10,000	10,000 / 10,000
Back left center	13,600 / 13,000	—	—
Back right center	13,600 / 13,000	3,600	13,600 / 13,000
Back right	10,000 / 10,000	10,000	10,000 / 10,000
Total	max. 125,200 / 124,000	max. 111,100	max. 105,100 / 105,800
Features			
Fuel type	Dual Fuel	Dual Fuel	Dual Fuel
Controls	M Touch	M Touch	M Touch
Handle	ComfortSwivel handle	ComfortSwivel handle	ComfortSwivel handle
WiFi + MotionReact	•	•	•
Motorised lift-up control panel	•	•	•
Burners / DW-safe grates	8 / •	6 + Grill / •	6 + Griddle / •
Automatic programs	• / •	• / •	• / •
M Pro griddle / M Pro grill	—	— / •	• / —
Wireless Precision Probe	•	•	•
Moisture Plus	•	•	•

30" and 36" Rangetops



Models			
30"	36"	36"	36"
KMR 1124-3	KMR 1134-3	KMR 1135-3 GR	KMR 1136-3 GD
Gas Material # 11852270 LP Material # 11852330	Gas Material # 11852340 LP Material # 11852370	Gas Material # 11852380	Gas Material # 11852460 LP Material # 11852550



BTU Output: G / LP				
Models	30"	36"	36"	36"
	KMR 1124-3	KMR 1134-3	KMR 1124-3	KMR 1124-3
Front left	19,500 / 19,500	19,500 / 19,500	19,500	19,500 / 19,500
Front center	—	19,500 / 19,500	Grill: 19,000	Griddle: 13,000 / 14,300
Front left center	—	—	—	—
Front right center	—	—	—	—
Front right	19,500 / 19,500	19,500 / 19,500	19,500	19,500 / 19,500
Back left	12,500 / 12,500	12,500 / 12,500	12,500	12,500 / 12,500
Back center	—	13,600 / 13,000	—	—
Back left center	—	—	—	—
Back right center	—	—	—	—
Back right	19,500 / 19,500	13,600 / 13,000	13,600	13,600 / 13,000
Total	max. 71,000 / 71,000	max. 98,200 / 97,000	max. 84,100	max. 78,100 / 78,800
Features				
Fuel type	Gas	Gas	Gas	Gas
Controls	Precision knobs	Precision knobs	Precision knobs	Precision knobs
Burners / DW-safe grates	4 / •	6 / •	4 + Grill / •	4 + Griddle / •
M Pro griddle / M Pro grill	— / —	— / —	— / •	• / —

48" Rangetops




Models		
48"	48"	48"
KMR 1354-3	KMR 1355-3 GR	KMR 1356-3 GD
Gas Material # 11852560 LP Material # 11852570	Gas Material # 11852600	Gas Material # 11852640 LP Material # 11852660



BTU Output: G / LP

Models	48"	48"	48"
	KMR 1354-3	KMR 1355-3 GR	KMR 1356-3 GD
Front left	19,500 / 19,500	19,500	19,500 / 19,500
Front center	—	—	—
Front left center	19,500 / 19,500	Grill: 19,000	Griddle: 13,000 / 14,300
Front right center	19,500 / 19,500	19,500	19,500 / 19,500
Front right	19,500 / 19,500	19,500	19,500 / 19,500
Back left	10,000 / 10,000	10,000	10,000 / 10,000
Back center	—	13,600 / 13,000	—
Back left center	13,600 / 13,000	—	—
Back right center	13,600 / 13,000	13,600	13,600 / 13,000
Back right	10,000 / 10,000	10,000	10,000 / 10,000
Total	max. 125,200 / 124,000	max. 111,100	max. 105,100 / 105,800
Features			
Fuel type	Gas	Gas	Gas
Controls	Precision knobs	Precision knobs	Precision knobs
Burners / DW-safe grates	8 / •	6 + Grill / •	6 + Griddle / •
M Pro griddle / M Pro grill	— / —	— / •	• / —

30", 36" and 48" Range Hoods



Models				
36"	48"	30"	36"	48"
DAR 1130	DAR 1150	DAR 1220-3	DAR 1230-3	DAR 1250-3
Material # 09753480	Material # 09753510	Material # 11898130	Material # 11898170	Material # 11898190

Models	36"	48"	30"	36"	48"
	DAR 1130	DAR 1150	DAR 1220-3	DAR 1230-3	DAR 1250-3
DRIB XL 700 CFM Internal Blower	•	—	•	•	—
DRIB XXL 1100 CFM Internal Blower	•	•	—	•	•
DREB XL 700 CFM External Blower	•	—	•	•	—
DREB XXL 1100 CFM External Blower	•	•	—	•	•
Installation type	Insert	Insert	Wall	Wall	Wall
Vented/Recirculating	•/—	•/—	•/•	•/•	•/—
Controls	Recessed knobs	Recessed knobs	Recessed knobs	Recessed knobs	Recessed knobs
LED ClearView lighting	•	•	•	•	•
Dishwasher-safe baffle filters	3	4	2	3	4
Auto-vent safety sensors	•	•	•	•	•
CleanCover	•	•	•	•	•
Fan speeds (incl. intensive)	4	4	4	4	4
6" Duct cover	—	—	DRDC 3006	DRDC 3606	DRDC 4806
12" Duct cover	—	—	DRDC 3012	DRDC 3612	DRDC 4812
18" Duct cover	—	—	DRDC 3018	DRDC 3618	DRDC 4818
24" Duct cover	—	—	DRDC 3024	DRDC 3624	DRDC 4824
Backsplash	RBS36	RBS48	RBS30	RBS36	RBS48

The **Range** That Makes **Anything** Possible



MotionReact

No need to touch the appliance, MotionReact is a sensor that turns on the light when it detects movement at close range. It is especially useful if your hands are full or dirty from prepping food.



Connectivity

Operate your Miele Range from anywhere on your smart phone or tablet with WiFiConn@ct. Explore different settings and programs, while having the ability to network your Miele appliances with the Miele@home app.



Moisture Plus

Adds a burst of steam for extraordinary roasting and baking results ensuring an incredibly light dough and a nicely browned crust.



Wireless Precision Probe

Precise temperature control, with correct-to-the-minute information on how long a program has to run. With a wireless connection, the roast probe is extremely safe to use as you can insert the probe outside of the oven.



Backlit Knobs

Backlit precision knobs allow you to see if the burner has been turned off after cooking. Cooling system and cool-touch front allow maximum protection keeping all surfaces around the Range cool.



M Touch

Innovative M Touch controls allow for easy navigation through an intuitive swipe of the screen. The touch-activated ComfortLift Panel is designed to provide optimum comfort and ease.



Harmonious Design

Redefined professional look aligns harmoniously with Miele products. Available in All Gas, Dual Fuel, Electric and Induction, ranging in widths from 30", 36" and 48", which features a unique 3-door concept.



Burner Performance

The M Pro dual stacked burner system, with TrueSimmer, delivers a maximum of 19,500 BTUs; allowing for absolute control whether simmering or searing your favorite foods. M Pro infrared griddle and M Pro grill options are available.