

**Miele**



# Cleaning Price List

2026

# Table of Contents

<b>Dishwashers</b>	<b>03</b>
Dishwasher Feature Highlights	03
<b>Professional for the Home Dishwashers</b>	<b>18</b>
Professional for the Home Dishwasher Feature Highlights	18
Professional for the Home Dishwasher	19
<b>Laundry</b>	<b>32</b>
Laundry Feature Highlights	32
Laundry	33
Rotary Ironer	43
<b>Professional for the Home Laundry</b>	<b>44</b>
Professional for the Home Laundry Feature Highlights	44
Professional for the Home Laundry	45
Professional Rotary Ironer	47
<b>Accessories &amp; Consumables – Laundry</b>	<b>48</b>
<b>Accessories &amp; Consumables – Dishwashers</b>	<b>49</b>
<b>Handles</b>	<b>50</b>

# Product Highlights – Dishwashers

<b>Feature</b>	<b>Description</b> (see specific models for details)
<b>EcoPower Technology</b>	With a innovative water flow system, G 7000 dishwashers save both water and energy. In the Auto program, run a full cycle using less than 1.6 gallons of water.
<b>3D MultiFlex Cutlery Tray</b>	Provides a new level of convenience by adapting instantly to accommodate larger utensils, as well as taller stemware in the upper basket.
<b>BrilliantLight</b>	Four powerful LED lights illuminate the dishwasher from the inside out.
<b>AutoOpen Drying</b>	The dishwasher door automatically opens at the end of the cycle, allowing air to escape and circulate for perfect drying.
<b>AutoDosing with PowerDisk®</b>	In G 7000 dishwashers, the integrated PowerDisk® automatically dispenses the correct amount of detergent in accordance with the selected program and degree of soiling.
<b>FlexLine Baskets</b>	Easily adjustable to accommodate a wide array of dishware, utensils, stemware, pots and pans.
<b>Knock2Open</b>	Automatic door opening after two knocks. Integrates seamlessly in a handleless kitchen.
<b>QuickIntenseWash</b>	Excellent cleaning and drying results for normally soiled dishes in only 58 minutes.
<b>SaniWash</b>	High temperature program for deep cleaning results.
<b>Miele@home</b>	Access your appliance from your smart device for maximum convenience.
<b>AutoSensor</b>	Automatically adjusts program Time, Temperature, & Water volume based on multiple measurements of turbidity.
<b>Certified Hygiene Seal</b>	All Miele dishwashers remove more than 99.9% of specific bacteria.*
<b>Golden Virus Seal</b>	All Miele dishwashers remove more than 99.9% of all viruses.*



### Certified Hygiene Seal

\*Approved by Rhein-Waal University. This certification attests that all G 5000 and G 7000 dishwashers with the SaniWash or Pots & Pans program offer particularly hygienic cleaning. This applies both with (standard) detergent or even without cleaning agent altogether.



### Golden Virus Seal

\*According to the InFluenc\_H – Institute for Integrative Hygiene and Virology, cleaning with Profiline dishwashers using Miele's ProCare Shine 12 GC cleaning agents removes enveloped and non-enveloped viruses (e.g. coronavirus, influenza, or noroviruses) in the Pots & Pans and Sanitize programs, as well as enveloped viruses (excluding Hepatitis B) in the QuickIntenseWash and Universal programs, even if load items are difficult to reprocess.

## Dishwashers – 24" Pre-Finished



Model	Handle Type	Material	UMRP
<b>G 5008 SCU</b> Clean Touch Steel™	Integrated	11966810	\$1,599

### Specifications

Width	23 9/16 in (598 mm)
Height	33 11/16 – 36 1/4 in (855 – 920 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	121 lbs (55 kg)
Annual Energy Usage	230 kWh
Decibel rating	44 dBA

### Features

- Controls – DirectSelect, front
- EcoPower Technology
- Original Cutlery Tray
- Basket Design – Comfort
- Door design – ComfortClose
- No. of Standard Place Settings – 16
- Double Waterproof System
- AutoSensor / Load Sensor

### Programs

- Normal
- QuickIntenseWash
- Pots & Pans
- SaniWash
- Rinse & Hold

### Options

- Express
- Extra Clean
- Extra Dry
- Delay Start

## Dishwashers – 24" Fully Integrated



Model	Handle Type	Material	UMRP
<b>G 5051 SCVi ADA</b> Custom Panel	No Handle	11636710	\$1,599

### Specifications

Width	23 9/16 in (598 mm)
Height	32 1/16 – 34 1/4 in (814 – 870 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	121 lbs (55 kg)
Annual Energy Usage	230 kWh
Decibel rating	44 dBA
ADA Compliant	Yes

### Features

- Controls – DirectSelect, hidden
- EcoPower Technology
- Original Cutlery Tray
- Basket Design – Comfort
- Door design – ComfortClose
- No. of Standard Place Settings – 16
- Double Waterproof System
- AutoSensor / Load Sensor

### Programs

- Normal
- QuickIntenseWash
- Pots & Pans
- SaniWash
- Rinse & Hold

### Options

- Express
- Extra Clean
- Extra Dry
- Delay Start

Optional Accessories	Material	UMRP
GFVi 701/72 Fully Integrated Panel Full Size, Clean Touch Steel™, 6" Toe-Kick, no handle	12670590	\$379

# Dishwashers – 24" Fully Integrated



Model	Handle Type	Material	UMRP	Optional Accessories Vi	Material	UMRP
<b>G 5056 SCVi</b> Custom Panel	No Handle	11636720	\$1,599	GFVi 701/72 Fully Integrated Panel Full Size, Clean Touch Steel™, 6" Toe-Kick, no handle	12670590	\$379
<b>G 5056 SCVi SF</b> Clean Touch Steel™	PureLine Handle*	11695330	\$1,749	GFVi 701/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, no handle	12670600	\$379
<b>G 5058 SCVi SFP</b>	Pocket Handle	11966820	\$1,749	GFVi 710/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, PureLine handle	12074350	\$489
<b>Specifications</b>						
Width	23 9/16 in (598 mm)					
Height	33 11/16 – 36 1/4 in (855 – 920 mm)					
Depth	22 7/16 in (570 mm)					
Shipping Weight	121 lbs (55 kg)					
Annual Energy Usage	230 kWh					
Decibel rating	44 dBA					
ADA Compliant	No					
<b>Features</b>						
<ul style="list-style-type: none"> <li>• Controls – DirectSelect, hidden</li> <li>• EcoPower Technology</li> <li>• Original Cutlery Tray</li> <li>• Basket Design – Comfort</li> <li>• Door design – ComfortClose</li> <li>• No. of Standard Place Settings – 16</li> <li>• Double Waterproof System</li> <li>• AutoSensor / Load Sensor</li> </ul>						
<b>Programs</b>						
<ul style="list-style-type: none"> <li>• Normal</li> <li>• QuickIntenseWash</li> <li>• Pots &amp; Pans</li> <li>• SaniWash</li> <li>• Rinse &amp; Hold</li> </ul>						
<b>Options</b>						
<ul style="list-style-type: none"> <li>• Express</li> <li>• Extra Clean</li> <li>• Extra Dry</li> <li>• Delay Start</li> </ul>						

\*Handle not included in the UMRP – available for purchase separately.

# Dishwashers – 24" Fully Integrated



Model	Handle Type	Material	UMRP	Optional Accessories Vi	Material	UMRP
<b>G 5266 SCVi</b> Custom Panel	No Handle	11636740	\$1,899	GFVi 701/72 Fully Integrated Panel Full Size, Clean Touch Steel™, 6" Toe-Kick, no handle	12670590	\$379
<b>G 5266 SCVi SF</b> Clean Touch Steel™	PureLine Handle*	11636750	\$2,099	GFVi 701/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, no handle	12670600	\$379
<b>G 5266 SCVi SFP</b>	Pocket Handle	11695340	\$2,099	GFVi 710/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, PureLine handle	12074350	\$489
<b>Specifications</b>						
Width	23 9/16 in (598 mm)					
Height	33 11/16 – 36 1/4 in (855 – 920 mm)					
Depth	22 7/16 in (570 mm)					
Shipping Weight	121 lbs (55 kg)					
Annual Energy Usage	230 kWh					
Decibel rating	42 dBA					
ADA Compliant	No					
<b>Features</b>						
<ul style="list-style-type: none"> <li>• Controls – DirectSelect, hidden</li> <li>• EcoPower Technology</li> <li>• 3D MultiFlex Cutlery Tray</li> <li>• Basket Design – Comfort</li> <li>• AutoOpen Drying</li> <li>• No. of Standard Place Settings – 16</li> <li>• SensorDry</li> <li>• Double Waterproof System</li> <li>• AutoSensor / Load Sensor</li> <li>• Door design – CofmortClose</li> </ul>						
<b>Programs</b>						
<ul style="list-style-type: none"> <li>• Normal</li> <li>• QuickIntenseWash</li> <li>• Pots &amp; Pans</li> <li>• SaniWash</li> <li>• Rinse &amp; Hold</li> </ul>						
<b>Options</b>						
<ul style="list-style-type: none"> <li>• Express</li> <li>• Extra Clean</li> <li>• Extra Dry</li> <li>• Delay Start</li> </ul>						

\*Handle not included in the UMRP – available for purchase separately.

# Dishwashers – 24" Pre-Finished



Model	Handle Type	Material	UMRP
<b>G 7216 SCU</b> Clean Touch Steel™	Integrated Handle*	12497130	\$1,999

Specifications	
Width	23 9/16 in (598 mm)
Height	33 11/16 – 36 1/4 in (855 – 920 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	121 lbs (55 kg)
Annual Energy Usage	230 kWh
Decibel rating	42 dBA
ADA Compliant	No

Features	
<ul style="list-style-type: none"> <li>Controls – DirectSelect, front</li> <li>EcoPower Technology</li> <li>3D MultiFlex Cutlery Tray</li> <li>AutoOpen Drying</li> <li>No. of Standard Place Settings – 16</li> </ul>	<ul style="list-style-type: none"> <li>Basket Design – ExtraComfort</li> <li>SensorDry</li> <li>Double Waterproof System</li> <li>AutoSensor / Load Sensor</li> <li>Water Softener</li> </ul>

Programs	
<ul style="list-style-type: none"> <li>Normal</li> <li>QuickIntenseWash</li> <li>Pots &amp; Pans</li> <li>SaniWash</li> <li>Rinse &amp; Hold</li> <li>China &amp; Crystal</li> </ul>	

Options	
<ul style="list-style-type: none"> <li>Express</li> <li>Extra Clean</li> <li>Extra Dry</li> <li>Intense Zone</li> <li>Delay Start</li> </ul>	

\*Handle not included in the UMRP – available for purchase separately.

# Dishwashers – 24" Fully Integrated



Model	Handle Type	Material	UMRP
<b>G 7266 SCVi</b> Custom Panel	No Handle	12497140	\$1,999

<b>G 7266 SCVi SF</b> Clean Touch Steel™	ContourLine Handle*	12497150	\$2,199
---	---------------------	----------	---------

Specifications	
Width	23 9/16 in (598 mm)
Height	33 11/16 – 36 1/4 in (855 – 920 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	121 lbs (55 kg)
Annual Energy Usage	230 kWh
Decibel rating	42 dBA
ADA Compliant	No

Features	
<ul style="list-style-type: none"> <li>Controls – DirectSelect, front</li> <li>EcoPower Technology</li> <li>3D MultiFlex Cutlery Tray</li> <li>AutoOpen Drying</li> <li>SensorDry</li> <li>No. of Standard Place Settings – 16</li> </ul>	<ul style="list-style-type: none"> <li>Miele@home</li> <li>Basket Design – ExtraComfort</li> <li>Double Waterproof System</li> <li>AutoSensor / Load Sensor</li> <li>Water Softener</li> </ul>

Programs	
<ul style="list-style-type: none"> <li>Normal</li> <li>QuickIntenseWash</li> <li>Pots &amp; Pans</li> </ul>	<ul style="list-style-type: none"> <li>SaniWash</li> <li>Rinse &amp; Hold</li> <li>China &amp; Crystal</li> </ul>

Options	
<ul style="list-style-type: none"> <li>Express</li> <li>Extra Clean</li> <li>Extra Dry</li> </ul>	<ul style="list-style-type: none"> <li>Intense Zone</li> <li>Delay Start</li> </ul>

\*Handle not included in the UMRP – available for purchase separately.



Optional Accessories Vi	Material	UMRP
GFVi 701/72 Fully Integrated Panel Full Size, Clean Touch Steel™, 6" Toe-Kick, no handle	12670590	\$379
GFVi 701/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, no handle	12670600	\$379
GFVi 710/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, PureLine handle	12074350	\$489
GFVi 711/72 Fully Integrated Panel Full Size, Clean Touch Steel™, 6" Toe-Kick, ContourLine handle	12074400	\$489
GFVi 711/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, ContourLine handle	12074450	\$489
GFVi 712/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, Range Panel	12074470	\$489
GFVi 709/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, Pocket handle	12672750	\$489

## Dishwashers – 24" Fully Integrated



Model	Handle Type	Material	UMRP
-------	-------------	----------	------

<b>G 7186 SCVi</b> Custom Panel	No Handle	12496990	\$2,199
<b>G 7186 SCVi SFP</b>	Pocket Handle*	12496690	\$2,399

### Specifications

Width	23 9/16 in (598 mm)
Height	33 11/16 – 36 1/4 in (855 – 920 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	121 lbs (55 kg)
Annual Energy Usage	230 kWh
Decibel rating	42 dBA
ADA Compliant	No

### Features

- Controls – DirectSelect, hidden
- EcoPower Technology
- 3D MultiFlex Cutlery Tray
- Basket Design – Comfort
- AutoOpen Drying
- No. of Standard Place Settings – 16
- SensorDry
- Double Waterproof System
- AutoSensor / Load Sensor
- Water Softener
- Door design – CofmortClose
- AutoDosing with PowerDisk®

### Programs

- Normal
- QuickIntenseWash
- Pots & Pans
- SaniWash
- Rinse & Hold
- China & Crystal

### Options

- Express
- Extra Clean
- Extra Dry
- Intense Zone
- Delay Start

Optional Accessories Vi	Material	UMRP
-------------------------	----------	------

GFVi 701/72 Fully Integrated Panel Full Size, Clean Touch Steel™, 6" Toe-Kick, no handle	12670590	\$379
GFVi 701/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, no handle	12670600	\$379
GFVi 710/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, PureLine handle	12074350	\$489
GFVi 711/72 Fully Integrated Panel Full Size, Clean Touch Steel™, 6" Toe-Kick, ContourLine handle	12074400	\$489
GFVi 711/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, ContourLine handle	12074450	\$489
GFVi 712/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, Range Panel	12074470	\$489
GFVi 709/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, Pocket handle	12672750	\$489

## Dishwashers – 24" Pre-Finished



Model	Handle Type	Material	UMRP
-------	-------------	----------	------

<b>G 7196 SCVi SF</b> Clean Touch Steel™	PureLine Handle*	12496710	\$2,399
---	---------------------	----------	---------

### Specifications

Width	23 9/16 in (598 mm)
Height	33 11/16 – 36 1/4 in (855 – 920 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	121 lbs (55 kg)
Annual Energy Usage	230 kWh
Decibel rating	42 dBA
ADA Compliant	No

### Features

- Controls – DirectSelect, hidden
- EcoPower Technology
- 3D MultiFlex Cutlery Tray
- AutoOpen Drying
- SensorDry
- No. of Standard Place Settings – 16
- AutoDosing with PowerDisk®
- Basket Design – ExtraComfort
- Double Waterproof System
- Miele@home
- AutoSensor / Load Sensor
- Water Softener

### Programs

- Normal
- QuickIntenseWash
- Pots & Pans
- SaniWash
- Rinse & Hold
- China & Crystal

### Options

- Express
- Extra Clean
- Intense Zone
- Delay Start

Model	Handle Type	Material	UMRP
-------	-------------	----------	------

<b>G 7193 SCVi ADA</b> Custom Panel	No Handle	12496700	\$2,199
--	-----------	----------	---------

### Specifications

Width	23 9/16 in (598 mm)
Height	32 1/16 – 34 1/4 in (814 – 870 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	121 lbs (55 kg)
Annual Energy Usage	230 kWh
Decibel rating	42 dBA
ADA Compliant	Yes

### Features

- Controls – DirectSelect, hidden
- EcoPower Technology
- 3D MultiFlex Cutlery Tray
- AutoOpen Drying
- SensorDry
- No. of Standard Place Settings – 16
- AutoDosing with PowerDisk®
- Basket Design – ExtraComfort
- Double Waterproof System
- Miele@home
- AutoSensor / Load Sensor
- Water Softener

### Programs

- Normal
- QuickIntenseWash
- Pots & Pans
- SaniWash
- Rinse & Hold
- China & Crystal
- Express
- Extra Clean
- Extra Dry
- Intense Zone
- Delay Start

Optional Accessories	Material	UMRP
----------------------	----------	------

GFVi 701/72 Fully Integrated Panel Full Size, Clean Touch Steel™, 6" Toe-Kick, no handle	12670590	\$379
--	----------	-------

\*Handle not included in the UMRP – available for purchase separately.

\*Handle not included in the UMRP – available for purchase separately.

# Dishwashers – 24" Fully Integrated



Model	Handle Type	Material	UMRP
<b>G 7766 SCVi</b> Custom Panel	No Handle	12496900	\$2,999

<b>G 7766 SCVi SF</b>	ContourLine Handle*	12496910	\$3,199
-----------------------	---------------------	----------	---------

### Specifications

Width	23 9/16 in (598 mm)
Height	33 11/16 – 36 1/4 in (855 – 920 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	121 lbs (55 kg)
Annual Energy Usage	230 kWh
Decibel rating	39 dBA (37 Extra Quiet Program)

### Features

- Controls – DirectSensor, hidden
- EcoPower Technology
- 3D MultiFlex Cutlery Tray
- BrilliantLight
- AutoOpen Drying
- SensorDry
- No. of Standard Place Settings – 16
- AutoDosing with PowerDisk®
- Basket Design – MaxiComfort
- Double Waterproof System
- Miele@home/AutoStart
- AutoSensor / Load Sensor
- Water Softener

### Programs

- Normal
- QuickIntenseWash
- Pots & Pans
- SaniWash
- Rinse & Hold
- China & Crystal
- Clean Machine
- Economy
- Energy Saver
- Extra Quiet – 37 dBA
- Filters
- SensorWash

### Options

- Express
- FlexiTimer
- Extra Economical
- Extra Clean
- Extra Dry
- Intense Zone
- Delay Start

### Optional Accessories Vi

Material	UMRP
GFVi 701/72 Fully Integrated Panel Full Size, Clean Touch Steel™, 6" Toe-Kick, no handle	10986740 \$379
GFVi 701/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, no handle	12670600 \$379
GFVi 710/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, PureLine handle	12074350 \$489
GFVi 711/72 Fully Integrated Panel Full Size, Clean Touch Steel™, 6" Toe-Kick, ContourLine handle	12074400 \$489
GFVi 711/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, ContourLine handle	12074450 \$489
GFVi 712/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, Range Panel	12074470 \$489
GFVi 709/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, Pocket handle	12672750 \$489

\*Handle not included in the UMRP – available for purchase separately.

# Dishwashers – 24" Fully Integrated Knock2Open



Model	Handle Type	Material	UMRP
<b>G 7791 SCVi K2O ADA</b>	No Handle	12496920	\$3,499

### Specifications

Width	23 9/16 in (598 mm)
Height	32 1/16 – 34 1/4 in (814 – 870 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	121 lbs (55 kg)
Annual Energy Usage	230 kWh
Decibel rating	39 dBA (37 Extra Quiet Program)
ADA Compliant	Yes

### Features

- Controls – DirectSensor, hidden
- EcoPower Technology
- 3D MultiFlex Cutlery Tray
- BrilliantLight
- AutoOpen Drying
- SensorDry
- No. of Standard Place Settings – 16
- AutoDosing with PowerDisk®
- Basket Design – MaxiComfort
- Double Waterproof System
- Miele@home/AutoStart
- Knock2Open
- AutoSensor / Load Sensor
- Water Softener

### Programs

- Normal
- QuickIntenseWash
- Pots & Pans
- SaniWash
- Rinse & Hold
- Filters
- China & Crystal
- Clean Machine
- Economy
- Extra Quiet – 37 dBA
- Energy Saver
- SensorWash

### Options

- Express
- FlexiTimer
- Extra Economical
- Extra Clean
- Extra Dry
- Intense Zone
- Delay Start

### Optional Accessories

Material	UMRP
GFVi 701/72 Fully Integrated Panel Full Size, Clean Touch Steel™, 6" Toe-Kick, no handle	12670590 \$379

# Dishwashers – 24" Integrated



Model	Handle Type	Material	UMRP
<b>G 7936 SCi</b> Custom Panel	No Handle	12496970	\$3,999

Specifications	
Width	23 9/16 in (598 mm)
Height	33 11/16 – 36 1/4 in (855 – 920 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	121 lbs (55 kg)
Annual Energy Usage	230 kWh
Decibel rating	39 dBA (37 Extra Quiet Program)

- Features**
- Controls – M Touch, front
  - EcoPower Technology
  - 3D MultiFlex Cutlery Tray
  - BrilliantLight
  - AutoOpen Drying
  - SensorDry
  - No. of Standard Place Settings – 16
  - AutoDosing with PowerDisk®
  - Basket Design – MaxiComfort
  - Double Waterproof System
  - Miele@home/AutoStart
  - AutoSensor / Load Sensor
  - Water Softener

- Programs**
- Normal
  - QuickIntenseWash
  - Pots & Pans
  - SaniWash
  - Rinse & Hold
  - China & Crystal
  - Economy
  - Energy Saver
  - Extra Quiet – 37 dBA
  - Tall Items
  - Filters
  - Glass – No Rinse Aid (Warm)
  - Clean Machine
  - SensorWash

- Options**
- Express
  - FlexiTimer
  - Extra Economical
  - Extra Clean
  - Extra Dry
  - Intense Zone
  - Soak
  - Pre-Rinse
  - Delay Start

# Dishwashers – 24" Fully Integrated Knock2Open



Model	Handle Type	Material	UMRP
<b>G 7986 SCVi K2O</b> Custom Panel	No Handle	12496980	\$4,099

Specifications	
Width	23 9/16 in (598 mm)
Height	33 11/16 – 36 1/4 in (855 – 920 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	121 lbs (55 kg)
Annual Energy Usage	230 kWh
Decibel rating	39 dBA (37 Extra Quiet Program)
ADA Compliant	No

- Features**
- Controls – M Touch, hidden
  - EcoPower Technology
  - 3D MultiFlex Cutlery Tray
  - BrilliantLight
  - AutoOpen Drying
  - SensorDry
  - No. of Standard Place Settings – 16
  - AutoDosing with PowerDisk®
  - Basket Design – MaxiComfort
  - Double Waterproof System
  - Miele@home/AutoStart
  - Knock2Open
  - AutoSensor / Load Sensor
  - Water Softener

- Programs**
- Normal
  - QuickIntenseWash
  - Pots & Pans
  - SaniWash
  - Rinse & Hold
  - China & Crystal
  - Economy
  - Extra Quiet – 37 dBA
  - Filters
  - Glass – No Rinse Aid (Warm)
  - Clean Machine
  - Energy Saver
  - Tall Items
  - SensorWash

- Options**
- Express
  - FlexiTimer
  - Extra Economical
  - Extra Clean
  - Extra Dry
  - Intense Zone
  - Soak
  - Pre-Rinse
  - Delay Start

Optional Accessories Vi	Material	UMRP
GFVi 701/72 Fully Integrated Panel Full Size, Clean Touch Steel™, 6" Toe-Kick, no handle	12670590	\$379
GFVi 701/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, no handle	12670600	\$379
GFVi 710/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, PureLine handle	12074350	\$489
GFVi 711/72 Fully Integrated Panel Full Size, Clean Touch Steel™, 6" Toe-Kick, ContourLine handle	12074400	\$489
GFVi 711/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, ContourLine handle	12074450	\$489
GFVi 712/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, Range Panel	12074470	\$489
GFVi 709/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, Pocket handle	12672750	\$489

## Dishwashers – 18" SlimLine Fully Integrated

G 5482 SCVi



Model	Handle Type	Material	UMRP
<b>G 5482 SCVi</b> Custom Panel	No Handle	11636760	\$1,699

Specifications	
Width	17 5/8 in (448 mm)
Height	32 1/16 – 34 1/4 in (814 – 880 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	121 lbs (55 kg)
Annual Energy Usage	230 kWh
Decibel rating	44 dBA
ADA Compliant	Yes

- Features**
- Controls – DirectSelect, hidden
  - EcoPower Technology
  - Original Cutlery Tray
  - Basket Design – Comfort
  - No. of Standard Place Settings – 10
  - Double Waterproof System
  - AutoSensor / Load Sensor

- Programs**
- Normal
  - QuickIntenseWash
  - Pots & Pans
  - SaniWash
  - Rinse & Hold

- Options**
- Express
  - Extra Clean

Optional Accessories	Material	UMRP
GFVi 706/77 SlimLine Clean Touch Steel™ panel without Handle, 4" Toe-Kick	11573740	\$319
GFVi 453/72 7 SlimLine Clean Touch Steel™ panel without Handle, 6" Toe-Kick	12670470	\$319
GFVi 453/77 7 SlimLine Clean Touch Steel™ panel without Handle, 4" Toe-Kick	12670480	\$319

## Dishwashers – 18" SlimLine Fully Integrated

G 5892 SCVi



Model	Handle Type	Material	UMRP
<b>G 5892 SCVi</b> Custom Panel	No Handle	11636790	\$2,699

Specifications	
Width	17 5/8 in (448 mm)
Height	32 1/16 – 34 1/4 in (814 – 880 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	107 lbs (48.5kg)
Annual Energy Usage	200 kWh
Decibel rating	42 dBA
ADA Compliant	Yes

- Features**
- Controls – DirectSelect, hidden
  - EcoPower Technology
  - 3D MultiFlex Cutlery Tray
  - BrilliantLight
  - AutoOpen Drying
  - No. of Standard Place Settings – 10
  - SensorDry
  - Basket Design – MaxiComfort
  - Double Waterproof System
  - Miele@home/AutoStart
  - AutoSensor / Load Sensor
  - Water Softener

- Programs**
- Normal
  - QuickIntenseWash
  - Pots & Pans
  - SaniWash
  - Rinse & Hold
  - China & Crystal
  - Economy
  - Energy Saver
  - Extra Quiet – 40 dBA
  - Filters
  - Clean Machine
  - SensorWash

- Options**
- Express
  - Extra Clean
  - Extra Dry
  - Intense Zone

# Product Highlights – Professional for the Home Dishwashers

## ProfiLine

With their impressively short cycle times, ProfiLine Dishwashers are 2.5x faster than domestic dishwashers with only a 24-minute cycle time.

Feature	Description (see specific models for details)
<b>Exemplary Hygiene</b>	Special 'SaniWash' program achieve temperatures of 180°F / 82°C. Final rinse temperatures for selected programs can also be increased for even greater hygiene.
<b>12,500 Program Cycles</b>	ProfiLine dishwashers are tested under laboratory conditions to ensure that they last 12,500 typical cycles and are designed for up to 5 cycles per day.
<b>Intuitive Operation</b>	All programs use intuitive sensor controls. Self-explanatory symbols and key content in plain text speed up program selection and avoid operating errors.
<b>Versatile Baskets</b>	For simple loading and a large volume of dishware ProfiLine represents the perfect stepping stone into the world of commercial dish care.
<b>Golden Virus Seal</b>	All Miele dishwashers remove more than 99.9% of all viruses.*

## MasterLine

Intelligent dishwashing technology and a powerful heater pump ensure optimum program durations and cleaning results.

Feature	Description (see specific models for details)
<b>Plastic Baskets on two levels</b>	Plastic baskets can be used on two levels in dishwasher models PFD 401, PFD 404 and PFD 408. Three spray arms allow perfect cleaning results to be achieved on both washing levels.
<b>Connection for Dispenser Module</b>	To simplify the use of liquid detergents and rinse aid, up to 2 liquid dispensing modules can be optionally connected, in the PFD 401, PFD 404 and PFD 408 dishwashers.
<b>Perfect GlassCare</b>	Miele Professional dishwashers use Perfect GlassCare in the glasses program. This technology adjusts the water hardness precisely so that all the glasses are thoroughly but gently cleaned.
<b>NSF/ANSI 3 Certified for Sanitization</b>	For facilities that require a NSF/ANSI 3 certified dishwasher, the PFD 408 features a final rinse temperature of 185°F with a 1 minute holding time.



### Certified Hygiene Seal

\*Approved by Rhein-Waal University. This certification attests that all G 5000 and G 7000 dishwashers with the SaniWash or Pots & Pans program offer particularly hygienic cleaning. This applies both with (standard) detergent or even without cleaning agent altogether.



### Golden Virus Seal

\*According to the InFluenc\_H – Institute for Integrative Hygiene and Virology, cleaning with ProfiLine dishwashers using Miele's ProCare Shine 12 G/C cleaning agents removes enveloped and non-enveloped viruses (e.g. coronavirus, influenza, or noroviruses) in the Pots & Pans and Sanitize programs, as well as enveloped viruses (excluding Hepatitis B) in the QuickIntenseWash and Universal programs, even if load items are difficult to reprocess.

# Dishwashers – 24" Dishwasher Pre-Finished



Model	Handle Type	Material	MAP/Retail
<b>PFD 101U</b>	Integrated Handle	11605420	\$4,260 / \$4,360

## Specifications

Width	23 9/16 in (598 mm)
Height	31 11/16 – 34 1/4 in (805 – 870 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	113 lbs (51 kg)
Decibel Rating	48 dBA
ADA Compliant	Yes
Electrical Configuration	AC 120V 60 Hz, 15A
Plug	NEMA 5-15P

## Features

- Ideal for Offices, Showrooms, Active Kitchens and Private Homes
- Original Cutlery Basket
- ExtraComfort Basket Design
- No of Standard Place Settings – 13
- Up to 5 Wash Cycles per Day
- AutoOpen Assisted Drying
- Integrated Water Softener
- WiFiConn@ct
- Tested for 12,500 Program Cycles
- Final Rinse Temperature Up to 180°F (82°C) with a Holding Time of 15 Seconds
- Shortest Cycle with Hot Water Connection – 52 min.

## Programs

- QuickIntenseWash
- Universal
- Pots & Pans
- Plastic
- China & Crystal
- SaniWash
- Rinse & Hold
- ECO

## Dishwashers – 24" Dishwasher Integrated

PFD 102i 120V



Model	Handle Type	Material	MAP/Retail
<b>PFD 102i 120V</b>	Integrated Handle	11605430	\$5,245 / \$5,345

### Specifications

Width	23 9/16 in (598 mm)
Height	31 11/16 – 34 1/4 in (805 – 870 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	109 lbs (49 kg)
Decibel Rating	48 dBA
ADA Compliant	Yes
Electrical Configuration	AC 120V 60 Hz, 15A
Plug	NEMA 5-15P

### Features

- Ideal for Offices, Showrooms, Active Kitchens and Private Homes
- Original Cutlery Basket
- ExtraComfort Basket Design
- No of Standard Place Settings – 13
- Up to 5 Wash Cycles per Day
- AutoOpen Assisted Drying
- Integrated Water Softener
- WiFiConn@ct
- BrilliantLight Interior Lighting
- Tested for 12,500 Program Cycles
- Final Rinse Temperature Up to 180°F (82°C) with a Holding Time of 15 Seconds
- Shortest Cycle with Hot Water Connection – 52 min.

### Programs

- QuickIntenseWash
- Universal
- Pots & Pans
- Plastic
- China & Crystal
- SaniWash
- Rinse & Hold
- ECO

### Optional Accessories

Material	MAP/Retail
GFV 60/60-7 Integrated Panel Full Size, Clean Touch Steel™, 6" Toe-Kick, no handle	\$319 / \$369
GFV 60/65-7 Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, no handle	\$319 / \$369

## Dishwashers – 24" Dishwasher Integrated

PFD 102i 208/240V



Model	Handle Type	Material	MAP/Retail
<b>PFD 102i 208/240V</b>	Integrated Handle	11605500	\$5,245 / \$5,345

### Specifications

Width	23 9/16 in (598 mm)
Height	31 11/16 – 34 1/4 in (805 – 870 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	109 lbs (49 kg)
Decibel Rating	48 dBA
ADA Compliant	Yes
Electrical Configuration	2N AC 120/208-240V, 60 Hz, 2x30A
Plug	NEMA 14-30P

### Features

- Ideal for Offices, Showrooms, Active Kitchens and Private Homes
- Original Cutlery Basket
- ExtraComfort Basket Design
- No of Standard Place Settings – 13
- Up to 5 Wash Cycles per Day
- AutoOpen Assisted Drying
- Integrated Water Softener
- WiFiConn@ct
- BrilliantLight Interior Lighting
- Tested for 12,500 Program Cycles
- Final Rinse Temperature Up to 180°F (82°C) with a Holding Time of 15 Seconds
- Shortest Cycle with Hot Water Connection – 24 min.

### Programs

- QuickIntenseWash
- Universal
- Pots & Pans
- Plastic
- China & Crystal
- SaniWash
- Rinse & Hold
- ECO

### Optional Accessories

Material	MAP/Retail
GFV 60/60-7 Integrated Panel Full Size, Clean Touch Steel™, 6" Toe-Kick, no handle	\$319 / \$369
GFV 60/65-7 Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, no handle	\$319 / \$369

# Dishwashers – 24" Dishwasher Integrated

PFD 104 SCVi 120V



Model	Handle Type	Material	MAP/Retail
<b>PFD 104 SCVi 120V</b>	No Handle	11605450	\$6,100 / \$6,200

### Specifications

Width	23 9/16 in (598 mm)
Height	33 1/4 – 35 13/16 in (845 – 910 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	128 lbs (58 kg)
Decibel Rating	45 dBA
ADA Compliant	No
Electrical Configuration	AC 120V 60 Hz, 15A
Plug	NEMA 5-15P

### Features

- Ideal for Offices, Showrooms, Active Kitchens and Private Homes
- 3D MultiFlex Cutlery Tray
- MaxiComfort Basket Design with 3D MultiFlex Drawer
- No of Standard Place Settings – 16
- Up to 5 Wash Cycles per Day
- AutoOpen Assisted Drying
- Integrated Water Softener
- WiFiConn@ct
- BrilliantLight Interior Lighting
- Knock2open
- AutoOpen and AutoClose
- Tested for 12,500 Program Cycles
- Final Rinse Temperature Up to 180°F (82°C) with a Holding Time of 15 Seconds
- Shortest Cycle with Hot Water Connection – 52 min.

### Programs

- |                    |                   |
|--------------------|-------------------|
| • QuickIntenseWash | • China & Crystal |
| • Universal        | • SaniWash        |
| • Pots & Pans      | • Rinse & Hold    |
| • Plastic          | • ECO             |

Optional Accessories	Material	MAP/Retail
GFVi 701/72 Fully Integrated Panel Full Size, Clean Touch Steel™, 6" Toe-Kick, no handle	12670590	\$379 / \$429
GFVi 701/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, no handle	12670600	\$379 / \$429
GFVi 710/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, PureLine handle	12074350	\$489 / \$539
GFVi 711/72 Fully Integrated Panel Full Size, Clean Touch Steel™, 6" Toe-Kick, ContourLine handle	12074400	\$489 / \$539
GFVi 711/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, ContourLine handle	12074450	\$489 / \$539
GFVi 712/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, Range Panel	12074470	\$489 / \$539
GFVi 709/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, Pocket handle	12672750	\$489 / \$539

# Dishwashers – 24" Dishwasher Integrated

PFD 104 SCVi 208/240V



Model	Handle Type	Material	MAP/Retail
<b>PFD 104 SCVi 208/240V</b>	No Handle	11605520	\$6,100 / \$6,200

### Specifications

Width	23 9/16 in (598 mm)
Height	33 1/4 – 35 13/16 in (845 – 910 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	128 lbs (58 kg)
Decibel Rating	45 dBA
ADA Compliant	No
Electrical Configuration	2N AC 120/208-240V, 60 Hz, 2x30A
Plug	NEMA 14-30P

### Features

- Ideal for Offices, Showrooms, Active Kitchens and Private Homes
- 3D MultiFlex Cutlery Tray
- MaxiComfort Basket Design with 3D MultiFlex Drawer
- No of Standard Place Settings – 16
- Up to 5 Wash Cycles per Day
- AutoOpen Assisted Drying
- Integrated Water Softener
- WiFiConn@ct
- BrilliantLight Interior Lighting
- Knock2open
- AutoOpen and AutoClose
- Tested for 12,500 Program Cycles
- Final Rinse Temperature Up to 180°F (82°C) with a Holding Time of 15 Seconds
- Shortest Cycle with Hot Water Connection – 24 min.

### Programs

- |                    |                   |
|--------------------|-------------------|
| • QuickIntenseWash | • China & Crystal |
| • Universal        | • SaniWash        |
| • Pots & Pans      | • Rinse & Hold    |
| • Plastic          | • ECO             |

Optional Accessories	Material	MAP/Retail
GFVi 701/72 Fully Integrated Panel Full Size, Clean Touch Steel™, 6" Toe-Kick, no handle	12670590	\$379 / \$429
GFVi 701/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, no handle	12670600	\$379 / \$429
GFVi 710/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, PureLine handle	12074350	\$489 / \$539
GFVi 711/72 Fully Integrated Panel Full Size, Clean Touch Steel™, 6" Toe-Kick, ContourLine handle	12074400	\$489 / \$539
GFVi 711/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, ContourLine handle	12074450	\$489 / \$539
GFVi 712/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, Range Panel	12074470	\$489 / \$539
GFVi 709/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, Pocket handle	12672750	\$489 / \$539

# Dishwashers – 24" Dishwasher Pre-Finished

PFD 401 208V



Model	Handle Type	Material	MAP/Retail
<b>PFD 401 208V</b>	Integrated Handle	12066560	\$7,245 / \$7,445

### Specifications

Width	23 9/16 in (598 mm)
Height	32 1/4 in (820 mm)
Depth	22 13/16 in (580 mm)
Shipping Weight	164.5 lbs (74.5 kg)
Decibel Rating	59 dBA
ADA Compliant	Yes
Electrical Configuration	2AC 208V, 60 Hz, 2x30A
Plug	NEMA L6-30

### Features

- Suitable for Offices, Active Kitchens, Private Homes, Restaurants, Bars etc.
- Large Variety of Baskets and Inserts, Including Commercial Plastic Baskets
- Integrated Water Softener
- Large Capacity and Multi-Level Cleaning for High Throughput
- Connection for Dispenser Modules
- Tested for Up to 40 Cycles per Day
- Tested for at Least 28,000 Operating Hours (10 years)
- Final Rinse Temperature Up to 158°F (70°C) with a Holding Time of 10 min.
- Shortest Cycle Time – 6 min.

### Programs

- |                   |                |
|-------------------|----------------|
| • Rapid           | • Utensils     |
| • Normal          | • Plastic      |
| • Normal plus     | • Economy      |
| • Intensive       | • Reactivation |
| • SaniWash        | • Rinse & Hold |
| • China & Crystal | • Drain        |
| • Glasses         |                |

Included Accessories	Material	MAP/Retail
----------------------	----------	------------

1 x APFD 215 Upper Basket for Cups (Height Adjustable)	12106020	\$255
1 x APFD 220 Lower Basket for Inserts	12107590	\$165
1 x APFD 415 Insert for Dessert Plates	12106030	\$70
2 x E 816 Inserts for Plates	12611640	\$60
2 x APFD 420 Inserts for Cutlery	12118550	\$65

**Optional Accessories** – See pages 30-31.

# Dishwashers – 24" Dishwasher Pre-Finished

PFD 401



Model	Handle Type	Material	MAP/Retail
<b>PFD 401 Stainless Steel 240V</b>	Integrated Handle	12066590	\$7,245 / \$7,445

### Specifications

Width	23 9/16 in (598 mm)
Height	32 1/4 in (820 mm)
Depth	22 13/16 in (580 mm)
Shipping Weight	164.5 lbs (74.5 kg)
Decibel Rating	59 dBA
ADA Compliant	Yes
Electrical Configuration	2AC 240V, 60 Hz, 2x30A
Plug	NEMA L6-30

### Features

- Suitable for Offices, Active Kitchens, Private Homes, Restaurants, Bars etc.
- Large Variety of Baskets and Inserts, Including Commercial Plastic Baskets
- Integrated Water Softener
- Large Capacity and Multi-Level Cleaning for High Throughput
- Connection for Dispenser Modules
- Tested for Up to 40 Cycles per Day
- Tested for at Least 28,000 Operating Hours (10 years)
- Final Rinse Temperature Up to 158°F (70°C) with a Holding Time of 10 min.
- Shortest Cycle Time – 6 min.

### Programs

- |                   |                |
|-------------------|----------------|
| • Rapid           | • Utensils     |
| • Normal          | • Plastic      |
| • Normal plus     | • Economy      |
| • Intensive       | • Reactivation |
| • SaniWash        | • Rinse & Hold |
| • China & Crystal | • Drain        |
| • Glasses         |                |

Included Accessories	Material	MAP/Retail
----------------------	----------	------------

1 x APFD 215 Upper Basket for Cups (Height Adjustable)	12106020	\$255
1 x APFD 220 Lower Basket for Inserts	12107590	\$165
1 x APFD 415 Insert for Dessert Plates	12106030	\$70
2 x E 816 Inserts for Plates	12611640	\$60
2 x APFD 420 Inserts for Cutlery	12118550	\$65

**Optional Accessories** – See pages 30-31.

# Dishwashers – 24" Dishwasher Pre-Finished

PFD 404 208V



Model	Handle Type	Material	MAP/Retail
<b>PFD 404 208V</b>	Integrated Handle	12066570	\$7,730 / \$7,930

### Specifications

Width	23 9/16 in (598 mm)
Height	32 1/4 in (820 mm)
Depth	22 13/16 in (580 mm)
Shipping Weight	164.5 lbs (74.5 kg)
Decibel Rating	59 dBA
ADA Compliant	Yes
Electrical Configuration	2AC 208V, 60 Hz, 2x30A
Plug	NEMA L6-30

### Features

- Suitable for Offices, Active Kitchens, Private Homes, Restaurants, Bars etc.
- Large Variety of Baskets and Inserts, Including Commercial Plastic Baskets
- Integrated Water Softener
- Large Capacity and Multi-Level Cleaning for High Throughput
- Connection for Dispenser Modules
- Tested for Up to 40 Cycles per Day
- Tested for at Least 28,000 Operating Hours (10 years)
- Final Rinse Temperature Up to 185°F (85°C) with a Holding Time of 4 min.
- Shortest Cycle Time – 6 min.

### Programs

- |               |                   |
|---------------|-------------------|
| • Rapid       | • China & Crystal |
| • Normal      | • Glasses         |
| • Normal plus | • Utensils        |
| • Intensive   | • Plastic         |
| • SaniWash    | • SaniWash Plus   |

Included Accessories	Material	MAP/Retail
----------------------	----------	------------

1 x APFD 215 Upper Basket for Cups (Height Adjustable)	12106020	\$255
1 x APFD 220 Lower Basket for Inserts	12107590	\$165
1 x APFD 415 Insert for Dessert Plates	12106030	\$70
2 x E 816 Inserts for Plates	12611640	\$70
2 x APFD 420 Inserts for Cutlery	12118550	\$65

**Optional Accessories** – See pages 30-31.

# Dishwashers – 24" Dishwasher Pre-Finished

PFD 404 240V



Model	Handle Type	Material	MAP/Retail
<b>PFD 404 240V</b>	Integrated Handle	12066600	\$7,730 / \$7,930

### Specifications

Width	23 9/16 in (598 mm)
Height	32 1/4 in (820 mm)
Depth	22 13/16 in (580 mm)
Shipping Weight	164.5 lbs (74.5 kg)
Decibel Rating	59 dBA
ADA Compliant	Yes
Electrical Configuration	2AC 240V, 60 Hz, 2x30A
Plug	NEMA L6-30

### Features

- Suitable for Offices, Active Kitchens, Private Homes, Restaurants, Bars etc.
- Large Variety of Baskets and Inserts, Including Commercial Plastic Baskets
- Integrated Water Softener
- Large Capacity and Multi-Level Cleaning for High Throughput
- Connection for Dispenser Modules
- Tested for Up to 40 Cycles per Day
- Tested for at Least 28,000 Operating Hours (10 years)
- Final Rinse Temperature Up to 185°F (85°C) with a Holding Time of 4 min.
- Shortest Cycle Time – 6 min.

### Programs

- |                   |                 |
|-------------------|-----------------|
| • Rapid           | • Glasses       |
| • Normal          | • Utensils      |
| • Normal plus     | • Plastic       |
| • Intensive       | • Economy       |
| • SaniWash        | • SaniWash Plus |
| • China & Crystal |                 |

Included Accessories	Material	MAP/Retail
----------------------	----------	------------

1 x APFD 215 Upper Basket for Cups (Height Adjustable)	12106020	\$255
1 x APFD 220 Lower Basket for Inserts	12107590	\$165
1 x APFD 415 Insert for Dessert Plates	12106030	\$70
2 x E 816 Inserts for Plates	12611640	\$70
2 x APFD 420 Inserts for Cutlery	12118550	\$65

**Optional Accessories** – See pages 30-31.

## Dishwashers – 24" Dishwasher Pre-Finished

PFD 408 208V



Model	Handle Type	Material	MAP/Retail	Included Accessories	Material	MAP/Retail
<b>PFD 408 208V*</b>	Integrated Handle	12066580	\$8,455 / \$8,655	1 x APFD 215 Upper Basket for Cups (Height Adjustable)	12106020	\$255
<b>Specifications</b>				1 x APFD 220 Lower Basket for Inserts	12107590	\$165
Width	23 9/16 in (598 mm)			1 x APFD 415 Insert for Dessert Plates	12106030	\$70
Height	32 1/4 in (820 mm)			2 x E 816 Inserts for Plates	12611640	\$70
Depth	23 7/16 in (595 mm)			2 x APFD 420 Inserts for Cutlery	12118550	\$65
Shipping Weight	187 lbs (84.5 kg)			<b>Optional Accessories</b> – See pages 30-31.		
Decibel Rating	57 dBA					
ADA Compliant	Yes					
NSF/ANSI 3	Yes					
Electrical Configuration*	3AC 208V, 60 Hz, 3x20A					
Plug	NEMA L15-20					

### Features

- Suitable for Customers That Require a NSF 3 Classified Dishwasher like Pre-Schools, Assisted Living, Medical Offices etc.
- Large Variety of Baskets and Inserts, Including Commercial Plastic Baskets
- Up to 40 Wash Cycles per Day
- Integrated Water Softener
- Large Capacity and Multi-Level Cleaning
- Connection for Dispenser Modules
- Tested for at least 28,000 operating hours (10 years)
- Final Rinse Temperature Up to 185°F (85°C) with a Holding Time of 1 min.
- Shortest Cycle Time – 15 min.

### Programs

- |               |                |
|---------------|----------------|
| • Normal      | • Reactivation |
| • Normal plus | • Rinse & Hold |
| • Intensive   | • Drain        |

\*Special order product – Contact [prosales@mieleusa.com](mailto:prosales@mieleusa.com)  
 \*Option to convert unit to 2 AC 208V, 60 Hz, 2x30A with NEMA L6-30 plug. Conversion must take place before delivery. A special order must be placed to [prosales@mieleusa.com](mailto:prosales@mieleusa.com) (MATERIAL 94001810 / UMRP \$355).

## Dishwashers – 24" Dishwasher Pre-Finished

PFD 408



Model	Handle Type	Material	MAP/Retail	Included Accessories	Material	MAP/Retail
<b>PFD 408 Stainless Steel 240V*</b>	Integrated Handle	12066610	\$8,455 / \$8,655	1 x APFD 215 Upper Basket for Cups (Height Adjustable)	12106020	\$255
<b>Specifications</b>				1 x APFD 220 Lower Basket for Inserts	12107590	\$165
Width	23 9/16 in (598 mm)			1 x APFD 415 Insert for Dessert Plates	12106030	\$70
Height	32 1/4 in (820 mm)			2 x E 816 Inserts for Plates	12611640	\$70
Depth	23 7/16 in (595 mm)			2 x APFD 420 Inserts for Cutlery	12118550	\$65
Shipping Weight	187 lbs (84.5 kg)			<b>Optional Accessories</b> – See pages 30-31.		
Decibel Rating	57 dBA					
ADA Compliant	Yes					
NSF/ANSI 3	Yes					
Electrical Configuration*	3AC 240V, 60 Hz, 3x20A					
Plug	NEMA L15-20					

### Features

- Suitable for Customers That Require a NSF 3 Classified Dishwasher like Pre-Schools, Assisted Living, Medical Offices etc.
- Large Variety of Baskets and Inserts, Including Commercial Plastic Baskets
- Up to 40 Wash Cycles per Day
- Integrated Water Softener
- Large Capacity and Multi-Level Cleaning
- Tested for at least 28,000 operating hours (10 years)
- Final Rinse Temperature Up to 185°F (85°C) with a Holding Time of 1 min.
- Shortest Cycle Time – 15 min.

### Programs

- |               |                |
|---------------|----------------|
| • Normal      | • Reactivation |
| • Normal plus | • Rinse & Hold |
| • Intensive   | • Drain        |

\*Special order product – Contact [prosales@mieleusa.com](mailto:prosales@mieleusa.com)  
 \*Option to convert unit to 2 AC 208V, 60 Hz, 2x30A with NEMA L6-30 plug. Conversion must take place before delivery. A special order must be placed to [prosales@mieleusa.com](mailto:prosales@mieleusa.com) (MATERIAL 94001810 / UMRP \$355).



# Product Highlights – Washers & Dryers

## Washing Machines

Feature	Description (see specific models for details)
<b>Honeycomb Drum</b>	The Honeycomb drum has a special sculptured surface which allows fabrics to glide on a thin cushion of water.
<b>TwinDos</b>	Liquid detergent automatic dispensing system for achieving the best wash results. Save up to 30% detergent compared to manual dispensing.
<b>IntenseWash</b>	IntenseWash offers the highest level of cleaning, with Spin&Spray technology using less water and heating energy.
<b>QuickIntenseWash</b>	Utilizing the IntenseWash technology, the QuickIntenseWash program provides excellent cleanliness in just 49 minutes.
<b>SingleWash</b>	An efficient solution for washing single garments quickly, while saving water and energy.
<b>CapDosing</b>	Dispense special detergent for different types of fabric by placing a portioned capsule into the fabric softener compartment.
<b>Certified Hygiene Seal</b>	All Miele W1 Washing Machines remove more than 99.99% of specific bacteria.*
<b>Golden Virus Seal</b>	WXI 860 WCS and WXR 860 WCS Miele Washing Machines remove more than 99.9% of all viruses.*

## Dryers

Feature	Description (see specific models for details)
<b>Honeycomb Drum</b>	Fewer creases and easier ironing, the honeycomb structure allows laundry to be dried gently and evenly.
<b>Heat-Pump Technology</b>	Saving up to 60% in energy consumption, the heat generated is reused and low temperatures protect the high-quality fibers in the most delicate fabrics.
<b>FragranceDos and FragranceDos<sup>2</sup></b>	Miele fragrance flacons add your favorite scent to your laundry during the drying process. With FragranceDos <sup>2</sup> , you can insert two flacons into the machine at once to switch between your two favorite fragrances.
<b>SteamFinish</b>	A great alternative to ironing, steam and smooth your laundry during the drying process.
<b>PerfectDry</b>	PerfectDry takes the mineral content of your water into account and modifies the drying process accordingly



### Certified Hygiene Seal

\*Approved by Rhein-Waal University. This certification attests that all G 5000 and G 7000 dishwashers with the SaniWash or Pots & Pans program offer particularly hygienic cleaning. This applies both with (standard) detergent or even without cleaning agent altogether.



### Golden Virus Seal

\*According to the InFluenc\_H – Institute for Integrative Hygiene and Virology, cleaning with ProfiLine dishwashers using Miele's ProCare Shine 12 GC cleaning agents removes enveloped and non-enveloped viruses (e.g. coronavirus, influenza, or noroviruses) in the Pots & Pans and Sanitize programs, as well as enveloped viruses (excluding Hepatitis B) in the QuickIntenseWash and Universal programs, even if load items are difficult to reprocess.

# Washing Machines – W1

WXD 160 WCS



Model	Material	UMRP	Matching Dryers	Material	UMRP
<b>WXD 160 WCS</b>	11614070	\$1,999	TXD 160 WP	11619650	
Specifications			Accessories		
Overall Width	23 1/2 in (596 mm)		WTV 502 (Stacking Kit)	9256140	\$129
Overall Height	33 1/2 in (850 mm)		WTV 512 (Stacking Kit w/ Drawer 4 5/8" H)	9351790	\$299
Overall Depth	25 5/16 in (643 mm)		WTS 610 (Pedestal 13 7/8" H)	12349900	\$649
Shipping weight	221 lbs (100 kg)		Adaptor NEMA 14-30*	10983750	\$79
Capacity	17.6 lbs. / 2.26 cu. ft.				
Electrical Connection	120V, 15A				

### Features

- DirectSensor user interface
- HoneyComb drum
- 11 Wash Programs including SoftSteam option
- WiFiConn@ct and Mobile Control
- CapDosing
- Add Laundry Feature
- White door ring
- 1600 rpm max spin speed

### Wash Programs

- Darks/Denims
- Express
- Handwash
- Delicates
- Proofing
- Dress Shirts
- Outdoor
- Drain/Spin
- Normal
- Extra White
- Sanitize

### Wash Options

- SoftSteam
- Buzzer

\*A NEMA 14-30 adapter is required for any installation connected to a 208/240V household electrical supply.

# Washing Machines – W1



Model	Material	UMRP
WWD 160 WCS	11614040	\$1,999

Specifications	
Overall Width	23 1/2 in (596 mm)
Overall Height	33 1/2 in (850 mm)
Overall Depth	25 5/16 in (643 mm)
Shipping weight	221 lbs (100 kg)
Capacity	17.6 lbs. / 2.26 cu. ft.
Electrical Connection	120V, 15A

### Features

- DirectSensor user interface
- HoneyComb drum
- 11 Wash Programs including SoftSteam option
- WiFiConn@ct and Mobile Control
- CapDosing
- Add Laundry Feature
- Black door ring
- 1600 rpm max spin speed

### Wash Programs

- Darks/Denims
- Express
- Handwash
- Delicates
- Proofing
- Dress Shirts
- Outdoor
- Drain/Spin
- Normal
- Extra White
- Sanitize

### Wash Options

- SoftSteam
- Buzzer

# Washing Machines – W1



Model	Material	UMRP
WWD 660 WCS	11614100	\$2,199

Specifications	
Overall Width	23 1/2 in (596 mm)
Overall Height	33 1/2 in (850 mm)
Overall Depth	25 5/16 in (643 mm)
Shipping weight	221 lbs (100 kg)
Capacity	17.6 lbs. / 2.26 cu. ft.
Electrical Connection	120V, 15A

### Features

- DirectSensor user interface
- HoneyComb drum
- TwinDos automatic detergent dispensing
- 11 Wash Programs including SoftSteam option
- WiFiConn@ct and mobile control
- CapDosing
- Add Laundry Feature
- Black door ring
- 1,600 rpm max spin speed

### Wash Programs

- Darks/Denims
- Express
- Handwash
- Delicates
- Proofing
- Dress Shirts
- Outdoor
- Drain/Spin
- Normal
- Extra White
- Sanitize

### Wash Options

- SoftSteam
- Buzzer
- Soak
- Pre-rinse
- AllergyWash

# Washing Machines – W1



Model	Material	UMRP
<b>WXF 660 WCS</b>	11614130	\$2,399

## Specifications

Overall Width	23 1/2 in (596 mm)
Overall Height	33 1/2 in (850 mm)
Overall Depth	25 5/16 in (643 mm)
Shipping weight	221 lbs (100 kg)
Capacity	17.6 lbs. / 2.26 cu. ft.
Electrical Connection	120V, 15A

## Features

- ComfortSensor user interface
- HoneyComb drum
- TwinDos automatic detergent dispensing
- 20 Wash Programs including SoftSteam option
- WiFiConn@ct and mobile control
- CapDosing
- Add Laundry Feature
- White door ring
- 1600 rpm max spin speed

## Wash Programs

- |                |                       |
|----------------|-----------------------|
| • Darks/Denims | • Wrinkle-free        |
| • Express      | • Silks               |
| • Handwash     | • Towels              |
| • Delicates    | • Sportswear          |
| • Proofing     | • Woolens             |
| • Pillows      | • Table Linens/Drapes |
| • Baby clothes | • Normal              |
| • Quick rinse  | • Extra White         |
| • Dress Shirts | • Sanitize            |
| • Outdoor      | • Downs               |

# Washing Machines – W1



Model	Material	UMRP
<b>WXI 860 WCS</b>	11614140	\$2,599

## Specifications

Overall Width	23 1/2 in (596 mm)
Overall Height	33 1/2 in (850 mm)
Overall Depth	25 5/16 in (643 mm)
Shipping weight	221 lbs (100 kg)
Capacity	17.6 lbs. / 2.26 cu. ft.
Electrical Connection	120V, 15A

## Features

- ComfortSensor user interface
- HoneyComb drum
- TwinDos automatic detergent dispensing
- 21 Wash Programs including SoftSteam option
- QuickIntenseWash and SingleWash option
- WiFiConn@ct and mobile control
- CapDosing
- 1,600 rpm max spin speed
- White door ring

## Wash Programs

- |                |                       |
|----------------|-----------------------|
| • Darks/Denims | • QuickIntenseWash    |
| • Express      | • Silks               |
| • Handwash     | • Towels              |
| • Delicates    | • Sportswear          |
| • Proofing     | • Woolens             |
| • Pillows      | • Table Linens/Drapes |
| • Baby clothes | • Normal              |
| • Quick rinse  | • Extra White         |
| • Dress Shirts | • Sanitize            |
| • Outdoor      | • Downs               |
| • Wrinkle-free |                       |

## Wash Options

• SoftSteam	• Pre-rinse
• Buzzer	• AllergyWash
• Soak	

## Matching Dryers

Model	Material
TXI 680 WP	11619850

## Accessories

Model	Material	UMRP
WTV 502 (Stacking Kit)	9256140	\$129
WTV 512 (Stacking Kit w/ Drawer 4 5/8" H)	9351790	\$299
WTS 610 (Pedestal 13 7/8" H)	12349900	\$649
Adaptor NEMA 14-30*	10983750	\$79

## Wash Options

• SoftSteam	• Pre-rinse
• Buzzer	• AllergyWash
• Soak	• SingleWash

## Matching Dryers

Model	Material
TXI 680 WP	11619850

## Accessories

Model	Material	UMRP
WTV 502 (Stacking Kit)	9256140	\$129
WTV 512 (Stacking Kit w/ Drawer 4 5/8" H)	9351790	\$299
WTS 610 (Pedestal 13 7/8" H)	12349900	\$649
Adaptor NEMA 14-30*	10983750	\$79

# Washing Machines – W1



Model	Material	UMRP
<b>WXR 860 WCS</b>	11613700	\$2,899

Specifications	
Overall Width	23 1/2 in (596 mm)
Overall Height	33 1/2 in (850 mm)
Overall Depth	25 5/16 in (643 mm)
Shipping weight	221 lbs (100 kg)
Capacity	17.6 lbs. / 2.26 cu. ft.
Electrical Connection	120V, 15A

- Features**
- M Touch premium user interface
  - HoneyComb drum
  - TwinDos automatic detergent dispensing
  - 25 Wash Programs including SoftSteam option
  - QuickIntenseWash and SingleWash option
  - CapDosing
  - 1,600 rpm max spin speed
  - White door ring

Wash Programs	
• Express	• QuickIntenseWash
• Handwash	• Silks
• Delicates	• Towels
• Curtains	• Sportswear
• Proofing	• Starch
• Denim	• Woolens
• Pillows	• Table Linens/Drapes
• Baby clothes	• Normal
• Quick rinse	• Extra White
• Sneakers	• Sanitize
• Dress Shirts	• Downs
• Outdoor	• Dark garments
• Wrinkle-free	

# Dryers – T1 Heat Pump



Model	Material	UMRP
<b>TXD 160 WP</b>	11619650	\$1,899

Specifications	
Overall Width	23 1/2 in (596 mm)
Overall Height	33 1/2 in (850 mm)
Overall Depth	25 5/16 in (643 mm)
Shipping weight	137 lbs (62 kg)
Capacity	4.02 cu. ft.
Electrical Connection	120V, 15A

- Features**
- DirectSensor user interface
  - Ventless Heat-Pump Dryer
  - Honeycomb drum
  - PerfectDry moisture sensing technology
  - WiFiConn@ct and Mobile Control
  - FragranceDos
  - EnergyStar Most Efficient

Drying Programs	
• Normal	• Proofing
• Bed linens	• Denim
• Express	• Time dry/DryFresh
• Delicates	• Dress Shirts
• Woolens/Silks	• Outdoor

- Drying Options**
- Anti-Crease
  - Gentle
  - Buzzer

## Dryers – T1 Heat Pump



Model	Material	UMRP
TWD 360 WP	11619730	\$1,999

### Specifications

Overall Width	23 1/2 in (596 mm)
Overall Height	33 1/2 in (850 mm)
Overall Depth	25 5/16 in (643 mm)
Shipping weight	137 lbs (62 kg)
Capacity	4.02 cu. ft.
Electrical Connection	120V, 15A

### Features

- DirectSensor user interface
- Ventless Heat-Pump Dryer
- Honeycomb drum
- PerfectDry moisture sensing technology
- WiFiConn@ct and Mobile Control
- FragranceDos<sup>2</sup>
- Black door ring
- EnergyStar Most Efficient

### Drying Programs

- |                 |                     |
|-----------------|---------------------|
| • Normal        | • Proofing          |
| • Bed linens    | • Denim             |
| • Express       | • Time dry/DryFresh |
| • Delicates     | • Dress Shirts      |
| • Woolens/Silks | • Outdoor           |

### Drying Options

- Anti-Crease
- Gentle
- Buzzer

## Dryers – T1 Heat Pump



Model	Material	UMRP
TXI 680 WP	11619850	\$2,499

### Specifications

Overall Width	23 1/2 in (596 mm)
Overall Height	33 1/2 in (850 mm)
Overall Depth	25 5/16 in (643 mm)
Shipping weight	137 lbs (62 kg)
Capacity	4.02 cu. ft.
Electrical Connection	120V, 15A

### Features

- ComfortSensor user interface
- Ventless Heat-Pump Dryer
- Honeycomb drum
- PerfectDry moisture sensing technology
- 19 Programs including SoftSteam
- FragranceDos<sup>2</sup>
- EnergyStar Most Efficient
- White door ring

### Drying Programs

- |                       |                |
|-----------------------|----------------|
| • Table Linens/Drapes | • Basket       |
| • Normal              | • Cold air     |
| • Bed linens          | • Time dry     |
| • Express             | • DryFresh     |
| • Delicates           | • Dress Shirts |
| • SoftSteam           | • Outdoor      |
| • Woolens/Silks       | • Wrinkle-free |
| • Proofing            | • Sportswear   |
| • Denim               | • Smoothing    |
| • Pillows             |                |

### Drying Options

- |               |              |
|---------------|--------------|
| • Anti-Crease | • Buzzer     |
| • Gentle      | • Freshen Up |

# Dryers – T1 Heat Pump



Model	Material	UMRP
TXR 860 WP	11620030	\$2,899

Specifications	
Overall Width	23 1/2 in (596 mm)
Overall Height	33 1/2 in (850 mm)
Overall Depth	25 5/16 in (643 mm)
Shipping weight	137 lbs (62 kg)
Capacity	4.02 cu. ft.
Electrical Connection	120V, 15A

- Features**
- M Touch premium user interface
  - Ventless Heat-Pump Dryer
  - Honeycomb drum
  - PerfectDry moisture sensing technology
  - 19 Programs including SoftSteam
  - FragranceDos<sup>2</sup>
  - EnergyStar Most Efficient
  - White door ring

Drying Programs	
• Table Linens/Drapes	• Basket
• Normal	• Cold air
• Bed linens	• Time dry
• Express	• DryFresh
• Delicates	• Dress Shirts
• SoftSteam	• Outdoor
• Woolens/Silks	• Wrinkle-free
• Proofing	• Sportswear
• Denim	• Smoothing
• Pillows	

- Drying Options**
- Anti-Crease
  - Gentle
  - Buzzer
  - Freshen Up

# Rotary Ironer



Model	Material	UMRP
B 990 Rotary Ironer	7222730	\$2,699

**Finish**  
Lotus White

Specifications	
Width	38 3/4 in (985 mm)
Height	37 3/4 in (959 mm)
Depth	15 in (380 mm)
Shipping Weight	92.5 lbs (45 kg)
Roller Width	32.5 in
Electrical Connection	120V 15A

- Features**
- 32.5" Wide Roller
  - Three Heating Elements for Optimum Heat Distribution
  - Variable Roller Speed
  - Temperature Selection to Suit Textiles
  - Laundry Feed Board for Easy Laundry Handling
  - Convenient Infeed Board with Ample Storage Space
  - Airing Bar for Crease-Free Cooling
  - Moisture – Absorbing Roller Padding
  - Convenient Folding Mechanism
  - Easily Maneuverable with Four Castors
  - Wide Foot Control Bar
  - Automatic Finger Guard
  - Emergency Release

# Product Highlights – Professional for the Home Laundry

## Washing Machines

Feature	Description <small>(see specific models for details)</small>
<b>Honeycomb Drum</b>	Has a perforated rear panel for fast wetting of laundry. The perforated rear panel Honeycomb Drum combined with high spin speeds supports shorter cycle time without compromising on performance.
<b>Express Wash</b>	Providing excellent cleanliness in just 25 minutes.
<b>Ultimate Convenience</b>	With intuitive M Touch controls, easily select your settings with the swipe of a finger. Choose from 50+ programs – 5 are customizable.
<b>CapDosing</b>	Dispense special detergent for different types of fabric by placing a portioned capsule into the fabric softener compartment.
<b>Professional Grade Laundry for the Home</b>	The Little Giant Washers have a 2.58 ft <sup>3</sup> drum size and provide professional-grade disinfection and fabric care in a high-efficiency, compact system.

## Dryers

Feature	Description <small>(see specific models for details)</small>
<b>Honeycomb Drum</b>	Fewer creases and easier ironing, the honeycomb structure allows laundry to be dried gently and evenly.
<b>Heat-Pump Technology</b>	Saving on energy consumption, the heat generated is reused and low temperatures protect the high-quality fibers in the most delicate fabrics.
<b>Ultimate Convenience</b>	With intuitive M Touch controls, easily select your settings with the swipe of a finger. Choose from 35 programs – 5 are customizable.
<b>PerfectDry</b>	PerfectDry takes the residual moisture level into account and modifies the drying process accordingly.
<b>Powerful Drive System</b>	Two separate motors for a quicker and more efficient drying process with even less creasing.

# Washing Machines – Little Giant Performance Plus

PWM 908 DP, Lotus White



PWM 908 DP, Stainless Steel



Model	Material	Map/Retail
<b>PWM 908 DP</b> Lotus White	11204460	\$6,930 / \$7,130
<b>PWM 908 DP</b> Stainless Steel	11204470	\$7,365 / \$7,565

### Specifications

Width	23 7/16 in (596 mm)
Height	33 7/16 in (850 mm)
Depth	28 1/8 in (714 mm)
Shipping Weight	230 lbs (104 kg)
Front Material (Lotus White Model)	Porcelain Enameled White
Front Material (Stainless Steel Model)	Stainless Steel
Side Panels (both models)	Powder Coated White
Electrical Connection	2 AC 208-240V, 60 Hz, 30 A
Plug	NEMA L6-30
Capacity	2.58 cu.ft – 73 Liter

### Features

- Spin Speed – 1600 rpm
- Detergent Dispenser Drawer, 3 Compartments
- CapDosing
- Possible Connections to Dispensing Pumps – 6
- M Touch Flex User Interface (No Buttons or Dials)
- 49-minute Cotton 140°F Program (with Hot Water Connection)
- 25-minute Express Wash Cycle
- 50+ Programs – 5 Customizable
- High Temperature Disinfection Programs (up to 200°F)
- Bearing Designed for 30,000 Operating Hours
- Stackable or Side-by-Side Configuration – 3D Imbalance Monitoring
- Commercial Soft-Mounted
- HoneyComb Drum (for Washers) with Perforated Rear Wall

Matching Dryers	Material
PDR 908 HP Lotus White	11204480
PDR 908 HP Stainless Steel	11204490

### Programs

- Standard Programs – 16
- Sport Programs – 4
- Down Filled Items
- Outwear
- Work Wear like Oil/fat Special, Dust/Flour Special
- Wellness/Hair Salon Programs – 3
- Proofing
- Thermal Disinfection – 16
- Wet Care Programs – 5

Optional Accessories	Material	Map/Retail
APCL 001 Stainless Steel Stacking Kit	11167420	\$275
APCL 084 Iron-Grey Base, Open, 6" Tall	11776560	\$585
APCL 085 Iron-Grey Base, Open, 12" Tall	11776570	\$625
APCL 087 Iron-Grey Base, Open, 19" Tall	11776600	\$830
APCL 005 Stainless Steel Base, Closed, 12" Tall	11318800	\$835
APCL 011 Stainless Steel Base, Closed, 19" Tall	11318830	\$1,045
APCL 043 XCI-Box	11492730	\$260
APCL 046 XCI PWM/PDR EL.	11537560	\$305
APCL 047 XCI PWM/PDR HP.	11537570	\$305
APCL 016 Dispensing adapter kit LD 6xD6	11229320	\$105
APCL 017 Dispensing adapter kit LD 4xD9	11229340	\$105

## Dryers – Little Giant Performance Plus

PDR 908 HP, Lotus White



PDR 908 HP, Stainless Steel



Model	Material	Map/Retail
<b>PDR 908 HP</b> Lotus White	11204480	\$5,455 / \$5,655
<b>PDR 908 HP</b> Stainless Steel	11204490	\$5,895 / 6,095

Specifications	
Width	23 7/16 in (596 mm)
Height	33 7/16 in (850 mm)
Depth	30 9/16 in (777 mm)
Shipping Weight	170 lbs (77 kg)
Front Material (Lotus White Model)	Porcelain Enameled White
Front Material (Stainless Steel Model)	Stainless Steel
Side Panels (both models)	Powder Coated White
Electrical Connection	2 AC 208-240V, 60 Hz, 30 A
Plug	NEMA L6-30
Capacity	4.59 cu.ft – 130 Liter

- Features**
- M Touch Flex User Interface (No Buttons or Dials)
  - Stackable or Side-by-Side Configuration
  - Heat Pump Dryer Technology
  - 50+ Programs – 5 Customizable Rated Energy Star Most Efficient
  - FragranceDos Capable
  - Dryer Featuring 4D Filtration System
  - HoneyComb Drum (for Dryers) with Perforated Rear Wall
  - PerfectDry System – Residual Moisture Controlled
  - Axial Airflow

Matching Washers	Material
PWM 908 Lotus White	DP 11204460
PWM 908 DP Stainless Steel	11204470

- Programs**
- Standard Programs – 17
  - Sport Programs – 4
  - Down Bedding
  - Synthetic Bedding
  - Large Items
  - Hygiene Programs – 3
  - Wet Care Programs – 3
  - Flatwork Programs – 3
  - Special Programs – 5
  - Timed Drying Programs – 4

Optional Accessories	Material	Map/Retail
TRK 555 Dryer Basket	9614800	\$99
APCL 001 Stainless Steel Stacking Kit	11167420	\$275
APCL 084 Iron-Grey Base, Open, 6" Tall	11776560	\$585
APCL 085 Iron-Grey Base, Open, 12" Tall	11776570	\$625
APCL 087 Iron-Grey Base, Open, 19" Tall	11776600	\$830
APCL 005 Stainless Steel Base, Closed, 12" Tall	11318800	\$835
APCL 011 Stainless Steel Base, Closed, 19" Tall	11318830	\$1,045

## Professional Rotary Ironer



Model	Material	Map/Retail
<b>HM 16-80</b>	10238590	\$4,490 / \$4,880

Optional Accessories	Material	Map/Retail
APRI 310 Dust Cover	11563330	\$80

**Finish**  
Lotus White

Specifications	
Width	38 3/4 in (985 mm)
Height	37 3/4 in (959 mm)
Depth	14 15/16 in (380 mm)
Drum Diameter	6 5/16 in (160 mm)
Working Width	32 11/16 in (830 mm)
Shipping Weight	100 lbs (45 kg)
Electrical Connection	2 AC 208-240V, 50-60 Hz, 20 A
Plug	NEMA L6-20

- Features**
- Heater Plate Material – Aluminium
  - Padding – Polyester Needle-Felt Cloth
  - Control System – Rotary Selector
  - Minimum Ironer Speed, Can Be Set in ft/min – 2
  - Feed-In Board
  - Maximum Ironer Speed, Can Be Set in ft/min – 4.5
  - Steam Function
  - Fold-Away Function
  - Foot Switch
  - Airing Bar

## Accessories & Consumables – Laundry

<b>W1 TwinDos Cartridges</b>	<b>Material</b>	<b>UMRP</b>	<b>Product</b>	<b>Material</b>	<b>UMRP</b>
TwinDos Cartridge UltraPhase 1	11504560	\$34.99	UltraColor Liquid Detergent	11979450	\$31.99
TwinDos Cartridge UltraPhase 2	12517250	\$34.99	UltraDark Liquid Detergent	11986840	\$33.99
TwinDos Cartridge UltraPhase 2 – Refresh Elixir	11615060	\$36.99	UltraSoft Fabric Softener	11987230	\$19.99
TwinDos Care	11171450	\$20.99	WoolCare Liquid Detergent	11979320	\$29.99
TwinDos Cartridge UltraPhase – Sensitive	11716880	\$36.99	UltraColor Powder Detergent	10459790	\$44.99
TwinDos Cartridge UltraPhase 2 – Sensitive	11716960	\$36.99	UltraWhite Powder Detergent	10459720	\$44.99
			Sensitive Skin Powder Detergent	10459870	\$44.99

<b>W1 CapDosing Capsules</b>	<b>Material</b>	<b>UMRP</b>
Sport – Box of 6	12625960	\$10.99
Booster – Box of 6	11703400	\$13.99
Outdoor – Box of 6	12637180	\$13.99
Aqua – Box of 9	11698240	\$12.99
WoolCare – Box of 9	11703130	\$16.99
ImpraProtect – Box of 3	11703420	\$26.99
DownCare – Box of 6	12636470	\$13.99
SilkCare – Box of 6	11703280	\$13.99
Cocoon – Box of 9	11698260	\$12.99
CottonRepair – Box of 3	11703360	\$26.99

<b>T1 Flacon</b>	<b>Material</b>	<b>UMRP</b>
Nature Flacon Capsule – Box of 1	10813410	\$23.99
Aqua Flacon Capsule – Box of 1	12021190	\$23.99
Cocoon Flacon Capsule – Box of 1	12023700	\$23.99
DryFresh Flacon Capsule – Box of 1	12026960	\$23.99
Set 3x Aqua Flacon Capsules	12021630	\$64.99
Set 3x Cocoon Flacon Capsules	12023770	\$64.99
Set 3x DryFresh Flacon Capsules	12026080	\$64.99
Set 3x Nature Flacon Capsules	11614600	\$64.99

## Accessories & Consumables – Dishwashers

### Dishwashers

<b>Product</b>	<b>Material</b>	<b>UMRP</b>
UltraTabs All in 1 (3-Pack, 60 Tabs)	12738130	\$39.99
UltraTab 120 Series Promo Pack	11347040	\$71.99
PowerDisk® (6-pack)	11841390	\$118.99
PowerDisk® (Single Pack)	11841540	\$21.99
Dishwasher Salt	10248600	\$15.99
Dishwasher Rinse Aid	13025390	\$15.99
DishClean Dishwasher Conditioner	9959340	\$18.99
Dishwasher Freshener	10118510	\$11.99

### Professional for the Home Dishwashers

<b>Product</b>	<b>Material</b>	<b>UMRP</b>
ProCare Shine 12 GC Dishwasher Tabs – 80 tabs	11712580	\$65
ProCare Shine 10 MA Liquid Detergent – 5 L	10923610	\$65
ProCare Shine 40 Rinse Aid – 1 L	10923710	\$40
ProCare Shine 40 Rinse – 5 L	10328030	\$125
ProCare Universal Dishwasher Salt	9195780	\$65
CK/1 DIN 51 Canister Key	11851600	\$20

# Handle Options

GEN 7000	MODEL	MATERIAL	TRIM / COLOR	HANDLE WIDTH	COOKING	Vi DISH-WASHERS	Vi COOLING	SF MASTER-COOL	UMRP
	<b>DS 7000</b>	11345890	PureLine Stainless steel <sup>1</sup>	15 3/4 in	•	•	•	–	\$164
	<b>DS 7000</b>	11345930	VitroLine Obsidian black <sup>1</sup>	15 3/4 in	•	•	•	–	\$340
	<b>DS 7000</b>	11345940	VitroLine Brilliant white <sup>1</sup>	15 3/4 in	•	•	•	–	\$340
	<b>DS 7000</b>	11345950	VitroLine Graphite grey <sup>1</sup>	15 3/4 in	•	•	•	–	\$340
	<b>DS 7308</b>	12047020	ContourLine Stainless steel standard handle	21 1/8 in	•	•	•	•	\$186
	<b>DS 7708</b>	12047000	ContourLine Stainless steel swiveling handle	21 1/8 in	•	•	•	•	\$230
	<b>DS 7808</b>	12047030	VitroLine Obsidian black	19 11/16 in	•	•	•	–	\$384
	<b>DS 7808</b>	12047050	VitroLine Graphite grey	19 11/16 in	•	•	•	–	\$384
	<b>DS 7808</b>	12047060	VitroLine Brilliant white	19 11/16 in	•	•	•	–	\$384
	<b>DS 7808</b>	12046910	PureLine Stainless steel	19 11/16 in	•	•	•	–	\$186

**Miele**

Miele, Inc.  
9 Independence Way  
Princeton, NJ 08540

**mieleusa.com**  
**1-800-843-7231**

**Find your nearest Miele Experience Center in –**

Beverly Hills  
Chicago  
Coral Gables  
Manhattan  
Princeton  
Seattle  
Tysons Corner