

**Miele**



# Cooling Price List

2026

# Table of Contents

<b>PerfectCool Refrigeration</b>	<b>03</b>
PerfectCool Refrigeration Product Highlights	03
PerfectCool Refrigeration	04
<b>PerfectCool Wine Storage</b>	<b>10</b>
PerfectCool Wine Storage Product Highlights	10
PerfectCool Wine Storage	11
<b>MasterCool Refrigeration</b>	<b>13</b>
MasterCool Refrigeration Product Highlights	13
MasterCool Refrigeration	14
<b>MasterCool Wine Storage</b>	<b>27</b>
MasterCool Wine Storage Product Highlights	27
MasterCool Wine Storage	28
<b>Handle Options</b>	<b>30</b>

# Product Highlights – PerfectCool Refrigeration

<b>Feature</b>	<b>Description</b> <small>(see specific models for details)</small>
<b>PerfectFresh Pro</b>	Food stays fresh for up to five times longer. With automatically controlled temperature zones, PerfectFreshPro is Miele's best system for perfect storage conditions of fresh produce.
<b>FlexiLight</b>	Glare-free, LED glass shelf lighting.
<b>ComfortClean</b>	The shelves on the inside of the door are dishwasher-safe for easy cleaning.
<b>DynaCool</b>	With uniform distribution and circulation of temperature, store your food anywhere in the fridge and freezer.
<b>SuperCool</b>	Rapid and gentle freezing of food.
<b>PerfectFresh</b>	Active Perfect humidity at all times – whenever the door is opened and every 90 minutes, a fine water mist is sprayed into the drawer for a gentle layer of moisture.
<b>FlexiLight 2.0</b>	Individually adjustable glass shelf lighting; illuminated shelves can be custom-positioned and are entirely glare-free.
<b>FlexiTray</b>	Pivot-able glass shelf allows for items to be removed easily, even from a full refrigerator.
<b>Miele@home</b>	Access your appliance from your smart device for maximum convenience. Adjust fridge or freezer temperature, setting it to SuperCool while on the go.

## PerfectCool Refrigeration – 30" Freestanding



Model	Material	UMRP
<b>KFN 4776 ED</b> 30" Freestanding	11954030	\$3,199

Finish	Hinge
Clean Touch Steel™	Right (convertible)

Specifications	
Width	29 1/2 in (750 mm)
Height	73 1/4 in (2020 mm)
Depth	24 13/16 in (630 mm)
Refrigerator Capacity	11.7 cu.ft. (331 l)
Freezer Capacity	4.3 cu.ft. (121 l)
Shipping Weight	261 lbs (118 kg)
Annual Energy Usage	496 kWh

### Fridge Features

- Lighting: LED
- ComfortClean Door Shelves
- WifiConn@ct
- Daily Fresh
- FlexiBoard Shelves: FlexiBoard is a split glass shelf
- DynaCool
- Active AirClean Filter
- SuperCool
- DuplexCool – separate circuits for fridge and freezer

### Freezer Features

- Maximum Storage Capacity and Flexibility:  
4 Removable Drawers
- SuperCool



Model	Material	UMRP
<b>KFN 4799</b> 24" Freestanding	11951210	\$3,999

Finish	Hinge
Clean Touch Steel™	Right (convertible)

Specifications	
Width	23 1/2 in (597 mm)
Height	79 1/2 in (2020 mm)
Depth	24 3/16 in (630 mm)
Refrigerator Capacity	9.43 cu.ft. (267 l)
Freezer Capacity	3.32 cu.ft. (94 l)
Shipping Weight	203 lbs (92 kg)


### Fridge Features

- Sabbath, Party & Holiday Mode
- 2 Temperature Zones
- LED lighting
- ComfortClean Door Shelves
- TouchControls
- Maximum Storage Capacity and Flexibility:  
5 Door Bins, 2 Drawers, 4 Movable Shelves, 1 Bottle Rack
- Acoustic Door and Temperature Alarm
- DynaCool

### Freezer Features

- Illuminated IceMaker w/ plumbed water connection
- Maximum Storage Capacity and Flexibility:  
3 Removable Drawers
- SuperCool

## PerfectCool Refrigeration – 24" Bottom Mount



Model	Material	UMRP
<b>KFN 7795 D</b> 24" Bottom Mount	11749900	\$4,999

Finish	Hinge
Custom Panel	Right (convertible)

Specifications	
Width	22 in (559 mm)
Height	69 11/16 in (1770 mm)
Depth	21 1/2 in (545 mm)
Refrigerator Capacity	6.2 cu.ft. (175 l)
Freezer Capacity	2.5 cu.ft. (71 l)
Shipping Weight	175.7 lbs (79.7 kg)

### Fridge Features

- PerfectFresh Active
- FlexiLight 2.0 LED Shelves: 2
- FlexiTray
- ComfortClean Door Shelves
- TouchControls
- SoftClose Door
- Temperature Zones: 3
- Sabbath Mode
- Maximum Storage Capacity and Flexibility:  
2 Door Bins, 2 Drawers, 3 Movable Shelves
- DynaCool
- SuperCool
- Acoustic Door and Temperature Alarm
- CleanSteel back panel

### Freezer Features

- IceMaker w/ Plumbed Water Connection
- Maximum Storage Capacity and Flexibility:  
3 Removable Drawers
- SuperCool

## PerfectCool Refrigeration – 30" Bottom Mount



Model	Hinge	Material	UMRP
<b>KFN 9859 iDE</b> 30" Bottom Mount Custom Panel	Right	12153750	\$8,199
<b>KFN 9859 iDE</b> 30" Bottom Mount Custom Panel	Left	12153760	\$8,199

Optional Accessories	Material	UMRP
KFN 9855 K Fridge Panel (w/o handle)	9699670	\$629
KFN 9855 GF Freezer Panels (2 panels required, w/o handles)	9699700	\$629

### Specifications

Width	29 7/8 in (759 mm)
Height	79 13/16 in (2027 mm)
Depth	24 in (610 mm)
Refrigerator Capacity	9.8 cu.ft. (277.5 l)
Freezer Capacity	4.3 cu.ft. (127 l)
Shipping Weight	345 lbs (156.6 kg)

### Fridge Features

- Lighting: LED
- ComfortClean Door Shelves
- TouchControls
- SoftClose Door
- Temperature Zones: 2
- Sabbath Mode
- Maximum Storage Capacity and Flexibility:  
3 Door Bins, 2 Drawers, 3 Movable Shelves, 1 Bottle Rack
- DynaCool
- SuperCool
- Acoustic Door and Temperature Alarm

### Freezer Features

- IceMaker w/ Plumbed Water Connection
- Maximum Storage Capacity and Flexibility: 2 Drawers
- SuperCool

## PerfectCool Refrigeration – Columns



Model	Material	UMRP
<b>FNS 7794 E</b> 24" Freezer Column	11911910	\$4,699

Finish	Hinge
Custom Panel	Left (convertible)

### Specifications

Width	22 in (559 mm)
Height	69 11/16 in (1770 mm)
Depth	21 1/2 in (545 mm)
Freezer Capacity	7.5 cu.ft. (213 l)
Shipping Weight	175.5 lbs (79 kg)

### Freezer Features

- Lighting: LED
- SoftClose Door
- SuperFreeze
- Illuminated icemaker w/ plumbed water connection
- Miele@home
- Sabbath mode
- TouchControls
- Temperature Zones: 1
- Acoustic Door and Temperature Alarm

Model	Material	UMRP
<b>KS 7793 D</b> 24" Refrigerator Column	11749850	\$4,199

Finish	Hinge
Custom Panel	Right (convertible)

### Specifications

Width	22 in (559 mm)
Height	69 11/16 in (1770 mm)
Depth	21 1/2 in (545 mm)
Refrigerator Capacity	10.45 cu.ft. (296 l)
Shipping Weight	167.6 lbs (76 kg)

### Fridge Features

- PerfectFresh Active – keeps food up to 5 times longer fresh, small water container inside, releases steam every 90 min
- FlexiLight 2.0
- Temperature Zones: 2
- FlexiTray – turns the glass shelf into a turntable, can be rotated by 180°
- DynaCool
- SuperCool
- CleanSteel back wall
- SoftClose Door
- Sabbath, Party & Holiday Mode
- ComfortClean Door Shelves
- TouchControls
- Maximum Storage Capacity and Flexibility: 4 Door Bins, 3 Drawers, 6 Movable Shelves, 1 Bottle Rack
- Acoustic Door and Temperature Alarm

## PerfectCool Refrigeration – 36" French Door



Model	Material	UMRP
<b>KFNF 9959 iDE</b> 36" French Door Custom Panel	12153770	\$9,449
<b>Specifications</b>		
Width	35 13/16 in (910 mm)	
Height	79 13/16 in (2027 mm)	
Depth	24 in (610 mm)	
Refrigerator Capacity	12.9 cu.ft. (365 l)	
Freezer Capacity	6.0 cu.ft. (170 l)	
Shipping Weight	383.5 lbs (174 kg)	

### Fridge Features

- Lighting: LED
- ComfortClean Door Shelves
- TouchControls
- SoftClose Door
- Temperature Zones: 3
- Sabbath Mode
- Maximum Storage Capacity and Flexibility:  
6 Door Bins, 2 Drawers, 4 Movable Shelves
- DynaCool
- SuperCool
- Acoustic Door and Temperature Alarm

### Freezer Features

- IceMaker w/ Plumbed Water Connection
- Maximum Storage Capacity and Flexibility: 2 Drawers
- SuperCool

## PerfectCool Refrigeration – 24" Under-Counter



Model	Material	UMRP
<b>KD 7175 D</b> 24" Under-Counter Refrigerator	12930520	\$3,999
<b>Finish</b>		<b>Hinge</b>
Panel Ready		Pull-out front
<b>Specifications</b>		
Width	23 5/8 in (597 mm)	
Height	33 7/8 in (859 mm)	
Depth	22 in (556 mm)	
Refrigerator Capacity	4.2 cu.ft. (119 l)	
Shipping Weight	84 lbs (38.0 kg)	

### Fridge Features

- Two individually adjustable temperature zones for more flexibility
- From 32°F (0°C) for chilled drinks to 57°F (14°C) for an ideal cellar climate
- Optimum and maintenance-free LED lighting
- Uniform temperature distribution inside the appliance – DynaCool
- Cool food down quickly thanks to SuperCool
- Soft closing of the door with SoftClose

Available Spring 2026.

## Product Highlights – PerfectCool Wine Storage

Feature	Description <small>(see specific models for details)</small>
<b>TouchControl Display</b>	Incredibly convenient – a whole range of settings can be controlled easily with the tap of a finger on the touch display.
<b>LED Lighting</b>	Flush lighting strips present your appliance in the perfect light.
<b>Push2Open</b>	For a handleless design, just apply slight pressure to the door to open.
<b>SoftClose</b>	With just a gentle touch, our dynamic doors close on their own. Integrates perfectly within a handleless kitchen.
<b>FlexiFrame Racks</b>	Individual Beechwood slats can be easily moved to make room for larger wine bottles.
<b>SommelierSet</b>	Perfect for wine connoisseurs – prepare cooled wine glasses and wine for decanting. Drink perfectly conditioned wine even from opened bottles.
<b>3D Bottle Presenter Shelf</b>	Place your favorite bottles on display.
<b>Temperature Zones</b>	Precise temperature regulation, ensuring the best storage conditions for different wine types.
<b>NoteBoard</b>	Every bottle rack features a removable magnetic strip for labeling the types of wine bottles on the rack.

## PerfectCool Wine Storage – 24" Wine Storage



Model	Material	UMRP
<b>KWT 6722 iS</b> 24" Built-in Wine	11329860	\$5,669

Finish	Hinge
Custom Panel	Right (convertible)

Specifications	
Width	21 15/16 in (557 mm)
Height	69 11/16 in (1770 mm)
Depth	21 3/4 in (553 mm)
Shipping Weight	223 lbs (101 kg)

- Features**
- Lighting: LED
  - TouchControls
  - SoftClose Door
  - Temperature Zones: 2
  - Maximum Storage Capacity and Flexibility: 80 x 0.75 l bottles
  - DynaCool
  - Acoustic Door and Temperature Alarm
  - FlexiFrame Racks: 8
  - 3D Bottle Presenter Shelf: 1
  - UV Tinted Glass
  - SommelierSet
  - NoteBoard
  - CleanSteel Back Wall

Optional Accessories	Material	UMRP
KFP 6700 Clean Touch Steel™ Panel (w/o handle)	11329620	\$999

Model	Material	UMRP
<b>KWTUS 7172 F</b> 24" Under-Counter Wine	12519520	\$3,799

Finish	Hinge
Custom Panel	Right (convertible)

Specifications	
Width	23 5/8 in (597 mm)
Height	33 7/8 in (859 mm)
Depth	22 1/4 in (563 mm)
Shipping Weight	102 lbs (46.0 kg)

- Features**
- Storage of all bottle sizes/shapes thanks to FlexiFrame
  - Perfect regulation of humidity with ActiveHumidity
  - Writing on the wooden shelves on the NoteBoard
  - UV-resistant insulated glass
  - Presented in perfect light – LED lighting

Optional Accessories	Material	UMRP
KSK 6300 Merging Kit	9799630	\$249

# PerfectCool Wine Storage – 24" Wine Storage



Model	Material	UMRP
<b>KWT 6322 UG</b> 24" Under-Counter Wine	11545800	\$4,599

Finish	Hinge
Clean Touch Steel™ Frame	Right (convertible)

## Specifications

Width	23 7/16 in (596 mm)
Height	32 1/4 – 34 1/4 in (819 – 870 mm)
Depth	22 1/2 in (571 mm)
Shipping Weight	116.8 lbs (53 kg)

## Features

- Lighting: LED
- TouchControls
- SoftClose Door
- Temperature Zones: 2
- Maximum Storage Capacity and Flexibility:  
34 x 0.75 l bottles
- Active AirClean Filter
- Acoustic Door and Temperature Alarm
- FlexiFrame Racks: 3, 1 fixed shelf
- UV Tinted Glass
- NoteBoard
- Push2Open Door

Optional Accessories	Material	UMRP
KSK 6300 Merging Kit	9799630	\$249

# Product Highlights – MasterCool Refrigeration

Feature	Description <small>(see specific models for details)</small>
<b>BrilliantLight Pro</b>	Flush-fit LED lighting in the side panels, top frame, and backwall flood the interior with bright, even illumination – so everything is easy to see and beautifully showcased.
<b>SmartLight</b>	No more blinding fridge light at night. Every model is equipped with a light sensor that automatically adjusts its brightness.
<b>M Touch Pro</b>	New user interface with large high-resolution full-touch display that is conveniently positioned at the center of the appliance. Integrated tips for ensuring effortless maintenance such as changing the filter.
<b>Gallon Bins</b>	To prevent spills, open bottles are best stored upright. The new gallon bins make it easy to store even large containers in the door, keeping them accessible while freeing up shelf space.
<b>Internal Water Dispenser</b>	Seamlessly integrated water dispenser on the left side panel, providing cold, fresh water at any time. Thanks to the built-in filter, the water is always clean and ready to drink. Dispense manually or pre-set your favorites for your preferred glass or bottle size.
<b>Spillproof Shelves</b>	Spills and leaks are contained by the aluminum-framed glass shelves, preventing messes and making cleaning quick and easy. The shelves are height-adjustable and, depending on the model, available as full-width or split versions for flexible storage.
<b>MaxLoad Hinge</b>	Ensures safe storage of large amounts of food in the door shelves, while also offering flexible options for door panel materials.
<b>FoodView</b>	Up to four cameras inside the appliance capture images of key areas, including drawers, whenever doors are opened and closed. Viewable via the Miele app, these images help simplify shopping and reduce food waste.
<b>Longlife</b>	For food storage in an odor-free environment. This innovative filter system combines an active charcoal filter
<b>AirClean Filter</b>	integrated into the rear panel of the appliance's air circuit, effectively neutralizing odors. It is regenerable – cleanable up to five times in an oven – and only needs replacement every three years, hence reducing waste.
<b>Freeze&amp;Cool</b>	Features a temperature range of +39.2° F to -0.4° F and 5 pre-set settings for maximum flexibility.
<b>Dual IceMaker</b>	Produce two different types of ice cubes (small and large) at the same time.
<b>IceMaker</b>	Always have daily, fresh ice cubes on hand. For ultimate convenience, use the included ice scoop.
<b>MasterFresh Pro</b>	Now standard in all models, MasterFresh Pro optimizes freshness by keeping food fresh up to 5× longer. It automatically adjusts humidity based on food type, ensuring ideal conditions and less waste.
<b>DailyFresh ExtraCool</b>	Fruit and vegetables stay fresh up to twice as long with the spacious and extra drawer. Featuring a temperature ExtraCool at approx. 35.6° F lower than the set refrigerator temperature – it's the perfect place for meat, fish and dairy products.
<b>SlidingShelf</b>	Store small items within easy reach without using much fridge space. Attached beneath a glass shelf, the sliding box keeps items organized and easily accessible without stacking.

All handles sold separately – See page 30 for full list of handle options.

## MasterCool Refrigeration – 30" Bottom Mount

KFMC 3632 R



KFMC 3632 L



Model	Hinge	Material	UMRP
<b>KFMC 3632 R</b> 30" Premium Bottom Mount Fridge/Freezer	Right	12489450	\$12,499
<b>KFMC 3632 L</b> 30" Premium Bottom Mount Fridge/Freeze	Left	12489460	\$12,499

### Specifications

Width	29 3/4 in (756 mm)
Height	83 9/16 – 85 1/2 in (2123 – 2171 mm)
Depth	24 in (610 mm)
Shipping Weight	472 lbs (214 kg)
Finish	Panel-ready

### Features

- BrilliantLight
- M Touch Pro
- SmartLight
- Longlife AirClean System
- IceMaker
- MasterFresh Pro
- Miele@Home

Included Accessories
Ice scoop
Longlife AirClean filter
Water filter

Optional Accessories	Material	UMRP
KWF 2000 Water filter	11480330	\$189
KFP 3031 ed/cs Front Panel fridge 30"	12687730	\$749
KFP 3032 ed/cs Front Panel freezer 30"	12687750	\$399
KFK 3001 Frame set – 30" BM (For SS Proud Installation)	12687400	\$799
KTK 3030 ed Toe kick cover 30" Stainless steel	12687180	\$149
KHK 3002 Door direction change kit	12687710	\$399

## MasterCool Refrigeration – 30" Bottom Mount

KFCM 3836 R



KFCM 3836 L



Model	Hinge	Material	UMRP
<b>KFCM 3836 R</b> Custom Panel 30" Prestige Bottom Mount Fridge/Freeze	Right	12489320	\$13,499
<b>KFCM 3836 L</b> Custom Panel 30" Prestige Bottom Mount Fridge/Freeze	Left	12489330	\$13,499

### Specifications

Width	29 3/4 in (756 mm)
Height	83 9/16 – 85 1/2 in (2123 – 2171 mm)
Depth	24 in (610 mm)
Shipping Weight	472 lbs (214 kg)
Finish	Panel-ready

### Features

- BrilliantLight
- M Touch Pro
- SmartLight
- Longlife AirClean System
- IceMaker
- MasterFresh Pro
- Miele@Home

Optional Accessories	Material	UMRP
KWF 2000 Water filter	11480330	\$189
KFP 3031 ed/cs Front Panel fridge 30"	12687730	\$749
KFP 3032 ed/cs Front Panel freezer 30"	12687750	\$399
KFK 3001 Frame set – 30" BM (For SS Proud Installation)	12687400	\$799
KTK 3030ed Toe kick cover 30" Stainless steel	12687180	\$149
KHK 3002 Door direction change kit	12687710	\$399
KSK 3001 Merge Kit with a 30" BM	12686320	\$349
KSK 3002 Merge Kit with a 30" BM	12687090	\$349
KSK 3004 Merge Kit with a Column	12687140	\$649

## MasterCool Refrigeration – 36" Bottom Mount



Model	Hinge	Material	UMRP	Optional Accessories	Material	UMRP
<b>KFMC 3642 R</b> Custom Panel 36" Premium Bottom Mount Fridge/Freezer	Right	12489480	\$12,999	KWF 2000 Water filter	11480330	\$189
<b>KFMC 3642 L</b> Custom Panel 36" Premium Bottom Mount Fridge/Freezer	Left	12489490	\$12,999	KFP 3631 ed/cs Front Panel fridge 36"	12687780	\$899
				KFP 3632 ed/cs Front Panel freezer 36"	12687790	\$449
				KFP 3633 ed/cs* FD Front Panel fridge (lower BeltLine) 36" SS	12687800	\$499
<b>KFMC 3642 FD</b> Custom Panel 36" Premium Bottom Mount Fridge/Freezer	French Door	12489500	\$13,499	KFK 3601 Frame set – 36" (For SS Proud Installation)	12687420	\$849
				KTK 3630 ed Toe kick cover 36" Stainless steel	12687210	\$149
				KTT 3001 Trim kit (For traditional 36" and 42" openings)	12687150	\$249
				KHK 3002 Door direction change kit	12687710	\$399
				KSK 3002 Merge Kit with a 30" BM	12687090	\$349
				KSK 3003 Merge Kit with either a 36" or 42" BM	12687120	\$349
				KSK 3004 Merge Kit with a Column	12687140	\$649

### Specifications

Width	35 1/4 in (895 mm)
Height	83 9/16 – 85 1/2 in (2123 – 2171 mm)
Depth	24 in (610 mm)
Shipping Weight	483 lbs (219 kg) – 499 lbs (226 kg)
Finish	Panel-ready

### Features

- FoodView
- Longlife AirClean System
- Freeze&Cool
- IceMaker
- Water dispenser
- BrilliantLight Pro
- M Touch Pro

\*Two of these panels must be ordered separately for both refrigerator doors.

## MasterCool Refrigeration – 36" Bottom Mount



Model	Hinge	Material	UMRP	Optional Accessories	Material	UMRP
<b>KFMC 3846 R</b> Custom Panel 36" Prestige Bottom Mount Fridge/Freeze	Right	12489400	\$14,499	KWF 2000 Water filter	11480330	\$189
<b>KFMC 3846 L</b> Custom Panel 36" Prestige Bottom Mount Fridge/Freeze	Left	12489410	\$14,499	KFP 3638 ed/cs Front Panel fridge 36" SS	12687810	\$899
				KFP 3639 ed/cs Front Panel freezer, upper drawer 36" SS	12687830	\$249
				KFP 3636 ed/cs* Front Panel freezer, lower drawer 36" SS	12687840	\$429
<b>KFMC 3846 FD</b> Custom Panel 36" Prestige Bottom Mount Fridge/Freeze	French Door	12489430	\$14,999	KFP 3637 ed/cs FD Front Panel fridge (Higher BeltLine) 36" SS	12687860	\$499
				KFK 3601 Frame set - 36" (For SS Proud Installation)	12687420	\$849
				KTK 3630 ed Toe kick cover 36" Stainless steel	12687210	\$149
				KTT 3001 Trim kit (For traditional 36" and 42" openings)	12687150	\$249
				KHK 3002 Door direction change kit	12687710	\$399
				KSK 3002 Merge Kit with a 30" BM	12687090	\$349
				KSK 3003 Merge Kit with either a 36" or 42" BM	12687120	\$349
				KSK 3004 Merge Kit with a Column	12687140	\$649

### Specifications

Width	35 1/4 in (895 mm)
Height	83 9/16 – 85 1/2 in (2123 – 2171 mm)
Depth	24 in (610 mm)
Shipping Weight	488 lbs (221 kg) – 501 lbs (227 kg)
Finish	Panel-ready

### Features

- FoodView
- Longlife AirClean System
- Freeze&Cool
- IceMaker

\*Two of these panels must be ordered separately for both refrigerator doors.



## MasterCool Refrigeration – 30" Columns



Model	Hinge	Material	UMRP
<b>K2802 Vi</b> Custom Panel	Right	11502590	\$9,699
<b>K2802 SF</b> Clean Touch Steel™ w/ DS6708 ContourLine Handle	Right	11502700	\$10,499

### Specifications

Width	29 3/4 in (756 mm)
Height	83 3/4 – 85 3/16 in (2127 – 2164 mm)
Depth	24 in (610 mm)
Refrigerator Capacity	16.77 cu.ft. (475 l)
Shipping Weight	395 lbs (179 kg)
Annual Energy Usage	279 kWh

### Fridge Features

- Push2Open Door
- MasterFresh
- BrilliantLight
- MasterSensor Controls
- SoftClose Door
- Temperature Zones: 2
- Maximum Storage Capacity and Flexibility:  
4 Door Bins, 3 Drawers, 2 Movable Shelves
- DynaCool
- MaxLoad Hinge
- Active AirClean Filter
- SuperCool
- Acoustic Door and Temperature Alarm
- Sabbath Mode
- CleanSteel Back Wall

Optional Accessories Vi	Material	UMRP
KFP 3005 30 in Clean Touch Steel™ Panel (No Logo, w/o handle)	11499080	\$1,149
KTK 3020 SS 30 in Toekick	10984090	\$199
KSK 2002 Merge Kit	10984130	\$1,499

Optional Accessories SF	Material	UMRP
KTF 1048 48 in Top Frame	12556870	\$399
KTF 1054 54 in Top Frame	12556860	\$399
KTF 1060 60 in Top Frame	12556850	\$399
KTF 1066 66 in Top Frame	12556810	\$399
KTF 1072 72 in Top Frame	12556830	\$399
KTK 3020 SS 30 in Toekick	10984090	\$199
KSK 2002 Merge Kit	10984130	\$1,499
DS 7308 GEN 7000 ContourLine Handle	12047020	\$185.90

## MasterCool Refrigeration – 36" Columns



Model	Hinge	Material	UMRP
<b>K2902 Vi</b> Custom Panel	Right	11502710	\$9,999
<b>K2902 SF</b> Clean Touch Steel™ w/ DS6708 ContourLine Handle	Right	11502840	\$10,999
<b>K2912 Vi</b> Custom Panel	Left	11502720	\$9,999

### Specifications

Width	35 3/4 in (908 mm)
Height	83 3/4 – 85 3/16 in (2127 – 2164 mm)
Depth	24 in (610 mm)
Refrigerator Capacity	20.55 cu.ft. (582 l)
Shipping Weight	435 lbs (197 kg)
Annual Energy Usage	312 kWh

### Fridge Features

- Push2Open Door
- MasterFresh
- BrilliantLight
- MasterSensor Controls
- SoftClose Door
- Temperature Zones: 2
- Maximum Storage Capacity and Flexibility:  
4 Door Bins, 3 Drawers, 2 Movable Shelves
- DynaCool
- MaxLoad Hinge
- Active AirClean Filter
- SuperCool
- Acoustic Door and Temperature Alarm
- Sabbath Mode
- CleanSteel Back Wall

Optional Accessories Vi	Material	UMRP
KFP 3605 36 in Clean Touch Steel™ Panel (No Logo, w/o handle)	11499100	\$1,199
KTK 3620 SS 36 in Toekick	10984110	\$199
KSK 2002 Merge Kit	10984130	\$1,499

Optional Accessories SF	Material	UMRP
KTF 1054 54 in Top Frame	12556860	\$399
KTF 1060 60 in Top Frame	12556850	\$399
KTF 1066 66 in Top Frame	112556810)	\$399
KTF 1072 72 in Top Frame	12556830	\$399
KTK 3620 SS 36 in Toekick	10984110	\$199
KSK 2002 Merge Kit	10984130	\$1,499
DS 7308 GEN 7000 ContourLine Handle	12047020	\$185.90

## MasterCool Freezers – 18" Columns



## MasterCool Freezers – 18" Columns



Model	Hinge	Material	UMRP
<b>F2412 Vi</b> Custom Panel	Left	11503300	\$8,799
<b>F2412 SF</b> Clean Touch Steel™ w/ DS6708 ContourLine Handle	Left	11503310	\$9,449

Specifications	
Width	17 3/4 in (451 mm)
Height	83 3/4 – 85 3/16 in (2127 – 2164 mm)
Depth	24 in (610 mm)
Freezer Capacity	8.55 cu.ft. (242 l)
Shipping Weight	306 lbs (139 kg)
Annual Energy Usage	404 kWh

### Fridge Features

- Push2Open Door
- MasterFresh
- BrilliantLight
- MasterSensor Controls
- SoftClose Door
- Temperature Zones: 1
- MaxLoad Hinge
- Acoustic Door and Temperature Alarm
- Ice & Water Dispenser
- Maximum Storage Capacity and Flexibility:  
3 Shelves, 2 Drawers, 1 small Door basket,  
3 large Door baskets
- SuperCool
- Sabbath Mode
- CleanSteel Back Wall

Optional Accessories Vi	Material	UMRP
KFP 1805 18 in Clean Touch Steel™ Panel (No Logo, w/o handle)	11499020	\$989
KTK 1820 SS 18 in Toekick	10984060	\$199
KSK 2002 Merge Kit	10984130	\$1,499
KWF 2000 Water Filter 2.0 (MC 2xx2)	11480330	\$189

Optional Accessories SF	Material	UMRP
KTF 1042 42 in Top Frame	10984920	\$399
KTF 1048 48 in Top Frame	12556870	\$399
KTF 1054 54 in Top Frame	12556860	\$399
KTF 1060 60 in Top Frame	12556850	\$399
KTF 1066 66 in Top Frame	12556810	\$399
KTF 1072 72 in Top Frame	12556830	\$399
KTK 1820 SS 18 in Toekick	10984060	\$199
KSK 2002 Merge Kit	10984130	\$1,499
KWF 2000 Water Filter 2.0 (MC 2xx2) Handle	11480330	\$189
DS 7308 GEN 7000 ContourLine Handle	12047020	\$185.90

Model	Hinge	Material	UMRP
<b>F2462 Vi</b> Custom Panel	Right	11503420	\$8,799
<b>F2472 Vi</b> Custom Panel	Left	11503430	\$9,249
<b>F2472 SF</b> Clean Touch Steel™ w/ DS6708 ContourLine Handle	Left	11503530	\$9,499

### Specifications

Width	17 3/4 in (451 mm)
Height	83 3/4 – 85 3/16 in (2127 – 2164 mm)
Depth	24 in (610 mm)
Freezer Capacity	7.73 cu.ft. (219 l)
Shipping Weight	328 lbs (149 kg)
Annual Energy Usage	428 kWh

### Fridge Features

- Push2Open Door
- MasterFresh
- BrilliantLight
- MasterSensor Controls
- SoftClose Door
- Temperature Zones: 1
- MaxLoad Hinge
- Acoustic Door and Temperature Alarm
- Ice & Water Dispenser
- Maximum Storage Capacity and Flexibility:  
3 Shelves, 2 Drawers, 1 small Door basket,  
3 large Door baskets
- SuperCool
- Sabbath Mode
- CleanSteel Back Wall

Optional Accessories Vi	Material	UMRP
KFP 1845 18 in Clean Touch Steel™ Panel (No Logo, w/o handle)	11499570	\$999
KTK 1820 SS 18 in Toekick	10984060	\$199
KSK 2002 Merge Kit	10984130	\$1,499
KWF 2000 Water Filter 2.0 (MC 2xx2)	11480330	\$189

Optional Accessories SF	Material	UMRP
KTF 1042 42 in Top Frame	10984920	\$399
KTF 1048 48 in Top Frame	12556870	\$399
KTF 1054 54 in Top Frame	12556860	\$399
KTF 1060 60 in Top Frame	12556850	\$399
KTF 1066 66 in Top Frame	12556810	\$399
KTF 1072 72 in Top Frame	12556830	\$399
KTK 1820 SS 18 in Toekick	10984060	\$199
KSK 2002 Merge Kit	10984130	\$1,499
KWF 2000 Water Filter 2.0 (MC 2xx2) Handle	11480330	\$189
DS 7308 GEN 7000 ContourLine Handle	12047020	\$185.90

## MasterCool Freezers – 24" Columns



Model	Hinge	Material	UMRP
<b>F2672 Vi</b> Custom Panel	Left	11503550	\$9,849
<b>Specifications</b>			
Width	23 3/4 in (604 mm)		
Height	83 3/4 – 85 3/16 in (2127 – 2164 mm)		
Depth	24 in (610 mm)		
Freezer Capacity	11.23 cu.ft. (318 l)		
Shipping Weight	375 lbs (170 kg)		
Annual Energy Usage	454 kWh		

Fridge Features
<ul style="list-style-type: none"> <li>• Push2Open Door</li> <li>• MasterFresh</li> <li>• BrilliantLight</li> <li>• MasterSensor Controls</li> <li>• SoftClose Door</li> <li>• Temperature Zones: 1</li> <li>• MaxLoad Hinge</li> <li>• Acoustic Door and Temperature Alarm</li> <li>• Ice &amp; Water Dispenser</li> <li>• Maximum Storage Capacity and Flexibility: 3 Shelves, 2 Drawers, 1 small Door basket, 3 large Door baskets</li> <li>• SuperCool</li> <li>• Sabbath Mode</li> <li>• CleanSteel Back Wall</li> </ul>

Optional Accessories Vi	Material	UMRP
KFP 2445 24 in Clean Touch Steel™ Panel (No Logo, w/o handle)	11499620	\$1,149
KTK 2420 SS 24 in Toekick	10984070	\$199
KSK 2002 Merge Kit	10984130	\$1,499
KWF 2000 Water Filter 2.0 (MC 2xx2)	11480330	\$189

Optional Accessories SF	Material	UMRP
KTF 1042 42 in Top Frame	10984920	\$399
KTF 1048 48 in Top Frame	12556870	\$399
KTF 1054 54 in Top Frame	12556860	\$399
KTF 1060 60 in Top Frame	1255685	\$399
KTF 1066 66 in Top Frame	12556810	\$399
KTF 1072 72 in Top Frame	12556830	\$399
KTK 2420 SS 24 in Toekick	10984070	\$199
KSK 2002 Merge Kit	10984130	\$1,499
DS 7308 GEN 7000 ContourLine Handle	12047020	\$185.90

## MasterCool Freezers – 30" Columns

F2802 Vi



F2812 Vi



F2812 SF



Model	Hinge	Material	UMRP
<b>F2802 Vi</b> Custom Panel	Right	11503330	\$9,999
<b>F2812 Vi</b> Custom Panel	Left	11503340	\$10,499
<b>F2812 SF</b> Clean Touch Steel™ w/ DS6708 ContourLine Handle	Left	11503350	\$11,549

Specifications	
Width	29 3/4 in (756 mm)
Height	83 3/4 – 85 3/16 in (2127 – 2164 mm)
Depth	24 in (610 mm)
Freezer Capacity	15.75 cu.ft. (446 l)
Shipping Weight	395 lbs (179 kg)
Annual Energy Usage	479 kWh

Fridge Features
<ul style="list-style-type: none"> <li>• Push2Open Door</li> <li>• MasterFresh</li> <li>• BrilliantLight</li> <li>• MasterSensor Controls</li> <li>• SoftClose Door</li> <li>• Temperature Zones: 1</li> <li>• MaxLoad Hinge</li> <li>• Acoustic Door and Temperature Alarm</li> <li>• IceMaker w/ plumbed water connection</li> <li>• Maximum Storage Capacity and Flexibility: 3 Shelves, 2 Drawers, 1 small Door basket, 3 large Door baskets</li> <li>• SuperCool</li> <li>• Sabbath Mode</li> <li>• CleanSteel Back Wall</li> </ul>

Optional Accessories Vi	Material	UMRP
KFP 3005 24 in Clean Touch Steel™ Panel (No Logo, w/o handle)	11499080	\$1,149
KTK 3020 SS 30 in Toekick	10984090	\$199
KSK 2002 Merge Kit	10984130	\$1,499

Optional Accessories SF	Material	UMRP
KTF 1048 48 in Top Frame	12556870	\$399
KTF 1054 54 in Top Frame	12556860	\$399
KTF 1060 60 in Top Frame	12556850	\$399
KTF 1066 66 in Top Frame	12556810	\$399
KTF 1072 72 in Top Frame	12556830	\$399
KTK 3020 SS 30 in Toekick	0984090	\$199
KSK 2002 Merge Kit	10984130	\$1,499
KWF 2000 Water Filter 2.0 (MC 2xx2) Handle	11480330	\$189
DS 7308 GEN 7000 ContourLine Handle	12047020	\$185.90

# MasterCool Freezers – 36" Columns



Model	Hinge	Material	UMRP	Optional Accessories Vi	Material	UMRP
<b>F2902 Vi</b> Custom Panel	Right	11503360	\$10,799	KFP 3605 36 in Clean Touch Steel™ Panel (No Logo, w/o handle)	11499100	\$1,199
<b>F2912 Vi</b> Custom Panel	Left	11503390	\$10,799	KTK 3620 SS 24 in Toekick	10984110	\$199
<b>F2912 SF</b> Clean Touch Steel™ w/ DS6708 ContourLine Handle	Left	11503410	\$11,549	KSK 2002 Merge Kit	10984130	\$1,499
				KWF 2000 Water Filter 2.0 (MC 2x2)	11480330	\$189

Specifications	
Width	35 3/4 in (908 mm)
Height	83 3/4 – 85 3/16 in (2127 – 2164 mm)
Depth	24 in (610 mm)
Freezer Capacity	19.39 cu.ft. (549 l)
Shipping Weight	462 lbs (210 kg)
Annual Energy Usage	528 kWh

- Fridge Features**
- Push2Open Door
  - MasterFresh
  - BrilliantLight
  - MasterSensor Controls
  - SoftClose Door
  - Temperature Zones: 1
  - MaxLoad Hinge
  - Acoustic Door and Temperature Alarm
  - IceMaker w/ plumbed water connection
  - Maximum Storage Capacity and Flexibility:  
3 Shelves, 2 Drawers, 1 small Door basket,  
3 large Door baskets
  - SuperCool
  - Sabbath Mode
  - CleanSteel Back Wall

Optional Accessories SF	Material	UMRP
KTF 1054 54 in Top Frame	12556860	\$399
KTF 1060 60 in Top Frame	12556850	\$399
KTF 1066 66 in Top Frame	12556810	\$399
KTF 1072 72 in Top Frame	12556830	\$399
KTK 3620 SS 36 in Toekick	10984110	\$399
KSK 2002 Merge Kit	10984130	\$1,499
KWF 2000 Water Filter 2.0 (MC 2x2) Handle	11480330	\$189
DS 7308 GEN 7000 ContourLine Handle	12047020	\$185.90

# Product Highlights – MasterCool Wine Storage

Feature	Description (see specific models for details)
<b>MasterSensor Controls</b>	Incredibly convenient: a whole range of settings can be controlled easily with the tap of a finger on the color touch display.
<b>BrilliantLight</b>	Each area of the unit is perfectly illuminated by many LED light strips strategically placed throughout.
<b>Push2Open</b>	For a handleless design, just apply slight pressure to the door to open.
<b>SoftClose</b>	With just a gentle touch, our dynamic doors close on their own. Integrates perfectly within a handleless kitchen.
<b>Temperature Zones</b>	Store up to three different types of wine with different temperature zones.
<b>FlexiFrame Racks</b>	Individual wooden slats can be easily moved to make room for larger wine bottles.
<b>SommelierSet</b>	Perfect for wine connoisseurs: prepare cooled wine glasses and wine for decanting. Drink perfectly conditioned wine even from opened bottles.
<b>NoteBoard</b>	Every bottle rack features a removable, magnetic strip for labeling bottles.
<b>Miele@home/ Mobile Control</b>	Access your appliance from your smart device for maximum convenience.

# MasterCool Wine Storage – 24" Columns



Model	Hinge	Material	UMRP
<b>KWT 2602 Vi</b> Custom Panel	Right	11503590	\$9,449
<b>KWT 2602 SF</b> Clean Touch Steel™ w/ DS6708 ContourLine Handle	Right	11503620	\$10,099
<b>KWT 2612 Vi</b> Custom Panel	Left	11503610	\$9,449
<b>KWT 2612 SF</b> Clean Touch Steel™ w/ DS6708 ContourLine Handle	Left	11503640	\$10,099

### Specifications

Width	23 3/4 in (604 mm)
Height	83 3/4 – 853/16 in (2127 – 2164 mm)
Depth	24 in (610 mm)
Shipping Weight	357 lbs (162 kg)
Annual Energy Usage	179 kWh

### Features

- Push2Open Door
- MasterFresh
- BrilliantLight
- MasterSensor Controls
- SoftClose Door
- Temperature Zones: 3
- Maximum Storage Capacity and Flexibility:  
104 x 0.75 l bottlesDynaCool
- MaxLoad Hinge
- Acoustic Door and Temperature Alarm
- FlexiFrame Racks: 13
- UV Tinted Glass
- NoteBoard
- Sabbath Mode

Optional Accessories (Vi)	Material	UMRP
KFP 2455 Clean Touch Steel™ Panel (No Logo, w/o handle)	11499630	\$1,279
KTK 2420 SS 24 in Toekick	10984070	\$199
KSK 2002 Merge Kit	10984130	\$1,499

Optional Accessories (SF)	Material	UMRP
KTF 1042 42 in Top Frame	10984920	\$399
KTF 1048 48 in Top Frame	12556870	\$399
KTF 1054 54 in Top Frame	12556860	\$399
KTF 1060 60 in Top Frame	12556850	\$399
KTF 1066 66 in Top Frame	12556810	\$399
KTF 1072 72 in Top Frame	12556830	\$399
KTK 2420 SS 24 in Toekick	10984070	\$199
KSK 2002 Merge Kit	10984130	\$1,499
DS 7308 GEN 7000 ContourLine Handle	12047020	\$185.90

# MasterCool Wine Storage – 24" Columns w/ SommelierSet



Model	Hinge	Material	UMRP
<b>KWT 2662 ViS</b> Custom Panel	Right	11503650	\$10,599
<b>KWT 2672 ViS</b> Custom Panel	Left	11503660	\$10,599

### Specifications

Width	23 3/4 in (604 mm)
Height	83 3/4 – 853/16 in (2127 – 2164 mm)
Depth	24 in (610 mm)
Shipping Weight	357 lbs (162 kg)
Annual Energy Usage	179 kWh

### Features

- Push2Open Door
- MasterFresh
- BrilliantLight
- MasterSensor Controls
- SoftClose Door
- Temperature Zones: 3
- Maximum Storage Capacity and Flexibility:  
77 x 0.75 l bottles
- DynaCool
- MaxLoad Hinge
- Acoustic Door and Temperature Alarm
- FlexiFrame Racks: 9
- UV Tinted Glass
- SommelierSet
- NoteBoard
- Sabbath Mode

Optional Accessories (Vi)	Material	UMRP
KFP 2455 Clean Touch Steel™ Panel (No Logo, w/o handle)	11499630	\$1,279
KTK 2420 SS 24 in Toekick	10984070	\$199
KSK 2002 Merge Kit	10984130	\$1,499

Optional Accessories (SF)	Material	UMRP
KTF 1042 42 in Top Frame	10984920	\$399
KTF 1048 48 in Top Frame	12556870	\$399
KTF 1054 54 in Top Frame	12556860	\$399
KTF 1060 60 in Top Frame	12556850	\$399
KTF 1066 66 in Top Frame	12556810	\$399
KTF 1072 72 in Top Frame	12556830	\$399
KTK 2420 SS 24 in Toekick	10984070	\$199
KSK 2002 Merge Kit	10984130	\$1,499
DS 7308 GEN 7000 ContourLine Handle	12047020	\$185.90

# Handle Options

GEN 7000	MODEL	MATERIAL	TRIM / COLOR	HANDLE WIDTH	COOKING	Vi DISH-WASHERS	Vi COOLING	SF MASTER-COOL	UMRP
	<b>DS 7000</b>	11345890	PureLine Stainless steel <sup>1</sup>	15 3/4 in	•	•	•	–	\$164
	<b>DS 7000</b>	11345930	VitroLine Obsidian black <sup>1</sup>	15 3/4 in	•	•	•	–	\$340
	<b>DS 7000</b>	11345940	VitroLine Brilliant white <sup>1</sup>	15 3/4 in	•	•	•	–	\$340
	<b>DS 7000</b>	11345950	VitroLine Graphite grey <sup>1</sup>	15 3/4 in	•	•	•	–	\$340
	<b>DS 7308</b>	12047020	ContourLine Stainless steel standard handle	21 1/8 in	•	•	•	•	\$186
	<b>DS 7708</b>	12047000	ContourLine Stainless steel swiveling handle	21 1/8 in	•	•	•	•	\$230
	<b>DS 7808</b>	12047030	VitroLine Obsidian black	19 11/16 in	•	•	•	–	\$384
	<b>DS 7808</b>	12047050	VitroLine Graphite grey	19 11/16 in	•	•	•	–	\$384
	<b>DS 7808</b>	12047060	VitroLine Brilliant white	19 11/16 in	•	•	•	–	\$384
	<b>DS 7808</b>	12046910	PureLine Stainless steel	19 11/16 in	•	•	•	–	\$186

**Miele**

Miele, Inc.  
9 Independence Way  
Princeton, NJ 08540

**mieleusa.com**  
**1-800-843-7231**

**Find your nearest Miele Experience Center in:**

Beverly Hills  
Chicago  
Coral Gables  
Manhattan  
Princeton  
Seattle  
Tysons Corner