


Miele



Cleaning Price List

2026

Table of Contents

Dishwashers	03
Dishwasher Feature Highlights	03
Professional for the Home Dishwashers	18
Professional for the Home Dishwasher Feature Highlights	18
Professional for the Home Dishwasher	19
Laundry	32
Laundry Feature Highlights	32
Laundry	33
Rotary Ironer	39
Professional for the Home Laundry	40
Professional for the Home Laundry Feature Highlights	41
Professional for the Home Laundry	42
Professional Rotary Ironer	43
Accessories & Consumables – Laundry	44
Accessories & Consumables – Dishwashers	45
Handles	46

Product Highlights – Dishwashers

Feature	Description (see specific models for details)
EcoPower Technology	With an innovative water flow system, G 7000 dishwashers save both water and energy. In the Auto program, run a full cycle using less than 1.6 gallons of water.
3D MultiFlex Cutlery Tray	Provides a new level of convenience by adapting instantly to accommodate larger utensils, as well as taller stemware in the upper basket.
BrilliantLight	Four powerful LED lights illuminate the dishwasher from the inside out.
AutoOpen Drying	The dishwasher door automatically opens at the end of the cycle, allowing air to escape and circulate for perfect drying.
AutoDosing with PowerDisk®	In G 7000 dishwashers, the integrated PowerDisk® automatically dispenses the correct amount of detergent in accordance with the selected program and degree of soiling.
FlexLine Baskets	Easily adjustable to accommodate a wide array of dishware, utensils, stemware, pots and pans.
Knock2Open	Automatic door opening after two knocks. Integrates seamlessly in a handleless kitchen.
QuickIntenseWash	Excellent cleaning and drying results for normally soiled dishes in only 58 minutes.
SaniWash	High temperature program for deep cleaning results.
Miele@home	Access your appliance from your smart device for maximum convenience.
AutoSensor	Automatically adjusts program Time, Temperature, & Water volume based on multiple measurements of turbidity.
Certified Hygiene Seal	All Miele dishwashers remove more than 99.9% of specific bacteria.*
Golden Virus Seal	All Miele dishwashers remove more than 99.9% of all viruses.*



Certified Hygiene Seal

* Approved by Rhein-Waal University. This certification attests that all G 5000 and G 7000 dishwashers with the SaniWash or Pots & Pans program offer particularly hygienic cleaning. This applies both with (standard) detergent or even without cleaning agent altogether.



Golden Virus Seal

* According to the InFluenc_H – Institute for Integrative Hygiene and Virology, cleaning with ProfiLine dishwashers using Miele's ProCare Shine 12 GC cleaning agents removes enveloped and non-enveloped viruses (e.g. coronavirus, influenza, or noroviruses) in the Pots & Pans and Sanitize programs, as well as enveloped viruses (excluding Hepatitis B) in the QuickIntenseWash and Universal programs, even if load items are difficult to reprocess.

Dishwashers – 24" Pre-Finished



Model	Handle Type	Material	UMRP
G 5008 SCU Clean Touch Steel™	Integrated	11966810	\$1,599

Specifications

Width	23 9/16 in (598 mm)
Height	33 11/16 – 36 1/4 in (855 – 920 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	121 lbs (55 kg)
Annual Energy Usage	230 kWh
Decibel rating	44 dBA

Features

- Controls – DirectSelect, front
- EcoPower Technology
- Original Cutlery Tray
- Basket Design – Comfort
- Door design – ComfortClose
- No. of Standard Place Settings – 16
- Double Waterproof System
- AutoSensor / Load Sensor

Programs

- Normal
- QuickIntenseWash
- Pots & Pans
- SaniWash
- Rinse & Hold

Options

- Express
- Extra Clean
- Extra Dry
- Delay Start

Dishwashers – 24" Fully Integrated

G 5051 SCVi ADA



Model	Handle Type	Material	UMRP
G 5051 SCVi ADA Custom Panel	No Handle	11636710	\$1,599

Specifications

Width	23 9/16 in (598 mm)
Height	32 1/16 – 34 1/4 in (814 – 870 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	121 lbs (55 kg)
Annual Energy Usage	230 kWh
Decibel rating	44 dBA
ADA Compliant	Yes

Features

- Controls – DirectSelect, hidden
- EcoPower Technology
- Original Cutlery Tray
- Basket Design – Comfort
- Door design – ComfortClose
- No. of Standard Place Settings – 16
- Double Waterproof System
- AutoSensor / Load Sensor

Programs

- Normal
- QuickIntenseWash
- Pots & Pans
- SaniWash
- Rinse & Hold

Options

- Express
- Extra Clean
- Extra Dry
- Delay Start

Optional Accessories	Material	UMRP
GFVi 701/72 Fully Integrated Panel Full Size, Clean Touch Steel™ 6" Toe-Kick, no handle	12670590	\$379
GFVi 711/72 Fully Integrated Panel Full Size Clean Touch Steel™ 6" Toe-Kick ContourLine handle	12074400	\$489
GBU 5000 Cutlery basket	9614020	\$42

Dishwashers – 24" Fully Integrated

G 5056 SCVi



G 5056 SCVi SF



G 5058 SCVi SFP



Model	Handle Type	Material	UMRP
G 5056 SCVi Custom Panel	No Handle	11636720	\$1,599
G 5056 SCVi SF Clean Touch Steel™	PureLine Handle*	11695330	\$1,749
G 5058 SCVi SFP	Pocket Handle	11966820	\$1,749

Specifications

Width	23 9/16 in (598 mm)
Height	33 11/16 – 36 1/4 in (855 – 920 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	121 lbs (55 kg)
Annual Energy Usage	230 kWh
Decibel rating	44 dBA
ADA Compliant	No

Features

- Controls – DirectSelect, hidden
- EcoPower Technology
- Original Cutlery Tray
- Basket Design – Comfort
- Door design – ComfortClose
- No. of Standard Place Settings – 16
- Double Waterproof System
- AutoSensor / Load Sensor

Programs

- Normal
- QuickIntenseWash
- Pots & Pans
- SaniWash
- Rinse & Hold

Options

- Express
- Extra Clean
- Extra Dry
- Delay Start

Optional Accessories Vi

Material	UMRP
GFVi 701/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, no handle	12670600 \$379
GFVi 710/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, PureLine handle	12074350 \$489
GFVi 711/72 Fully Integrated Panel Full Size, Clean Touch Steel™, 6" Toe-Kick, ContourLine handle	12074400 \$489
GFVi 711/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, ContourLine handle	12074450 \$489
GFVi 712/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, Range Panel	12074470 \$489
GFVi 709/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, Pocket handle	12672750 \$489
GBU 5000 Cutlery basket	9614020 \$42

*Handle not included in the UMRP – available for purchase separately.

Dishwashers – 24" Fully Integrated

G 5266 SCVi



G 5266 SCVi SF



G 5266 SCVi SFP



Model	Handle Type	Material	UMRP	Optional Accessories Vi	Material	UMRP
G 5266 SCVi Custom Panel	No Handle	11636740	\$1,899	GFVi 701/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, no handle	12670600	\$379
G 5266 SCVi SF Clean Touch Steel™	PureLine Handle*	11636750	\$2,099	GFVi 710/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, PureLine handle	12074350	\$489
G 5266 SCVi SFP	Pocket Handle	11695340	\$2,099	GFVi 711/72 Fully Integrated Panel Full Size, Clean Touch Steel™, 6" Toe-Kick, ContourLine handle	12074400	\$489
Specifications				GFVi 711/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, ContourLine handle	12074450	\$489
Width	23 9/16 in (598 mm)			GFVi 712/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, Range Panel	12074470	\$489
Height	33 11/16 – 36 1/4 in (855 – 920 mm)			GFVi 709/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, Pocket handle	12672750	\$489
Depth	22 7/16 in (570 mm)			GBU 5000 Cutlery basket	9614020	\$42
Shipping Weight	121 lbs (55 kg)					
Annual Energy Usage	230 kWh					
Decibel rating	42 dBA					
ADA Compliant	No					
Features						
• Controls – DirectSelect, hidden		• SensorDry				
• EcoPower Technology		• Double Waterproof System				
• 3D MultiFlex Cutlery Tray		• AutoSensor / Load Sensor				
• Basket Design – Comfort		• Door design – ComfortClose				
• AutoOpen Drying		• Water Softener				
• No. of Standard Place Settings – 16						
Programs						
• Normal		• SaniWash				
• QuickIntenseWash		• Rinse & Hold				
• Pots & Pans						
Options						
• Express		• Extra Dry				
• Extra Clean		• Delay Start				

*Handle not included in the UMRP – available for purchase separately.

Dishwashers – 24" Pre-Finished

G 7216 SCU



Model	Handle Type	Material	UMRP
G 7216 SCU Clean Touch Steel™	Integrated Handle*	12497130	\$1,999

Specifications

Width	23 9/16 in (598 mm)
Height	33 11/16 – 36 1/4 in (855 – 920 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	121 lbs (55 kg)
Annual Energy Usage	230 kWh
Decibel rating	42 dBA
ADA Compliant	No

Features

- | | |
|---------------------------------------|--------------------------------|
| • Controls – DirectSelect, front | • Basket Design – ExtraComfort |
| • EcoPower Technology | • SensorDry |
| • 3D MultiFlex Cutlery Tray | • Double Waterproof System |
| • AutoOpen Drying | • AutoSensor / Load Sensor |
| • No. of Standard Place Settings – 16 | • Water Softener |
| | • Miele@home |

Programs

- Normal
- QuickIntenseWash
- Pots & Pans
- SaniWash
- Rinse & Hold
- China & Crystal

Options

- Express
- Extra Clean
- Extra Dry
- Intense Zone
- Delay Start

*Handle not included in the UMRP – available for purchase separately.

Dishwashers – 24" Fully Integrated

G 7266 SCVi



G 7266 SCVi SF



Model	Handle Type	Material	UMRP
G 7266 SCVi Custom Panel	No Handle	12497140	\$1,999
G 7266 SCVi SF Clean Touch Steel™	ContourLine Handle*	12497150	\$2,199

Specifications

Width	23 9/16 in (598 mm)
Height	33 11/16 – 36 1/4 in (855 – 920 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	121 lbs (55 kg)
Annual Energy Usage	230 kWh
Decibel rating	42 dBA
ADA Compliant	No

Features

- Controls – DirectSelect, front
- EcoPower Technology
- 3D MultiFlex Cutlery Tray
- AutoOpen Drying
- SensorDry
- No. of Standard Place Settings – 16
- Miele@home
- Basket Design – ExtraComfort
- Double Waterproof System
- AutoSensor / Load Sensor
- Water Softener

Programs

- Normal
- QuickIntenseWash
- Pots & Pans
- SaniWash
- Rinse & Hold
- China & Crystal

Options

- Express
- Extra Clean
- Extra Dry
- Intense Zone
- Delay Start

Optional

Accessories Vi	Material	UMRP
GFVi 701/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, no handle	12670600	\$379
GFVi 710/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, PureLine handle	12074350	\$489
GFVi 711/72 Fully Integrated Panel Full Size, Clean Touch Steel™, 6" Toe-Kick, ContourLine handle	12074400	\$489
GFVi 711/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, ContourLine handle	12074450	\$489
GFVi 712/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, Range Panel	12074470	\$489
GFVi 709/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, Pocket handle	12672750	\$489
GBU 5000 Cutlery basket	9614020	\$42

*Handle not included in the UMRP – available for purchase separately.

Dishwashers – 24" Fully Integrated

G 7186 SCVi



G 7186 SCVi SFP



Model	Handle Type	Material	UMRP
G 7186 SCVi Custom Panel	No Handle	12496990	\$2,199
G 7186 SCVi SFP	Pocket Handle*	12496690	\$2,399

Specifications

Width	23 9/16 in (598 mm)
Height	33 11/16 – 36 1/4 in (855 – 920 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	121 lbs (55 kg)
Annual Energy Usage	230 kWh
Decibel rating	42 dBA
ADA Compliant	No

Features

• Controls – DirectSelect, hidden	• SensorDry
• EcoPower Technology	• Double Waterproof System
• 3D MultiFlex Cutlery Tray	• AutoSensor / Load Sensor
• Basket Design – Comfort	• Water Softener
• AutoOpen Drying	• Door design – ComfortClose
• No. of Standard Place Settings – 16	• AutoDosing with PowerDisk®

Programs

• Normal	• SaniWash
• QuickIntenseWash	• Rinse & Hold
• Pots & Pans	• China & Crystal

Options

• Express	• Intense Zone
• Extra Clean	• Delay Start
• Extra Dry	

Optional Accessories Vi

Material	UMRP
GFVi 701/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, no handle	12670600 \$379
GFVi 710/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, PureLine handle	12074350 \$489
GFVi 711/72 Fully Integrated Panel Full Size, Clean Touch Steel™, 6" Toe-Kick, ContourLine handle	12074400 \$489
GFVi 711/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, ContourLine handle	12074450 \$489
GFVi 712/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, Range Panel	12074470 \$489
GFVi 709/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, Pocket handle	12672750 \$489
GBU 5000 Cutlery basket	9614020 \$42

*Handle not included in the UMRP – available for purchase separately.

Dishwashers – 24" Pre-Finished

G 7196 SCVi SF



G 7193 SCVi ADA



Model	Handle Type	Material	UMRP
G 7196 SCVi SF Clean Touch Steel™	PureLine Handle*	12496710	\$2,399

Specifications

Width	23 9/16 in (598 mm)
Height	33 11/16 – 36 1/4 in (855 – 920 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	121 lbs (55 kg)
Annual Energy Usage	230 kWh
Decibel rating	42 dBA
ADA Compliant	No

Features

- Controls – DirectSelect, hidden
- EcoPower Technology
- 3D MultiFlex Cutlery Tray
- AutoOpen Drying
- SensorDry
- No. of Standard Place Settings – 16
- AutoDosing with PowerDisk®
- Basket Design – ExtraComfort
- Double Waterproof System
- Miele@home
- AutoSensor / Load Sensor
- Water Softener

Programs

- Normal
- QuickIntenseWash
- Pots & Pans
- SaniWash
- Rinse & Hold
- China & Crystal

Options

- Express
- Extra Clean
- Intense Zone
- Delay Start

Model	Handle Type	Material	UMRP
G 7193 SCVi ADA Custom Panel	No Handle	12496700	\$2,199

Specifications

Width	23 9/16 in (598 mm)
Height	32 1/16 – 34 1/4 in (814 – 870 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	121 lbs (55 kg)
Annual Energy Usage	230 kWh
Decibel rating	42 dBA
ADA Compliant	Yes

Features

- Controls – DirectSelect, hidden
- EcoPower Technology
- 3D MultiFlex Cutlery Tray
- AutoOpen Drying
- SensorDry
- No. of Standard Place Settings – 16
- AutoDosing with PowerDisk®
- Basket Design – ExtraComfort
- Double Waterproof System
- Miele@home
- AutoSensor / Load Sensor
- Water Softener

Programs

- Normal
- QuickIntenseWash
- Pots & Pans
- SaniWash
- Rinse & Hold
- China & Crystal

Options

- Express
- Extra Clean
- Extra Dry
- Intense Zone
- Delay Start

Optional Accessories	Material	UMRP
GFVi 701/72 Fully Integrated Panel Full Size Clean Touch Steel™ 6" Toe-Kick no handle	12670590	\$379
GFVi 711/72 Fully Integrated Panel Full Size Clean Touch Steel™ 6" Toe-Kick ContourLine handle	12074400	\$489
GBU 5000 Cutlery basket	9614020	\$42

*Handle not included in the UMRP – available for purchase separately.

Dishwashers – 24" Fully Integrated



Model	Handle Type	Material	UMRP
G 7766 SCVi Custom Panel	No Handle	12496900	\$2,999

G 7766 SCVi SF	ContourLine Handle*	12496910	\$3,199
-----------------------	---------------------	----------	---------

Specifications

Width	23 9/16 in (598 mm)
Height	33 11/16 – 36 1/4 in (855 – 920 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	121 lbs (55 kg)
Annual Energy Usage	230 kWh
Decibel rating	39 dBA (37 Extra Quiet Program)

Features

- Controls – DirectSensor, hidden
- EcoPower Technology
- 3D MultiFlex Cutlery Tray
- BrilliantLight
- AutoOpen Drying
- SensorDry
- No. of Standard Place Settings – 16
- AutoDosing with PowerDisk®
- Basket Design – MaxiComfort
- Double Waterproof System
- Miele@home/AutoStart
- AutoSensor/ Load Sensor
- Water Softener

Programs

- Normal
- QuickIntenseWash
- Pots & Pans
- SaniWash
- Rinse & Hold
- China & Crystal
- Clean Machine
- Economy
- Energy Saver
- Extra Quiet – 37 dBA
- Filters
- SensorWash

Options

- Express
- FlexiTimer
- Extra Economical
- Extra Clean
- Extra Dry
- Intense Zone
- Delay Start

Optional Accessories Vi

Material	UMRP
GFVi 701/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, no handle	12670600 \$379
GFVi 710/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, PureLine handle	12074350 \$489
GFVi 711/72 Fully Integrated Panel Full Size, Clean Touch Steel™, 6" Toe-Kick, ContourLine handle	12074400 \$489
GFVi 711/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, ContourLine handle	12074450 \$489
GFVi 712/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, Range Panel	12074470 \$489
GFVi 709/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, Pocket handle	12672750 \$489
GBU 5000 Cutlery basket	9614020 \$42

*Handle not included in the UMRP – available for purchase separately.

Dishwashers – 24" Fully Integrated Knock2Open

G 7791 SCVi K2O ADA



Model	Handle Type	Material	UMRP
G 7791 SCVi K2O ADA	No Handle	12496920	\$3,499

Specifications

Width	23 9/16 in (598 mm)
Height	32 1/16 – 34 1/4 in (814 – 870 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	121 lbs (55 kg)
Annual Energy Usage	230 kWh
Decibel rating	39 dBA (37 Extra Quiet Program)
ADA Compliant	Yes

Features

- Controls – DirectSensor, hidden
- EcoPower Technology
- 3D MultiFlex Cutlery Tray
- BrilliantLight
- AutoOpen Drying
- SensorDry
- No. of Standard Place Settings – 16
- AutoDosing with PowerDisk®
- Basket Design – MaxiComfort
- Double Waterproof System
- Miele@home/AutoStart
- Knock2Open
- AutoSensor / Load Sensor
- Water Softener

Programs

- Normal
- QuickIntenseWash
- Pots & Pans
- SaniWash
- Rinse & Hold
- Filters
- China & Crystal
- Clean Machine
- Economy
- Extra Quiet – 37 dBA
- Energy Saver
- SensorWash

Options

- Express
- FlexiTimer
- Extra Economical
- Extra Clean
- Extra Dry
- Intense Zone
- Delay Start

Optional Accessories	Material	UMRP
GFVi 701/72 Fully Integrated Panel Full Size Clean Touch Steel™ 6" Toe-Kick no handle	12670590	\$379
GBU 5000 Cutlery basket	9614020	\$42

Dishwashers – 24" Integrated

G 7936 SCi



Model	Handle Type	Material	UMRP
G 7936 SCi Custom Panel	No Handle	12496970	\$3,999

Specifications

Width	23 9/16 in (598 mm)
Height	33 11/16 – 36 1/4 in (855 – 920 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	121 lbs (55 kg)
Annual Energy Usage	230 kWh
Decibel rating	39 dBA (37 Extra Quiet Program)

Features

- Controls – M Touch, front
- EcoPower Technology
- 3D MultiFlex Cutlery Tray
- BrilliantLight
- AutoOpen Drying
- SensorDry
- No. of Standard Place Settings – 16
- AutoDosing with PowerDisk®
- Basket Design – MaxiComfort
- Double Waterproof System
- Miele@home/AutoStart
- AutoSensor / Load Sensor
- Water Softener

Programs

- Normal
- QuickIntenseWash
- Pots & Pans
- SaniWash
- Rinse & Hold
- China & Crystal
- Economy
- Energy Saver
- Extra Quiet – 37 dBA
- Tall Items
- Filters
- Glass – No Rinse Aid (Warm)
- Clean Machine
- SensorWash

Options

- Express
- FlexiTimer
- Extra Economical
- Extra Clean
- Extra Dry
- Intense Zone
- Soak
- Pre-Rinse
- Delay Start

Optional Accessories	Material	UMRP
GFV 60/60-7 Fully Integrated Panel Full Size, Clean Touch Steel™, 6" Toe-Kick	12670320	\$319
GFV 60/65-7 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick	12670410	\$319
GBU 5000 Cutlery basket	9614020	\$42

Dishwashers – 24" Fully Integrated Knock2Open

G 7986 SCVi K2O



Model	Handle Type	Material	UMRP
G 7986 SCVi K2O Custom Panel	No Handle	12496980	\$4,099

Specifications

Width	23 9/16 in (598 mm)
Height	33 11/16 – 36 1/4 in (855 – 920 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	121 lbs (55 kg)
Annual Energy Usage	230 kWh
Decibel rating	39 dBA (37 Extra Quiet Program)
ADA Compliant	No

Features

• Controls – M Touch, hidden	• AutoDosing with PowerDisk®
• EcoPower Technology	• Basket Design – MaxiComfort
• 3D MultiFlex Cutlery Tray	• Double Waterproof System
• BrilliantLight	• Miele@home/AutoStart
• AutoOpen Drying	• Knock2Open
• SensorDry	• AutoSensor / Load Sensor
• No. of Standard Place Settings – 16	• Water Softener

Programs

• Normal	• Extra Quiet – 37 dBA
• QuickIntenseWash	• Filters
• Pots & Pans	• Glass – No Rinse Aid (Warm)
• SaniWash	• Clean Machine
• Rinse & Hold	• Energy Saver
• China & Crystal	• Tall Items
• Economy	• SensorWash

Options

• Express	• Extra Dry
• FlexiTimer	• Intense Zone
• Extra Economical	• Soak
• Extra Clean	• Pre-Rinse
	• Delay Start

Optional Accessories Vi	Material	UMRP
GFVi 701/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, no handle	12670600	\$379
GFVi 710/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, PureLine handle	12074350	\$489
GFVi 711/72 Fully Integrated Panel Full Size, Clean Touch Steel™, 6" Toe-Kick, ContourLine handle	12074400	\$489
GFVi 711/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, ContourLine handle	12074450	\$489
GFVi 712/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, Range Panel	12074470	\$489
GFVi 709/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, Pocket handle	12672750	\$489
GBU 5000 Cutlery basket	9614020	\$42

Dishwashers – 18" SlimLine Fully Integrated

G 5482 SCVi



Model	Handle Type	Material	UMRP
G 5482 SCVi Custom Panel	No Handle	11636760	\$1,699

Specifications

Width	17 5/8 in (448 mm)
Height	32 1/16 – 34 1/4 in (814 – 880 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	121 lbs (55 kg)
Annual Energy Usage	230 kWh
Decibel rating	44 dBA
ADA Compliant	Yes

Features

- Controls – DirectSelect, hidden
- EcoPower Technology
- Original Cutlery Tray
- Basket Design – Comfort
- No. of Standard Place Settings – 10
- Double Waterproof System
- AutoSensor / Load Sensor

Programs

- Normal
- QuickIntenseWash
- Pots & Pans
- SaniWash
- Rinse & Hold

Options

- Express
- Extra Clean

Optional Accessories	Material	UMRP
GFVi 453/72 7 SlimLine Clean Touch Steel™ panel without Handle, 6" Toe-Kick	12670470	\$319
GFVi 453/77 7 SlimLine Clean Touch Steel™ panel without Handle, 4" Toe-Kick	12670480	\$319
GBU 5000 Cutlery basket	9614020	\$42

Dishwashers – 18" SlimLine Fully Integrated

G 5892 SCVi



Model	Handle Type	Material	UMRP
G 5892 SCVi Custom Panel	No Handle	11636790	\$2,699

Specifications

Width	17 5/8 in (448 mm)
Height	32 1/16 – 34 1/4 in (814 – 880 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	107 lbs (48.5kg)
Annual Energy Usage	200 kWh
Decibel rating	42 dBA
ADA Compliant	Yes

Features

- Controls – DirectSelect, hidden
- EcoPower Technology
- 3D MultiFlex Cutlery Tray
- BrilliantLight
- AutoOpen Drying
- No. of Standard Place Settings – 10
- SensorDry
- Basket Design – MaxiComfort
- Double Waterproof System
- Miele@home/AutoStart
- AutoSensor / Load Sensor
- Water Softener

Programs

- Normal
- QuickIntenseWash
- Pots & Pans
- SaniWash
- Rinse & Hold
- China & Crystal
- Economy
- Energy Saver
- Extra Quiet – 40 dBA
- Filters
- Clean Machine
- SensorWash

Options

- Express
- Extra Clean
- Extra Dry
- Intense Zone

Optional Accessories Vi	Material	UMRP
GFVi 706/77 SlimLine Clean Touch Steel™ panel without Handle, 4" Toe-Kick	11573740	\$319
GFVi 453/72 7 SlimLine Clean Touch Steel™ panel without Handle, 6" Toe-Kick	12670470	\$319
GFVi 453/77 7 SlimLine Clean Touch Steel™ panel without Handle, 4" Toe-Kick	12670480	\$319
GBU 5000 Cutlery basket	9614020	\$42

Product Highlights —

Professional for the Home Dishwashers

ProfiLine

With their impressively short cycle times, ProfiLine Dishwashers are 2.5x faster than domestic dishwashers with only a 24-minute cycle time.

Feature	Description (see specific models for details)
Exemplary Hygiene	Special 'SaniWash' program achieves temperatures of 180°F / 82°C. Final rinse temperatures for selected programs can also be increased for even greater hygiene.
12,500 Program Cycles	ProfiLine dishwashers are tested under laboratory conditions to ensure that they last 12,500 typical cycles and are designed for up to 5 cycles per day.
Intuitive Operation	All programs use intuitive sensor controls. Self-explanatory symbols and key content in plain text speed up program selection and avoid operating errors.
Versatile Baskets	For simple loading and high dishware capacity, ProfiLine represents the perfect stepping stone.
Golden Virus Seal	All Miele dishwashers remove more than 99.9% of all viruses.*

MasterLine

Intelligent dishwashing technology and a powerful heater pump ensure optimum program durations and cleaning results.

Feature	Description (see specific models for details)
Plastic Baskets on two levels	Plastic baskets can be used on two levels in dishwasher models PFD 401, PFD 404 and PFD 408. Three spray arms allow perfect cleaning results to be achieved on both washing levels.
Connection for Dispenser Module	To simplify the use of liquid detergents and rinse aid, up to 2 liquid dispensing modules can be optionally connected, in the PFD 401, PFD 404 and PFD 408 dishwashers.
Perfect GlassCare	Miele Professional dishwashers use Perfect GlassCare in the glasses program. This technology adjusts the water hardness precisely so that all the glasses are thoroughly but gently cleaned.
NSF/ANSI 3 Certified for Sanitization	For facilities that require a NSF/ANSI 3 certified dishwasher, the PFD 408 features a final rinse temperature of 185°F with a 1 minute holding time.



Certified Hygiene Seal

* Approved by Rhein-Waal University. This certification attests that all G 5000 and G 7000 dishwashers with the SaniWash or Pots & Pans program offer particularly hygienic cleaning. This applies both with (standard) detergent or even without cleaning agent altogether.



Golden Virus Seal

* According to the InFluenc_H – Institute for Integrative Hygiene and Virology, cleaning with ProfiLine dishwashers using Miele's ProCare Shine 12 GC cleaning agents removes enveloped and non-enveloped viruses (e.g. coronavirus, influenza, or noroviruses) in the Pots & Pans and Sanitize programs, as well as enveloped viruses (excluding Hepatitis B) in the QuickIntenseWash and Universal programs, even if load items are difficult to reprocess.

Dishwashers – **24" Dishwasher** Pre-Finished

PFD 101U



Model	Handle Type	Material	MAP/Retail
PFD 101U	Integrated Handle	11605420	\$3,920 / 4,020

Specifications

Width	23 9/16 in (598 mm)
Height	31 11/16 – 34 1/4 in (805 – 870 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	113 lbs (51 kg)
Decibel Rating	48 dBA
ADA Compliant	Yes
Electrical Configuration	AC 120V 60 Hz, 15A
Plug	NEMA 5-15P

Programs

- QuickIntenseWash (with hot water connection: 52 mins)
- Universal
- Pots & Pans
- Plastic
- China & Crystal
- SaniWash
- Rinse & Hold
- ECO

Features

- Ideal for Offices, Showrooms, Active Kitchens and Private Homes
- Original Cutlery Basket
- ExtraComfort Basket Design
- No of Standard Place Settings – 13
- Up to 5 Wash Cycles per Day
- AutoOpen Assisted Drying
- Integrated Water Softener
- WiFiConn@ct
- Tested for 12,500 Program Cycles
- Final Rinse Temperature Up to 180°F (82°C) with a Holding Time of 15 Seconds
- Shortest Cycle with Hot Water Connection – 52 min.

Dishwashers – **24" Dishwasher** Integrated

PFD 102i 120V



Model	Handle Type	Material	MAP/Retail
PFD 102i 120V	Integrated Handle	11605430	\$4,825 / \$4,925

Specifications

Width	23 9/16 in (598 mm)
Height	31 11/16 – 34 1/4 in (805 – 870 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	109 lbs (49 kg)
Decibel Rating	48 dBA
ADA Compliant	Yes
Electrical Configuration	AC 120V 60 Hz, 15A
Plug	NEMA 5-15P

Features

- Ideal for Offices, Showrooms, Active Kitchens and Private Homes
- Original Cutlery Basket
- ExtraComfort Basket Design
- No of Standard Place Settings – 13
- Up to 5 Wash Cycles per Day
- AutoOpen Assisted Drying
- Integrated Water Softener
- WiFiConn@ct
- BrilliantLight Interior Lighting
- Tested for 12,500 Program Cycles
- Final Rinse Temperature Up to 180°F (82°C) with a Holding Time of 15 Seconds
- Shortest Cycle with Hot Water Connection – 52 min.

Programs

- QuickIntenseWash (with hot water connection: 52 mins)
- Universal
- Pots & Pans
- Plastic
- China & Crystal
- SaniWash
- Rinse & Hold
- ECO

Optional Accessories	Material	MAP/Retail
GFV 60/60-7 Integrated Panel Full Size, Clean Touch Steel™, 6" Toe-Kick, no handle	12670320	\$319 / \$369
GFV 60/65-7 Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, no handle	12670410	\$319 / \$369
GBU 5000 Cutlery basket	9614020	\$42 / \$42

Dishwashers – **24" Dishwasher** Integrated

PFD 102i 208/240V



Model	Handle Type	Material	MAP/Retail
PFD 102i 208/240V	Integrated Handle	11605500	\$ 4,825 /\$4,925

Specifications

Width	23 9/16 in (598 mm)
Height	31 11/16 – 34 1/4 in (805 – 870 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	109 lbs (49 kg)
Decibel Rating	48 dBA
ADA Compliant	Yes
Electrical Configuration	2N AC 120/208-240V, 60 Hz, 2x30A
Plug	NEMA 14-30P

Features

- Ideal for Offices, Showrooms, Active Kitchens and Private Homes
- Original Cutlery Basket
- ExtraComfort Basket Design
- No of Standard Place Settings – 13
- Up to 5 Wash Cycles per Day
- AutoOpen Assisted Drying
- Integrated Water Softener
- WiFiConn@ct
- BrilliantLight Interior Lighting
- Tested for 12,500 Program Cycles
- Final Rinse Temperature Up to 180°F (82°C) with a Holding Time of 15 Seconds
- Shortest Cycle with Hot Water Connection – 24 min.

Programs

- QuickIntenseWash (with hot water connection: 24 mins)
- Universal
- Pots & Pans
- Plastic
- China & Crystal
- SaniWash
- Rinse & Hold
- ECO

Optional Accessories	Material	MAP/Retail
GFV 60/60-7 Integrated Panel Full Size, Clean Touch Steel™, 6" Toe-Kick, no handle	12670320	\$319 / \$369
GFV 60/65-7 Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, no handle	12670410	\$319 / \$369
GBU 5000 Cutlery basket	9614020	\$42 / \$42

Dishwashers – **24" Dishwasher** Integrated

PFD 104 SCVi 120V



Model	Handle Type	Material	MAP/Retail
PFD 104 SCVi 120V	No Handle	11605450	\$5,610 / \$5,710

Specifications

Width	23 9/16 in (598 mm)
Height	33 1/4 – 35 13/16 in (845 – 910 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	128 lbs (58 kg)
Decibel Rating	45 dBA
ADA Compliant	No
Electrical Configuration	AC 120V 60 Hz, 15A
Plug	NEMA 5-15P

Features

- Ideal for Offices, Showrooms, Active Kitchens and Private Homes
- 3D MultiFlex Cutlery Tray
- MaxiComfort Basket Design with 3D MultiFlex Drawer
- No of Standard Place Settings – 16
- Up to 5 Wash Cycles per Day
- AutoOpen Assisted Drying
- Integrated Water Softener
- WiFiConn@ct
- BrilliantLight Interior Lighting
- Knock2open
- AutoOpen and AutoClose
- Tested for 12,500 Program Cycles
- Final Rinse Temperature Up to 180°F (82°C) with a Holding Time of 15 Seconds
- Shortest Cycle with Hot Water Connection – 52 min.

Programs

- | | |
|---|--|
| <ul style="list-style-type: none"> • QuickIntenseWash (with hot water connection: 52 min) • Universal • Pots & Pans • Plastic | <ul style="list-style-type: none"> • China & Crystal • SaniWash • Rinse & Hold • ECO |
|---|--|

Optional Accessories	Material	MAP/Retail
GFVi 701/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, no handle	12670600	\$379 / \$429
GFVi 710/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, PureLine handle	12074350	\$489 / \$539
GFVi 711/72 Fully Integrated Panel Full Size, Clean Touch Steel™, 6" Toe-Kick, ContourLine handle	12074400	\$489 / \$539
GFVi 711/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, ContourLine handle	12074450	\$489 / \$539
GFVi 712/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, Range Panel	12074470	\$489 / \$539
GFVi 709/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, Pocket handle	12672750	\$489 / \$539
GBU 5000 Cutlery basket	9614020	\$42 / \$42

Dishwashers – **24" Dishwasher** Integrated

PFD 104 SCVi 208/240V



Model	Handle Type	Material	MAP/Retail
PFD 104 SCVi 208/240V	No Handle	11605520	\$5,610 / \$5,710

Specifications

Width	23 9/16 in (598 mm)
Height	33 1/4 – 35 13/16 in (845 – 910 mm)
Depth	22 7/16 in (570 mm)
Shipping Weight	128 lbs (58 kg)
Decibel Rating	45 dBA
ADA Compliant	No
Electrical Configuration	2N AC 120/208-240V, 60 Hz, 2x30A
Plug	NEMA 14-30P

Features

- Ideal for Offices, Showrooms, Active Kitchens and Private Homes
- 3D MultiFlex Cutlery Tray
- MaxiComfort Basket Design with 3D MultiFlex Drawer
- No of Standard Place Settings – 16
- Up to 5 Wash Cycles per Day
- AutoOpen Assisted Drying
- Integrated Water Softener
- WiFiConn@ct
- BrilliantLight Interior Lighting
- Knock2open
- AutoOpen and AutoClose
- Tested for 12,500 Program Cycles
- Final Rinse Temperature Up to 180°F (82°C) with a Holding Time of 15 Seconds
- Shortest Cycle with Hot Water Connection – 24 min.

Programs

- QuickIntenseWash (with hot water connection: 24 min)
- Universal
- Pots & Pans
- Plastic
- China & Crystal
- SaniWash
- Rinse & Hold
- ECO

Optional Accessories

Material	MAP/Retail
GFVi 701/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, no handle	12670600 \$379 / \$429
GFVi 710/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, PureLine handle	12074350 \$489 / \$539
GFVi 711/72 Fully Integrated Panel Full Size, Clean Touch Steel™, 6" Toe-Kick, ContourLine handle	12074400 \$489 / \$539
GFVi 711/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, ContourLine handle	12074450 \$489 / \$539
GFVi 712/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, Range Panel	12074470 \$489 / \$539
GFVi 709/77 Fully Integrated Panel Full Size, Clean Touch Steel™, 4" Toe-Kick, Pocket handle	12672750 \$489 / \$539
GBU 5000 Cutlery basket	9614020 \$42 / \$42

Dishwashers — **24" Dishwasher** Pre-Finished

PFD 401 208V



Model	Handle Type	Material	MAP/Retail
PFD 401 208V	Integrated Handle	12066560	\$7,245 / \$7,445

Specifications

Width	23 9/16 in (598 mm)
Height	32 1/4 in (820 mm)
Depth	22 13/16 in (580 mm)
Shipping Weight	164.5 lbs (74.5 kg)
Decibel Rating	59 dBA
ADA Compliant	Yes
Electrical Configuration	2AC 208V, 60 Hz, 2x30A
Plug	NEMA L6-30

Features

- Suitable for offices, active kitchens, private homes, restaurants, bars etc.
- Large Variety of Baskets and Inserts, Including Commercial Plastic Baskets
- Integrated Water Softener
- Large Capacity and Multi-Level Cleaning for High Throughput
- Connection for Dispenser Modules
- Tested for Up to 40 Cycles per Day
- Tested for at Least 28,000 Operating Hours (10 years)
- Final Rinse Temperature Up to 158°F (70°C) with a Holding Time of 10 min.
- Shortest Cycle Time — 6 min.

Programs

- | | |
|-------------------|----------------|
| • Rapid | • Utensils |
| • Normal | • Plastic |
| • Normal plus | • Economy |
| • Intensive | • Reactivation |
| • SaniWash | • Rinse & Hold |
| • China & Crystal | • Drain |
| • Glasses | |

Included Accessories	Material	MAP/Retail
1 x APFD 215 Upper Basket for Cups (Height Adjustable)	12106020	\$255
1 x APFD 220 Lower Basket for Inserts	12107590	\$165
1 x APFD 415 Insert for Dessert Plates	12106030	\$70
2 x E 816 Inserts for Plates	12611640	\$70
2 x APFD 420 Inserts for Cutlery	12118550	\$65

Optional Accessories — See pages 30–31.

Dishwashers — **24" Dishwasher** Pre-Finished

PFD 401



Model	Handle Type	Material	MAP/Retail
PFD 401 Stainless Steel 240V	Integrated Handle	12066590	\$7,245 / \$7,445

Specifications

Width	23 9/16 in (598 mm)
Height	32 1/4 in (820 mm)
Depth	22 13/16 in (580 mm)
Shipping Weight	164.5 lbs (74.5 kg)
Decibel Rating	59 dBA
ADA Compliant	Yes
Electrical Configuration	2AC 240V, 60 Hz, 2x30A
Plug	NEMA L6-30

Features

- Suitable for Offices, Active Kitchens, Private Homes, Restaurants, Bars etc.
- Large Variety of Baskets and Inserts, Including Commercial Plastic Baskets
- Integrated Water Softener
- Large Capacity and Multi-Level Cleaning for High Throughput
- Connection for Dispenser Modules
- Tested for Up to 40 Cycles per Day
- Tested for at Least 28,000 Operating Hours (10 years)
- Final Rinse Temperature Up to 158°F (70°C) with a Holding Time of 10 min.
- Shortest Cycle Time — 6 min.

Programs

- | | |
|-------------------|----------------|
| • Rapid | • Utensils |
| • Normal | • Plastic |
| • Normal plus | • Economy |
| • Intensive | • Reactivation |
| • SaniWash | • Rinse & Hold |
| • China & Crystal | • Drain |
| • Glasses | |

Included Accessories	Material	MAP/Retail
1 x APFD 215 Upper Basket for Cups (Height Adjustable)	12106020	\$255
1 x APFD 220 Lower Basket for Inserts	12107590	\$165
1 x APFD 415 Insert for Dessert Plates	12106030	\$70
2 x E 816 Inserts for Plates	12611640	\$70
2 x APFD 420 Inserts for Cutlery	12118550	\$65

Optional Accessories — See pages 30–31.

Dishwashers – **24" Dishwasher** Pre-Finished

PFD 404 208V



Model	Handle Type	Material	MAP/Retail
PFD 404 208V	Integrated Handle	12066570	\$7,730 / \$7,930

Specifications

Width	23 9/16 in (598 mm)
Height	32 1/4 in (820 mm)
Depth	22 13/16 in (580 mm)
Shipping Weight	164.5 lbs (74.5 kg)
Decibel Rating	59 dBA
ADA Compliant	Yes
Electrical Configuration	2AC 208V, 60 Hz, 2x30A
Plug	NEMA L6-30

Features

- Suitable for Offices, Active Kitchens, Private Homes, Restaurants, Bars etc.
- Large Variety of Baskets and Inserts, Including Commercial Plastic Baskets
- Integrated Water Softener
- Large Capacity and Multi-Level Cleaning for High Throughput
- Connection for Dispenser Modules
- Tested for Up to 40 Cycles per Day
- Tested for at Least 28,000 Operating Hours (10 years)
- Final Rinse Temperature Up to 185°F (85°C) with a Holding Time of 4 min.
- Shortest Cycle Time – 6 min.

Programs

- | | |
|---------------|-------------------|
| • Rapid | • China & Crystal |
| • Normal | • Glasses |
| • Normal plus | • Utensils |
| • Intensive | • Plastic |
| • SaniWash | • SaniWash Plus |

Included

Accessories	Material	MAP/Retail
1 x APFD 215 Upper Basket for Cups (Height Adjustable)	12106020	\$255
1 x APFD 220 Lower Basket for Inserts	12107590	\$165
1 x APFD 415 Insert for Dessert Plates	12106030	\$70
2 x E 816 Inserts for Plates	12611640	\$70
2 x APFD 420 Inserts for Cutlery	12118550	\$65

Optional Accessories – See pages 30–31.

Dishwashers – **24" Dishwasher** Pre-Finished

PFD 404 240V



Model	Handle Type	Material	MAP/Retail
PFD 404 240V	Integrated Handle	12066600	\$7,730 / \$7,930

Specifications

Width	23 9/16 in (598 mm)
Height	32 1/4 in (820 mm)
Depth	22 13/16 in (580 mm)
Shipping Weight	164.5 lbs (74.5 kg)
Decibel Rating	59 dBA
ADA Compliant	Yes
Electrical Configuration	2AC 240V, 60 Hz, 2x30A
Plug	NEMA L6-30

Features

- Suitable for Offices, Active Kitchens, Private Homes, Restaurants, Bars etc.
- Large Variety of Baskets and Inserts, Including Commercial Plastic Baskets
- Integrated Water Softener
- Large Capacity and Multi-Level Cleaning for High Throughput
- Connection for Dispenser Modules
- Tested for Up to 40 Cycles per Day
- Tested for at Least 28,000 Operating Hours (10 years)
- Final Rinse Temperature Up to 185°F (85°C) with a Holding Time of 4 min.
- Shortest Cycle Time – 6 min.

Programs

- | | |
|-------------------|-----------------|
| • Rapid | • Glasses |
| • Normal | • Utensils |
| • Normal plus | • Plastic |
| • Intensive | • Economy |
| • SaniWash | • SaniWash Plus |
| • China & Crystal | |

Included

Accessories	Material	MAP/Retail
1 x APFD 215 Upper Basket for Cups (Height Adjustable)	12106020	\$255
1 x APFD 220 Lower Basket for Inserts	12107590	\$165
1 x APFD 415 Insert for Dessert Plates	12106030	\$70
2 x E 816 Inserts for Plates	12611640	\$70
2 x APFD 420 Inserts for Cutlery	12118550	\$65

Optional Accessories – See pages 30–31.

Dishwashers – **24" Dishwasher** Pre-Finished

PFD 408 208V



Model	Handle Type	Material	MAP/Retail
PFD 408 208V*	Integrated Handle	12066580	\$8,455 / \$8,655

Specifications

Width	23 9/16 in (598 mm)
Height	32 1/4 in (820 mm)
Depth	23 7/16 in (595 mm)
Shipping Weight	187 lbs (84.5 kg)
Decibel Rating	57 dBA
ADA Compliant	Yes
NSF/ANSI 3	Yes
Electrical Configuration*	3AC 208V, 60 Hz, 3x20A
Plug	NEMA L15-20

Features

- Suitable for Customers That Require a NSF 3 Classified Dishwasher like Pre-Schools, Assisted Living, Medical Offices etc.
- Large Variety of Baskets and Inserts, Including Commercial Plastic Baskets
- Up to 40 Wash Cycles per Day
- Integrated Water Softener
- Large Capacity and Multi-Level Cleaning
- Connection for Dispenser Modules
- Tested for at least 28,000 operating hours (10 years)
- Final Rinse Temperature Up to 185°F (85°C) with a Holding Time of 1 min.
- Shortest Cycle Time – 15 min.

Programs

- | | |
|---------------|----------------|
| • Normal | • Reactivation |
| • Normal plus | • Rinse & Hold |
| • Intensive | • Drain |

Included Accessories	Material	MAP/Retail
1 x APFD 215 Upper Basket for Cups (Height Adjustable)	12106020	\$255
1 x APFD 220 Lower Basket for Inserts	12107590	\$165
1 x APFD 415 Insert for Dessert Plates	12106030	\$70
2 x E 816 Inserts for Plates	12611640	\$70
2 x APFD 420 Inserts for Cutlery	12118550	\$65

Optional Accessories – See pages 30–31.

* Special order product – Contact prosales@mieleusa.com

* Option to convert unit to 2 AC 208V, 60 Hz, 2x30A with NEMA L6-30 plug. Conversion must take place before delivery. A special order must be placed to prosales@mieleusa.com (MATERIAL 94001810 / UMRP \$355).

Dishwashers – **24" Dishwasher** Pre-Finished

PFD 408



Model	Handle Type	Material	MAP/Retail
PFD 408 Stainless Steel 240V*	Integrated Handle	12066610	\$8,455 / \$8,655

Specifications

Width	23 9/16 in (598 mm)
Height	32 1/4 in (820 mm)
Depth	23 7/16 in (595 mm)
Shipping Weight	187 lbs (84.5 kg)
Decibel Rating	57 dBA
ADA Compliant	Yes
NSF/ANSI 3	Yes
Electrical Configuration*	3AC 240V, 60 Hz, 3x20A
Plug	NEMA L15-20

Features

- Suitable for customers that require a NSF 3 classified dishwasher like pre-schools, assisted living, medical offices etc.
- Large Variety of Baskets and Inserts, Including Commercial Plastic Baskets
- Up to 40 Wash Cycles per Day
- Integrated Water Softener
- Large Capacity and Multi-Level Cleaning
- Tested for at least 28,000 operating hours (10 years)
- Final Rinse Temperature Up to 185°F (85°C) with a Holding Time of 1 min.
- Shortest Cycle Time – 15 min.

Programs

- | | |
|---------------|----------------|
| • Normal | • Reactivation |
| • Normal plus | • Rinse & Hold |
| • Intensive | • Drain |

Included Accessories

Material	MAP/Retail
1 x APFD 215 Upper Basket for Cups (Height Adjustable)	\$255
1 x APFD 220 Lower Basket for Inserts	\$165
1 x APFD 415 Insert for Dessert Plates	\$70
2 x E 816 Inserts for Plates	\$70
2 x APFD 420 Inserts for Cutlery	\$65

Optional Accessories – See pages 30–31.

* Special order product – Contact prosales@mieleusa.com

* Option to convert unit to 2 AC 208V, 60 Hz, 2x30A with NEMA L6-30 plug. Conversion must take place before delivery. A special order must be placed to prosales@mieleusa.com (MATERIAL 94001810 / UMRP \$355).

Optional Accessories – Models PFD 401, PFD 404 and PFD 408

Baskets And Inserts	Material	MAP/Retail	Baskets And Inserts	Material	MAP/Retail
APFD 215 Upper Basket	12106020	\$255	U 502 Plate Basket	12654760	\$205
APFD 214 Upper Basket	12107560	\$370	U 503 Cutlery Basket	12654770	\$205
O 885 Upper Basket Carrier	12616510	\$450	U 504 Cutlery Basket	12655860	\$265
O 898 Upper Basket	12616580	\$655	U 505 Multi-Purpose Basket	12655920	\$265
APFD 220 Lower Basket	12107590	\$165	U 506 Plate Basket	12655880	\$255
U 881 Lower Basket	4906620	\$295	U 507 Bistro Basket	12655900	\$255
U 876 Lower Basket Carrier	12616640	\$450	APFD 222 Basket	12294760	\$185
APFD 210 Bottle Basket	11717360	\$920	APFD 418 Insert	12476350	\$185
APFD 211 Adapter to	11717390	\$140	U 525/1 Basket	10094780	\$265
APFD 212 Adapter to	11717430	\$140	U 508 Basket for cups	12655940	\$230
E 816 Insert for plates	12611640	\$70	U 520 Glassware Basket	12663380	\$155
E 810 Insert for small	12610680	\$70	U 524/1 Glassware Basket	10094770	\$265
APFD 415 Insert for small	12106030	\$70	U 534 16 Glasses, Shallow Top Frame	12655970	\$265
E 809 Insert for lower basket	5018650	\$125	U 535 25 Glasses, Shallow Top Frame	12655980	\$265
E9 Insert for Large	3808260	\$90	U 536 36 Glasses, Shallow Top Frame	12655990	\$265
APFD 417 Insert for beakers	12293790	\$205	U 537 42 Glasses, Shallow Top Frame	12662550	\$265
E 165 Cutlery Holder	3808830	\$30	U 544 16 Glasses, Deep Top Frame	12662560	\$265
APFD 420 Cutlery basket	12118550	\$65	U 545 25 Glasses, Deep Top Frame	12662570	\$265
E 437 Cutlery holder	4326640	\$525	U 546 36 Glasses, Deep Top Frame	12662580	\$265
E 884 Insert for Baking Sheets, Platters	5018680	\$90	U 547 42 Glasses, Deep Top Frame	12663000	\$265
APFD 401 Insert For Medication Cups	10869810	\$205	U 634-S 16 Glasses, With Sloping Bases	12663010	\$345
APFD 402 Insert For Medication Cup Lids	10869850	\$30	U 635-S 20 Glasses, With Sloping Bases	12663080	\$345
APFD 419 Rail for cup lids	12298740	\$90	U 644-S 16 Tall Glasses, With Sloping Bases	12663090	\$345
E 167 Cutlery Holder	12663060	\$70	U 645-S 20 Tall Glasses, With Sloping Bases	12663100	\$345
E 205 Insert for glasses	3808980	\$100			
E 815 Glassware Insert	5018670	\$125			
E 812 Glassware Insert	12611590	\$185			
E 166 Perforated Plate	3808850	\$125			
E 10 Perforated Plate	12610570	\$140			
APFD 416 Perforated Plate	12174880	\$205			

Optional Accessories – Models PFD 401, PFD 404 and PFD 408

Installation	Material	MAP/Retail	Plinths And Bases	Material	MAP/Retail
AABL 50 Spacer Trim, Stainless Steel	12621600	\$85	UO 30-60/80 Open Base, 1113/16 in (30cm)	12611920	\$875
ABL 110 Spacer Trim, Stainless Steel	12621480	\$165	UO 52-60/80 Open Base, 201/2 in (52cm)	12611900	\$1,100
Stand 2 Toe-Kick, Stainless Steel	12614960	\$100	UG 30-60/80 Box Base, 1113/16 in (30cm)	12611810	\$875
APFD 001 Toe-kick, Stainless Steel, Height Adjustable	12084170	\$185	UG 52-60/80 Box Base 201/2 in (52cm)	12611830	\$1,100
DEF-80 Lid In Stainless Steel	12612130	\$265	UG 70-60/80 Box Plinth With Door, 279/16 in (30cm)	12650230	\$2,615
BKS-80 Mounting Kit To Fix A Support Facing At The End Of A Kitchen Island	12615070	\$85			
ADB Cover Plate For Built-In Dishwasher	9715590	\$90	Dispensing	Material	MAP/Retail
BBF-80 Floor Anchoring	12612100	\$80	DOS G Comfort Dispenser Module	12187400	\$615
APFD 007 Extended Machine Feet	12298200	\$85	DTD 2 Drip Tray	10695460	\$100
Conversion Fee – To convert PG8061 from 3AC to 2AC (3AC requires 20A, 2AC requires 30A)	94001810	\$355			

Product Highlights – Washers & Dryers

Washing Machines

Feature	Description (see specific models for details)
Honeycomb Drum	The Honeycomb drum has a special sculptured surface which allows fabrics to glide on a thin cushion of water.
TwinDos	Liquid detergent automatic dispensing system for achieving the best wash results. Save up to 30% detergent compared to manual dispensing.
IntenseWash	IntenseWash offers the highest level of cleaning, with Spin&Spray technology using less water and heating energy.
QuickIntenseWash	Utilizing the IntenseWash technology, the QuickIntenseWash program provides excellent cleanliness in just 49 minutes.
SingleWash	An efficient solution for washing single garments quickly, while saving water and energy.
CapDosing	Dispense special detergent for different types of fabric by placing a portioned capsule into the fabric softener compartment.
Golden Virus Seal	WXI 860 WCS and WXR 860 WCS Miele Washing Machines remove more than 99.9% of all viruses.*

Dryers

Feature	Description (see specific models for details)
Honeycomb Drum	Fewer creases and easier ironing, the honeycomb structure allows laundry to be dried gently and evenly.
Heat-Pump Technology	Saving up to 60% in energy consumption, the heat generated is reused and low temperatures protect the high-quality fibers in the most delicate fabrics.
FragranceDos and FragranceDos²	Miele fragrance flacons add your favorite scent to your laundry during the drying process. With FragranceDos ² , you can insert two flacons into the machine at once to switch between your two favorite fragrances.
SteamFinish	A great alternative to ironing, steam and smooth your laundry during the drying process.
PerfectDry	PerfectDry takes the mineral content of your water into account and modifies the drying process accordingly.

Washing Machines – W1

WXC 280 WCS



Model	Material	UMRP
WXC 280 WCS	12962080	\$1,999

Specifications

Overall Width	23 1/2 in (596 mm)
Overall Height	33 1/2 in (850 mm)
Overall Depth	25 5/16 in (643 mm)
Shipping weight	221 lbs (100 kg)
Capacity	17.6 lbs. / 2.26 cu. ft.
Electrical Connection	120V, 15A

Features

- DirectSensor user interface
- HoneyComb drum
- 11 Wash Programs
- Wi-FiConn@ct and Mobile Control
- Miele@Home and Wash2Dry (if paired with a Miele dryer)
- CapDosing
- Add Laundry Feature
- Black door ring
- 1600 rpm max spin speed

Wash Programs

- | | |
|----------------|---------------|
| • Darks/Denims | • Outdoor |
| • Express | • Drain/Spin |
| • Handwash | • Normal |
| • Delicates | • Extra White |
| • Freshen-up | • Sanitize |
| • Dress Shirts | |

Wash Options

- SoftSteam

Matching Dryers	Material
TXB 360	12819070
TXF 360	12819080

Accessories	Material	UMRP
WTV 502 (Stacking Kit)	9256140	\$129
WTV 512 (Stacking Kit w/ Drawer 4 5/8" H)	9351790	\$299
WTS 610 (Pedestal 13 7/8" H)	12349900	\$649
Adaptor NEMA 14-30*	10983750	\$79

*A NEMA 14-30 adapter is required for any installation connected to a 208/240V household electrical supply.

Washing Machines – W1

WXF 980 WCS



Model	Material	UMRP
WXF 980 WCS	12962090	\$2,499

Specifications

Overall Width	23 1/2 in (596 mm)
Overall Height	33 1/2 in (850 mm)
Overall Depth	25 5/16 in (643 mm)
Shipping weight	221 lbs (100 kg)
Capacity	17.6 lbs. / 2.26 cu. ft.
Electrical Connection	120V, 15A

Features

- DirectSensor user interface
- HoneyComb drum
- TwinDos automatic detergent dispensing
- 14 Wash Programs including 3 programs via MobileStart
- QuickIntenseWash and SingleWash option
- WiFiConn@ct and mobile control
- Miele@Home and Wash2Dry (if paired with a Miele dryer)
- CapDosing
- 1,600 rpm max spin speed
- Black door ring

Wash Programs

- | | |
|----------------|-------------------------|
| • Darks/Denims | • Outdoor |
| • Express | • Drain/Spin |
| • Handwash | • Normal |
| • Delicates | • Extra White |
| • Freshen-up | • Sanitize |
| • Dress Shirts | • Water+Prewash Soaking |

Wash Options

- | | |
|-------------|---------------|
| • SoftSteam | • Pre-rinse |
| • Buzzer | • AllergyWash |
| • Soak | • SingleWash |

Matching Dryers	Material
TXB 360	12819070
TXF 360	12819080

Accessories	Material	UMRP
WTV 502 (Stacking Kit)	9256140	\$129
WTV 512 (Stacking Kit w/ Drawer 4 5/8" H)	9351790	\$299
WTS 610 (Pedestal 13 7/8" H)	12349900	\$649
Adaptor NEMA 14-30*	10983750	\$79

*A NEMA 14-30 adaptor is required for any installation connected to a 208/240V household electrical supply.

Washing Machines – W1

WXR 960 WCS



Model	Material	UMRP
WXR 960 WCS	12864100	\$2,999

Specifications

Overall Width	23 1/2 in (596 mm)
Overall Height	33 1/2 in (850 mm)
Overall Depth	25 5/16 in (643 mm)
Shipping weight	221 lbs (100 kg)
Capacity	17.6 lbs. / 2.26 cu. ft.
Electrical Connection	120V, 15A

Features

- M Touch premium user interface
- HoneyComb drum
- TwinDos automatic detergent dispensing
- 25 Wash Programs
- QuickIntenseWash and SingleWash option
- CapDosing
- 1,600 rpm max spin speed
- Black door ring

Wash Programs

- | | |
|----------------|-----------------------|
| • Express | • QuickIntenseWash |
| • Handwash | • Silks |
| • Delicates | • Towels |
| • Curtains | • Sportswear |
| • Proofing | • Starch |
| • Denim | • Woolens |
| • Pillows | • Table Linens/Drapes |
| • Baby clothes | • Normal |
| • Quick rinse | • Extra White |
| • Sneakers | • Sanitize |
| • Dress Shirts | • Downs |
| • Outdoor | • Dark garments |
| • Wrinkle-free | |

Wash Options

- | | |
|-------------|---------------|
| • SoftSteam | • Pre-rinse |
| • Buzzer | • AllergyWash |
| • Soak | • SingleWash |

Matching Dryers	Material
TXR 960 WP	11620030

Accessories	Material	UMRP
WTV 502 (Stacking Kit)	9256140	\$129
WTV 512 (Stacking Kit w/ Drawer 4 5/8" H)	9351790	\$299
WTS 610 (Pedestal 13 7/8" H)	12349900	\$649
Adaptor NEMA 14-30*	10983750	\$79

*A NEMA 14-30 adapter is required for any installation connected to a 208/240V household electrical supply.

Dryers – T1 Heat Pump

TXB 360 WP



Model	Material	UMRP
TXB 360 WP	12819070	\$1,899

Specifications

Overall Width	23 1/2 in (596 mm)
Overall Height	33 1/2 in (850 mm)
Overall Depth	25 5/16 in (643 mm)
Shipping weight	137 lbs (62 kg)
Capacity	4.02 cu. ft.
Electrical Connection	120V, 15A

Features

- DirectSensor user interface
- Ventless Heat-Pump Dryer
- Honeycomb drum
- PerfectDry moisture sensing technology
- WiFiConn@ct and Mobile Control
- Miele@Home and Wash2Dry (if paired with a Miele washer)
- FragranceDos
- EnergyStar Most Efficient

Drying Programs

- | | |
|-----------------|---------------------|
| • Normal | • Proofing |
| • Bed linens | • Denim |
| • Express | • Time dry/DryFresh |
| • Delicates | • Dress Shirts |
| • Woolens/Silks | • Outdoor |

Drying Options

- Anti-Crease
- Gentle
- Buzzer

Matching Washers	Material
WXC 280 WCS	12962080
WXF 980 WCS	12962090

Accessories	Material	UMRP
WTV 502 (Stacking Kit)	9256140	\$129
WTV 512 (Stacking Kit w/ Drawer 4 5/8" H)	9351790	\$299
WTS 610 (Pedestal 13 7/8" H)	12349900	\$649
Adaptor NEMA 14-30*	10983750	\$79
TRK 555 Dryer Basket	9614800	\$99
Dryer Plinth Filter (spare part) BG Filter	9164762	\$40
Dryer Plinth Filter (spare part) BG Filter w/logo	12551630	\$40

*A NEMA 14-30 adapter is required for any installation connected to a 208/240V household electrical supply.

Dryers – T1 Heat Pump



Model	Material	UMRP
TXF 360 WP	12819080	\$2,399

Specifications

Overall Width	23 1/2 in (596 mm)
Overall Height	33 1/2 in (850 mm)
Overall Depth	25 5/16 in (643 mm)
Shipping weight	137 lbs (62 kg)
Capacity	4.02 cu. ft.
Electrical Connection	120V, 15A

Features

- DirectSensor user interface
- Ventless Heat-Pump Dryer
- Honeycomb drum
- PerfectDry moisture sensing technology
- 10 drying programs
- Miele@Home and Wash2Dry (if paired with a Miele W1 washer)
- FragranceDos²
- EnergyStar Most Efficient
- Black door ring

Drying Programs

- | | |
|-----------------|---------------------|
| • Normal | • Proofing |
| • Bed linens | • Denim |
| • Express | • Time dry/DryFresh |
| • Delicates | • Dress Shirts |
| • Woolens/Silks | • Outdoor |

Drying Options

- | | |
|---------------|--------------|
| • Anti-Crease | • Buzzer |
| • Gentle | • Freshen Up |

Matching Washers	Material
WXC 280 WCS	12962080
WXF 980 WCS	12962090

Accessories	Material	UMRP
WTV 502 (Stacking Kit)	9256140	\$129
WTV 512 (Stacking Kit w/ Drawer 4 5/8" H)	9351790	\$299
WTS 610 (Pedestal 13 7/8" H)	12349900	\$649
Adaptor NEMA 14-30*	10983750	\$79
TRK 555 Dryer Basket	9614800	\$99
Dryer Plinth Filter (spare part) BG Filter	9164762	\$40
Dryer Plinth Filter (spare part) BG Filter w/logo	12551630	\$40

*A NEMA 14-30 adapter is required for any installation connected to a 208/240V household electrical supply.

Dryers – T1 Heat Pump



Model	Material	UMRP
TXR 960 WP	12864160	\$2,999

Specifications

Overall Width	23 1/2 in (596 mm)
Overall Height	33 1/2 in (850 mm)
Overall Depth	25 5/16 in (643 mm)
Shipping weight	137 lbs (62 kg)
Capacity	4.02 cu. ft.
Electrical Connection	120V, 15A

Features

- M Touch premium user interface
- Ventless Heat-Pump Dryer
- Honeycomb drum
- PerfectDry moisture sensing technology
- 19 Programs including SteamFinish
- Miele@Home and Wash2Dry (if paired with a Miele W1 washer)
- FragranceDos²
- EnergyStar Most Efficient
- Black door ring

Drying Programs

- | | |
|-----------------------|----------------|
| • Table Linens/Drapes | • Basket |
| • Normal | • Cold air |
| • Bed linens | • Time dry |
| • Express | • DryFresh |
| • Delicates | • Dress Shirts |
| • SoftSteam | • Outdoor |
| • Woolens/Silks | • Wrinkle-free |
| • Proofing | • Sportswear |
| • Denim | • Smoothing |
| • Pillows | |

Drying Options

- | | |
|---------------|--------------|
| • Anti-Crease | • Buzzer |
| • Gentle | • Freshen Up |

Matching Dryers	Material
WXR 960 WCS	12864100

Accessories	Material	UMRP
WTV 502 (Stacking Kit)	9256140	\$129
WTV 512 (Stacking Kit w/ Drawer 4 5/8" H)	9351790	\$299
WTS 610 (Pedestal 13 7/8" H)	12349900	\$649
Adaptor NEMA 14-30*	10983750	\$79
TRK 555 Dryer Basket	9614800	\$99
Dryer Plinth Filter (spare part) BG Filter	9164762	\$40
Dryer Plinth Filter (spare part) BG Filter w/logo	12551630	\$40

*A NEMA 14-30 adapter is required for any installation connected to a 208/240V household electrical supply.

Rotary Ironer



Model	Material	UMRP
B 990 Rotary Ironer	7222730	\$2,699

Finish

Lotus White

Specifications

Width	38 3/4 in (985 mm)
Height	37 3/4 in (959 mm)
Depth	15 in (380 mm)
Shipping Weight	92.5 lbs (45 kg)
Roller Width	32.5 in
Electrical Connection	120V 15A

Features

- 32.5" Wide Roller
- Three Heating Elements for Optimum Heat Distribution
- Variable Roller Speed
- Temperature Selection to Suit Textiles
- Laundry Feed Board for Easy Laundry Handling
- Convenient Infeed Board with Ample Storage Space
- Airing Bar for Crease-Free Cooling
- Moisture – Absorbing Roller Padding
- Convenient Folding Mechanism
- Easily Maneuverable with Four Castors
- Wide Foot Control Bar
- Automatic Finger Guard
- Emergency Release

Product Highlights – Professional for the Home Laundry

Washing Machines

Feature	Description (see specific models for details)
Honeycomb Drum	Has a perforated rear panel for fast wetting of laundry. The perforated rear panel Honeycomb Drum combined with high spin speeds supports shorter cycle time without compromising on performance.
Express Wash	Providing excellent cleanliness in just 25 minutes.
Ultimate Convenience	With intuitive M Touch controls, easily select your settings with the swipe of a finger. Choose from 50+ programs – 5 are customizable.
CapDosing	Dispense special detergent for different types of fabric by placing a portioned capsule into the fabric softener compartment.
Professional Grade Laundry for the Home	The Little Giant Washers have a 2.58 ft ³ drum size and provide professional-grade disinfection and fabric care in a high-efficiency, compact system.

Dryers

Feature	Description (see specific models for details)
Honeycomb Drum	Fewer creases and easier ironing, the honeycomb structure allows laundry to be dried gently and evenly.
Heat-Pump Technology	Saving on energy consumption, the heat generated is reused and low temperatures protect the high-quality fibers in the most delicate fabrics.
Ultimate Convenience	With intuitive M Touch controls, easily select your settings with the swipe of a finger. Choose from 35 programs – 5 are customizable.
PerfectDry	PerfectDry takes the residual moisture level into account and modifies the drying process accordingly.
Powerful Drive System	Two separate motors for a quicker and more efficient drying process with fewer creases.

Washing Machines – Little Giant Performance Plus

PWM 908 DP, Lotus White



PWM 908 DP, Stainless Steel



Model	Material	Map/Retail
PWM 908 DP Lotus White	11204460	\$6,375 / \$6,575
PWM 908 DP Stainless Steel	11204470	\$6,775 / \$6,975

Specifications

Width	23 7/16 in (596 mm)
Height	33 7/16 in (850 mm)
Depth	28 1/8 in (714 mm)
Shipping Weight	230 lbs (104 kg)
Front Material (Lotus White Model)	Porcelain Enameled White
Front Material (Stainless Steel Model)	Stainless Steel
Side Panels (both models)	Powder Coated White
Electrical Connection	2 AC 208-240V, 60 Hz, 30 A
Plug	NEMA L6-30
Capacity	2.58 cu.ft – 73 Liter

Features

- Spin Speed – 1600 rpm
- Detergent Dispenser Drawer, 3 Compartments
- CapDosing
- Possible Connections to Dispensing Pumps – 6
- M Touch Flex User Interface (No Buttons or Dials)
- 49-minute Cotton 140°F Program (with Hot Water Connection)
- 25-minute Express Wash Cycle
- 50+ Programs – 5 Customizable
- High Temperature Disinfection Programs (up to 200°F)
- Bearing Designed for 30,000 Operating Hours
- Stackable or Side-by-Side Configuration – 3D Imbalance Monitoring
- Commercial Soft-Mounted
- HoneyComb Drum (for Washers) with Perforated Rear Wall

Matching Dryers	Material
PDR 908 HP Lotus White	11204480
PDR 908 HP Stainless Steel	11204490

Programs

- Standard Programs – 16
- Sport Programs – 4
- Down Filled Items
- Outwear
- Work Wear like Oil/fat Special, Dust/Flour Special
- Wellness/Hair Salon Programs – 3
- Proofing
- Thermal Disinfection – 16
- Wet Care Programs – 5

Optional Accessories	Material	Map/Retail
APCL 001 Stainless Steel Stacking Kit	11167420	\$275
APCL 084 Iron-Grey Base, Open, 6" Tall	11776560	\$585
APCL 085 Iron-Grey Base, Open, 12" Tall	11776570	\$625
APCL 087 Iron-Grey Base, Open, 19" Tall	11776600	\$830
APCL 005 Stainless Steel Base, Closed, 12" Tall	11318800	\$835
APCL 011 Stainless Steel Base, Closed, 19" Tall	11318830	\$1,045
APCL 043 XCI-Box	11492730	\$260
APCL 046 XCI PWM/PDR EL.	11537560	\$305
APCL 047 XCI PWM/PDR HP.	11537570	\$305
APCL 016 Dispensing adapter kit LD 6xD6	11229320	\$105
APCL 017 Dispensing adapter kit LD 4xD9	11229340	\$105

Dryers – Little Giant Performance Plus

PDR 908 HP, Lotus White



PDR 908 HP, Stainless Steel



Model	Material	Map/Retail
PDR 908 HP Lotus White	11204480	\$5,020 / \$5,220
PDR 908 HP Stainless Steel	11204490	\$5,425 / \$5,625

Specifications

Width	23 7/16 in (596 mm)
Height	33 7/16 in (850 mm)
Depth	30 9/16 in (777 mm)
Shipping Weight	170 lbs (77 kg)
Front Material (Lotus White Model)	Porcelain Enameled White
Front Material (Stainless Steel Model)	Stainless Steel
Side Panels (both models)	Powder Coated White
Electrical Connection	2 AC 208-240V, 60 Hz, 30 A
Plug	NEMA L6-30
Capacity	4.59 cu.ft – 130 Liter

Features

- M Touch Flex User Interface (No Buttons or Dials)
- Stackable or Side-by-Side Configuration
- Heat Pump Dryer Technology
- 50+ Programs – 5 Customizable Rated Energy Star Most Efficient
- FragranceDos Capable
- Dryer Featuring 4D Filtration System
- HoneyComb Drum (for Dryers) with Perforated Rear Wall
- PerfectDry System – Residual Moisture Controlled
- Axial Airflow

Matching Washers	Material
PWM 908 Lotus White	DP 11204460
PWM 908 DP Stainless Steel	11204470

Programs

- Standard Programs – 17
- Sport Programs – 4
- Down Bedding
- Synthetic Bedding
- Large Items
- Hygiene Programs – 3
- Wet Care Programs – 3
- Flatwork Programs – 3
- Special Programs – 5
- Timed Drying Programs – 4

Optional Accessories	Material	Map/Retail
TRK 555 Dryer Basket	9614800	\$99
APCL 001 Stainless Steel Stacking Kit	11167420	\$275
APCL 084 Iron-Grey Base, Open, 6" Tall	11776560	\$585
APCL 085 Iron-Grey Base, Open, 12" Tall	11776570	\$625
APCL 087 Iron-Grey Base, Open, 19" Tall	11776600	\$830
APCL 005 Stainless Steel Base, Closed, 12" Tall	11318800	\$835
APCL 011 Stainless Steel Base, Closed, 19" Tall	11318830	\$1,045

Professional Rotary Ironer



Model	Material	Map/Retail
HM 16-80	10238590	\$4,490 / \$4,880

Optional Accessories	Material	Map/Retail
APRI 310 Dust Cover	11563330	\$80

Finish

Lotus White

Specifications

Width	38 3/4 in (985 mm)
Height	37 3/4 in (959 mm)
Depth	14 15/16 in (380 mm)
Drum Diameter	6 5/16 in (160 mm)
Working Width	32 11/16 in (830 mm)
Shipping Weight	100 lbs (45 kg)
Electrical Connection	2 AC 208-240V, 50-60 Hz, 20 A
Plug	NEMA L6-20

Features

- Heater Plate Material – Aluminium
- Padding – Polyester Needle-Felt Cloth
- Control System – Rotary Selector
- Minimum Ironer Speed, Can Be Set in ft/min – 2
- Feed-In Board
- Maximum Ironer Speed, Can Be Set in ft/min – 4.5
- Steam Function
- Fold-Away Function
- Foot Switch
- Airing Bar

Accessories & Consumables — Laundry

W1 TwinDos Cartridges	Material	UMRP	Product	Material	UMRP
TwinDos Cartridge UltraPhase 1	11504560	\$34.99	UltraColor Liquid Detergent	11979450	\$31.99
TwinDos Cartridge UltraPhase 2	12517250	\$34.99	UltraDark Liquid Detergent	11986840	\$33.99
TwinDos Cartridge UltraPhase 2 – Refresh Elixir	11615060	\$36.99	UltraSoft Fabric Softener	11987230	\$19.99
TwinDos Care	11171450	\$20.99	WoolCare Liquid Detergent	11979320	\$29.99
TwinDos Cartridge UltraPhase – Sensitive	11716880	\$36.99	UltraColor Powder Detergent	10459790	\$44.99
TwinDos Cartridge UltraPhase 2 – Sensitive	11716960	\$36.99	UltraWhite Powder Detergent	10459720	\$44.99
			Sensitive Skin Powder Detergent	10459870	\$44.99
W1 CapDosing Capsules	Material	UMRP			
Sport – Box of 6	12625960	\$10.99			
Booster – Box of 6	11703400	\$13.99			
Outdoor – Box of 6	12637180	\$13.99			
Aqua – Box of 9	11698240	\$12.99			
WoolCare – Box of 9	11703130	\$16.99			
ImpraProtect – Box of 3	11703420	\$26.99			
DownCare – Box of 6	12636470	\$13.99			
SilkCare – Box of 6	11703280	\$13.99			
Cocoon – Box of 9	11698260	\$12.99			
CottonRepair – Box of 3	11703360	\$26.99			
T1 Flacon	Material	UMRP			
Nature Flacon Capsule – Box of 1	10813410	\$23.99			
Aqua Flacon Capsule – Box of 1	12021190	\$23.99			
Cocoon Flacon Capsule – Box of 1	12023700	\$23.99			
DryFresh Flacon Capsule – Box of 1	12026960	\$23.99			
Set 3x Aqua Flacon Capsules	12021630	\$64.99			
Set 3x Cocoon Flacon Capsules	12023770	\$64.99			
Set 3x DryFresh Flacon Capsules	12026080	\$64.99			
Set 3x Nature Flacon Capsules	11614600	\$64.99			

Accessories & Consumables – Dishwashers

Dishwashers

Product	Material	UMRP
UltraTabs All in 1 (3-Pack, 60 Tabs)	12738130	\$39.99
UltraTab 120 Series Promo Pack	11347040	\$71.99
PowerDisk® (6-pack)	11841390	\$118.99
PowerDisk® (Single Pack)	11841540	\$21.99
OptiSalt	13071560	\$15.99
Dishwasher Rinse Aid	13025390	\$15.99
DishClean Dishwasher Conditioner	9959340	\$18.99
Dishwasher Freshener	10118510	\$11.99

Professional for the Home Dishwashers

Product	Material	UMRP
ProCare Shine 12 GC Dishwasher Tabs – 80 tabs	11712580	\$65
ProCare Shine 10 MA Liquid Detergent – 5 L	10923610	\$65
ProCare Shine 40 Rinse Aid – 1 L	10923710	\$40
ProCare Shine 40 Rinse – 5 L	10328030	\$125
ProCare Universal Dishwasher Salt	9195780	\$65
CK/1 DIN 51 Canister Key	11851600	\$20

Handle Options

GEN 7000	MODEL	MATERIAL	TRIM / COLOR	HANDLE WIDTH	COOKING	Vi DISH-WASHERS	Vi COOLING	SF MASTER-COOL	UMRP
	DS 7000	11345890	PureLine Stainless steel ¹	15 3/4 in	•	•	•	—	\$164
	DS 7000	11345930	VitroLine Obsidian black ¹	15 3/4 in	•	•	•	—	\$340
	DS 7000	11345940	VitroLine Brilliant white ¹	15 3/4 in	•	•	•	—	\$340
	DS 7000	11345950	VitroLine Graphite grey ¹	15 3/4 in	•	•	•	—	\$340
	DS 7308	12047020	ContourLine Stainless steel standard handle	21 1/8 in	•	•	•	•	\$186
	DS 7708	12047000	ContourLine Stainless steel swiveling handle	21 1/8 in	•	•	•	•	\$230
	DS 7808	12047030	VitroLine Obsidian black	19 11/16 in	•	•	•	—	\$384
	DS 7808	12047050	VitroLine Graphite grey	19 11/16 in	•	•	•	—	\$384
	DS 7808	12047060	VitroLine Brilliant white	19 11/16 in	•	•	•	—	\$384
	DS 7808	12046910	PureLine Stainless steel	19 11/16 in	•	•	•	—	\$186



Miele, Inc.
9 Independence Way
Princeton, NJ 08540

mieleusa.com
1-800-843-7231

Find your nearest Miele Experience Center in –

Beverly Hills
Chicago
Coral Gables
Manhattan
Princeton
Seattle
Tysons Corner