

Miele



Cooking Price List

2026

Table of Contents

Ranges	04
Range Product Highlights	04
Ranges	05
Rangetops	17
Rangetops Product Highlights	17
Rangetops	18
Gas Cooktops	23
Gas Cooktops Product Highlights	23
Gas Cooktops	24
Electric & Induction Cooktops	29
Electric & Induction Cooktops Product Highlights	29
Electric & Induction Cooktops	30
Full Surface Induction Cooktops	33
Convection Ovens	38
Convection Ovens Product Highlights	38
Convection Ovens	39
Speed, Combi-Steam & Microwave Ovens	50
Speed, Combi-Steam & Microwave Ovens Product Highlights	50
Speed, Combi-Steam & Microwave Ovens	51
Combi-Steam Ovens Optional Accessories	81
Ventilation Hoods	83
Ventilation Hoods Product Highlights	83

Table of Contents

Warming Drawers & Vacuum Sealing Drawers	101
Warming Drawers & Vacuum Sealing Drawers Product Highlights	101
Warming Drawers & Vacuum Sealing Drawers	103
CVA Built-In Coffee	108
CVA Built-In Coffee Product Highlights	108
CVA Built-In Coffee	109
CM Countertop Coffee	115
CM Countertop Coffee Product Highlights	115
CM Countertop Coffee	116
Accessories & Consumables	119
Handle Options	120

Product Highlights — Ranges

Feature	Description (see specific models for details)
Wireless Precision Probe	Precise temperature control, with 4 points of temperature monitoring and wireless connection.
Moisture Plus	Adds a burst of steam for extraordinary roasting and baking results.
M Touch Controls with MotionReact	Operate your appliance quickly and intuitively by tapping and swiping the touch display. MotionReact turns on the light when it detects movement near the oven.
Automatic Programs	Miele guides you through hundreds of easy-to-use cooking programs.
M Pro Griddle	Engineered with an infrared heating element, the M Pro Griddle delivers fast, even heat for flawless results on everything from pancakes to fish and steak.
M Pro Infrared Grill	The M Pro Infrared Grill provides powerful, even radiant heat beneath a durable grill grate for precise, restaurant-quality indoor grilling and exceptional searing performance.
Backlit Precision Knobs	This elegant feature let's you know at a glance whether your burners are on or off.
Miele@home	Interact with your Miele appliances from your mobile device with Miele@home.

Note: Ranges are not convertible, choose the correct fuel for the application when selecting a range.

Ranges — 30" Dual Fuel Range



Model	Material	UMRP
HR 1724-3 DF 30" Dual Fuel Range	11791530	\$7,999
HR 1724-3 DF LP	11791540	\$7,999

Specifications

Burners	3 x 19,500 BTU 1 x 12,500 BTU
Width	29 15/16 in (760 mm)
Height	35 1/5 – 37 in (902 – 940 mm)
Depth	27 1/2 in (698 mm)
Shipping Weight	337.3 lbs (153 kg)

Features

- EasyControl – Easy to Read and Control
- Four Powerful Burners – Plenty of Cooking Space
- Self Clean Oven – For Easy Cleaning
- TwinPower Fans – Convection Oven for more even Baking and Better Roasting
- Dual Fuel – Superior Control of Oven Temperatures

Standard Accessories	Material	UMRP	Included
PerfectClean Universal Tray	9811950	\$198	1
30 in Wire Rack w/ PyroFit	9811970	\$203.50	1
30 in Telescopic Rack w/ PyroFit	12072650	\$357.50	1

Optional Accessories	Material	UMRP
Backsplash 30 in width	12566150	\$289
Backguard DF 12 in / 30 in width	9908760	\$383.90
Backguard DF 20 in / 30 in width	9908860	\$427.90
WokRing	9974600	\$104.50
PerfectClean Grilling and Roasting Insert	9520630	\$137.50
PerfectClean Perforated Baking Tray	9520620	\$121
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50

Ranges — 30" Dual Fuel Range



Model	Material	UMRP
HR 1924-3 DF 30" Dual Fuel Range	11791550	\$9,799
HR 1924-3 DF LP	11791560	\$9,799

Specifications

Burners	3 x 19,500 BTU 1 x 12,500 BTU
Width	29 15/16 in (760 mm)
Height	38 5/8 in (980 mm)
Depth	27 1/2 in (698 mm)
Shipping Weight	337.3 lbs (153 kg)

Features

- M Touch Display — Simple to use Touch Controls
- Automatic Programs — Easily Master New Recipes
- Moisture Plus — For Perfect Baking and Roasting Results
- Wireless Precision Probe — Simple to Monitor Food Temperature
- Miele@home — Monitor Appliances from your Mobile Device
- MotionReact — Appliance Reacts to you when Approached

Standard Accessories	Material	UMRP	Included
PerfectClean Universal Tray	9811950	\$198	1
30 in Wire Rack w/ PyroFit	9811970	\$203.50	2
30 in Telescopic Rack w/ PyroFit	12072650	\$357.50	1
PerfectClean Grilling and Roasting Insert	9520630	\$137.50	1
PerfectClean Perforated Baking Tray	9520620	\$121	1

Optional Accessories	Material	UMRP
Backsplash 30 in width	12566150	\$289
Backguard DF 12 in / 30 in width	9908760	\$383.90
Backguard DF 20 in / 30 in width	9908860	\$427.90
WokRing	9974600	\$104.50
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50

Ranges — 30" Induction Range



Model	Material	UMRP
HR 1422-3 I 30" All Induction Range	12298850	\$7,999

Specifications

Burners	4 – 6 1/4 in diameter 1,250 – 2,000W (208V) 1,450 – 2,300W (240V) 5 1/2 – 7 3/4 in diameter 1,700 – 2,700W (208V) 1,950 – 3,100W (240V) 6 1/4 – 9 in diameter 2,100 – 3,500W (208V) 2,400 – 3,850W (240V) 7 – 11 in diameter 2,300 – 3,350W (208V) 2,700 – 3,850W (240V) Total Power Output 6,700W (208V) 7,700W (240V)
Width	29 15/16 in (760 mm)
Height	35 1/5 – 37 in (902 – 940 mm)
Depth	27 1/2 in (698 mm)
Shipping Weight	337.3 lbs (153 kg)

Features

- Easy Control
- Twin Power – Fast and Even Heating Time
- Self Cleaning – Minimal Cleaning Effort
- State of the Art Cooking Technology
- Easy Opening and Closing and Noise and Vibration Absorbers
- MotionReact – Appliance Reacts to you when Approached
- 4 Zone Induction Cooktop – Precise Temperature Control

Standard Accessories	Material	UMRP	Included
PerfectClean Universal Tray	9811950	\$198	1
30 in Wire Rack w/ PyroFit	9811970	\$203.50	2
30 in Telescopic Rack w/ PyroFit	12072650	\$357.50	1
PerfectClean Grilling and Roasting Insert	9520630	\$137.50	1
PerfectClean Perforated Baking Tray	9520620	\$121	1

Optional Accessories	Material	UMRP
Backsplash 30 in width	12566150	\$289
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50

Ranges — 30" Induction Range



Model	Material	UMRP
HR 1622-3 I 30" All Induction Range	11791520	\$10,299

Specifications

Burners	4 – 6 1/4 in diameter 1,250 – 2,000W (208V) 1,450 – 2,300W (240V) 5 1/2 – 7 3/4 in diameter 1,700 – 2,700W (208V) 1,950 – 3,100W (240V) 6 1/4 – 9 in diameter 2,100 – 3,500W (208V) 2,400 – 3,850W (240V) 7 – 11 in diameter 2,300 – 3,350W (208V) 2,700 – 3,850W (240V) Total Power Output 6,700W (208V) 7,700W (240V)
Width	29 15/16 in (760 mm)
Height	35 1/5 – 37 in (902 – 940 mm)
Depth	27 1/2 in (698 mm)
Shipping Weight	337.3 lbs (153 kg)

Features

- M Touch Display – Simple to use Touch Controls
- Automatic Programs – Easily Master New Recipes
- Moisture Plus – For Perfect Baking and Roasting Results
- Wireless Precision Probe – Simple to Monitor Food Temperature
- Miele@home – Monitor Appliances from your Mobile Device
- MotionReact – Appliance Reacts to you when Approached
- 4 Zone Induction Cooktop – Precise Temperature Control

Standard Accessories	Material	UMRP	Included
PerfectClean Universal Tray	9811950	\$198	1
30 in Wire Rack w/ PyroFit	9811970	\$203.50	2
30 in Telescopic Rack w/ PyroFit	12072650	\$357.50	1
PerfectClean Grilling and Roasting Insert	9520630	\$137.50	1
PerfectClean Perforated Baking Tray	9520620	\$121	1

Optional Accessories	Material	UMRP
Backsplash 30 in width	12566150	\$289
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50

Ranges — 36" Induction Range



Model	Material	UMRP
HR 1432-3 I 36" All Induction Range	12535250	\$11,399

Specifications

Burners	Total Number of Burners: 5 9" Burners: 4 11" Round Burner: 1 PowerFlex Zones: 2 Burner Output in Watts: 2,100 – 3,700 – 7,400 Max Rating Max. Boost power rating Max. TwinBooster power rating Burner Output in Watts: 2,600 – 3,700 Max Rating Max. Boost power rating Max. TwinBooster power rating Burner Output in Watts: 2,100 – 3,700 – 7,400 Max Rating Max. Boost power rating Max. TwinBooster power rating
Width	35 15/16 in (913 mm)
Height	35 1/5 – 37 in (902 – 940 mm)
Depth	27 5/8 in (702 mm)
Shipping Weight	337.3 lbs (153 kg)

Features

- DirectSelect – 7-segment display with rotary selector
- 5-zone induction cooktop including two PowerFlex zones and 1 round zone
- Rapid heating and even heat distribution – TwinPower
- Minimal cleaning effort – Pyrolytic cleaning
- Easy opening & closing, door with noise & vibration absorbers

Standard Accessories	Material	UMRP	Included
PerfectClean Universal Tray	9811950	\$198	1
36 in Wire Rack w/ PyroFit	9858830	\$247.50	1
36 in Telescopic Rack w/ PyroFit	12072710	\$379.50	1

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50

Ranges — 36" Induction Range



Model	Material	UMRP
HR 1632-3 I 36" All Induction Range	12535260	\$13,699

Specifications

Burners	Total Number of Burners: 5 9" Burners: 4 11" Round Burner: 1 PowerFlex Zones: 2 Burner Output in Watts: 2,100 – 3,700 – 7,400 Max Rating Max. Boost power rating Max. TwinBooster power rating Burner Output in Watts: 2,600 – 3,700 Max Rating Max. Boost power rating Max. TwinBooster power rating Burner Output in Watts: 2,100 – 3,700 – 7,400 Max Rating Max. Boost power rating Max. TwinBooster power rating
Width	35 15/16 in (913 mm)
Height	35 1/5 – 37 in (902 – 940 mm)
Depth	27 5/8 in (702 mm)
Shipping Weight	337.3 lbs (153 kg)

Features

- M Touch display – intuitive touch interface
- 5-zone induction cooktop including two PowerFlex zones and 1 round zone
- Moisture Plus for perfect baking and roasting results
- Wireless Precision Probe – Precisely monitor food temperature
- WifiConn@ct – Monitor your appliances from your mobile device
- Motion React – Appliance reacts to you when approached
- Automatic programs – Master new recipes easily

Standard Accessories	Material	UMRP	Included
PerfectClean Universal Tray	9811950	\$198	1
36 in Wire Rack w/ PyroFit	9858830	\$247.50	1
36 in Telescopic Rack w/ PyroFit	12072710	\$379.50	1
PerfectClean Perforated Baking Tray	9520620	\$121	1

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50

Ranges — 36" Dual Fuel Range



Model	Material	UMRP	Standard Accessories	Material	UMRP	Included
HR 1934-3 DF 36" Dual Fuel Range	11791570	\$11,399	PerfectClean Universal Tray	9811950	\$198	1
HR 1934-3 DF LP	11791590	\$11,399	36 in Wire Rack w/ PyroFit	9858830	\$247.50	2
			36 in Telescopic Rack w/ PyroFit	12072710	\$379.50	1
			PerfectClean Grilling and Roasting Insert	9520630	\$137.50	1
			PerfectClean Perforated Baking Tray	9520620	\$121	1
Specifications			Optional Accessories	Material	UMRP	
Burners	3 x 19,500 BTU 2 x 9,000 BTU 1 x 8,000 BTU		Backsplash DF 12 in – 36 in width	9908770	\$412.50	
Width	35 15/16 in (915 mm)		Backsplash DF 20 in – 36 in width	9908900	\$449.90	
Height	35 1/5 – 37 in (902 – 940 mm)		WokRing	9974600	\$104.50	
Depth	27 1/2 in (698 mm)		Round Baking Tray	9520720	\$71.50	
Shipping Weight	448.6 lbs (203.5 kg)		Round Baking Tray w/ Logo	9520730	\$82.50	
Features						
• M Touch Display – Simple to Use Touch Controls • Automatic Programs – Easily Master New Recipes • Moisture Plus – For Perfect Baking and Roasting Results • Wireless Precision Probe – Simple to Monitor Food Temperature • Miele@home – Monitor your Appliances from your Mobile Device • MotionReact – Appliance Reacts to you when Approached						

Ranges — **36" Dual Fuel Range** with M Pro Infrared Grill



Model	Material	UMRP
HR 1935-3 DF GR 36" Dual Fuel Range with Infrared Grill	11791600	\$13,099

Specifications

Burners	2 x 19,500 BTU 1 x 9,000 BTU 1 x 8,000 BTU
Width	35 15/16 in (915 mm)
Height	35 1/5 – 37 in (902 – 940 mm)
Depth	27 1/2 in (698 mm)
Shipping Weight	448.6 lbs (203.5 kg)

Features

- M Touch Display – Simple to use Touch Controls
- Automatic Programs – Easily Master New Recipes
- Moisture Plus – For Perfect Baking and Roasting Results
- Wireless Precision Probe – Simple to Monitor Food Temperature
- Miele@home – Monitor your Appliances from your Mobile Device
- MotionReact – Appliance Reacts to you when Approached
- M Pro Grill – A Powerful Grill on your Cooktop

Standard Accessories	Material	UMRP	Included
PerfectClean Universal Tray	9811950	\$198	1
36 in Wire Rack w/ PyroFit	9858830	\$247.50	2
36 in Telescopic Rack w/ PyroFit	12072710	\$379.50	1
PerfectClean Grilling and Roasting Insert	9520630	\$137.50	1
PerfectClean Perforated Baking Tray	9520620	\$121	1
Grill / Griddle Cover*	9974610	\$275	1

Optional Accessories

Material	UMRP
Backsplash DF 12 in / 36 in width	9908770 \$412.50
Backsplash DF 20 in / 36 in width	9908900 \$449.90
WokRing	9974600 \$104.50
Round Baking Tray	9520720 \$71.50
Round Baking Tray w/ Logo	9520730 \$82.50

*Ships separate from the unit.

Ranges — **36" Dual Fuel Range** with M Pro Infrared Griddle



Model	Material	UMRP
HR 1936-3 DF GD 36" Dual Fuel Range with Infrared Griddle	11791610	\$13,099
HR 1936-3 DF GD LP	11791630	\$13,099

Specifications

Burners	2 x 19,500 BTU 1 x 9,000 BTU 1 x 8,000 BTU
Width	35 15/16 in (915 mm)
Height	35 1/5 – 37 in (902 – 940 mm)
Depth	27 1/2 in (698 mm)
Shipping Weight	448.6 lbs (203.5 kg)

Features

- M Touch Display – Simple to use Touch Controls
- Automatic Programs – Easily Master New Recipes
- Moisture Plus – For Perfect Baking and Roasting Results
- Wireless Precision Probe – Simple to Monitor Food Temperature
- Miele@home – Monitor your Appliances from your Mobile Device
- MotionReact – Appliance Reacts to you when Approached
- M Pro Infrared Griddle – Great Results for Everything from Pancakes to Hamburgers

Standard Accessories	Material	UMRP	Included
PerfectClean Universal Tray	9811950	\$198	1
36 in Wire Rack w/ PyroFit	9858830	\$247.50	2
36 in Telescopic Rack w/ PyroFit	12072710	\$379.50	1
PerfectClean Grilling and Roasting Insert	9520630	\$137.50	1
PerfectClean Perforated Baking Tray	9520620	\$121	1
Grill / Griddle Cover*	9974610	\$275	1

Optional Accessories	Material	UMRP
Backsplash DF 12 in / 36 in width	9908770	\$412.50
Backsplash DF 20 in / 36 in width	9908900	\$449.90
WokRing	9974600	\$104.50
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50

*Ships separate from the unit.

Ranges – 48" Dual Fuel Range



Model	Material	UMRP
HR 1954-3 DF 48" Dual Fuel Range	11791670	\$16,699
HR 1954-3 DF LP	11791680	\$16,999

Specifications

Burners	4 x 19,500 BTU (G/LP) 2 x 13,600 BTU (G) and 13,000 BTU (LP) 2 x 10,000 BTU (G/LP)
Width	47 15/16 in (1,220 mm)
Height	35 1/5 – 37 in (902 – 940 mm)
Depth	27 1/2 in (698 mm)
Shipping Weight	637 lbs (289 kg)

Features

- M Touch Display – Simple to use Touch Controls
- Automatic Programs – Easily Master New Recipes
- Moisture Plus – For Perfect Baking and Roasting Results
- Wireless Precision Probe – Simple to Monitor Food Temperature
- Miele@home – Monitor your Appliances from your Mobile Device
- Speed Oven – Maximum Versatility in One Appliance

Standard Accessories	Material	UMRP	Included
PerfectClean Universal Tray	9811950	\$198	1
48 in Wire Rack w/ PyroFit	9858840	\$207.90	3
FlexiClips w/ PyroFit	9520710	\$247.50	2
PerfectClean Grilling and Roasting Insert	9520630	\$137.50	1
PerfectClean Perforated Baking Tray	9520620	\$121	1

Optional Accessories	Material	UMRP
Backguard 12 in / 48 in width	9908790	\$504.90
Backguard 20 in / 48 in width	9908910	\$548.90
WokRing	9974600	\$104.50
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50

Ranges — **48" Dual Fuel Range** with M Pro Infrared Grill



Model	Material	UMRP
HR 1955-3 DF GR 48" Dual Fuel Range with Infrared Grill	11791690	\$17,999

Specifications

Burners	3 x 19,500 BTU (G) 1 x 13,600 BTU (G) 2 x 10,000 BTU (G)
Width	47 15/16 in (1,220 mm)
Height	35 1/5 – 37 in (902 – 940 mm)
Depth	27 1/2 in (698 mm)

Features

- M Touch Display – Simple to use Touch Controls
- Automatic Programs – Easily Master New Recipes
- Moisture Plus – For Perfect Baking and Roasting Results
- Wireless Precision Probe – Simple to Monitor Food Temperature
- Miele@home – Monitor your Appliances from your Mobile Device
- Speed Oven – Maximum Versatility in One Appliance
- M Pro Grill – A powerful Grill on your Cooktop

Standard Accessories	Material	UMRP	Included
PerfectClean Universal Tray	9811950	\$198	1
48 in Wire Rack w/ PyroFit	9858840	\$207.90	3
FlexiClips w/ PyroFit	9520710	\$247.50	2
PerfectClean Grilling and Roasting Insert	9520630	\$137.50	1
PerfectClean Perforated Baking Tray	9520620	\$121	1
Grill / Griddle Cover*	9974610		\$275 1

Optional Accessories	Material	UMRP
Backsplash 12 in / 48 in width	9908790	\$504.90
Backsplash 20 in / 48 in width	9908910	\$548.90
WokRing	9974600	\$104.50
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50

*Ships separate from the unit.

Ranges — **48" Dual Fuel Range** with M Pro Infrared Griddle



Model	Material	UMRP
HR 1956-3 DF GD 48" Dual Fuel Range with Infrared Griddle	11791700	\$17,999
HR 1956-3 DF GD LP	11791750	\$17,999

Specifications

Burners	3 x 19,500 BTU (G) 1 x 13,600 BTU (G) 2 x 10,000 BTU (G)
Width	47 15/16 in (1,220 mm)
Height	35 1/5 – 37 in (902 – 940 mm)
Depth	27 1/2 in (698 mm)
Shipping Weight	637 lbs (289 kg)

Features

- M Touch Display – Simple to use Touch Controls
- Automatic Programs – Easily Master New Recipes
- Moisture Plus – For Perfect Baking and Roasting Results
- Wireless Precision Probe – Simple to Monitor Food Temperature
- Miele@home – Monitor your Appliances from your Mobile Device
- Speed Oven – Maximum Versatility in One Appliance
- M Pro Infrared Griddle – Great Results for Everything from Pancakes to Hamburgers

Standard Accessories	Material	UMRP	Included
PerfectClean Universal Tray	9811950	\$198	1
48 in Wire Rack w/ PyroFit	9858840	\$207.90	3
FlexiClips w/ PyroFit	9520710	\$247.50	2
PerfectClean Grilling and Roasting Insert	9520630	\$137.50	1
PerfectClean Perforated Baking Tray	9520620	\$121	1
Grill / Griddle Cover*	9974610	\$275	1

Optional Accessories	Material	UMRP
Backguard 12 in / 48 in width	9908790	\$504.90
Backguard 20 in / 48 in width	9908910	\$548.90
WokRing	9974600	\$104.50
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50

*Ships separate from the unit.

Product Highlights — RangeTops

Feature	Description (see specific models for details)
TrueSimmer Function	Achieve the perfect temperature and even heat for simmering.
M Pro Griddle	Engineered with an infrared heating element, the M Pro Griddle delivers fast, even heat for flawless results on everything from pancakes to fish and steak.
M Pro Infrared Grill	The M Pro Infrared Grill provides powerful, even radiant heat beneath a durable grill grate for precise, restaurant-quality indoor grilling and exceptional searing performance.
Backlit Precision Knobs	This elegant feature lets you know at a glance whether your burners are on or off.
Convenient and Safe	Automatic re-ignition for all burners.
Easy Cleaning	ComfortClean dishwasher safe grates. Clean Touch Steel™ finish which resists fingerprints, scratches and smudges, for a clean looking exterior.

Ranges — 30" All Gas RangeTop



Model	Material	UMRP
KMR 1124-3 G 30" All Gas RangeTop	11852270	\$4,499
KMR 1124-3 LP	11852330	\$4,499

Specifications

Burners	Simmer burner 12,500 BTU Power burner 19,500 BTU Total cooktop output 71,000 BTU
Width	29 15/16 in (762 mm)
Height	7 1/2 in (191 mm)
Depth	26 1/2 in (673 mm)
Shipping Weight	110.3 lbs (50 kg)

Features

- Direct Control
- ComfortClean Grates
- Clean Touch Steel™ finish
- 4 Powerful Burners
- 1 Continuous Simmer Burner

Optional Accessories	Material	UMRP
Backguard 12 in / 30 in width	9908760	\$383.90
Backguard 20 in / 30 in width	9908900	\$449.90
WokRing	9974600	\$104.50

Ranges — 36" All Gas RangeTop



Model	Material	UMRP
KMR 1134-3 G 36" All Gas RangeTop	11852340	\$5,399
KMR 1134-3 LP	11852370	\$5,399

Specifications

Burners	Simmer burner 12,500 BTU Power burner, rear 13,600 BTU Power burner, front 19,500 BTU Total cooktop output 98,200 BTU
Width	35 15/16 in (915 mm)
Height	7 1/2 in (191 mm)
Depth	26 1/2 in (673 mm)
Shipping Weight	134.5 lbs (61 kg)

Features

- Direct Control
- ComfortClean Grates
- Clean Touch Steel™ finish
- 1 Continuous Simmer Burner
- 6 Powerful Burners

Optional Accessories	Material	UMRP
WokRing	9974600	\$104.50
Backguard 12 in / 36 in width	9908770	\$412.50
Backguard 20 in / 36 in width	9908900	\$449.90

Model	Material	UMRP
KMR 1135-3 G GR 36" All Gas RangeTop with Grill	11852380	\$6,499

Specifications

Burners	Simmer burner 12,500 BTU Power burner, rear 13,600 BTU Power burner, front 19,500 BTU Grill 19,000 BTU Total cooktop output 84,100 BTU
Width	35 15/16 in (915 mm)
Height	7 1/2 in (191 mm)
Depth	26 1/2 in (673 mm)
Shipping Weight	145.5 lbs (66 kg)

Features

- Direct Control
- ComfortClean Grates
- Clean Touch Steel™ finish
- 4 Powerful Burners
- 1 Continuous Simmer Burner
- M Pro Grill

Standard Accessories	Material	UMRP
Grill / Griddle Cover*	9974610	\$275

Optional Accessories	Material	UMRP
WokRing	9974600	\$104.50
Backguard 12 in / 36 in width	9908770	\$412.50
Backguard 20 in / 36 in width	9908900	\$449.90

*Ships separate from the unit.

Ranges — 36" All Gas RangeTop



Model	Material	UMRP
KMR 1136-3 G GD 36" All Gas RangeTop with Griddle	11852460	\$6,499
KMR 1136-3 LP GD	11852550	\$6,499

Specifications

Burners	Simmer burner 12,500 BTU Power burner, rear 13,600 BTU Power burner, front 19,500 BTU Griddle 13,000 BTU Total cooktop output 78,100 BTU
Width	35 15/16 in (915 mm)
Height	7 1/2 in (191 mm)
Depth	26 1/2 in (673 mm)
Shipping Weight	164.3 lbs (74.5 kg)

Features

- Direct Control
- ComfortClean Grates
- Clean Touch Steel™ finish
- 4 Powerful Burners
- 1 Continuous Simmer Burner
- M Pro Infrared Griddle

Standard Accessories	Material	UMRP
Grill / Griddle Cover*	9974610	\$275

Optional Accessories	Material	UMRP
WokRing	9974600	\$104.50
Backguard 12 in / 36 in width	9908770	\$412.50
Backguard 20 in / 36 in width	9908900	\$449.90

*Ships separate from the unit.

Ranges — 48" All Gas RangeTop



Model	Material	UMRP
KMR 1354-3 G 48" All Gas RangeTop	11852560	\$6,799
KMR 1354-3 LP	11852570	\$6,799

Specifications

Burners	Simmer burner 10,000 BTU Power burner, rear 13,600 BTU Power burner, front 19,500 BTU Total cooktop output 125,200 BTU
Width	47 15/16 in (1220 mm)
Height	7 1/2 in (191 mm)
Depth	26 1/2 in (673 mm)
Shipping Weight	165.3 lbs (75 kg)

Features

- Direct Control
- ComfortClean Grates
- Clean Touch Steel™ finish
- 2 Continuous Simmer Burners

Optional Accessories	Material	UMRP
WokRing	9974600	\$104.50
Backguard 12 in / 48 in width	9908790	\$504.90
Backguard 20 in / 48 in width	9908910	\$548.90

Model	Material	UMRP
KMR 1355-3 G GR 48" All Gas RangeTop with Grill	11852600	\$7,199

Specifications

Burners	Simmer burner 10,000 BTU Power burner, rear 13,600 BTU Power burner, front 19,500 BTU Grill 19,000 BTU Total cooktop output 111,100 BTU
Width	47 15/16 in (1220 mm)
Height	7 1/2 in (191 mm)
Depth	26 1/2 in (673 mm)
Shipping Weight	174 lbs (79 kg)

Features

- Direct Control
- ComfortClean Grates
- Clean Touch Steel™ finish
- M Pro Grill
- 2 Continuous Simmer Burners

Standard Accessories	Material	UMRP
Grill / Griddle Cover*	9974610	\$275

Optional Accessories	Material	UMRP
WokRing	9974600	\$104.50
Backguard 12 in / 48 in width	9908790	\$504.90
Backguard 20 in / 48 in width	9908910	\$548.90

*Ships separate from the unit.

Ranges — 48" All Gas RangeTop



Model	Material	UMRP
KMR 1356-3 G GD 48" All Gas RangeTop with Griddle	11852640	\$7,199
KMR 1356-3 LP GD	11852660	\$7,199

Specifications

Burners	Simmer burner 10,000 BTU Power burner, rear 13,600 BTU Power burner, front 19,500 BTU Griddle 13,000 BTU Total cooktop output 105,100 BTU
Width	47 15/16 in (1220 mm)
Height	7 1/2 in (191 mm)
Depth	26 1/2 in (673 mm)
Shipping Weight	187.4 lbs (85 kg)

Features

- Direct Control
- ComfortClean Grates
- Clean Touch Steel™ finish
- M Pro Infrared Griddle
- 2 Continuous Simmer Burners

Standard Accessories	Material	UMRP
Grill / Griddle Cover*	9974610	\$275

Optional Accessories	Material	UMRP
WokRing	9974600	\$104.50
Backguard 12 in / 48 in width	9908790	\$504.90
Backguard 20 in / 48 in width	9908910	\$548.90

*Ships separate from the unit.

Product Highlights — **Gas Cooktops**

Feature	Description (see specific models for details)
ComfortClean Grates	Enjoy the convenience of removable, dishwasher safe grates.
Powerful Burners	Option of natural gas or liquid propane.
Wok Burners	Single or dual-wok burner for uniform and/or separate power regulation of both flame rings.
Simple controls	Single-handed operation via rotary dial control.
Installation and Design Options	Choose a flush mounted cooktop for a more seamless look, or a proud installation including a lip of stainless steel above your countertop. Choose from stainless steel or elegant ceramic glass to suit your design needs.

Cooktops — Gas Cooktop



Model	Material	UMRP
KM 3010 G 24" Gas on Glass Cooktop	9272050	\$2,099

Specifications

Width	24 3/4 in (626 mm)
Height	2 1/4 in (54 mm)
Depth	20 3/4 in (526 mm)
Shipping Weight	37 lbs (17 kg)
Number of Burners	4
Burner Output in BTU	9300
Burner Output in BTU	5800
Burner Output in BTU	5800
Burner Output in BTU	3700



Model	Material	UMRP
KM 2012 G All Gas Cooktop	11471350	\$1,699

Specifications

Width	25 9/16 in (650 mm)
Height	3 5/8 in (90 mm)
Depth	20 1/2 in (520 mm)
Shipping Weight	36 lbs (16 kg)
Number of Burners	4
Burner Output in BTU	11300
Burner Output in BTU	5500
Burner Output in BTU	5500
Burner Output in BTU	3800

Standard Accessories

Accessories	Material	UMRP
RWR1000 Wok Ring	9974600	\$104.50

Cooktops — 30" Gas Cooktop



Model	Material	UMRP
KM 3465 G 30" All Gas Cooktop	6792700	\$2,799
KM 3465 LP	6792730	\$2,799

Specifications

Width	30 in (762 mm)
Height	3 1/4 in (83 mm)
Depth	21 3/8 in (542 mm)
Shipping Weight	50 lbs (22.7 kg)
Number of Burners	4
Burner Output in BTU	15300
Burner Output in BTU	12000
Burner Output in BTU	9000
Burner Output in BTU	9000

Features

- Wok Burner

Standard Accessories	Material	UMRP
RWR1000 Wok Ring	9974600	\$104.50



Model	Material	UMRP
KM 2032 G All Gas Cooktop	10735660	\$1,699

Specifications

Width	29 1/2 in (750 mm)
Height	2 1/8 in (54 mm)
Depth	20 1/2 in (520 mm)
Shipping Weight	40 lbs (19 kg)
Number of Burners	5
Burner Output in BTU	11300
Burner Output in BTU	8600
Burner Output in BTU	5500
Burner Output in BTU	5500
Burner Output in BTU	3800

Features

- Wok Burner

Standard Accessories	Material	UMRP
RWR1000 Wok Ring	9974600	\$104.50

Cooktops — 36" Gas Cooktop



Model	Material	UMRP
KM 2355 G 36" Flush Gas Cooktop	9450190	\$3,199
KM 2355 LP	9456920	\$3,199

Specifications

Width	35 1/8 in (892 mm)
Height	4 1/16 in (102 mm)
Depth	20 3/16 in (512 mm)
Shipping Weight	51.8 lbs (23.5 kg)
Number of Burners	5
Burner Output in BTU	15000
Burner Output in BTU	9800
Burner Output in BTU	5900
Burner Output in BTU	5900
Burner Output in BTU	3900

Features

- Wok Burner

Standard Accessories	Material	UMRP
RWR1000 Wok Ring	9974600	\$104.50



Model	Material	UMRP
KM 3475 G 36" Gas Cooktop Linear	6792770	\$3,099

Specifications

Width	36 in (914 mm)
Height	5 in (125 mm)
Depth	21 3/8 in (542 mm)
Shipping Weight	55 lbs (25 kg)
Number of Burners	5
Burner Output in BTU	15300
Burner Output in BTU	12500
Burner Output in BTU	9000
Burner Output in BTU	9000
Burner Output in BTU	9000

Features

- Wok Burner

Standard Accessories	Material	UMRP
RWR1000 Wok Ring	9974600	\$104.50

Cooktops — 36" Gas Cooktop



Model	Material	UMRP
KM 3054-1G 36" Gas on Glass Cooktop	11766750	\$3,199

Specifications

Width	37 1/8 in (942 mm)
Height	2 13/16 in (71 mm)
Depth	20 3/4 in (526 mm)
Shipping Weight	54 lbs (24.5 kg)
Number of Burners	5
Burner Output in BTU	16500
Burner Output in BTU	9300
Burner Output in BTU	5800
Burner Output in BTU	5800
Burner Output in BTU	3750

Features

- Wok Burner

Standard Accessories	Material	UMRP
RWR1000 Wok Ring	9974600	\$104.50

Cooktops — 42" Gas Cooktop



Model	Material	UMRP
KM 3485 G 42" Gas Cooktop Linear	6792850	\$3,299
KM 3485 LP	6792870	\$3,299

Specifications

Width	42 1/2 in (1079 mm)
Height	3 1/4 in (83 mm)
Depth	21 3/8 in (542 mm)
Shipping Weight	75 lbs (34 kg)
Number of Burners	6
Burner Output in BTU	15300
Burner Output in BTU	15300
Burner Output in BTU	12000
Burner Output in BTU	12000
Burner Output in BTU	9000
Burner Output in BTU	9000


Standard Accessories	Material	UMRP
RWR1000 Wok Ring	9974600	\$104.50

Product Highlights —

Electric Cooktops and Induction Cooktops

Feature	Description (see specific models for details)
Auto Heat-Up	Provides an initial power boost before reducing the power level for continued cooking.
Keep Warm Function	The temperature is controlled to keep food at serving temperature, while also preventing the food from burning.
Timer	Set a duration for cook time with automatic alert once complete.
TwinBoost	Booster function for the shortest boiling times.
Efficient Induction	Most energy efficient cooking method Miele offers.
Stylish Glass	Black glass surface adds a clean look to any kitchen.

Cooktops — Electric Cooktop



Model	Material	UMRP
KM 5621 240V 24" All Electric Cooktop with Frame	7821660	\$2,199
KM 5621 208V	7821670	\$2,199


Specifications

Width	24 3/4 in (626 mm)
Height	2 11/16 in (68 mm)
Depth	21 7/16 in (544 mm)
Shipping Weight	39 lbs (17.7 kg)
Number of Burners	3 (2 variable)
Burner Output in Watts	1100 – 2150 – 3100
Burner Output in Watts	700 – 1800
Burner Output in Watts	1200

Features

- Residual Heat Indicators for Each Zone
- Easy to use Direct Control

Optional Accessories	Material	UMRP
Razor Blade Glass Scraper	1065471	\$19.80
Glass Cooktop Cleaner	10173130	\$15.99



Model	Material	UMRP
KM 5624 240V 30" All Electric Cooktop with Frame	7821680	\$2,399

Specifications


Width	30 1/2 in (775 mm)
Height	2 15/16 in (75 mm)
Depth	21 7/16 in (544 mm)
Shipping Weight	41 lbs (18.8 kg)
Number of Burners	4 (3 variable)
Burner Output in Watts	1600 – 2500
Burner Output in Watts	700 – 1800
Burner Output in Watts	1200

Features

- Residual Heat Indicators for Each Zone
- Easy to use Direct Control

Optional Accessories	Material	UMRP
Razor Blade Glass Scraper	1065471	\$19.80
Glass Cooktop Cleaner	10173130	\$15.99

Cooktops — Electric Cooktop



Model	Material	UMRP
KM 5840 240V 30" All Electric Cooktop with Frame	7821740	\$2,599


Specifications

Width	30 1/2 in (775 mm)
Height	2 11/16 in (68 mm)
Depth	21 7/16 in (544 mm)
Shipping Weight	41 lbs (18.8 kg)
Number of Burners	4 (3 variable)
Burner Output in Watts	1600 – 2500
Burner Output in Watts	1600 – 2500
Burner Output in Watts	700 – 1800
Burner Output in Watts	1200

Features

- Residual Heat Indicators for Each Zone
- Easy to use Direct Control

Optional Accessories	Material	UMRP
Razor Blade Glass Scraper	1065471	\$19.80
Glass Cooktop Cleaner	10173130	\$15.99



Model	Material	UMRP
KM 5627 240V 36" All Electric Cooktop with Frame	7821700	\$2,599
KM 5627 208V	7821710	\$2,599

Specifications


Width	36 in (915 mm)
Height	2 15/16 in (75 mm)
Depth	21 7/16 in (544 mm)
Shipping Weight	50 lbs (22.7 kg)
Number of Burners	5 (4 variable)
Burner Output in Watts	2000 – 2700
Burner Output in Watts	1600 – 2500
Burner Output in Watts	700 – 1800
Burner Output in Watts	700 – 1800
Burner Output in Watts	1200

Features

- Residual Heat Indicators for Each Zone
- Easy to use Direct Control

Optional Accessories	Material	UMRP
Scraper Razor Blade Glass Scraper	1065471	\$19.80
Glass Cooktop Cleaner	10173130	\$15.99

Cooktops — Electric Cooktop



Model	Material	UMRP
KM 5860 240V 36" All Electric Cooktop with Frame	7821760	\$2,999


Specifications

Width	36 in (915 mm)
Height	2 11/16 in (68 mm)
Depth	21 7/16 in (544 mm)
Shipping Weight	48.5 lbs (22 kg)
Number of Burners	5 (4 variable)
Burner Output in Watts	1100 – 2150 – 3100
Burner Output in Watts	1600 – 2500
Burner Output in Watts	700 – 1800
Burner Output in Watts	700 – 1800
Burner Output in Watts	1200

Features

- Residual Heat Indicators for Each Zone
- Easy to use Direct Control

Optional Accessories	Material	UMRP
Razor Blade Glass Scraper	1065471	\$19.80
Glass Cooktop Cleaner	10173130	\$15.99



Model	Material	UMRP
KM 5880 240V 42" All Electric Cooktop with Frame	7821780	\$3,299

Specifications


Width	42 1/2 in (1079 mm)
Height	2 11/16 in (75 mm)
Depth	21 7/16 in (544 mm)
Shipping Weight	55 lbs (25 kg)
Number of Burners	5 (4 variable)
Burner Output in Watts	1100 – 2150 – 3100
Burner Output in Watts	1600 – 2500
Burner Output in Watts	700 – 1800
Burner Output in Watts	700 – 1800
Burner Output in Watts	1200

Features

- Residual Heat Indicators for Each Zone
- Easy to use Direct Control

Optional Accessories	Material	UMRP
Scraper Razor Blade Glass Scraper	1065471	\$19.80
Glass Cooktop Cleaner	10173130	\$15.99

Cooktops — Full Surface Induction Cooktop



Model	Material	UMRP
KM 7737 FR 30" Full Surface Induction Cooktop — Framed	13008680	\$5,999


Specifications

Width	31 3/4 in (806 mm)
Height	4 1/8 in (103 mm)
Depth	20 11/16 in (526 mm)
Shipping Weight	62 lbs (28 kg)
Electrical Requirements	208/240 V, 60 Hz
Circuit Breaker	40 A
Power Cord	6 ft 6 3/4 in (2 m)

Features

- Hard-wearing finish — DiamondFinish
- Intelligent pan recognition — for up to 6 pans
- Intuitive quick selection via numerical displays — SmartSelect White
- Communication with the ventilation hood — automatic Con@ctivity function
- With a width of 31 3/4 in (806 mm) for proud installation

Optional Accessories	Material	UMRP
Razor Blade Glass Scraper	1065471	\$19.80
Glass Cooktop Cleaner	10173130	\$15.99



Model	Material	UMRP
KM 7737 FL 30" Full Surface Induction Cooktop — Frameless	13008700	\$5,999

Specifications


Width	31 3/4 in (806 mm)
Height	4 1/8 in (103 mm)
Depth	20 11/16 in (526 mm)
Shipping Weight	62 lbs (28 kg)
Electrical Requirements	208/240 V, 60 Hz
Circuit Breaker	40 A
Power Cord	6 ft 6 3/4 in (2 m)

Features

- Hard-wearing finish — DiamondFinish
- Intelligent pan recognition — for up to 6 pans
- Intuitive quick selection via numerical displays — SmartSelect White
- Communication with the ventilation hood — automatic Con@ctivity function
- With a width of 31 3/4 in (806 mm) for proud or flush installation

Optional Accessories	Material	UMRP
Razor Blade Glass Scraper	1065471	\$19.80
Glass Cooktop Cleaner	10173130	\$15.99

Cooktops — Full Surface Induction Cooktop



Model	Material	UMRP
KM 7747 FR 36" Full Surface Induction Cooktop — Framed	13008690	\$6,999


Specifications

Width	37 1/16 in (942 mm)
Height	4 1/8 in (103 mm)
Depth	20 11/16 in (526 mm)
Shipping Weight	68 lbs (31 kg)
Electrical Requirements	208/240 V, 60 Hz
Circuit Breaker	50 A
Power Cord	6 ft 6 3/4 in (2 m)

Features

- Hard-wearing finish — DiamondFinish
- Intelligent pan recognition — for up to 6 pans
- Intuitive quick selection via numerical displays — SmartSelect White
- Communication with the ventilation hood — automatic Con@ctivity function
- With a width of 37 1/16 in (942 mm) for proud installation

Optional Accessories	Material	UMRP
Razor Blade Glass Scraper	1065471	\$19.80
Glass Cooktop Cleaner	10173130	\$15.99



Model	Material	UMRP
KM 7747 FL 36" Full Surface Induction Cooktop — Frameless	13008710	\$6,999

Specifications

Width	36 7/8 in (936 mm)
Height	4 1/8 in (103 mm)
Depth	20 1/2 in (520 mm)
Shipping Weight	66 lbs (30 kg)
Electrical Requirements	208/240 V, 60 Hz
Circuit Breaker	50 A
Power Cord	6 ft 6 3/4 in (2 m)

Features

- Hard-wearing finish — DiamondFinish
- Intelligent pan recognition — for up to 6 pans
- Intuitive quick selection via numerical displays — SmartSelect White
- Communication with the ventilation hood — automatic Con@ctivity function
- With a width of 36 7/8 in (936 mm) for proud or flush installation

Optional Accessories	Material	UMRP
Razor Blade Glass Scraper	1065471	\$19.80
Glass Cooktop Cleaner	10173130	\$15.99

Cooktops — Induction Cooktop



Model	Material	UMRP
KM 7720 24" All Induction Cooktop with Frame	12074190	\$2,299

Specifications

Width	24 5/8 in (626 mm)
Height	3 1/8 in (78 mm)
Depth	21 7/16 in (544 mm)
Shipping Weight	35.6 lbs (17.5 kg)
Number of Burners	3 (1)
Burner Output in Watts (208V – 240V)	2,400 – 2,750 – 3,350 / 2,600 – 3,000 – 3,700
Burner Output in Watts (208V – 240V)	1,700 – 2,300 – 2,750 / 1,850 – 2,500 – 3,000
Burner Output in Watts (208V – 240V)	1,300 – 1,550 – 2,000 / 1,850 – 2,500 – 3,000

Features

- SmartSelect controls with yellow display
- Boost function up to 3,700W
- 3 powerful cooking zones
- Stainless Steel Frame for surface mounting

Optional Accessories	Material	UMRP
Razor Blade Glass Scraper	1065471	\$19.80
Glass Cooktop Cleaner	10173130	\$15.99



Model	Material	UMRP
KM 7730 FR 30" All Induction Cooktop with Frame	12074200	\$2,799

Specifications


Width	30 1/2 in (775 mm)
Height	3 1/8 in (78 mm)
Depth	21 7/16 in (544 mm)
Shipping Weight	44 lbs (20 kg)
Number of Burners	4 (1)
Burner Output in Watts (208V – 240V)	2,400 – 2,750 – 3,350 / 2,600 – 3,000 – 3,700
Burner Output in Watts (208V – 240V)	1,300 – 1,550 – 2,000 / 1,400 – 1,700 – 2,200
Burner Output in Watts (208V – 240V)	1,700 – 2,300 – 1,750 / 1,850 – 2,300 – 3,300
Burner Output in Watts (208V – 240V)	1,700 – 2,300 – 2,750 / 1,850 – 2,500 – 3,000

Features

- SmartSelect controls with yellow display
- Boost function up to 3700W
- 4 powerful cooking zones
- Stainless Steel Frame for surface mounting

Optional Accessories	Material	UMRP
Razor Blade Glass Scraper	1065471	\$19.80
Glass Cooktop Cleaner	10173130	\$15.99

Cooktops — Induction Cooktop



Model	Material	UMRP
KM 7735 FL 30" All Induction Cooktop (Frameless)	12074210	\$3,299


Specifications

Width	30 3/8 in (769 mm)
Height	3 7/8 in (98 mm)
Depth	21 1/4 in (538 mm)
Shipping Weight	44.6 lbs (21.23 kg)
Number of Burners	4 (1)
Burner Output in Watts:	2,600 – 3,000 – 3,700
Max. Rating	
Max. Booster power rating	
Max. TwinBooster power rating (208V – 240V)	
Burner Output in Watts:	1,400 – 1,700 – 2,200
Max. Rating	
Max. Booster power rating	
Max. TwinBooster power rating (208V – 240V)	
Burner Output in Watts:	3,400 – 4,800 – 7,400
Max. Rating	
Max. Booster power rating	
Max. TwinBooster power rating (208V – 240V)	

Features

- SmartSelect controls with yellow display
- Boost function up to 4,800W
- 4 powerful cooking zones

Optional Accessories	Material	UMRP
Razor Blade Glass Scraper	1065471	\$19.80
Glass Cooktop Cleaner	10173130	\$15.99



Model	Material	UMRP
KM 7740 FR 36" All Induction Cooktop with Frame	12074220	\$3,199

Specifications


Width	36 in (915 mm)
Height	3 1/8 in (78 mm)
Depth	21 7/16 in (544 mm)
Shipping Weight	55 lbs (25 kg)
Number of Burners	5
Burner Output in Watts (208V – 240V)	1,300 – 1,550 – 2,000 / 1,400 – 1,700 – 2,200
Burner Output in Watts (208V – 240V)	2,100 – 2,750 – 3,350 / 2,300 – 3,000 – 3,700
Burner Output in Watts (208V – 240V)	2,400 – 2,750 – 3,350 / 2,600 – 3,000 – 3,700
Burner Output in Watts (208V – 240V)	1,700 – 2,300 – 2,750 / 1,850 – 2,500 – 3,000
Burner Output in Watts (208V – 240V)	1,700 – 2,300 – 2,750 / 1,850 – 2,500 – 3,000

Features

- SmartSelect controls with yellow display
- Boost function up to 3,700W
- 5 powerful cooking zones
- Stainless Steel Frame for surface mounting

Optional Accessories	Material	UMRP
Razor Blade Glass Scraper	1065471	\$19.80
Glass Cooktop Cleaner	10173130	\$15.99

Cooktops — Induction Cooktop



Model	Material	UMRP
KM 7745 FL 36" All Induction Cooktop (Frameless)	12074230	\$3,999

Specifications

Width	35 7/8 in (909 mm)
Height	4 1/8 in (103 mm)
Depth	21 1/4 in (538 mm)
Shipping Weight	68.34 lbs (31 kg)
Number of Burners	6
Burner Output in Watts:	3,100 – 3,400 – 3,700
Max. Rating	
Max. Booster power rating	
Max. TwinBooster power rating (208V – 240V)	
Burner Output in Watts:	3,400 – 4,800 – 7,400
Max. Rating	
Max. Booster power rating	
Max. TwinBooster power rating (208V – 240V)	
Burner Output in Watts:	3,400 – 4,800 – 7,400
Max. Rating	
Max. Booster power rating	
Max. TwinBooster power rating (208V – 240V)	

Features

- SmartSelect controls with yellow display
- Boost function up to 4,800W
- 3 PowerFlex zones

Optional Accessories	Material	UMRP
Razor Blade Glass Scraper	1065471	\$19.80
Glass Cooktop Cleaner	10173130	\$15.99



Model	Material	UMRP
KM 7755 FL 42" All Induction Cooktop (Frameless)	12074240	\$4,999

Specifications

Width	42 3/8 in (1074 mm)
Height	3 3/18 in (77 mm)
Depth	21 1/4 in (538 mm)
Shipping Weight	72.3 lbs (32.8 kg)
Number of Burners	5
Burner Output in Watts:	3,400 – 4,800 – 7,400
Max. Rating	
Max. Booster power rating	
Max. TwinBooster power rating (208V – 240V)	
Burner Output in Watts:	2,600 – 3,000 – 3,700
Max. Rating	
Max. Booster power rating	
Max. TwinBooster power rating (208V – 240V)	
Burner Output in Watts:	3,400 – 4,800 – 7,400
Max. Rating	
Max. Booster power rating	
Max. TwinBooster power rating (208V – 240V)	

Features

- SmartSelect controls with yellow display
- Boost function up to 4,800W
- 2 PowerFlex zones and 1 round element

Optional Accessories	Material	UMRP
Razor Blade Glass Scraper	1065471	\$19.80
Glass Cooktop Cleaner	10173130	\$15.99

Product Highlights – **Convection Ovens**

Feature	Description (see specific models for details)
FoodView	See the progress of your cooking on your mobile device with the in-oven camera.
Wireless Precision Probe	Precise temperature control, with 4 points of temperature monitoring and wireless connection.
M Touch Controls with MotionReact	Operate your appliance quickly and intuitively by tapping and swiping the touch display. Motion React turns on the light when it detects movement near the oven.
Moisture Plus	Adds a burst of steam for extraordinary roasting and baking results.
Automatic Programs	Miele guides you through hundreds of easy-to-use cooking programs.
Taste Control	Oven rapidly cools when cooking time is up, to ensure that your meals are never overcooked.
Miele@home	Interact with your Miele appliances from your mobile device with Miele@home.

Ovens — 30" Convection Oven



Model	Material	UMRP
H 7780 BP 30" Convection Oven	11805560	\$9,299

Design Line	Finish
ContourLine	Clean Touch Steel

Specifications	
Width	29 13/16 in (757 mm)
Height	28 5/8 in (727 mm)
Depth	23 3/4 in (603 mm)
Shipping Weight	215 lbs (98 kg)

Features
• M Touch Controls with MotionReact • FoodView – In Oven Camera • Wireless Precision Probe • Moisture Plus • TasteControl • Miele@home • Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray (1)	9811950	\$198
30" Wire Rack w/ PyroFit (2)	9811970	\$203.50
30" Telescopic Rack w/ PyroFit (1)	12072650	\$357.50
PerfectClean Grilling and Roasting Insert (1)	9520630	\$137.50
PerfectClean Perforated Baking Tray (1)	9520620	\$121

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
30" Vertical Cover Strip Stainless Steel	11956140	\$149



Model	Material	UMRP
H 7880 BP 30" Convection Oven	11805590	\$9,299

Design Line	Finish
PureLine	Clean Touch Steel

Specifications	
Width	29 13/16 in (757 mm)
Height	28 5/8 in (727 mm)
Depth	23 3/4 in (603 mm)
Shipping Weight	215 lbs (98 kg)

Features
• M Touch Controls with MotionReact • FoodView – In Oven Camera • Wireless Precision Probe • Moisture Plus • TasteControl • Miele@home • Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray (1)	9811950	\$198
30" Wire Rack w/ PyroFit (2)	9811970	\$203.50
30" Telescopic Rack w/ PyroFit (1)	12072650	\$357.50
PerfectClean Grilling and Roasting Insert (1)	9520630	\$137.50
PerfectClean Perforated Baking Tray (1)	9520620	\$121

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
30" Vertical Cover Strip Obsidian Black	11956100	\$149

Ovens — 30" Convection Oven



Model	Material	UMRP
H 7880 BP 30" Convection Oven	11805610	\$9,299

Design Line	Finish
VitroLine	Obsidian Black

Specifications	
Width	29 13/16 in (757 mm)
Height	28 5/8 in (727 mm)
Depth	23 3/4 in (603 mm)
Shipping Weight	215 lbs (98 kg)

Features
• M Touch Controls with MotionReact • FoodView – In Oven Camera • Wireless Precision Probe • Moisture Plus • TasteControl • Miele@home • Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray (1)	9811950	\$198
30" Wire Rack w/ PyroFit (2)	9811970	\$203.50
30" Telescopic Rack w/ PyroFit (1)	12072650	\$357.50
PerfectClean Grilling and Roasting Insert (1)	9520630	\$137.50
PerfectClean Perforated Baking Tray (1)	9520620	\$121

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
30" Vertical Cover Strip Obsidian Black	11956100	\$149



Model	Material	UMRP
H 7880 BP 30" Convection Oven	11805600	\$9,299

Design Line	Finish
VitroLine	Graphite Grey

Specifications	
Width	29 13/16 in (757 mm)
Height	28 5/8 in (727 mm)
Depth	23 3/4 in (603 mm)
Shipping Weight	215 lbs (98 kg)

Features
• M Touch Controls with MotionReact • FoodView – In Oven Camera • Wireless Precision Probe • Moisture Plus • TasteControl • Miele@home • Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray (1)	9811950	\$198
30" Wire Rack w/ PyroFit (2)	9811970	\$203.50
30" Telescopic Rack w/ PyroFit (1)	12072650	\$357.50
PerfectClean Grilling and Roasting Insert (1)	9520630	\$137.50
PerfectClean Perforated Baking Tray (1)	9520620	\$121

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
30" Vertical Cover Strip Graphite Grey	11956150	\$149

Ovens — 30" Convection Oven



Model	Material	UMRP
H 7880 BPX GRGR 30" Convection Oven	11805630	\$9,499

Design Line	Finish
ArtLine	Graphite Grey

Specifications	
Width	29 7/8 in (757 mm)
Height	28 5/8 in (727 mm)
Depth	24 5/8 in (625 mm)
Shipping Weight	177 lbs (80 kg)

Features
• M Touch Controls with MotionReact • FoodView – In Oven Camera • Wireless Precision Probe • Moisture Plus • TasteControl • Miele@home • Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray (1)	9811950	\$198
30" Wire Rack w/ PyroFit (2)	9811970	\$203.50
30" Telescopic Rack w/ PyroFit (1)	12072650	\$357.50
PerfectClean Grilling and Roasting Insert (1)	9520630	\$137.50
PerfectClean Perforated Baking Tray (1)	9520620	\$121

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
30" Vertical Cover Strip Graphite Grey	11956150	\$149



Model	Material	UMRP
H 7880 BPX OBSW 30" Convection Oven	12842580	\$9,499

Design Line	Finish
ArtLine	Obsidian Black

Specifications	
Width	29 7/8 in (757 mm)
Height	28 5/8 in (727 mm)
Depth	24 5/8 in (625 mm)
Shipping Weight	177 lbs (80 kg)

Features
• M Touch Controls with MotionReact • FoodView – In Oven Camera • Wireless Precision Probe • Moisture Plus • TasteControl • Miele@home • Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray (1)	9811950	\$198
30" Wire Rack w/ PyroFit (2)	9811970	\$203.50
30" Telescopic Rack w/ PyroFit (1)	12072650	\$357.50
PerfectClean Grilling and Roasting Insert (1)	9520630	\$137.50
PerfectClean Perforated Baking Tray (1)	9520620	\$121

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
30" Vertical Cover Strip Obsidian Black	11956100	\$149

Ovens — 30" Convection Oven



Model	Material	UMRP
H 7580 BP 30" Convection Oven	11805540	\$7,899

Design Line	Finish
ContourLine	Clean Touch Steel

Specifications	
Width	29 13/16 in (757 mm)
Height	28 5/8 in (727 mm)
Depth	23 3/4 in (603 mm)
Shipping Weight	215 lbs (98 kg)

Features
• M Touch S Controls with MotionReact • Moisture Plus • TasteControl • Miele@home • Wired Food Probe • Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray (1)	9811950	\$198
30" Wire Rack w/ PyroFit (2)	9811970	\$203.50
30" Telescopic Rack w/ PyroFit (1)	12072650	\$357.50
PerfectClean Grilling and Roasting Insert (1)	9520630	\$137.50

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Perforated Baking Tray	9520620	\$121
30" Vertical Cover Strip Stainless Steel	11956140	\$149



Model	Material	UMRP
H 7680 BP 30" Convection Oven	11805550	\$7,899

Design Line	Finish
PureLine	Clean Touch Steel

Specifications	
Width	29 13/16 in (757 mm)
Height	28 5/8 in (727 mm)
Depth	23 3/4 in (603 mm)
Shipping Weight	215 lbs (98 kg)

Features
• M Touch S Controls with MotionReact • Moisture Plus • TasteControl • Miele@home • Wired Food Probe • Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray (1)	9811950	\$198
30" Wire Rack w/ PyroFit (2)	9811970	\$203.50
30" Telescopic Rack w/ PyroFit (1)	12072650	\$357.50
PerfectClean Grilling and Roasting Insert (1)	9520630	\$137.50

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Perforated Baking Tray	9520620	\$121
30" Vertical Cover Strip Obsidian Black	11956100	\$149

Ovens — 30" Convection Oven



Model	Material	UMRP
H 7180 BP 30" Convection Oven	11805340	\$6,199

Design Line	Finish
ContourLine	Clean Touch Steel

Specifications	
Width	29 13/16 in (757 mm)
Height	28 5/8 in (727 mm)
Depth	23 3/4 in (603 mm)
Shipping Weight	215 lbs (98 kg)

Features
• DirectSensor S Controls • Miele@home • Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray (1)	9811950	\$198
30" Wire Rack w/ PyroFit (1)	9811970	\$203.50
30" Telescopic Rack w/ PyroFit (1)	12072650	\$357.50

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Perforated Baking Tray	9520620	\$121
PerfectClean Grilling and Roasting Insert	9520630	\$137.50
30" Vertical Cover Strip Stainless Steel	11956140	\$149

Model	Material	UMRP
H 7280 BP 30" Convection Oven	11805500	\$6,199

Design Line	Finish
PureLine	Clean Touch Steel

Specifications	
Width	29 13/16 in (757 mm)
Height	28 5/8 in (727 mm)
Depth	23 3/4 in (603 mm)
Shipping Weight	215 lbs (98 kg)

Features
• DirectSensor S Controls • Miele@home • Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray (1)	9811950	\$198
30" Wire Rack w/ PyroFit (1)	9811970	\$203.50
30" Telescopic Rack w/ PyroFit (1)	12072650	\$357.50

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Perforated Baking Tray	9520620	\$121
PerfectClean Grilling and Roasting Insert	9520630	\$137.50
30" Vertical Cover Strip Obsidian Black	11956100	\$149

Ovens — 30" Convection Oven



Model	Material	UMRP
H 7280 BP 30" Convection Oven	11805520	\$6,199

Design Line	Finish
VitroLine	Graphite Grey

Specifications	
Width	29 13/16 in (757 mm)
Height	28 5/8 in (727 mm)
Depth	23 3/4 in (603 mm)
Shipping Weight	215 lbs (98 kg)

Features
• DirectSensor S Controls • Miele@home • Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray (1)	9811950	\$198
30" Wire Rack w/ PyroFit (1)	9811970	\$203.50
30" Telescopic Rack w/ PyroFit (1)	12072650	\$357.50

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Perforated Baking Tray	9520620	\$121
PerfectClean Grilling and Roasting Insert	9520630	\$137.50
30" Vertical Cover Strip Graphite Grey	11956150	\$149



Model	Material	UMRP
H 7280 BP OBSW 30" Convection Oven	11968200	\$6,199

Design Line	Finish
VitroLine	Obsidian Black

Specifications	
Width	29 13/16 in (757 mm)
Height	28 5/8 in (727 mm)
Depth	23 3/4 in (603 mm)
Shipping Weight	215 lbs (98 kg)

Features
• DirectSensor S Controls • Miele@home • Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray (1)	9811950	\$198
30" Wire Rack w/ PyroFit (1)	9811970	\$203.50
30" Telescopic Rack w/ PyroFit (1)	12072650	\$357.50

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Perforated Baking Tray	9520620	\$121
PerfectClean Grilling and Roasting Insert	9520630	\$137.50
30" Vertical Cover Strip Obsidian Black	11956100	\$149

Ovens — 30" Convection Oven



Model	Material	UMRP
H 2780 BP 30" Convection Oven	11805320	\$5,299

Design Line	Finish
ContourLine	Clean Touch Steel

Specifications	
Width	29 13/16 in (757 mm)
Height	28 5/8 in (727 mm)
Depth	23 3/4 in (603 mm)
Shipping Weight	215 lbs (98 kg)

Features
• Easy Control

Standard Accessories	Material	UMRP
PerfectClean Universal Tray (1)	9811950	\$198
Baking and Roasting Rack (1)	9811970	\$203.50

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Perforated Baking Tray	9520620	\$121
PerfectClean Grilling and Roasting Insert	9520630	\$137.50
30" Rack w/ PyroFit	9811970	\$203.50
30" Telescopic Rack w/ PyroFit	12072650	\$357.50
30" Vertical Cover Strip Stainless Steel	11956140	\$149

Model	Material	UMRP
H 2880 BP 30" Convection Oven	11805330	\$5,299

Design Line	Finish
PureLine	Clean Touch Steel

Specifications	
Width	29 13/16 in (757 mm)
Height	28 5/8 in (727 mm)
Depth	23 3/4 in (603 mm)
Shipping Weight	215 lbs (98 kg)

Features
• Easy Control

Standard Accessories	Material	UMRP
PerfectClean Universal Tray (1)	9811950	\$198
Baking and Roasting Rack (1)	9811970	\$203.50

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Perforated Baking Tray	9520620	\$121
PerfectClean Grilling and Roasting Insert	9520630	\$137.50
30" Rack w/ PyroFit	9811970	\$203.50
30" Telescopic Rack w/ PyroFit	12072650	\$357.50
30" Vertical Cover Strip Obsidian Black	11956100	\$149

Ovens — 30" Double Oven



Model	Material	UMRP
H 7780 BP 2 30" Double Convection Oven	11805570	\$11,699

Design Line	Finish
ContourLine	Clean Touch Steel

Specifications	
Width	29 13/16 in (757 mm)
Height	50 7/8 in (1290 mm)
Depth	23 5/8 in (597 mm)
Shipping Weight	344 lbs (156 kg)

Features
• M Touch Controls with Motion React • Moisture Plus • Wireless Precision Probe • Miele@home • Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray (2)	9811950	\$198
30" Wire Rack w/ PyroFit (4)	9811970	\$203.50
30" Telescopic Rack w/ PyroFit (2)	12072650	\$357.50
Perfect Clean Grilling and Roasting Insert (1)	9520630	\$137.50
Perfect Clean Perforated Baking Tray (1)	9520620	\$121

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90

Ovens – 24" Convection Oven



Model	Material	UMRP
H 7660 BP 24" Convection Oven	11804810	\$5,099

Design Line	Finish
PureLine	Clean Touch Steel

Specifications	
Width	23 7/16 in (595 mm)
Height	23 7/16 in (596 mm)
Depth	21 1/2 in (546 mm)
Shipping Weight	119 lbs (54 kg)

Features
• M Touch S Controls with MotionReact • Moisture Plus • Taste Control • Miele@home • Wired Food Probe • Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack w/ Self Clean Ready (2)	9520640	\$130.90
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean Grill Insert 24" Oven (1)	9520630	\$137.50

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Perforated Baking Tray	9520620	\$121
PerfectClean Baking Tray	9519820	\$115.50
PerfectClean Grill Insert 24" Oven	9520630	\$137.50
Shelf Trim for 24" – Black	5165170	\$64.90
Shelf Trim for 24" – Stainless	7114780	\$64.90
Trim Kit: PureLine	11515790	\$499



Model	Material	UMRP
H 7660 BP 24" Convection Oven	11804860	\$5,099

Design Line	Finish
VitroLine	Obsidian Black

Specifications	
Width	23 7/16 in (595 mm)
Height	23 7/16 in (596 mm)
Depth	21 1/2 in (546 mm)
Shipping Weight	119 lbs (54 kg)

Features
• M Touch S Controls with MotionReact • Moisture Plus • Taste Control • Miele@home • Wired Food Probe • Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack w/ Self Clean Ready (2)	9520640	\$130.90
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean Grill Insert 24" Oven (1)	9520630	\$137.50

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Perforated Baking Tray	9520620	\$121
PerfectClean Baking Tray	9519820	\$115.50
PerfectClean Grill Insert 24" Oven	9520630	\$137.50
Shelf Trim for 24" – Black	5165170	\$64.90
Shelf Trim for 24" – Stainless	7114780	\$64.90
Trim Kit: Obsidian Black	11515800	\$479

Ovens — 24" Convection Oven



Model	Material	UMRP
H 7660 BP 24" Convection Oven	11804840	\$5,099

Design Line	Finish
VitroLine	Graphite Grey

Specifications	
Width	23 7/16 in (595 mm)
Height	23 7/16 in (596 mm)
Depth	21 1/2 in (546 mm)
Shipping Weight	119 lbs (54 kg)

Features	
• M Touch S Controls with MotionReact • Moisture Plus • Taste Control • Miele@home • Wired Food Probe • Automatic Programs	

Standard Accessories	Material	UMRP
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack w/ Self Clean Ready (2)	9520640	\$130.90
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean Grill Insert 24" Oven (1)	9520630	\$137.50

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Perforated Baking Tray	9520620	\$121
PerfectClean Baking Tray	9519820	\$115.50
PerfectClean Grill Insert 24" Oven	9520630	\$137.50
Shelf Trim for 24" — Black	5165170	\$64.90
Shelf Trim for 24" — Stainless	7114780	\$64.90
Trim Kit: Graphite Grey	11515820	\$479

Model	Material	UMRP
H 7263 BP 24" Convection Oven	11804760	\$3,499

Design Line	Finish
PureLine	Clean Touch Steel

Specifications	
Width	23 7/16 in (595 mm)
Height	23 7/16 in (596 mm)
Depth	21 1/2 in (546 mm)
Shipping Weight	119 lbs (54 kg)

Features	
• DirectSensor S Controls • Miele@home • Automatic Programs	

Standard Accessories	Material	UMRP
Wire Rack w/ Self Clean (Ready 1)	9520640	\$130.90
PerfectClean Universal Tray 24" Oven	9519840	\$165

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Perforated Baking Tray	9520620	\$121
PerfectClean Baking Tray	9519820	\$115.50
PerfectClean Grill Insert 24" Oven	9520630	\$137.50
PerfectClean FlexiClips	9520660	\$203.50
Shelf Trim for 24" — Black	5165170	\$64.90
Shelf Trim for 24" — Stainless	7114780	\$64.90
Trim Kit: PureLine	11515790	\$499

Ovens — 24" Convection Oven



Model	Material	UMRP
H 7263 BP 24" Convection Oven	11804780	\$3,499

Design Line	Finish
VitroLine	Graphite Grey

Specifications

Width	23 7/16 in (595 mm)
Height	23 7/16 in (596 mm)
Depth	21 1/2 in (546 mm)
Shipping Weight	119 lbs (54 kg)

Features

- DirectSensor S Controls
- Miele@home
- Automatic Programs

Standard Accessories	Material	UMRP
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
PerfectClean Universal Tray 24" Oven	9519840	\$165

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Perforated Baking Tray	9520620	\$121
PerfectClean Baking Tray	9519820	\$115.50
PerfectClean Grill Insert 24" Oven	9520630	\$137.50
PerfectClean FlexiClips	9520660	\$203.50
Shelf Trim for 24" — Black	5165170	\$64.90
Shelf Trim for 24" — Stainless	7114780	\$64.90
Trim Kit: Graphite Grey	11515820	\$449



Model	Material	UMRP
H 7263 BP OBSW 24" Convection Oven	12842730	\$3,499

Design Line	Finish
VitroLine	Obsidian Black

Specifications

Width	23 7/16 in (595 mm)
Height	23 7/16 in (596 mm)
Depth	21 1/2 in (546 mm)
Shipping Weight	119 lbs (54 kg)

Features

- DirectSensor S Controls
- Miele@home
- Automatic Programs

Standard Accessories	Material	UMRP
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
PerfectClean Universal Tray 24" Oven	9519840	\$165

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Perforated Baking Tray	9520620	\$121
PerfectClean Baking Tray	9519820	\$115.50
PerfectClean Grill Insert 24" Oven	9520630	\$137.50
PerfectClean FlexiClips	9520660	\$203.50
Shelf Trim for 24" — Black	5165170	\$64.90
Shelf Trim for 24" — Stainless	7114780	\$64.90
Trim Kit: Obsidian Black	11515800	\$449

Product Highlights — **Speed Ovens, Combi-Steam Ovens and Microwave Ovens**

Feature	Description (see specific models for details)
New Inverter Technology	True variable power levels cook food faster and more evenly than conventional microwaves.
Easy Maintenance	The stainless steel interior cavity makes for easy wipe down and clean-up.
Automatic Programs	Miele guides you through hundreds of easy-to-use cooking programs.
Combination Microwave/ Convection Mode	Speed ovens can reduce cook time up to 30% in combining microwave technology with conventional heat.
Mix & Match	Use your Miele app to select ingredients you already have to quickly cook a perfect meal in your Combi-Steam oven.
Popcorn and Beverage Function	With Miele microwave ovens, reheat beverages or make popcorn with one touch of a button.

Ovens — 30" Speed Oven



Model	Material	UMRP
H 7770 BM 30" Speed Oven	11804620	\$5,799

Design Line	Finish
ContourLine	Clean Touch Steel

Specifications	
Width	29 13/16 in (757 mm)
Height	18 7/8 in (479 mm)
Depth	21 11/16 in (551 mm)
Shipping Weight	128 lbs (58 kg)

Features
• M Touch Controls with MotionReact • Miele@home • Wired Food Probe • Automatic Programs

Standard Accessories	Material	UMRP
2 Glass Tray	10141820	\$309
Wire Rack	6881872	\$119

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Perforated Baking Tray	9520620	\$121
PerfectClean Baking Tray	9519820	\$115.50
PerfectClean Grill Insert 24" Oven	9520630	\$137.50
30" Vertical Cover Strip Stainless Steel	11956140	\$149

Note: Metal trays not for use in microwave modes



Model	Material	UMRP
H 7870 BM 30" Speed Oven	11804680	\$5,799

Design Line	Finish
PureLine	Clean Touch Steel

Specifications	
Width	29 13/16 in (757 mm)
Height	18 7/8 in (479 mm)
Depth	21 11/16 in (551 mm)
Shipping Weight	128 lbs (58 kg)

Features
• M Touch Controls with MotionReact • Miele@home • Wired Food Probe • Automatic Programs

Standard Accessories	Material	UMRP
2 Glass Tray	10141820	\$309
Wire Rack	6881872	\$119

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Perforated Baking Tray	9520620	\$121
PerfectClean Baking Tray	9519820	\$115.50
PerfectClean Grill Insert 24" Oven	9520630	\$137.50
30" Vertical Cover Strip Obsidian Black	11956100	\$149

Ovens — 30" Speed Oven



Model	Material	UMRP
H 7870 BM 30" Speed Oven	11804700	\$5,799

Design Line	Finish
VitroLine	Obsidian Black

Specifications	
Width	29 13/16 in (757 mm)
Height	18 7/8 in (479 mm)
Depth	21 11/16 in (551 mm)
Shipping Weight	128 lbs (58 kg)

Features
• M Touch Controls with MotionReact • Miele@home • Wired Food Probe • Automatic Programs

Standard Accessories	Material	UMRP
2 Glass Tray	10141820	\$309
Wire Rack	6881872	\$119

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Perforated Baking Tray	9520620	\$121
PerfectClean Baking Tray	9519820	\$115.50
PerfectClean Grill Insert 24" Oven	9520630	\$137.50
30" Vertical Cover Strip Obsidian Black	11956100	\$149

Note: Metal trays not for use in microwave modes



Model	Material	UMRP
H 7870 BM 30" Speed Oven	11804690	\$5,799

Design Line	Finish
VitroLine	Graphite Grey

Specifications	
Width	29 13/16 in (757 mm)
Height	18 7/8 in (479 mm)
Depth	21 11/16 in (551 mm)
Shipping Weight	128 lbs (58 kg)

Features
• M Touch Controls with MotionReact • Miele@home • Automatic Programs • Wired Food Probe

Standard Accessories	Material	UMRP
2 Glass Tray	10141820	\$309
Wire Rack	6881872	\$119

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Perforated Baking Tray	9520620	\$121
PerfectClean Baking Tray	9519820	\$115.50
PerfectClean Grill Insert 24" Oven	9520630	\$137.50
30" Vertical Cover Strip Graphite Grey	11956150	\$149

Ovens — 30" Speed Oven



Model	Material	UMRP
H 7870 BMX GRG 30" Speed Oven	11804710	\$5,999

Design Line	Finish
ArtLine	Graphite Grey

Specifications

Width	29 13/16 in (757 mm)
Height	18 7/8 in (479 mm)
Depth	21 11/16 in (551 mm)
Shipping Weight	128 lbs (58 kg)

Features

- M Touch Controls with MotionReact
- Miele@home
- Automatic Programs
- Wired Food Probe

Standard Accessories	Material	UMRP
2 Glass Tray	10141820	\$309
Wire Rack	6881872	\$119

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Perforated Baking Tray	9520620	\$121
PerfectClean Baking Tray	9519820	\$115.50
PerfectClean Grill Insert 24" Oven	9520630	\$137.50
30" Vertical Cover Strip Graphite Grey	11956150	\$149



Model	Material	UMRP
H 7870 BMX OBSW 30" Speed Oven	12842590	\$5,999

Design Line	Finish
ArtLine	Obsidian Black

Specifications

Width	29 13/16 in (757 mm)
Height	18 7/8 in (479 mm)
Depth	21 11/16 in (551 mm)
Shipping Weight	128 lbs (58 kg)

Features

- M Touch Controls with MotionReact
- Miele@home
- Automatic Programs
- Wired Food Probe

Standard Accessories	Material	UMRP
2 Glass Tray	10141820	\$309
Wire Rack	6881872	\$119

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Perforated Baking Tray	9520620	\$121
PerfectClean Baking Tray	9519820	\$115.50
PerfectClean Grill Insert 24" Oven	9520630	\$137.50
30" Vertical Cover Strip Obsidian Black	11956100	\$149

Ovens — 30" Speed Oven



Model	Material	UMRP
H 7570 BM 30" Speed Oven	11804590	\$5,199

Design Line	Finish
ContourLine	Clean Touch Steel

Specifications	
Width	29 13/16 in (757 mm)
Height	18 7/8 in (479 mm)
Depth	21 11/16 in (551 mm)
Shipping Weight	128 lbs (58 kg)

Features
• M Touch S Controls with MotionReact • Miele@home • Automatic Programs • DirectSensor Controls

Standard Accessories	Material	UMRP
2 Glass Tray	10141820	\$309
Wire Rack	6881872	\$119

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Perforated Baking Tray	9520620	\$121
PerfectClean Baking Tray	9519820	\$115.50
PerfectClean Grill Insert 24" Oven	9520630	\$137.50
30" Vertical Cover Strip Stainless Steel	11956140	\$149

Note: Metal trays not for use in microwave modes



Model	Material	UMRP
H 7670 BM 30" Speed Oven	11804610	\$5,199

Design Line	Finish
PureLine	Clean Touch Steel

Specifications	
Width	29 13/16 in (757 mm)
Height	18 7/8 in (479 mm)
Depth	21 11/16 in (551 mm)
Shipping Weight	128 lbs (58 kg)

Features
• M Touch S Controls with MotionReact • Miele@home • Automatic Programs • DirectSensor Controls

Standard Accessories	Material	UMRP
2 Glass Tray	10141820	\$309
Wire Rack	6881872	\$119

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Perforated Baking Tray	9520620	\$121
PerfectClean Baking Tray	9519820	\$115.50
PerfectClean Grill Insert 24" Oven	9520630	\$137.50
30" Vertical Cover Strip Obsidian Black	11956100	\$149

Ovens — 30" Speed Oven



Model	Material	UMRP
H 7170 BM 30" Speed Oven	11804470	\$3,699

Design Line	Finish
ContourLine	Clean Touch Steel

Specifications	
Width	29 13/16 in (757 mm)
Height	18 7/8 in (479 mm)
Depth	21 11/16 in (551 mm)
Shipping Weight	128 lbs (58 kg)

Features
• DirectSensor S Controls • Miele@home

Standard Accessories	Material	UMRP
2 Glass Tray	10141820	\$309
Wire Rack	6881872	\$119

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Perforated Baking Tray	9520620	\$121
PerfectClean Baking Tray	9519820	\$115.50
PerfectClean Grill Insert 24" Oven	9520630	\$137.50
30" Vertical Cover Strip Stainless Steel	11956140	\$149

Note: Metal trays not for use in microwave modes



Model	Material	UMRP
H 7270 BM 30" Speed Oven	11804570	\$3,699

Design Line	Finish
PureLine	Clean Touch Steel

Specifications	
Width	29 13/16 in (757 mm)
Height	18 7/8 in (479 mm)
Depth	21 11/16 in (551 mm)
Shipping Weight	128 lbs (58 kg)

Features
• DirectSensor S Controls • Miele@home

Standard Accessories	Material	UMRP
2 Glass Tray	10141820	\$309
Wire Rack	6881872	\$119

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Perforated Baking Tray	9520620	\$121
PerfectClean Baking Tray	9519820	\$115.50
PerfectClean Grill Insert 24" Oven	9520630	\$137.50
30" Vertical Cover Strip Obsidian Black	11956100	\$149

Ovens — 30" Speed Oven



Model	Material	UMRP
H 7270 BM 30" Speed Oven	11804580	\$3,699

Design Line	Finish
VitroLine	Graphite Grey

Specifications	
Width	29 13/16 in (757 mm)
Height	18 7/8 in (479 mm)
Depth	21 11/16 in (551 mm)
Shipping Weight	128 lbs (58 kg)

Features
• DirectSensor S Controls • Miele@home

Standard Accessories	Material	UMRP
2 Glass Tray	10141820	\$309
Wire Rack	6881872	\$119

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Perforated Baking Tray	9520620	\$121
PerfectClean Baking Tray	9519820	\$115.50
PerfectClean Grill Insert 24" Oven	9520630	\$137.50
30" Vertical Cover Strip Graphite Grey	11956150	\$149

Note: Metal trays not for use in microwave modes



Model	Material	UMRP
H 7270 BM OBSW 30" Speed Oven	11968190	\$3,699

Design Line	Finish
VitroLine	Obsidian Black

Specifications	
Width	29 13/16 in (757 mm)
Height	18 7/8 in (479 mm)
Depth	21 11/16 in (551 mm)
Shipping Weight	128 lbs (58 kg)

Features
• DirectSensor S Controls • Miele@home

Standard Accessories	Material	UMRP
2 Glass Tray	10141820	\$309
Wire Rack	6881872	\$119

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Perforated Baking Tray	9520620	\$121
PerfectClean Baking Tray	9519820	\$115.50
PerfectClean Grill Insert 24" Oven	9520630	\$137.50
30" Vertical Cover Strip Obsidian Black	11956100	\$149

Note: Metal trays not for use in microwave modes

Ovens — 24" Speed Oven



Model	Material	UMRP
H 7840 BM 24" Speed Oven	11804640	\$5,199

Design Line	Finish
PureLine	Clean Touch Steel

Specifications	
Width	23 7/16 in (595 mm)
Height	17 15/16 in (455.5 mm)
Depth	21 5/8 in (549 mm)
Shipping Weight	101 lbs (46 kg)

Features
• M Touch Controls with MotionReact • Miele@home • Wired Food Probe • Automatic Programs

Standard Accessories	Material	UMRP
2 Glass Tray	10141820	\$309
Wire Rack	6881872	\$119

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Universal Tray 24" Oven	9519840	\$165
PerfectClean Perforated Baking Tray	9520620	\$121
PerfectClean Baking Tray	9519820	\$115.50
PerfectClean Grill Insert 24" Oven	9520630	\$137.50
Shelf Trim for 24" — Black	5165170	\$64.90
Shelf Trim for 24" — Stainless	7114780	\$64.90
Trim Kit: PureLine	11410740	\$499



Model	Material	UMRP
H 7840 BM 24" Speed Oven	11804660	\$5,199

Design Line	Finish
VitroLine	Obsidian Black

Specifications	
Width	23 7/16 in (595 mm)
Height	17 15/16 in (455.5 mm)
Depth	21 5/8 in (549 mm)
Shipping Weight	101 lbs (46 kg)

Features
• M Touch Controls with MotionReact • Miele@home • Wired Food Probe • Automatic Programs

Standard Accessories	Material	UMRP
2 Glass Tray	10141820	\$309
Wire Rack	6881872	\$119

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Universal Tray 24" Oven	9519840	\$165
PerfectClean Perforated Baking Tray	9520620	\$121
PerfectClean Baking Tray	9519820	\$115.50
PerfectClean Grill Insert 24" Oven	9520630	\$137.50
Shelf Trim for 24" — Black	5165170	\$64.90
Shelf Trim for 24" — Stainless	7114780	\$64.90
Trim Kit: Obsidian Black	11410770	\$479

Note: Metal trays not for use in microwave modes

Ovens — 24" Speed Oven



Model	Material	UMRP
H 7840 BM 24" Speed Oven	11804650	\$5,199

Design Line	Finish
VitroLine	Graphite Grey

Specifications	
Width	23 7/16 in (595 mm)
Height	17 15/16 in (455.5 mm)
Depth	21 5/8 in (549 mm)
Shipping Weight	101 lbs (46 kg)

Features	
• M Touch Controls with MotionReact • Miele@home • Wired Food Probe • Automatic Programs	

Standard Accessories	Material	UMRP
2 Glass Tray	10141820	\$309
Wire Rack	6881872	\$119

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Universal Tray 24" Oven	9519840	\$165
PerfectClean Perforated Baking Tray	9520620	\$121
PerfectClean Baking Tray	9519820	\$115.50
PerfectClean Grill Insert 24" Oven	9520630	\$137.50
Shelf Trim for 24" — Black	5165170	\$64.90
Shelf Trim for 24" — Stainless	7114780	\$64.90
Trim Kit: Graphite Grey	11410800	\$499



Model	Material	UMRP
H 7640 BM 24" Speed Oven	11804600	\$4,399

Design Line	Finish
PureLine	Clean Touch Steel

Specifications	
Width	23 7/16 in (595 mm)
Height	17 15/16 in (455.5 mm)
Depth	21 5/8 in (549 mm)
Shipping Weight	101 lbs (46 kg)

Features	
• M Touch S Controls with MotionReact • Miele@home • Wired Food Probe • Automatic Programs	

Standard Accessories	Material	UMRP
2 Glass Tray	10141820	\$309
Wire Rack	6881872	\$119

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Universal Tray 24" Oven	9519840	\$165
PerfectClean Perforated Baking Tray	9520620	\$121
PerfectClean Baking Tray	9519820	\$115.50
PerfectClean Grill Insert 24" Oven	9520630	\$137.50
Shelf Trim for 24" — Black	5165170	\$64.90
Shelf Trim for 24" — Stainless	7114780	\$64.90
Trim Kit: PureLine	11410740	\$499

Note: Metal trays not for use in microwave modes

Ovens — 24" Speed Oven



Model	Material	UMRP
H 7240 BM 24" Speed Oven	11804510	\$3,399

Design Line	Finish
PureLine	Clean Touch Steel

Specifications

Width	23 7/16 in (595 mm)
Height	17 15/16 in (455.5 mm)
Depth	21 5/8 in (549 mm)
Shipping Weight	101 lbs (46 kg)

Features

- DirectSensor S Controls
- Miele@home

Standard Accessories	Material	UMRP
2 Glass Tray	10141820	\$309
Wire Rack	6881872	\$119

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Universal Tray 24" Oven	9519840	\$165
PerfectClean Perforated Baking Tray	9520620	\$121
PerfectClean Baking Tray	9519820	\$115.50
PerfectClean Grill Insert 24" Oven	9520630	\$137.50
Shelf Trim for 24" — Black	5165170	\$64.90
Shelf Trim for 24" — Stainless	7114780	\$64.90
Trim Kit: PureLine	11410740	\$499

Model	Material	UMRP
H 7240 BM 24" Speed Oven	11804520	\$3,399

Design Line	Finish
PureLine	Graphite Grey

Specifications

Width	23 7/16 in (595 mm)
Height	17 15/16 in (455.5 mm)
Depth	21 5/8 in (549 mm)
Shipping Weight	101 lbs (46 kg)

Features

- DirectSensor S Controls
- Miele@home

Standard Accessories	Material	UMRP
2 Glass Tray	10141820	\$309
Wire Rack	6881872	\$119

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Universal Tray 24" Oven	9519840	\$165
PerfectClean Perforated Baking Tray	9520620	\$121
PerfectClean Baking Tray	9519820	\$115.50
PerfectClean Grill Insert 24" Oven	9520630	\$137.50
Shelf Trim for 24" — Black	5165170	\$64.90
Shelf Trim for 24" — Stainless	7114780	\$64.90
Trim Kit: Graphite Grey	11410800	\$499

Note: Metal trays not for use in microwave modes

Ovens — 24" Speed Oven



Model	Material	UMRP
H 7240 BM OBSW 24" Speed Oven	12842740	\$3,399

Design Line	Finish
VitroLine	Obsidian Black

Specifications	
Width	23 7/16 in (595 mm)
Height	17 15/16 in (455.5 mm)
Depth	21 5/8 in (549 mm)
Shipping Weight	101 lbs (46 kg)

Features
• DirectSensor S Controls • Miele@home

Standard Accessories	Material	UMRP
Glass Tray	10141820	\$309
Wire Rack	6881872	\$119

Optional Accessories	Material	UMRP
Round Baking Tray	9520720	\$71.50
Round Baking Tray w/ Logo	9520730	\$82.50
Perforated Round Baking Tray	10116800	\$75.90
PerfectClean Universal Tray 24" Oven	9519840	\$165
PerfectClean Perforated Baking Tray	9520620	\$121
PerfectClean Baking Tray	9519820	\$115.50
PerfectClean Grill Insert 24" Oven	9520630	\$137.50
Shelf Trim for 24" — Black	5165170	\$64.90
Shelf Trim for 24" — Stainless	7114780	\$64.90
Trim Kit: Obsidian Black	11410770	\$479

Ovens — 24" Microwave



Model	Material	UMRP
M 2241 SC 24" Microwave	11845640	\$2,299

Specifications

Width	23 7/16 in (595 mm)
Height	17 15/16 in (455.5 mm)
Depth	15 1/4 in (387 mm)
Shipping Weight	48.5 lbs (22 kg)

Features

- 7-segment display with sensor controls — EasySensor
- Perfect defrosting and cooking — Automatic Programs
- Food remains at serving temperature — keep warm function
- Compact 0.92 cu. ft. oven capacity
- Popcorn and drinks at the touch of a button

Optional Accessories	Material	UMRP
Trim Kit ContourLine	11909130	\$499
Trim Kit Obsidian Black	11768890	\$499

Note: Metal trays not for use in microwave modes.



Model	Material	UMRP
M 7240 TC 24" Microwave	11845600	\$2,899

Design Line

PureLine	Clean Touch Steel
----------	-------------------

Specifications

Width	23 7/16 in (595 mm)
Height	17 15/16 in (455.5 mm)
Depth	16 5/16 in (490 mm)
Shipping Weight	70.5 lbs (32 kg)

Features

- Clear text display with sensor controls — Direct Sensor S
- Perfect defrosting and cooking — Automatic Programs
- Plenty of space — 1.62 cu. ft. oven capacity & 15 3/4" turntable
- Very powerful microwave — 900W
- What you want at the touch of a button — Popcorn button

Optional Accessories	Material	UMRP
Trim Kit: PureLine	11410740	\$499
27" Trim Kit	11515830	\$499

Ovens — 30" Combi-Steam XL



Model	Material	UMRP
DGC 7775 30" Combi-Steam XL	11875760	\$8,399

Design Line	Finish	Type
ContourLine	Clean Touch Steel	Plumbed

Specifications

Width	29 13/16 in (757 mm)
Height	18 7/8 in (479 mm)
Depth	23 1/8 in (587 mm)
Shipping Weight	143 lbs (65 kg)

Features

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$71.50
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90



Model	Material	UMRP
DGC 7770 30" Combi-Steam XL	11875780	\$7,899

Design Line	Finish	Type
ContourLine	Clean Touch Steel	Non-plumbed

Specifications

Width	29 13/16 in (757 mm)
Height	18 7/8 in (479 mm)
Depth	23 1/8 in (587 mm)
Shipping Weight	143 lbs (65 kg)

Features

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$71.50
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90

Ovens — 30" Combi-Steam XL



Model	Material	UMRP
DGC 7875 30" Combi-Steam XL	11876050	\$8,399

Design Line	Finish	Type
PureLine	Clean Touch Steel	Plumbed

Specifications

Width	29 13/16 in (757 mm)
Height	18 7/8 in (479 mm)
Depth	23 1/8 in (587 mm)
Shipping Weight	143 lbs (65 kg)

Features

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack – Self Clean Ready (1)	9520640	\$130.90
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$71.50
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90



Model	Material	UMRP
DGC 7870 30" Combi-Steam XL	11876080	\$7,899

Design Line	Finish	Type
PureLine	Clean Touch Steel	Non-plumbed

Specifications

Width	29 13/16 in (757 mm)
Height	18 7/8 in (479 mm)
Depth	23 1/8 in (587 mm)
Shipping Weight	143 lbs (65 kg)

Features

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack – Self Clean Ready (1)	9520640	\$130.90
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$71.50
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90

Ovens — 30" Combi-Steam XL



Model	Material	UMRP
DGC 7870 30" Combi-Steam XL	11876190	\$7,899

Design Line	Finish	Type
VitroLine	Obsidian Black	Non-plumbed

Specifications

Width	29 13/16 in (757 mm)
Height	18 7/8 in (479 mm)
Depth	23 1/8 in (587 mm)
Shipping Weight	143 lbs (65 kg)

Features

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$71.50
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90



Model	Material	UMRP
DGC 7870 30" Combi-Steam XL	11876180	\$7,899

Design Line	Finish	Type
VitroLine	Graphite Grey	Non-plumbed

Specifications

Width	29 13/16 in (757 mm)
Height	18 7/8 in (479 mm)
Depth	23 1/8 in (587 mm)
Shipping Weight	143 lbs (65 kg)

Features

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$71.50
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90

Ovens — 30" Combi-Steam XL



Model	Material	UMRP
DGC 7870 X OBSW 30" Combi-Steam XL	12940250	\$8,099

Design Line	Finish	Type
ArtLine	Obsidian Black	Non-plumbed

Specifications

Width	29 13/16 in (757 mm)
Height	18 7/8 in (479 mm)
Depth	23 1/8 in (587 mm)
Shipping Weight	143 lbs (65 kg)

Features

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$71.50
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90



Model	Material	UMRP
DGC 7570 30" Combi-Steam XL	11875790	\$7,299

Design Line	Finish	Type
ContourLine	Clean Touch Steel	Non-plumbed

Specifications

Width	29 13/16 in (757 mm)
Height	18 7/8 in (479 mm)
Depth	23 1/8 in (587 mm)
Shipping Weight	143 lbs (65 kg)

Features

- M Touch S Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90

Ovens — 30" Combi-Steam XL



Model	Material	UMRP
DGC 7670 30" Combi-Steam XL	11876210	\$7,299

Design Line	Finish	Type
PureLine	Clean Touch Steel	Non-plumbed

Specifications

Width	29 13/16 in (757 mm)
Height	18 7/8 in (479 mm)
Depth	23 1/8 in (587 mm)
Shipping Weight	143 lbs (65 kg)

Features

- M Touch S Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90



Model	Material	UMRP
DGC 7370 30" Combi-Steam XL	11875800	\$5,499

Design Line	Finish	Type
ContourLine	Clean Touch Steel	Non-plumbed

Specifications

Width	29 13/16 in (757 mm)
Height	18 7/8 in (479 mm)
Depth	23 1/8 in (587 mm)
Shipping Weight	143 lbs (65 kg)

Features

- DirectSensor Controls
- Miele@home with Miele Mix & Match
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90

Ovens — 30" Combi-Steam XL



Model	Material	UMRP
DGC 7470 30" Combi-Steam XL	11876230	\$5,499

Design Line	Finish	Type
PureLine	Clean Touch Steel	Non-plumbed

Specifications

Width	29 13/16 in (757 mm)
Height	18 7/8 in (479 mm)
Depth	23 1/8 in (587 mm)
Shipping Weight	143 lbs (65 kg)

Features

- DirectSensor Controls
- Miele@home with Miele Mix & Match

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90



Model	Material	UMRP
DGC 7470 30" Combi-Steam XL	11876250	\$5,499

Design Line	Finish	Type
VitroLine	Graphite Grey	Non-plumbed

Specifications

Width	29 13/16 in (757 mm)
Height	18 7/8 in (479 mm)
Depth	23 1/8 in (587 mm)
Shipping Weight	143 lbs (65 kg)

Features

- DirectSensor Controls
- Miele@home with Miele Mix & Match

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90

Ovens — 30" Combi-Steam XL



Model	Material	UMRP
DGC 7470 OBSW 30" Combi-Steam XL	11987060	\$5,499

Design Line	Finish	Type
VitroLine	Obsidian Black	Non-plumbed

Specifications	
Width	29 13/16 in (757 mm)
Height	18 7/8 in (479 mm)
Depth	23 1/8 in (587 mm)
Shipping Weight	143 lbs (65 kg)

Features
• DirectSensor Controls • Miele@home with Miele Mix & Match • Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90

Ovens — 30" Combi-Steam XXL



Model	Material	UMRP
DGC 7785 30" Combi-Steam XXL	11875810	\$9,299

Design Line	Finish	Type
ContourLine	Clean Touch Steel	Plumbed

Specifications

Width	29 13/16 in (757 mm)
Height	24 3/8 in (619.5 mm)
Depth	23 1/8 in (587 mm)
Shipping Weight	159 lbs (72 kg)

Features

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$71.50
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90



Model	Material	UMRP
DGC 7780 30" Combi-Steam XXL	11875830	\$8,799

Design Line	Finish	Type
ContourLine	Clean Touch Steel	Non-plumbed

Specifications


Width	29 13/16 in (757 mm)
Height	24 3/8 in (619.5 mm)
Depth	23 1/8 in (587 mm)
Shipping Weight	159 lbs (72 kg)

Features

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$71.50
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90

Ovens — 30" Combi-Steam XXL



Model	Material	UMRP
DGC 7880 X GRGR 30" Combi-Steam XXL	11877040	\$8,999

Design Line	Finish	Type
ArtLine	Graphite Grey	Non-plumbed


Specifications

Width	29 7/8 in (757 mm)
Height	24 1/2 in (620 mm)
Depth	22 5/8 in (573 mm)
Shipping Weight	110 lbs (49.7 kg)

Features

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$71.50
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90



Model	Material	UMRP
DGC 7880 X OBSW 30" Combi-Steam XXL	12940260	\$8,999

Design Line	Finish	Type
ArtLine	Obsidian Black	Non-plumbed

Specifications

Width	29 7/8 in (757 mm)
Height	24 1/2 in (620 mm)
Depth	22 5/8 in (573 mm)
Shipping Weight	110 lbs (49.7 kg)

Features

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$71.50
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90

Ovens — 30" Combi-Steam XXL



Model	Material	UMRP
DGC 7880 30" Combi-Steam XXL	11876350	\$8,799

Design Line	Finish	Type
ContourLine	Clean Touch Steel	Non-plumbed

Specifications

Width	29 13/16 in (757 mm)
Height	24 3/8 in (619.5 mm)
Depth	23 1/8 in (587 mm)
Shipping Weight	159 lbs (72 kg)

Features

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$71.50
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90



Model	Material	UMRP
DGC 7880 30" Combi-Steam XXL	11876420	\$8,799

Design Line	Finish	Type
VitroLine	Obsidian Black	Non-plumbed

Specifications

Width	29 13/16 in (757 mm)
Height	24 3/8 in (619.5 mm)
Depth	23 1/8 in (587 mm)
Shipping Weight	159 lbs (72 kg)

Features

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$71.50
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90

Ovens — 30" Combi-Steam XXL



Model	Material	UMRP
DGC 7880 30" Combi-Steam XXL	11876370	\$8,799

Design Line	Finish	Type
VitroLine	Graphite Grey	Non-plumbed

Specifications

Width	29 13/16 in (757 mm)
Height	24 3/8 in (619.5 mm)
Depth	23 1/8 in (587 mm)
Shipping Weight	159 lbs (72 kg)

Features

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$71.50
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90



Model	Material	UMRP
DGC 7680 30" Combi-Steam XXL	11876470	\$8,099

Design Line	Finish	Type
PureLine	Clean Touch Steel	Non-plumbed

Specifications

Width	29 13/16 in (757 mm)
Height	24 3/8 in (619.5 mm)
Depth	23 1/8 in (587 mm)
Shipping Weight	159 lbs (72 kg)

Features

- M Touch S Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack — Self Clean Ready	9520640	\$130.90
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90

Ovens — 30" Combi-Steam XXL



Model	Material	UMRP
DGC 7685 30" Combi-Steam XXL	11876450	\$8,599

Design Line	Finish	Type
PureLine	Clean Touch Steel	Plumbed

Specifications

Width	29 13/16 in (757 mm)
Height	24 3/8 in (619.5 mm)
Depth	23 1/8 in (587 mm)
Shipping Weight	159 lbs (72 kg)

Features

- M Touch S Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack — Self Clean Ready	9520640	\$130.90
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90



Model	Material	UMRP
DGC 7885 30" Combi-Steam XXL	11876310	\$9,299

Design Line	Finish	Type
PureLine	Clean Touch Steel	Plumbed

Specifications

Width	29 13/16 in (757 mm)
Height	24 3/8 in (619.5 mm)
Depth	23 1/8 in (587 mm)
Shipping Weight	159 lbs (72 kg)

Features

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$71.50
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90

Ovens — 30" Combi-Steam XXL



Model	Material	UMRP
DGC 7580 30" Combi-Steam XXL	11876020	\$8,099

Design Line	Finish	Type
ContourLine	Clean Touch Steel	Non-plumbed

Specifications

Width	29 13/16 in (757 mm)
Height	24 3/8 in (619.5 mm)
Depth	23 1/8 in (587 mm)
Shipping Weight	159 lbs (72 kg)

Features

- M Touch S Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack – Self Clean Ready (1)	9520640	\$130.90
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90

|



Model	Material	UMRP
DGC 7585 30" Combi-Steam XXL	11875850	\$8,599

Design Line	Finish	Type
ContourLine	Clean Touch Steel	Plumbed

Specifications

Width	29 13/16 in (757 mm)
Height	24 3/8 in (619.5 mm)
Depth	23 1/8 in (587 mm)
Shipping Weight	159 lbs (72 kg)

Features

- M Touch S Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack – Self Clean Ready (1)	9520640	\$130.90
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90

Ovens — 24" Combi-Steam XL



Model	Material	UMRP
DGC 7845 24" Combi-Steam XL	11876580	\$7,299

Design Line	Finish	Type
PureLine	Clean Touch Steel	Plumbed

Specifications

Width	23 7/16 in (595 mm)
Height	17 15/16 in (455.5 mm)
Depth	23 1/4 in (590 mm)
Shipping Weight	128 lbs (58 kg)

Features

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$71.50
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90



Model	Material	UMRP
DGC 7840 24" Combi-Steam XL	11876590	\$6,799

Design Line	Finish	Type
PureLine	Clean Touch Steel	Non-plumbed

Specifications

Width	23 7/16 in (595 mm)
Height	17 15/16 in (455.5 mm)
Depth	23 1/4 in (590 mm)
Shipping Weight	128 lbs (58 kg)

Features

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$71.50
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90

Ovens — 24" Combi-Steam XL



Model	Material	UMRP
DGC 7840 24" Combi-Steam XL	11876610	\$6,799

Design Line	Finish	Type
VitroLine	Obsidian Black	Non-plumbed

Specifications

Width	23 7/16 in (595 mm)
Height	17 15/16 in (455.5 mm)
Depth	23 1/4 in (590 mm)
Shipping Weight	128 lbs (58 kg)

Features

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$71.50
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90



Model	Material	UMRP
DGC 7840 24" Combi-Steam XL	11876600	\$6,799

Design Line	Finish	Type
VitroLine	Graphite Grey	Non-plumbed

Specifications

Width	23 7/16 in (595 mm)
Height	17 15/16 in (455.5 mm)
Depth	23 1/4 in (590 mm)
Shipping Weight	128 lbs (58 kg)

Features

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$71.50
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90

Ovens — 24" Combi-Steam XL



Model	Material	UMRP
DGC 7640 24" Combi-Steam XL	11876660	\$6,099

Design Line	Finish	Type
PureLine	Clean Touch Steel	Non-plumbed

Specifications

Width	23 7/16 in (595 mm)
Height	17 15/16 in (455.5 mm)
Depth	23 1/4 in (590 mm)
Shipping Weight	128 lbs (58 kg)

Features

- M Touch S Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90



Model	Material	UMRP
DGC 7440 24" Combi-Steam XL	11876950	\$4,499

Design Line	Finish	Type
PureLine	Clean Touch Steel	Non-plumbed

Specifications

Width	23 7/16 in (595 mm)
Height	17 15/16 in (455.5 mm)
Depth	23 1/4 in (590 mm)
Shipping Weight	128 lbs (58 kg)

Features

- DirectSensor Controls
- Miele@home with Miele Mix & Match
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90

Ovens — 24" Combi-Steam XL



Model	Material	UMRP
DGC 7440 24" Combi-Steam XL	11876960	\$4,499

Design Line	Finish	Type
VitroLine	Graphite Grey	Non-plumbed

Specifications

Width	23 7/16 in (595 mm)
Height	17 15/16 in (455.5 mm)
Depth	23 1/4 in (590 mm)
Shipping Weight	128 lbs (58 kg)

Features

- DirectSensor Controls
- Miele@home with Miele Mix & Match
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90



Model	Material	UMRP
DGC 7440 OBSW 24" Combi-Steam XL	12940270	\$4,499

Design Line	Finish	Type
VitroLine	Obsidian Black	Non-plumbed

Specifications

Width	23 7/16 in (595 mm)
Height	17 15/16 in (455.5 mm)
Depth	23 1/4 in (590 mm)
Shipping Weight	128 lbs (58 kg)

Features

- DirectSensor Controls
- Miele@home with Miele Mix & Match
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90

Ovens — 24" Combi-Steam XXL



Model	Material	UMRP
DGC 7865 24" Combi-Steam XXL	11877020	\$8,199

Design Line	Finish	Type
PureLine	Clean Touch Steel	Plumbed

Specifications

Width	23 7/16 in (595 mm)
Height	23 7/16 in (595 mm)
Depth	23 1/4 in (590 mm)
Shipping Weight	140 lbs (63.6 kg)

Features

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$71.50
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90



Model	Material	UMRP
DGC 7860 24" Combi-Steam XXL	11876980	\$7,699

Design Line	Finish	Type
PureLine	Clean Touch Steel	Non-plumbed

Specifications

Width	23 7/16 in (595 mm)
Height	23 7/16 in (595 mm)
Depth	23 1/4 in (590 mm)
Shipping Weight	140 lbs (63.6 kg)

Features

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$71.50
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90

Ovens — 24" Combi-Steam XXL



Model	Material	UMRP
DGC 7860 24" Combi-Steam XXL	11877000	\$7,699

Design Line	Finish	Type
VitroLine	Obsidian Black	Non-plumbed

Specifications

Width	23 7/16 in (595 mm)
Height	23 7/16 in (596 mm)
Depth	23 1/4 in (590 mm)
Shipping Weight	140 lbs (63.6 kg)

Features

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$71.50
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90



Model	Material	UMRP
DGC 7860 24" Combi-Steam XXL	11876990	\$7,699

Design Line	Finish	Type
VitroLine	Graphite Grey	Non-plumbed

Specifications

Width	23 7/16 in (595 mm)
Height	23 7/16 in (596 mm)
Depth	23 1/4 in (590 mm)
Shipping Weight	140 lbs (63.6 kg)

Features

- M Touch Controls with MotionReact
- Miele@home with Miele Mix & Match
- Wired Food Probe
- Automatic Programs

Standard Accessories	Material	UMRP
PerfectClean Universal Tray 24" Oven (1)	9519840	\$165
PerfectClean FlexiClips (1)	9520660	\$203.50
Wire Rack — Self Clean Ready (1)	9520640	\$130.90
DGGL 12 Perforated Stainless Cooking Pan Large (1)	8249430	\$71.50
DGGL 20 Perforated Stainless Cooking Pan Small (1)	8285410	\$53.90
DGG 20 Solid Cooking Pan (1)	8246340	\$53.90

Optional Accessories — **Combi-Steam Ovens**

Product	Material	UMRP	Product	Material	UMRP
Round Baking Tray	9520720	\$71.50	DGG7 Small, Deepest Solid Pan	8019361	\$53.90
Round Baking Tray w/ Logo	9520730	\$82.50	DGGL4 Large, Deep Perforated Pan	5379570	\$64.90
Perforated Round Baking Tray	10116800	\$75.90	DGGL8 Large, Shallow Perforated Dish	8227240	\$64.90
PerfectClean Perforated Baking Tray	9520620	\$121	EBA 7848 USA OBSW 30" Trim Kit: Obsidian Black XL	11410770	\$499
PerfectClean Baking Tray	9519820	\$115.50	EBA 7848 USA GRGR 30" Trim Kit: Graphite Grey XL	11410800	\$499
PerfectClean Grill Insert (24" Oven)	9811960	\$137.50	EBA 7868 USA OBSW 30" Trim Kit: Obsidian Black XXL	11515800	\$499
Side Runner for Holding Pans	8249560	\$53.90	EBA 7868 USA GRGR 30" Trim Kit: Graphite Grey XXL	11515820	\$499
DGGL 12 Perforated Stainless Cooking Pan Large	8249430	\$71.50	HKL30 TFSW (black) 30" Vertical Cover Strip Obsidian Black	11956100	\$149
DGGL1 Small Perforated SS Pan	5001370	\$53.90	HKL30 EDST/CLST 30" Vertical Cover Strip Stainless Steel	11956140	\$149
DGG2 Small, Deep Solid Pan	5001390	\$53.90	HKL30 GRGR 30" Vertical Cover Strip Graphite Grey	11956150	\$149
DGG3 Large, Deep Solid Pan	5001400	\$64.90			

Product Highlights – **Ventilation Hoods**

Feature	Description (see specific models for details)
LED Lighting	Shines a bright, more natural light and is energy efficient and long-lasting.
Miele@home	Control the airflow or turn your hood on/off by interacting with your appliance via the Miele@home app.
Delayed Shutdown	After cooking, program the hood to turn off automatically once the air is clear.
Stainless Steel Mesh Filters	Efficiently and effectively filter steam, odors and grease from your kitchen. Dishwasher safe and extremely durable.
Miele CleanCover	Smooth liner inside the canopy preventing exposure to live components, cables and sharp edges.
Odor Free Charcoal Filter	Works to neutralize any unpleasant odors.

Ventilation Hoods – Range Hood



Model	Material	UMRP
DAR 1220-3 30" Wall Range Hood	11898130	\$2,599

Specifications

Width	29 15/16 in (760 mm)
Height	18 in (457 mm)
Depth	24 1/16 in (611 mm)
Shipping Weight	90.4 lbs. (41 kg)

Features

- LED ClearView Lighting
- Vented or Recirculating Option
- Recessed Knob Controls

Blowers (one is required)	Material	UMRP
700 CFM Internal Blower DRIB XL	12564020	\$1,049
700 CFM External Blower DREB XL	12563990	\$1,349

Optional Accessories	Material	UMRP
30" Recirculating Kit DRUU 30	12566690	\$537.90
DKF23-1 Charcoal Filter 2 pcs.	9812040	\$130.90
Duct Cover 30" H 6" B	12564730	\$405.90
Duct Cover 30" H 12" B	12564750	\$427.90
Duct Cover 30" H 19" B	12564760	\$449.90
Duct Cover 30" H 24" B	12564770	\$504.90



Model	Material	UMRP
DAR 1230-3 36" Wall Range Hood	11898170	\$2,799

Specifications

Width	35 15/16 in (913 mm)
Height	18 in (457 mm)
Depth	24 1/16 in (611 mm)
Shipping Weight	103.6 lbs. (47 kg)

Features

- LED ClearView Lighting
- Vented or Recirculating Option
- Recessed Knob Controls

Blowers (one is required)	Material	UMRP
700 CFM Internal Blower DRIB XL	12564020	\$1,049
1100 CFM Internal Blower DRIB XXL	12564050	\$1,049
700 CFM External Blower DREB XL	12563990	\$1,349
1100 CFM External Blower DREB XXL	12564000	\$1,399

Optional Accessories	Material	UMRP
6" x 36" DuctCover DRDC 3606	12564780	\$405.90
12" x 36" DuctCover DRDC 3612	12564960	\$427.90
18" x 36" DuctCover DRDC 3618	12564980	\$449.90
24" x 36" DuctCover DRDC 3624	12564990	\$504.90
DKF24-1 Charcoal Filter 3 pcs.	9812050	\$163.90

Ventilation Hoods – Range Hood



Model	Material	UMRP
DAR 1250-3 48" Wall Range Hood	11898190	\$2,999

Specifications

Width	47 15/16 in (1218 mm)
Height	18 in (457 mm)
Depth	24 1/16 in (611 mm)
Shipping Weight	125.7 lbs. (57 kg)

Features

- LED ClearView Lighting
- Recessed Knob Controls

Blowers

(one is required)	Material	UMRP
1100 CFM Internal Blower DRIB XXL	12564050	\$1,049
1100 CFM External Blower DREB XXL	9764940	\$1,049

Optional Accessories

Material	UMRP
6" x 48" DuctCover DRDC 4806	\$369
12" x 48" DuctCover DRDC 4812	\$389
18" x 48" DuctCover DRDC 4818	\$409
24" x 48" DuctCover DRDC 4824	\$504.90



Model	Material	UMRP
DAR 1130 36" Insert Hood	9753480	\$2,099

Specifications

Width	33 7/16 in (850 mm)
Height	17 5/8 in (448 mm)
Depth	22 13/16 in (579 mm)
Shipping Weight	77.2 lbs. (35 kg)

Features

- LED ClearView Lighting
- Vented or Recirculating Option
- Recessed Knob Controls

Blowers

(one is required)	Material	UMRP
700 CFM Internal Blower DRIB XL	9764830	\$699
1100 CFM Internal Blower DRIB XXL	12564020	\$1,049
700 CFM External Blower DREB XL	9764930	\$949
1100 CFM External Blower DREB XXL	9764940	\$1,049

Optional Accessories

Material	UMRP
36" Recirculating Kit DRUU 36	\$529
DKF24-1 Charcoal Filter 3 pcs.	\$149

Ventilation Hoods — Range Hood



Model	Material	UMRP
DAR 1150 48" Insert Hood	9753510	\$2,299

Specifications

Width	45 1/2 in (1155 mm)
Height	17 5/8 in (448 mm)
Depth	22 13/16 in (579 mm)
Shipping Weight	92.6 lbs. (42 kg)

Features

- LED ClearView Lighting
- Recessed Knob Controls

Blowers (one is required)	Material	UMRP
1100 CFM Internal Blower DRIB XXL	12564020	\$1,049
1100 CFM External Blower DREB XXL	12564000	\$1,399

Ventilation Hoods — **Wall Hood**



Model	Material	UMRP
DA 399-7 36" Wall Hood	10558800	\$2,899

Specifications

Width	35 1/4 in (898 mm)
Height	4 3/4 in (120 mm)
Overall Height Vented	27 3/8 – 40 in (695 – 1015 mm)
Overall Height Recirculation	32 1/2 – 45 1/16 in (825 – 1145 mm)
Depth	20 1/2 in (520 mm)
Shipping Weight	55.3 lbs (25.1 kg)

Features

- Vented or Recirculating

Optional Accessories	Material	UMRP
Recirculating Kit DUW20	6264790	\$149
Charcoal Filter DKF12-900	10363780 12292030	\$149.99
Reducing Collar DRC 2000	12140450	\$137.50
Chimney Extension DATK1-760	12566460	\$284.90
Chimney Extension DATK2-1000	12566640	\$361.90

Ventilation Hoods – **Wall Hood**



Model	Material	UMRP
DA 6698 W 36" Puristic Edition 6000 Wall Hood w/ Wifi	10877010	\$3,899

Specifications

Width	35 3/8 in (898 mm)
Height	3 3/8 in (85 mm)
Overall Height Vented	28 – 40 9/16 in (710 – 1030 mm)
Overall Height Recirculation	33 1/16 – 45 11/16 in (840 – 1160 mm)
Depth	19 11/16 in (500 mm)
Shipping Weight	57.2 lbs (26 kg)

Features

- Con@ctivity
- Vented or Recirculating

Optional Accessories	Material	UMRP
Recirculating Kit DUW20	6264790	\$149
Charcoal Filter DKF12-900	10363780 12292030	\$149.99
Reducing Collar DRC 2000	12140450	\$137.50



Model	Material	UMRP
DA 6698 W 36" Puristic Edition 6000 Wall Hood OBSW w/ Wifi	10877060	\$3,899

Specifications

Width	35 3/8 in (898 mm)
Height	3 3/8 in (85 mm)
Overall Height Vented	28 – 40 9/16 in (710 – 1030 mm)
Overall Height Recirculation	33 1/16 – 45 11/16 in (840 – 1160 mm)
Depth	19 11/16 in (500 mm)
Shipping Weight	57.2 lbs (26 kg)

Features

- Con@ctivity
- Vented or Recirculating

Optional Accessories	Material	UMRP
Recirculating Kit DUW20	6264790	\$149
Charcoal Filter DKF12-900	10363780 12292030	\$149.99
Reducing Collar DRC 2000	12140450	\$137.50

Ventilation Hoods — Wall Hood



Model	Material	UMRP
PUR 88 W 30" PUR Wall Hood	10743170	\$1,599

Specifications

Width	29 7/16 in (748 mm)
Height	2 1/2 in (62 mm)
Overall Height Vented	26 15/16 in (685 mm) – 39 9/16 in (1005 mm)
Overall Height Recirculation	32 1/16 in (815 mm) – 44 11/16 in (1135 mm)
Depth	19 11/16 in (500 mm)
Shipping Weight	62 lbs (28 kg)

Features

- Vented or Recirculating

Optional Accessories	Material	UMRP
Recirculating Kit DUW20	6264790	\$149
Charcoal Filter DKF12-900	10363780 12292030	\$149.99
Reducing Collar DRC 2000	12140450	\$137.50



Model	Material	UMRP
PUR 98 W 36" PUR Wall Hood	10743150	\$1,699

Specifications

Width	35 3/8 in (898 mm)
Height	2 1/2 in (62mm)
Overall Height Vented	26 15/16 in (685 mm) – 39 9/16 in (1005 mm)
Overall Height Recirculation	32 1/16 in (815 mm) – 44 11/16 in (1135 mm)
Depth	19 11/16 in (500 mm)
Shipping Weight	62 lbs (28 kg)

Features

- Vented or Recirculating

Optional Accessories	Material	UMRP
Recirculating Kit DUW20	6264790	\$149
Charcoal Filter DKF12-900	10363780 12292030	\$149.99
Reducing Collar DRC 2000	12140450	\$137.50

Ventilation Hoods – Wall Hood



Model	Material	UMRP
DAP 1727 30" Wall Hood	12784040	\$1,199

Specifications

Width	29 7/16 in (748 mm)
Canopy Height	2 7/16 in (62 mm)
Overall Height Vented	26 15/16 in (685 mm) – 39 9/16 in (1005 mm)
Overall Height Recirculation	32 1/16 in (815 mm) – 44 11/16 in (1135 mm)
Depth	19 11/16 in (500 mm)
Shipping Weight	51 lbs (23 kg)

Features

- Vented or Recirculating
- With energy-efficient LED lighting

Optional Accessories	Material	UMRP
Recirculating Kit DUW20	6264790	\$149
Charcoal Filter DKF12-900	10363780 12292030	\$149.99
Reducing Collar DRC 2000	12140450	\$137.50



Model	Material	UMRP
DAP 1927 36" Wall Hood	12784050	\$1,299

Specifications

Width	35 3/8 in (898 mm)
Canopy Height	2 7/16 in (62mm)
Overall Height Vented	26 15/16 in (685 mm) – 39 9/16 in (1005 mm)
Overall Height Recirculation	32 1/16 in (815 mm) – 44 11/16 in (1135 mm)
Depth	19 11/16 in (500 mm)
Shipping Weight	56 lbs (25 kg)

Features

- Vented or Recirculating
- With energy-efficient LED lighting

Optional Accessories	Material	UMRP
Recirculating Kit DUW20	6264790	\$149
Charcoal Filter DKF12-900	10363780 12292030	\$149.99
Reducing Collar DRC 2000	12140450	\$137.50

Ventilation Hoods – Island Hood



Model	Material	UMRP
DA 4248 V D 48" Puristic Varia Island Hood w/ Wifi	10877250	\$5,999

Specifications

Width	47 3/16 in (1198 mm)
Height	2 3/4 in (70 mm)
Overall Height Vented	29 3/4 in (755 mm) – 41 7/16 in (1045 mm)
Depth	27 1/8 in (698 mm)
Shipping Weight	107.8 lbs (49 kg)

Features

- Con@ctivity

Optional Accessories	Material	UMRP
Reducing Collar DRC 2000	12140450	\$137.50



Model	Material	UMRP
DA 6698 D 36" Puristic Edition 6000 Island Hood w/ Wifi	10877210	\$5,199

Specifications

Width	35 3/8 in (898mm)
Height	3 3/8 in (85mm)
Overall Height Vented	27 3/4 – 39 9/16 in (705 –1005 mm)
Overall Height Recirculation	30 1/8 – 43 5/16 in (765 –1075 mm)
Depth	23 9/16 in (598 mm)
Shipping Weight	74.8 lbs (34 kg)

Features

- Con@ctivity
- Vented or Recirculating

Optional Accessories	Material	UMRP
Recirc. Kit for Island Hoods DUI32	9561760	\$199
Charcoal Filter DKF12-900	10363780 12292030	\$149.99
Reducing Collar DRC 2000	12140450	\$137.50

Ventilation Hoods – Island Hood



Model	Material	UMRP
DA 6698 D 36" Puristic Edition 6000 Island Hood OBSW w/ Wifi	10877240	\$5,199

Specifications

Width	35 3/8 in (898mm)
Height	3 3/8 in (85mm)
Overall Height Vented	27 3/4 – 39 9/16 in (705 – 1005 mm)
Overall Height Recirculation	30 1/8 – 43 5/16 in (765 – 1075 mm)
Depth	23 9/16 in (598 mm)
Shipping Weight	74.8 lbs (34 kg)

Features

- Con@ctivity
- Vented or Recirculating

Optional Accessories	Material	UMRP
Recirc. Kit for Island Hoods DUI32	9561760	\$199
Charcoal Filter DKF12-900	10363780 12292030	\$149.99
Reducing Collar DRC 2000	12140450	\$137.50



Model	Material	UMRP
PUR 98 D 36" PUR Island Hood	10743130	\$2,699

Specifications

Width	35 3/8 in (898 mm)
Height	2 3/4 in (70 mm)
Overall Height Vented	27 3/16 – 39 in (690 – 990 mm)
Overall Height Recirculation	29 1/2 – 41 3/4 in (750 – 1060 mm)
Depth	23 9/16 in (598 mm)
Shipping Weight	74.8 lbs (34 kg)

Features

- Vented or recirculating

Optional Accessories	Material	UMRP
Recirc. Kit for Island Hoods DUI32	9561760	\$199
Charcoal Filter DKF12-900	10363780 12292030	\$149.99
Reducing Collar DRC 2000	12140450	\$137.50

Ventilation Hoods — Built-In Hood



Model	Material	UMRP
DA 2518 44" Built-In Hood w/ Wifi	10876740	\$2,299

Specifications

Width	43 3/4 in (1102 mm)
Height	12 7/8 in (326 mm)
Depth	15 13/16 in (402 mm)
Shipping Weight	40.4 lbs (18.3 kg)

Features

- Con@ctivity
- Vented or Recirculating

Optional Accessories	Material	UMRP/Retail
Reducing Collar DRC 2000	12140450	\$137.50
Recirculating Kit DUU 150	5696270	\$126.50
Recirculating Kit DUU 151	7294230	\$126.50
OdorFree Charcoal Filter DKF 15-900	10363800	\$149.99



Model	Material	UMRP
DA 2588 32" Built-In Hood w/ Wifi	10876770	\$2,099

Specifications


Width	31 9/16 in (802 mm)
Height	12 7/8 in (326 mm)
Depth	15 13/16 in (402 mm)
Shipping Weight	40.4 lbs (18.3 kg)

Features

- Con@ctivity
- Vented or Recirculating

Optional Accessories	Material	UMRP
Reducing Collar DRC 2000	12140450	\$137.50
Recirculating Kit DUU 150	5696270	\$126.50
Recirculating Kit DUU 151	7294230	\$126.50
OdorFree Charcoal Filter DKF 15-900	10363800	\$149.99

Ventilation Hoods — Built-In Hood



Model	Material	UMRP
DAS 2620 24" Built-In Hood	11878490	\$1,399

Specifications

Width	23 1/2 in (596 mm)
Height	1 1/2 in (36 mm)
Depth	10 3/4 in (273 mm)
Shipping Weight	31 lbs (14.0 kg)

Features

- LED Strip lighting

Optional Accessories

Optional Accessories	Material	UMRP
Reducing Collar DRC 2000	12140450	\$137.50
Recirculating Kit DUU 150	5696270	\$126.50
Recirculating Kit DUU 151	7294230	\$126.50
OdorFree Charcoal Filter DKF 31-900 P	12123400	\$176



Model	Material	UMRP
DAS 4720 30" Built-In Hood	11878520	\$1,699

Specifications

Width	30 in (762 mm)
Height	1 1/2 in (36mm)
Depth	10 3/4 in (273mm)
Shipping Weight	36 lbs (16 kg)

Features

- LED Strip lighting
- WiFi Enabled

Optional Accessories

Optional Accessories	Material	UMRP
Reducing Collar DRC 2000	12140450	\$137.50
Recirculating Kit DUU 150	5696270	\$126.50
Recirculating Kit DUU 151	7294230	\$126.50
OdorFree Charcoal Filter DKF 31-900 P	12123400	\$176
Brackets for DAS hoods DML 2000	11839970	\$53.90

Ventilation Hoods — Built-In Hood



Model	Material	UMRP
DAS 8930 34" Built-In Hood w/ Wifi	11878590	\$2,399

Specifications

Width	34 in (861 mm)
Height	2 3/8 in (60 mm)
Depth	12 1/8 in (307 mm)
Shipping Weight	42 lbs (19.0 kg)

Features

- LED Strip lighting
- WiFi Enabled

Optional Accessories	Material	UMRP
Reducing Collar DRC 2000	12140450	\$137.50
Recirculating Kit DUU 150	5696270	\$126.50
Recirculating Kit DUU 151	7294230	\$126.50
OdorFree Charcoal Filter DKF 31-900 P	12123400	\$176



Model	Material	UMRP
DAS 2920 36" Built-In Hood	11878500	\$1,499

Specifications

Width	35 3/8 in (896 mm)
Height	1 1/2 in (36 mm)
Depth	10 3/4 in (273 mm)
Shipping Weight	36 lbs (16.0 kg)

Features

- LED Strip lighting

Optional Accessories	Material	UMRP
Reducing Collar DRC 2000	12140450	\$137.50
Recirculating Kit DUU 150	5696270	\$126.50
Recirculating Kit DUU 151	7294230	\$126.50
OdorFree Charcoal Filter DKF 31-900 P	12123400	\$176
Brackets for DAS hoods DML 2000	11839970	\$53.90

Ventilation Hoods — Built-In Hood



Model	Material	UMRP
DAS 4930 36" Built-In Hood w/ Wifi	11878550	\$1,799

Specifications

Width	35 3/8 in (896 mm)
Height	1 1/2 in (36 mm)
Depth	10 3/4 in (273 mm)
Shipping Weight	36 lbs (16.0 kg)

Features

- LED Strip lighting
- WiFi Enabled

Optional Accessories	Material	UMRP
Reducing Collar DRC 2000	12140450	\$137.50
Recirculating Kit DUU 150	5696270	\$126.50
Recirculating Kit DUU 151	7294230	\$126.50
OdorFree Charcoal Filter DKF 31-900 P	12123400	\$176



Model	Material	UMRP
DA 2698 SS 35" Extra Slim Insert ss w/ Wifi	10876810	\$2,699

Specifications

Width	34 5/8 in (880 mm)
Height	13 1/2 in (342 mm)
Depth	11 1/2 in (293 mm)
Shipping Weight	35.5 lbs (16.1 kg)

Features

- Con@ctivity
- Vented or Recirculating

Optional Accessories	Material	UMRP
Reducing Collar DRC 2000	12140450	\$137.50
Recirculating Kit DUU 150	5696270	\$126.50
Recirculating Kit DUU 151	7294230	\$126.50
OdorFree Charcoal Filter DKF 19-900	10794600	\$139
6" Adapter DAA6	12563760	\$97.90
Recirculating Kit DUU 2900-900	11131670	\$699

Ventilation Hoods — Built-In Hood



Model	Material	UMRP
DA 2628 44" Extra Slim Insert ss w/ Wifi	10876800	\$3,099

Specifications

Width	46 7/16 in (1180 mm)
Height	13 1/2 in (342 mm)
Depth	11 1/2 in (293 mm)
Shipping Weight	33 lbs (15 kg)

Features

- Con@ctivity

Optional Accessories	Material	UMRP
6" Adapter DAA6	12563760	\$97.90



Model	Material	UMRP
DA 2360 24" Extra Slim Insert	10765130	\$1,399

Specifications

Width	23 in (584 mm)
Height	13 5/16 in (338 mm)
Depth	11 11/16 in (297 mm)
Shipping Weight	24 lbs (11 kg)

Features

- Vented or Recirculating

Optional Accessories	Material	UMRP
Reducing Collar DRC 2000	12140450	\$137.50
Recirculating Kit DUU 150	5696270	\$126.50
Recirculating Kit DUU 151	7294230	\$126.50
OdorFree Charcoal Filter DKF 19-900	10794600	\$139
6" Adapter DAA6	12563760	\$97.90

Ventilation Hoods — **Built-In Hood**



Model	Material	UMRP
DA 2390 36" Extra Slim Insert	10743660	\$1,799

Specifications

Width	34 11/16 in (884 mm)
Height	13 5/16 in (338 mm)
Depth	11 11/16 in (297 mm)
Shipping Weight	24 lbs (11 kg)

Features

- Vented or Recirculating

Optional Accessories	Material	UMRP
Reducing Collar DRC 2000	12140450	\$137.50
Recirculating Kit DUU 150	5696270	\$126.50
Recirculating Kit DUU 151	7294230	\$126.50
OdorFree Charcoal Filter DKF 19-900	10794600	\$139
6" Adapter DAA6	12563760	\$97.90

Ventilation Hoods — Built-Under Hood



Model	Material	UMRP
DA 1260 24" Built-Under Hood	10662780	\$1,099

Specifications

Width	23 9/16 in (598 mm)
Height	5 in (125 mm)
Depth	19 11/16 in (500 mm)
Shipping Weight	30.5 lbs (14 kg)

Optional Accessories	Material	UMRP
Reducing Collar DRC 2000	12140450	\$137.50
OdorFree Charcoal Filter DKF 18-900P	12292010	\$121



Model	Material	UMRP
DA 1280 30" Built-Under Hood	10451490	\$1,199

Specifications

Width	29 15/16 in (760 mm)
Height	5 in (125 mm)
Depth	19 11/16 in (500 mm)
Shipping Weight	35 lbs (16 kg)

Optional Accessories	Material	UMRP
Reducing Collar DRC 2000	12140450	\$137.50
OdorFree Charcoal Filter DKF 18-900P	12292010	\$121

Ventilation Hoods – Downdraft Extractor



Model	Material	UMRP
DA 6881 30" Downdraft chassis (Requires One Blower – choose from below)	10595900	\$3,199
DA 6881 30" Downdraft w/ DAG 1000	94001370	\$4,448

Specifications

Width	30 in (762 mm)
Height	25 11/16 in (652 mm)
Depth	4 3/4 in (120 mm)
Shipping Weight	63 lbs (28.6 kg)

Features

- Vented or Recirculating

Blowers (One is Required)	Material	UMRP
DAG 600 Internal Blower	12562610	\$299
DAG 1000 External Blower	12562730	\$949

Optional Accessories	Material	UMRP
Reducing Collar DRC 2000	12140450	\$137.50
Recirculating Kit DUU 2900-900	11131670	\$699
OdorFree Charcoal Filter DKF 18-900P	12292010	\$121



Model	Material	UMRP
DA 6891 36" Downdraft chassis (Requires One Blower – choose from below)	10595910	\$3,399
DA 6891 36" Downdraft w/ DAG 1000	94001390	\$4,648

Specifications

Width	36 in (915 mm)
Height	25 11/16 in (652 mm)
Depth	4 3/4 in (120 mm)
Shipping Weight	74 lbs (33.6 kg)

Features

- Vented or Recirculating

Blowers (One is Required)	Material	UMRP
DAG 600 Internal Blower	12562610	\$299
DAG 1000 External Blower	12562730	\$949

Optional Accessories	Material	UMRP
Reducing Collar DRC 2000	12140450	\$137.50
Recirculating Kit DUU 2900-900	11131670	\$699
OdorFree Charcoal Filter DKF 18-900P	12292010	\$121

Ventilation Hoods — **Ceiling Extractor**



Model	Material	UMRP
DAC 2247 46" Ceiling Extractor Hood	12565890	\$2,999

Specifications

Width	45 7/8 in (1165 mm)
Height	11 5/8 in (296 mm)
Depth	19 11/16 in (500 mm)
Shipping Weight	71 lbs (32.2 kg)

Features

- Con@ctivity
- Vented or Recirculating

Accessories	Material	UMRP
Reducing Collar DRC 2000	12140450	\$137.50
Remote Control DARC6	9812060	\$149
Recirculating Kit DUU 2900	11131670	\$699
Long-life (3 years) Charcoal Filter DKF 40-R	12500160	\$548.90

Product Highlights – **Warming Drawers and Vacuum Sealing Drawers**

Feature	Description (see specific models for details)
Touch Controls	Program selection at the touch of a button via a flush touch control panel.
Push2Open Mechanism	Opening the drawer requires the lightest touch.
Four Operating Modes for Warming Drawers	Warm cups and plates or keep food at serving temperature with temperature settings from 104-185° F.
Fully Telescopic Runners	Drawers can be pulled out completely for easy loading and unloading.
Three Vacuum Settings	Vacuum-seal food for storage, portioning, marinating, and resealing.
Sous-Vide Cooking Preparation	Thanks to the vacuum drawer, you can optimally prepare all different types of food for Sous-Vide cooking.

Warming Drawers – 24" Handleless Warming Drawer



Model	Material	UMRP
ESW 7010 24" Handleless Warming Drawer	11794720	\$1,899

Design Line	Finish
VitroLine	Obsidian Black

Specifications	
Width	23 7/16 in (595 mm)
Height	5 9/16 in (141 mm)
Depth	22 1/2 in (587 mm)
Shipping Weight	45 lbs (20.3 kg)

Features
• Keep Food or Plates and Cups Warm • Push2Open • Fits 6 Place Settings • Non-Slip Liner • Control Panel with Sensor Controls • Miele@home Connected

Note: Can have DGC, CVA or BM sit directly on top of drawer.



Model	Material	UMRP
ESW 7010 24" Handleless Warming Drawer	11794740	\$1,899

Design Line	Finish
VitroLine	Graphite Grey

Specifications	
Width	23 7/16 in (595 mm)
Height	5 9/16 in (141 mm)
Depth	22 1/2 in (587 mm)
Shipping Weight	45 lbs (20.3 kg)

Features
• Keep Food or Plates and Cups Warm • Push2Open • Fits 6 Place Settings • Non-Slip Liner • Control Panel with Sensor Controls • Miele@home Connected

Note: Can have DGC, CVA or BM sit directly on top of drawer.

Warming Drawers – 30" Handleless Warming Drawer



Model	Material	UMRP
ESW 7570 30" Handleless Warming Drawer	11794790	\$2,899

Design Line

ContourLine

Specifications

Width	29 13/16 in (757 mm)
Height	9 13/16 in (250 mm)
Depth	21 3/4 in (542 mm)
Shipping Weight	70.5 lbs (32 kg)

Features

- Keep Food or Plates and Cups Warm
- Push2Open
- Fits 12 Place Settings
- Non-Slip Liner
- Control Panel with Sensor Controls
- Miele@home Connected

Note: Can have DGC, CVA or BM sit directly on top of drawer.



Model	Material	UMRP
ESW 7580 30" Handleless Warming Drawer	11794800	\$2,999

Design Line

ContourLine

Specifications

Width	29 13/16 in (757 mm)
Height	10 13/16 in (275 mm)
Depth	23 7/8 in (608 mm)
Shipping Weight	74.3 lbs (33.7 kg)

Features

- Keep Food or Plates and Cups Warm
- Push2Open
- Fits 12 Place Settings
- Non-Slip Liner
- Control Panel with Sensor Controls
- Miele@home Connected

Note: Requires shelf above drawer.

Warming Drawers – 30" Handleless Warming Drawer



Model	Material	UMRP
ESW 7670 30" Handleless Warming Drawer	11794840	\$2,899

Design Line	Finish
VitroLine	Obsidian Black

Specifications	
Width	29 13/16 in (757 mm)
Height	9 13/16 in (250 mm)
Depth	21 3/4 in (542 mm)
Shipping Weight	70.5 lbs (32 kg)

Features
• Keep Food or Plates and Cups Warm • Push2Open • Fits 12 Place Settings • Non-Slip Liner • Control Panel with Sensor Controls • Miele@home Connected

Note: Can have DGC, CVA or BM sit directly on top of drawer.



Model	Material	UMRP
ESW 7670 30" Handleless Warming Drawer	11794820	\$2,899

Design Line	Finish
VitroLine	Graphite Grey

Specifications	
Width	29 13/16 in (757 mm)
Height	9 13/16 in (250 mm)
Depth	21 3/4 in (542 mm)
Shipping Weight	70.5 lbs (32 kg)

Features
• Keep Food or Plates and Cups Warm • Push2Open • Fits 12 Place Settings • Control Panel with Sensor Controls • Miele@home Connected


Note: Can have DGC, CVA or BM sit directly on top of drawer.

Warming Drawers – 30" Handleless Warming Drawer



Model	Material	UMRP
ESW 7680 30" Handleless Warming Drawer	11794880	\$2,999
Design Line	Finish	
VitroLine	Obsidian Black	
Specifications		
Width	29 13/16 in (757 mm)	
Height	10 13/16 in (275 mm)	
Depth	23 7/8 in (608 mm)	
Shipping Weight	74.3 lbs (33.7 kg)	
Features		
• Keep Food or Plates and Cups Warm • Push2Open • Fits 12 Place Settings • Control Panel with Sensor Controls • Miele@home Connected		

Note: Requires shelf above drawer.



Model	Material	UMRP
ESW 7680 30" Handleless Warming Drawer	11794870	\$2,999
Design Line	Finish	
ArtLine	Graphite Grey	
Specifications		
Width	29 13/16 in (757 mm)	
Height	10 13/16 in (275 mm)	
Depth	23 7/8 in (608 mm)	
Shipping Weight	74.3 lbs (33.7 kg)	
Features		
• Keep Food or Plates and Cups Warm • Push2Open • Fits 12 Place Settings • Control Panel with Sensor Controls • Miele@home Connected		

Note: Requires shelf above drawer.

Warming Drawers – 30" Handleless Warming Drawer



Model	Material	UMRP
ESW 7680 30" Handleless Warming Drawer	11794860	\$2,999

Design Line	Finish
PureLine	Clean Touch Steel

Specifications	
Width	29 13/16 in (757 mm)
Height	10 13/16 in (275 mm)
Depth	23 7/8 in (608 mm)
Shipping Weight	74.3 lbs (33.7 kg)

Features
• Keep Food or Plates and Cups Warm • Push2Open • Fits 12 Place Settings • Control Panel with Sensor Controls • Miele@home Connected

Note: Requires shelf above drawer.

Model	Material	UMRP
ESW 6380 FB 30" Warming Drawer – Panel Ready	9685060	\$2,799

Design Line
Fully Integrated

Specifications	
Width	29 13/16 in (757 mm)
Height	10 13/16 in (275 mm)
Depth	24 3/4 in (629 mm)
Shipping Weight	70 lbs (31.7 kg)

Features
• Keep Food or Plates and Cups Warm • Fits 12 Place Settings • Control Panel with Sensor Controls

Note: Requires shelf above drawer.

Vacuum Sealing Drawers



Model	Material	UMRP
EVS 7010 24" Vacuum Sealing Drawer	11845430	\$3,899
Specifications		
Width	23 1/2 in (595 mm)	
Height	5 5/8 in (141 mm)	
Depth	22 1/2 in (570 mm)	
Shipping Weight	77 lbs (35 kg)	
Features		
• Three Vacuum Settings • Push2Open • Preparation for Sous-Vide Cooking • Large Usable Space		



Model	Material	UMRP
EVS 7670 30" Vacuum Sealing Drawer	11845480	\$4,999
Specifications		
Width	29 7/8 in (757 mm)	
Height	9 7/8 in (248 mm)	
Depth	22 1/2 in (570 mm)	
Shipping Weight	114.5 lbs (52 kg)	
Features		
• Three Vacuum Settings • Push2Open • Preparation for Sous-Vide Cooking • Large Usable Space		

Product Highlights — **Built-In Coffee Machines**

Feature	Description (see specific models for details)
Quality	Miele products are designed to last. Our machines are tested to a service life of 20 years.
AromaticSystemFresh	Intensive coffee aroma submerges the home with this intelligent technology.
OneTouch for Two	The OneTouch for Two function allows two glasses of latte macchiato, cappuccino, coffee or espresso to be made at the same time.
M Touch	Large touch display with MotionReact movement sensor.
Removable Brew Unit	Easy to remove and clean, your machine guarantees impeccable hygiene, long service life and perfect coffee enjoyment.
Miele@home	Convenient and time-saving, control your machine right from your mobile device.
AutoDescale & AutoClean	No manual descaling or cleaning: select CVA models clean fully-automatically.
CoffeeSelect	Featured on select CVA 7000 machines, enjoy 3 bean containers where your coffee specialty is always prepared with the right coffee bean.

Coffee Machines – Built-In Coffee System



Model	Material	UMRP
CVA 7440 Built-In Coffee System	11733860	\$5,399

Design Line	Finish	Type
PureLine	Clean Touch Steel™	Non-plumbed

Specifications

Width	23 7/16 in
Height	17 15/16 in
Depth	17 3/4 in
Shipping Weight	63.5 lbs

Features

- DirectSensor Touch Display
- AromaticSystemFresh
- Miele@home
- 26 Coffee & Tea Specialty Drinks
- Coffee Pot / Teapot / DoubleShot
- OneTouch for Two
- EasyClick Milk System
- Programmable Beverage Parameters
- Maximum Spout Height: 6.5"
- 10 Programmable User Profiles
- BrilliantLight
- CupSensor
- Removable Brew Unit / ComfortClean

Standard Accessories	Material	UMRP
EasyClick Milk System	11234120	\$199.99
Descaling Tablets	11201170	\$24.99
Cleaning Tablets	11201250	\$24.99
Milk Pipework Cleaner	10182210	\$47.99



Model	Material	UMRP
CVA 7440 Built-In Coffee System	11754280	\$5,399

Design Line	Finish	Type
VitroLine	Graphite Grey	Non-plumbed

Specifications

Width	23 7/16 in
Height	17 15/16 in
Depth	17 3/4 in
Shipping Weight	63.5 lbs

Features

- DirectSensor Touch Display
- AromaticSystemFresh
- Miele@home
- 26 Coffee & Tea Specialty Drinks
- Coffee Pot / Teapot / DoubleShot
- OneTouch for Two
- EasyClick Milk System
- Programmable Beverage Parameters
- Maximum Spout Height: 6.5"
- 10 Programmable User Profiles
- BrilliantLight
- CupSensor
- Removable Brew Unit / ComfortClean

Standard Accessories	Material	UMRP
EasyClick Milk System	11234120	\$199.99
Descaling Tablets	11201170	\$24.99
Cleaning Tablets	11201250	\$24.99
Milk Pipework Cleaner	10182210	\$47.99

Optional Accessories	Material	UMRP
EBA 7848 USA GRGR 30" Trim Kit	11410800	\$499

Coffee Machines – Built-In Coffee System



Model	Material	UMRP
CVA 7445 Built-In Coffee System	11754300	\$5,999

Design Line	Finish	Type
PureLine	Clean Touch Steel™	Plumbed

Specifications

Width	23 7/16 in
Height	17 15/16 in
Depth	19 5/8 in
Shipping Weight	65 lbs

Features

- DirectSensor Touch Display
- AromaticSystemFresh
- Miele@home
- 26 Coffee & Tea Specialty Drinks
- Coffee Pot / Teapot / DoubleShot
- OneTouch for Two
- EasyClick Milk System
- Programmable Beverage Parameters
- Maximum Spout Height: 6.5"
- 10 Programmable User Profiles
- BrilliantLight
- CupSensor
- Removable Brew Unit / ComfortClean

Standard

Accessories	Material	UMRP
Descaling Tablets	11201170	\$24.99
EasyClick Milk System	11234120	\$199.99

Optional Accessories

Material	UMRP
Cleaning Tablets	11201250 \$24.99
Milk Pipework Cleaner	10182210 \$47.99



Model	Material	UMRP
CVA 7775 Built-In Coffee System	11733820	\$7,499

Design Line	Finish	Type
ContourLine	Clean Touch Steel™	Plumbed

Specifications

Width	29 13/16 in
Height	18 7/8 in
Depth	18 5/8 in
Shipping Weight	83.7 lbs

Features

- M Touch display with MotionReact
- AromaticSystemFresh
- CoffeeSelect (3 Bean Containers)
- Miele@home
- 26 Coffee & Tea Specialty Drinks
- Coffee Pot / Teapot / DoubleShot
- OneTouch for Two
- EasyClick Milk System
- Programmable Beverage Parameters
- Maximum Spout Height: 6.5"
- 10 Programmable User Profiles
- BrilliantLight / Niche Lighting
- CupSensor
- AutoDescal / AutoClean
- Removable Brew Unit / ComfortClean

Standard

Accessories	Material	UMRP
Descaling Cartridge	12970380	\$109.99
AutoCleaner	10971480	\$109.99
EasyClick Milk System	11234120	\$199.99

Optional Accessories

Material	UMRP
Cleaning Tablets	11201250 \$24.99
Descaling Tablets	11201170 \$24.99
Milk Pipework Cleaner	10182210 \$47.99
30" Vertical Cover Strip Stainless Steel	11956140 \$149

Note: Trim kit not applicable on this model.

Coffee Machines – Built-In Coffee System



Model	Material	UMRP
CVA 7840 Built-In Coffee System	11754270	\$6,499

Design Line	Finish	Type
PureLine	Clean Touch Steel™	Non-plumbed

Specifications

Width	23 7/16 in
Height	17 15/16 in
Depth	17 3/4 in
Shipping Weight	63.5 lbs

Features

- AromaticSystemFresh
- CoffeeSelect (3 Bean Containers)
- M Touch display with MotionReact
- Miele@home
- 26 Coffee & Tea Specialty Drinks
- Coffee Pot / Teapot / DoubleShot
- OneTouch for Two
- EasyClick Milk System
- Programmable Beverage Parameters
- Maximum Spout Height: 6.5"
- 10 Programmable User Profiles
- BrilliantLight / Niche Lighting
- CupSensor
- AutoDescal / AutoClean
- Removable Brew Unit / ComfortClean

Standard Accessories	Material	UMRP
Descaling Cartridge	12970380	\$109.99
AutoCleaner	10971480	\$109.99
EasyClick Milk System	11234120	\$199.99

Optional Accessories	Material	UMRP
Cleaning Tablets	11201250	\$24.99
Descaling Tablets	11201170	\$24.99
Milk Pipework Cleaner	10182210	\$47.99



Model	Material	UMRP
CVA 7845 Built-In Coffee System	11733840	\$6,999

Design Line	Finish	Type
PureLine	Clean Touch Steel™	Plumbed

Specifications

Width	23 7/16 in
Height	17 15/16 in
Depth	19 5/8 in
Shipping Weight	65 lbs

Features

- AromaticSystemFresh
- CoffeeSelect (3 Bean Containers)
- M Touch display with MotionReact
- Miele@home
- 26 Coffee & Tea Specialty Drinks
- Coffee Pot / Teapot / DoubleShot
- OneTouch for Two
- EasyClick Milk System
- Programmable Beverage Parameters
- Maximum Spout Height: 6.5"
- 10 Programmable User Profiles
- BrilliantLight / Niche Lighting
- CupSensor
- AutoDescal / AutoClean
- Removable Brew Unit / ComfortClean

Standard Accessories	Material	UMRP
Descaling Cartridge	12970380	\$109.99
AutoCleaner	10971480	\$109.99
EasyClick Milk System	11234120	\$199.99

Optional Accessories	Material	UMRP
Cleaning Tablets	11201250	\$24.99
Descaling Tablets	11201170	\$24.99
Milk Pipework Cleaner	10182210	\$47.99

Coffee Machines – Built-In Coffee System



Model	Material	UMRP
CVA 7845 Built-In Coffee System	11733850	\$6,999

Design Line	Finish	Type
VitroLine	Graphite Grey	Plumbed

Specifications

Width	23 7/16 in
Height	17 15/16 in
Depth	19 5/8 in
Shipping Weight	65 lbs

Features

- M Touch display with MotionReact
- CoffeeSelect (3 Bean Containers)
- AromaticSystemFresh
- 26 Coffee & Tea Specialty Drinks
- Coffee Pot / Teapot / DoubleShot / CoffeeSelect
- OneTouch for Two
- EasyClick Milk System
- Programmable Beverage Parameters
- Maximum Spout Height: 6.5"
- 10 Programmable User Profiles
- BrilliantLight / Niche Lighting
- CupSensor
- Removable Brew Unit / ComfortClean

Standard Accessories	Material	UMRP
Descaling Cartridge	12970380	\$109.99
AutoCleaner	10971480	\$109.99
EasyClick Milk System	11234120	\$199.99

Optional Accessories	Material	UMRP
Descaling Tablets	11201170	\$24.99
Cleaning Tablets	11201250	\$24.99
Milk Pipework Cleaner	10182210	\$47.99
EBA 7848 USA GRGR 30" Trim Kit	11410800	\$499



Model	Material	UMRP
CVA 7845 Built-In Coffee System	11754250	\$6,999

Design Line	Finish	Type
VitroLine	Obsidian Black	Plumbed

Specifications

Width	23 7/16 in
Height	17 15/16 in
Depth	19 5/8 in
Shipping Weight	65 lbs

Features

- M Touch display with MotionReact
- CoffeeSelect (3 Bean Containers)
- AromaticSystemFresh
- 26 Coffee & Tea Specialty Drinks
- Coffee Pot / Teapot / DoubleShot / CoffeeSelect
- OneTouch for Two
- EasyClick Milk System
- Programmable Beverage Parameters
- Maximum Spout Height: 6.5"
- 10 Programmable User Profiles
- BrilliantLight / Niche Lighting
- CupSensor
- Removable Brew Unit / ComfortClean

Standard Accessories	Material	UMRP
Descaling Cartridge	12970380	\$109.99
AutoCleaner	10971480	\$109.99
EasyClick Milk System	11234120	\$199.99

Optional Accessories	Material	UMRP
Descaling Tablets	11201170	\$24.99
Cleaning Tablets	11201250	\$24.99
Milk Pipework Cleaner	10182210	\$47.99
EBA 7848 USA OBSW 30" Trim Kit	11410800	\$499

Coffee Machines – Built-In Coffee System



Model	Material	UMRP
CVA 7370 EDST Built-In Coffee System	11733830	\$5,899

Design Line	Finish	Type
ContourLine	Clean Touch Steel	Non-plumbed

Specifications

Width	29 7/8 in
Height	18 7/8 in
Depth	18 7/8 in
Shipping Weight	65 lbs

Features

- DirectSensor Touch Display
- AromaticSystemFresh
- Miele@home
- 26 Coffee & Tea Specialty Drinks
- Coffee Pot / Teapot / DoubleShot
- OneTouch for Two
- EasyClick Milk System
- Programmable Beverage Parameters
- Maximum Spout Height: 6.5"
- 10 Programmable User Profiles
- BrilliantLight
- CupSensor
- Removable Brew Unit / ComfortClean

Standard Accessories	Material	UMRP
EasyClick Milk System	11234120	\$199.99
Descaling Tablets	11201170	\$24.99

Optional Accessories	Material	UMRP
Descaling Tablets	11201170	\$24.99
Cleaning Tablets	11201250	\$24.99
Milk Pipework Cleaner	10182210	\$47.99
30" Vertical Cover Strip Stainless Steel	11956140	\$149



Model	Material	UMRP
CVA 7875 Built-In Coffee System	12635830	\$7,499

Design Line	Finish	Type
PureLine	Clean Touch Steel	Plumbed

Specifications

Width	29 7/8 in
Height	18 7/8 in
Depth	18 7/8 in
Shipping Weight	65 lbs

Features

- M Touch Display
- CoffeeSelect (3 Bean Containers)
- AromaticSystemFresh
- 26 Coffee & Tea Specialty Drinks
- Coffee Pot / Teapot / DoubleShot / CoffeeSelect
- OneTouch for Two
- EasyClick Milk System
- Programmable Beverage Parameters
- Maximum Spout Height: 6.5"
- 10 Programmable User Profiles
- BrilliantLight / Niche Lighting
- CupSensor
- Removable Brew Unit / ComfortClean

Standard Accessories	Material	UMRP
EasyClick Milk System	11234120	\$199.99
Descaling Cartridge	12970380	\$109.99
AutoCleaner	10971480	\$109.99

Optional Accessories	Material	UMRP
Descaling Tablets	11201170	\$24.99
Cleaning Tablets	11201250	\$24.99
Milk Pipework Cleaner	10182210	\$47.99
30" Vertical Cover Strip Obsidian Black	11956100	\$149

Coffee Machines – Built-In Coffee System



Model	Material	UMRP
CVA 7875 Built-In Coffee System	12635820	\$7,499

Design Line	Finish	Type
VitroLine	Graphite Grey	Plumbed

Specifications

Width	29 7/8 in
Height	18 7/8 in
Depth	18 7/8 in
Shipping Weight	65 lbs

Features

- M Touch Display
- CoffeeSelect (3 Bean Containers)
- AromaticSystemFresh
- 26 Coffee & Tea Specialty Drinks
- Coffee Pot / Teapot / DoubleShot / CoffeeSelect
- OneTouch for Two
- EasyClick Milk System
- Programmable Beverage Parameters
- Maximum Spout Height: 6.5"
- 10 Programmable User Profiles
- BrilliantLight / Niche Lighting
- CupSensor
- Removable Brew Unit / ComfortClean

Standard Accessories	Material	UMRP
Descaling Cartridge	12970380	\$109.99
Cleaning Tablets	11201250	\$24.99
AutoCleaner	10971480	\$109.99
Milk Pipework Cleaner	10182210	\$47.99

Optional Accessories	Material	UMRP
EasyClick Milk System	11234120	\$199.99
Descaling Tablets	11201170	\$24.99
Cleaning Tablets	11201250	\$24.99
Milk Pipework Cleaner	10182210	\$47.99
EBA 7848 USA GRGR 30" Trim Kit	11410800	\$499
30" Vertical Cover Strip Graphite Grey	11956150	\$149



Model	Material	UMRP
CVA 7875 Built-In Coffee System	12635800	\$7,499

Design Line	Finish	Type
VitroLine	Obsidian Black	Plumbed

Specifications

Width	29 7/8 in
Height	18 7/8 in
Depth	18 7/8 in
Shipping Weight	65 lbs

Features

- M Touch Display
- CoffeeSelect (3 Bean Containers)
- AromaticSystemFresh
- 26 Coffee & Tea Specialty Drinks
- Coffee Pot / Teapot / DoubleShot / CoffeeSelect
- OneTouch for Two
- EasyClick Milk System
- Programmable Beverage Parameters
- Maximum Spout Height: 6.5"
- 10 Programmable User Profiles
- BrilliantLight / Niche Lighting
- CupSensor
- Removable Brew Unit / ComfortClean

Standard Accessories	Material	UMRP
Descaling Cartridge	12970380	\$109.99
Cleaning Tablets	11201250	\$24.99
AutoCleaner	10971480	\$109.99
Milk Pipework Cleaner	10182210	\$47.99

Optional Accessories	Material	UMRP
EasyClick Milk System	11234120	\$199.99
Descaling Tablets	11201170	\$24.99
Cleaning Tablets	11201250	\$24.99
Milk Pipework Cleaner	10182210	\$47.99
EBA 7848 USA OBSW 30" Trim Kit	11410770	\$499
30" Vertical Cover Strip Obsidian Black	11956100	\$149

Product Highlights — **Countertop Coffee Machines**

Feature	Description (see specific models for details)
AromaticSystem	Intensive coffee aroma submerges the home with this intelligent technology.
OneTouch for Two	The OneTouch for Two function allows two glasses of latte macchiato, cappuccino, coffee or espresso to be made at the same time.
Removable Brew Unit	Easy to remove and clean, your machine guarantees impeccable hygiene, long service life and perfect coffee enjoyment.
Automatic Rinsing	After making special coffee drinks that require milk, the machine is cleaned automatically.
WiFiConn@ct	Convenient and time-saving, control your machine right from your mobile device.
50% Quieter	New grinder motor for a 50% reduction in sound while grinding on all CM5 Silence machines.
Double Venturi Technology	Featured on all CM6 MilkPerfection units, provides enhanced milk froth quality, temperature and quantity.
CoffeeSelect	Featured on the CM7 machine, enjoy 3 bean containers where your coffee specialty is always prepared with the right coffee bean.

Coffee Machines – Countertop Coffee Machine



Model	Material	UMRP
CM 5310 Silence Countertop Coffee Machine	11648150	\$2,199

Finish

Obsidian Black

Specifications

Width	9 1/2 in
Height	14 13/16 in
Depth	18 1/8 in
Shipping Weight	24.6 lbs (11 kg)

Features

- AromaticSystem
- 50% Quieter Grinding
- Creamy Milk Froth
- OneTouch for Two
- Coffee Pot Function
- Programmable Beverage Parameters
- 5.3" Maximum Spout Height
- ComfortClean

Standard Accessories	Material	UMRP
Descaling Tablets	11201170	\$24.99
Cleaning Tablets	11201250	\$24.99

Optional Accessories	Material	UMRP
Glass Milk Flask	11574240	\$99.99



Model	Material	UMRP
CM 6160 MilkPerfection Countertop Coffee Machine	11648170	\$2,699

Finish

Lotus white

Specifications

Width	9 7/8 in
Height	14 1/8 in
Depth	16 3/4 in
Shipping Weight	26 lbs (11.8 kg)

Features

- AromaticSystem
- Creamy Milk Froth
- Double Venturi Milk-Frothing Technology
- OneTouch for Two
- Coffee Pot Function
- Programmable Beverage Parameters
- 5.5" Maximum Spout Height
- ComfortClean
- Hot Water Function
- 4 Programmable User Profiles
- Miele@home
- BrilliantLight

Standard Accessories	Material	UMRP
Descaling Tablets	11201170	\$24.99
Cleaning Tablets	11201250	\$24.99

Optional Accessories	Material	UMRP
Glass Milk Flask	11574240	\$99.99

Coffee Machines – Countertop Coffee Machine



Model	Material	UMRP
CM 6160 MilkPerfection Countertop Coffee Machine	11648180	\$2,699

Finish

Obsidian Black

Specifications

Width	9 7/8 in
Height	14 1/8 in
Depth	16 3/4 in
Shipping Weight	26 lbs (11.8 kg)

Features

- AromaticSystem
- Creamy Milk Froth
- Double Venturi Milk-Frothing Technology
- OneTouch for Two
- Coffee Pot Function
- Programmable Beverage Parameters
- 5.5" Maximum Spout Height
- ComfortClean
- Hot Water Function
- 4 Programmable User Profiles
- Miele@home
- BrilliantLight

Standard

Accessories	Material	UMRP
Descaling Tablets	11201170	\$24.99
Cleaning Tablets	11201250	\$24.99

Optional

Accessories	Material	UMRP
Glass Milk Flask	11574240	\$99.99



Model	Material	UMRP
CM 6360 MilkPerfection Countertop Coffee Machine	11648190	\$2,999

Finish

Lotus white CleanSteel Metallic

Specifications

Width	9 7/8 in
Height	14 1/8 in
Depth	16 3/4 in
Shipping Weight	27.3 lbs (12.4 kg)

Features

- AromaticSystem
- Creamy Milk Froth
- Double Venturi Milk-Frothing Technology
- OneTouch for Two
- Coffee Pot Function
- Programmable Beverage Parameters
- 5.5" Maximum Spout Height
- ComfortClean
- Hot Water Function
- 8 Programmable User Profiles
- Miele@home
- BrilliantLight
- Cup Warmer

Standard

Accessories	Material	UMRP
Glass Milk Flask	11574240	\$99.99
Descaling Tablets	11201170	\$21.99
Cleaning Tablets	11201250	\$24.99

Coffee Machines – Countertop Coffee Machine



Model	Material	UMRP
CM 6360 MilkPerfection Countertop Coffee Machine	11648200	\$2,999

Finish

Obsidian Black CleanSteel Metallic

Specifications

Width	9 7/8 in
Height	14 1/8 in
Depth	16 3/4 in
Shipping Weight	27.3 lbs (12.4 kg)

Features

- AromaticSystem
- Creamy Milk Froth
- Double Venturi Milk–Frothing Technology
- OneTouch for Two
- Coffee Pot Function
- Programmable Beverage Parameters
- 5.5" Maximum Spout Height
- ComfortClean
- Hot Water Function
- 8 Programmable User Profiles
- Miele@home
- BrilliantLight
- Cup Warmer

Standard Accessories	Material	UMRP
Glass Milk Flask	11574240	\$99.99
Descaling Tablets	11201170	\$24.99
Cleaning Tablets	11201250	\$24.99



Model	Material	UMRP
CM 7750 Coffee Select Countertop Coffee Machine	11106260	\$6,599

Finish

Obsidian Black

Specifications

Width	12 1/4 in
Height	16 9/16 in
Depth	7 1/12 in
Shipping Weight	39.2 lbs (17.78 kg)

Features

- AromaticSystemFresh
- CoffeeSelect (3 Bean Containers)
- Creamy Milk Froth
- Double Venturi Milk–Frothing Technology
- OneTouch for Two
- Coffee Pot Function
- Programmable Beverage Parameters
- 6.3" Maximum Spout Height
- ComfortClean
- Hot Water Function
- 10 Programmable User Profiles
- Miele@home
- BrilliantLight
- Glass Milk Container
- Cup Warmer
- CupSensor
- AutoDescale

Standard Accessories	Material	UMRP
Glass Milk Flask	11574240	\$99.99
Descaling Tablets	11201170	\$24.99
Descaling Cartridge	12970380	\$109.99
Cleaning Tablets	11201250	\$24.99

Product Highlights – **Accessories & Consumables**

Cooktops

Product	Material	UMRP
Razor Blade	1065471	\$19.80
Glass Scraper		
Glass Cooktop Cleaner	10173130	\$15.99

Ovens

Product	Material	UMRP
Glass Cooktop Cleaner	10162910	\$15.99
DG Clean Cleaner	10172760	\$19.99
Descaling Tablets	11201170	\$24.99

Coffee Machines

Product	Material	UMRP
CJ Jug 1.0L Coffee Pot	10694310	\$128.99
Glass Milk Flask	11574240	\$99.99
Descaling Tablets	11201170	\$24.99
CoffeeCare Set	12123070	\$68.99
Descaling Cartridge	12970380	\$109.99
Cleaning Tablets	11201250	\$24.99
Coffee Machine Milk Pipework Cleaner	10182210	\$47.99
Coffee Machine Silicone Grease	5132001	\$12.99
Coffee Beans – One for All (4 x 8.8 oz)	11030100	\$44.99
Coffee Beans – Café Crema (4 x 8.8 oz)	11029370	\$44.99
Coffee Beans – Espresso (4 x 8.8 oz)	11029650	\$44.99
Coffee Beans – Decaf (4 x 8.8 oz)	11029870	\$44.99

Handle Options

GEN 7000	MODEL	MATERIAL	TRIM / COLOR	HANDLE WIDTH	COOKING	Vi DISH-WASHERS	Vi COOLING	SF MASTER-COOL	UMRP
	DS 7000	11345890	PureLine Stainless steel ¹	15 3/4 in	•	•	•	—	\$164
	DS 7000	11345930	VitroLine Obsidian Black ¹	15 3/4 in	•	•	•	—	\$340
	DS 7000	11345940	VitroLine Brilliant white ¹	15 3/4 in	•	•	•	—	\$340
	DS 7000	11345950	VitroLine Graphite Grey ¹	15 3/4 in	•	•	•	—	\$340
	DS 7308	12047020	ContourLine Stainless steel standard handle	21 1/8 in	•	•	•	•	\$186
	DS 7708	12047000	ContourLine Stainless steel swiveling handle	21 1/8 in	•	•	•	•	\$230
	DS 7808	12047030	VitroLine Obsidian Black	19 11/16 in	•	•	•	—	\$384
	DS 7808	12047050	VitroLine Graphite Grey	19 11/16 in	•	•	•	—	\$384
	DS 7808	12047060	VitroLine Brilliant white	19 11/16 in	•	•	•	—	\$384
	DS 7808	12046910	PureLine Stainless steel	19 11/16 in	•	•	•	—	\$186



Miele, Inc.
9 Independence Way
Princeton, NJ 08540

mieleusa.com
1-800-843-7231

Find your nearest Miele Experience Center in:

Beverly Hills
Chicago
Coral Gables
Manhattan
Princeton
Seattle
Tysons Corner