

Miele



Cooling Price List

2026

Table of Contents

PerfectCool Refrigeration	03
PerfectCool Refrigeration Product Highlights	03
PerfectCool Refrigeration	04
PerfectCool Wine Storage	10
PerfectCool Wine Storage Product Highlights	10
PerfectCool Wine Storage	11
MasterCool Refrigeration	13
MasterCool Refrigeration Product Highlights	13
MasterCool Refrigeration	14
MasterCool Wine Storage	27
MasterCool Wine Storage Product Highlights	27
MasterCool Wine Storage	28
Handle Options	30

Product Highlights – **PerfectCool Refrigeration**

Feature	Description (see specific models for details)
PerfectFresh Pro	Food stays fresh for up to five times longer. With automatically controlled temperature zones, PerfectFreshPro is Miele's best system for perfect storage conditions of fresh produce.
FlexiLight	Glare-free, LED glass shelf lighting.
ComfortClean	The shelves on the inside of the door are dishwasher-safe for easy cleaning.
DynaCool	With uniform distribution and circulation of temperature, store your food anywhere in the fridge and freezer.
SuperCool	Rapid and gentle freezing of food.
PerfectFresh	Active Perfect humidity at all times – whenever the door is opened and every 90 minutes, a fine water mist is sprayed into the drawer for a gentle layer of moisture.
FlexiLight 2.0	Individually adjustable glass shelf lighting; illuminated shelves can be custom-positioned and are entirely glare-free.
FlexiTray	Pivotable glass shelf allows for items to be removed easily, even from a full refrigerator.
Miele@home	Access your appliance from your smart device for maximum convenience. Adjust fridge or freezer temperature, setting it to SuperCool while on the go.

PerfectCool Refrigeration – 30" Freestanding



Model	Material	UMRP
KFN 4776 ED 30" Freestanding	11954030	\$3,199

Finish	Hinge
Clean Touch Steel™	Right (convertible)

Specifications

Width	29 1/2 in (750 mm)
Height	73 1/4 in (2020 mm)
Depth	24 13/16 in (630 mm)
Refrigerator Capacity	11.7 cu.ft. (331 l)
Freezer Capacity	4.3 cu.ft. (121 l)
Shipping Weight	261 lbs (118 kg)
Annual Energy Usage	496 kWh

Fridge Features

- Lighting: LED
- ComfortClean Door Shelves
- WifiConn@ct
- Daily Fresh
- FlexiBoard Shelves: FlexiBoard is a split glass shelf
- DynaCool
- SoftClose
- SuperCool
- DuplexCool – separate circuits for fridge and freezer

Freezer Features

- Maximum Storage Capacity and Flexibility:
3 Removable Drawers
- SuperCool



Model	Material	UMRP
KFN 4799 24" Freestanding	11951210	\$3,999

Finish	Hinge
Clean Touch Steel™	Right (convertible)

Specifications

Width	23 1/2 in (597 mm)
Height	79 1/2 in (2020 mm)
Depth	24 13/16 in (630 mm)
Refrigerator Capacity	9.43 cu.ft. (267 l)
Freezer Capacity	3.32 cu.ft. (94 l)
Shipping Weight	203 lbs (92 kg)

Fridge Features

- Sabbath, Party & Holiday Mode
- 2 Temperature Zones
- LED lighting
- ComfortClean Door Shelves
- TouchControls
- Maximum Storage Capacity and Flexibility:
4 Door Bins, 1 Drawer, 4 Movable Shelves, 1 Bottle Rack
- Acoustic Door and Temperature Alarm
- DynaCool

Freezer Features

- Illuminated IceMaker w/ plumbed water connection
- Maximum Storage Capacity and Flexibility:
3 Removable Drawers
- SuperCool

PerfectCool Refrigeration – 24" Bottom Mount



Model	Material	UMRP
KFN 7795 D 24" Bottom Mount	11749900	\$4,999

Finish	Hinge
Custom Panel	Right (convertible)

Specifications

Width	22 in (559 mm)
Height	69 11/16 in (1770 mm)
Depth	21 1/2 in (545 mm)
Refrigerator Capacity	6.2 cu.ft. (175 l)
Freezer Capacity	2.5 cu.ft. (71 l)
Shipping Weight	175.7 lbs (79.7 kg)

Fridge Features

- PerfectFresh Active
- FlexiLight 2.0 LED
- FlexiTray
- ComfortClean Door Shelves
- TouchControls
- SoftClose Door
- Temperature Zones: 3
- Sabbath Mode
- Maximum Storage Capacity and Flexibility:
2 Door Bins, 2 Drawers, 3 Movable Shelves
- DynaCool
- SuperCool
- Acoustic Door and Temperature Alarm
- CleanSteel back panel

Freezer Features

- IceMaker w/ Plumbed Water Connection
- Maximum Storage Capacity and Flexibility:
3 Removable Drawers
- SuperCool

PerfectCool Refrigeration – 30" Bottom Mount



Model	Hinge	Material	UMRP
KFN 9859 iDE 30" Bottom Mount Custom Panel	Right	12153750	\$8,199
KFN 9859 iDE 30" Bottom Mount Custom Panel	Left	12153760	\$8,199

Optional Accessories	Material	UMRP
KFN 9855 K Fridge Panel (w/o handle)	9699670	\$629
KFN 9855 GF Freezer Panels (2 panels required, w/o handles)	9699700	\$629

Specifications

Width	29 7/8 in (759 mm)
Height	79 13/16 in (2027 mm)
Depth	24 in (610 mm)
Refrigerator Capacity	9.8 cu.ft. (277.5 l)
Freezer Capacity	4.3 cu.ft. (127 l)
Shipping Weight	345 lbs (156.6 kg)

Fridge Features

- Lighting: LED
- ComfortClean Door Shelves
- TouchControls
- SoftClose Door
- Temperature Zones: 2
- Sabbath Mode
- Maximum Storage Capacity and Flexibility:
3 Door Bins, 2 Drawers, 3 Movable Shelves, 1 Bottle Rack
- DynaCool
- SuperCool
- Acoustic Door and Temperature Alarm

Freezer Features

- IceMaker w/ Plumbed Water Connection
- Maximum Storage Capacity and Flexibility: 2 Drawers
- SuperCool

PerfectCool Refrigeration – Columns



Model	Material	UMRP
FNS 7794 E 24" Freezer Column	11911910	\$4,699

Finish	Hinge
Custom Panel	Left (convertible)

Specifications

Width	22 in (559 mm)
Height	69 11/16 in (1770 mm)
Depth	21 1/2 in (545 mm)
Freezer Capacity	7.5 cu.ft. (213 l)
Shipping Weight	175.5 lbs (79 kg)

Freezer Features

- Lighting: LED
- SoftClose Door
- SuperFreeze
- Illuminated icemaker w/ plumbed water connection
- Miele@home
- Sabbath mode
- TouchControls
- Temperature Zones: 1
- Acoustic Door and Temperature Alarm



Model	Material	UMRP
KS 7793 D 24" Refrigerator Column	11749850	\$4,199

Finish	Hinge
Custom Panel	Right (convertible)

Specifications

Width	22 in (559 mm)
Height	69 11/16 in (1770 mm)
Depth	21 1/2 in (545 mm)
Refrigerator Capacity	10.45 cu.ft. (296 l)
Shipping Weight	167.6 lbs (76 kg)

Fridge Features

- PerfectFresh Active
- FlexiLight 2.0
- Temperature Zones: 2
- FlexiTray – turns the glass shelf into a turntable, can be rotated by 180°
- DynaCool
- SuperCool
- CleanSteel back wall
- SoftClose Door
- Sabbath, Party & Holiday Mode
- ComfortClean Door Shelves
- TouchControls
- Maximum Storage Capacity and Flexibility: 5 Door Bins, 3 Drawers, 4 Movable Shelves, 1 Bottle Rack
- Acoustic Door and Temperature Alarm

PerfectCool Refrigeration – 36" French Door



Model	Material	UMRP	Optional Accessories	Material	UMRP
KFNF 9959 iDE 36" French Door Custom Panel	12153770	\$9,449	KEDF 9955 K Fridge Panels (2 panels required w/o handle)	12556510	\$629
Specifications			KEDF 9955 GF Freezer Panels (2 panels required, w/o handles)	12556520	\$629
Width	35 13/16 in (910 mm)				
Height	79 13/16 in (2027 mm)				
Depth	24 in (610 mm)				
Refrigerator Capacity	12.9 cu.ft. (365 l)				
Freezer Capacity	6.0 cu.ft. (170 l)				
Shipping Weight	383.5 lbs (174 kg)				
Fridge Features					
• Lighting: LED • ComfortClean Door Shelves • TouchControls • SoftClose Door • Temperature Zones: 3 • Sabbath Mode • Maximum Storage Capacity and Flexibility: 6 Door Bins, 2 Drawers, 4 Movable Shelves • DynaCool • SuperCool • Acoustic Door and Temperature Alarm					
Freezer Features					
• IceMaker w/ Plumbed Water Connection • Maximum Storage Capacity and Flexibility: 2 Drawers • SuperCool					

PerfectCool Refrigeration – 24" Under-Counter



Model	Material	UMRP
KU 7175 D 24" Under-Counter Refrigerator	12930520	\$3,999

Finish	Hinge
Panel Ready	Pull-out front

Specifications

Width	23 5/8 in (597 mm)
Height	33 7/8 in (859 mm)
Depth	22 in (556 mm)
Refrigerator Capacity	4.2 cu.ft. (119 l)
Shipping Weight	84 lbs (38.0 kg)

Fridge Features

- Two individually adjustable temperature zones for more flexibility
- From 32°F (0°C) for chilled drinks to 57°F (14°C) for an ideal cellar climate
- Optimum and maintenance-free LED lighting
- Uniform temperature distribution inside the appliance – DynaCool
- Cool food down quickly thanks to SuperCool
- Soft closing of the door with SoftClose

Product Highlights — **PerfectCool Wine Storage**

Feature	Description (see specific models for details)
TouchControl Display	Incredibly convenient — a whole range of settings can be controlled easily with the tap of a finger on the touch display.
LED Lighting	Flush lighting strips present your appliance in the perfect light.
Push2Open	For a handleless design, just apply slight pressure to the door to open.
SoftClose	With just a gentle touch, our dynamic doors close on their own. Integrates perfectly within a handleless kitchen.
FlexiFrame Racks	Individual Beechwood slats can be easily moved to make room for larger wine bottles.
SommelierSet	Perfect for wine connoisseurs — prepare cooled wine glasses and wine for decanting. Drink perfectly conditioned wine even from opened bottles.
3D Bottle Presenter Shelf	Place your favorite bottles on display.
Temperature Zones	Precise temperature regulation, ensuring the best storage conditions for different wine types.
NoteBoard	Every bottle rack features a removable magnetic strip for labeling the types of wine bottles on the rack.

PerfectCool Wine Storage – 24" Wine Storage



Model	Material	UMRP
KWT 6722 iS 24" Built-in Wine	11329860	\$5,669

Finish	Hinge
Custom Panel	Right (convertible)

Specifications

Width	21 15/16 in (557 mm)
Height	69 11/16 in (1770 mm)
Depth	21 3/4 in (553 mm)
Shipping Weight	223 lbs (101 kg)

Features

- Lighting: LED
- TouchControls
- SoftClose Door
- Temperature Zones: 2
- Maximum Storage Capacity and Flexibility:
80 x 0.75 l bottles
- DynaCool
- Acoustic Door and Temperature Alarm
- FlexiFrame Racks: 8
- 3D Bottle Presenter Shelf: 1
- UV Tinted Glass
- SommelierSet
- NoteBoard
- CleanSteel Back Wall

Optional Accessories	Material	UMRP
KFP 6700 Clean Touch Steel™ Panel (w/o handle)	11329620	\$999

Model	Material	UMRP
KWTUS 7172 F 24" Under-Counter Wine	12519520	\$3,799

Finish	Hinge
Custom Panel	Right (convertible)

Specifications

Width	23 5/8 in (597 mm)
Height	33 7/8 in (859 mm)
Depth	22 1/4 in (563 mm)
Shipping Weight	102 lbs (46.0 kg)

Features

- Storage of all bottle sizes/shapes thanks to FlexiFrame
- Perfect regulation of humidity with ActiveHumidity
- Writing on the wooden shelves on the NoteBoard
- UV-resistant insulated glass
- Presented in perfect light – LED lighting

Optional Accessories	Material	UMRP
KSK 6300 Merging Kit	9799630	\$249

*Custom Toe Kick needed for Under-Counter wine.

PerfectCool Wine Storage – 24" Wine Storage



Model	Material	UMRP
KWT 6322 UG 24" Under-Counter Wine	11545800	\$4,599

Finish	Hinge
Clean Touch Steel™ Frame	Right (convertible)

Specifications	
Width	23 7/16 in (596 mm)
Height	32 1/4 – 34 1/4 in (819 – 870 mm)
Depth	22 1/2 in (571 mm)
Shipping Weight	116.8 lbs (53 kg)

Features
• Lighting: LED • TouchControls • SoftClose Door • Temperature Zones: 2 • Maximum Storage Capacity and Flexibility: 34 x 0.75 l bottles • Active AirClean Filter • Acoustic Door and Temperature Alarm • FlexiFrame Racks: 3, 1 fixed shelf • UV Tinted Glass • NoteBoard • Push2Open Door

Optional Accessories	Material	UMRP
KSK 6300 Merging Kit	9799630	\$249

Product Highlights – MasterCool Refrigeration

Feature	Description (see specific models for details)
BrilliantLight Pro	Flush-fit LED lighting in the side panels, top frame, and backwall flood the interior with bright, even illumination – so everything is easy to see and beautifully showcased.
SmartLight	No more blinding fridge light at night. Every model is equipped with a light sensor that automatically adjusts its brightness.
M Touch Pro	New user interface with large high-resolution full-touch display that is conveniently positioned at the center of the appliance. Integrated tips for ensuring effortless maintenance such as changing the filter.
Gallon Bins	To prevent spills, open bottles are best stored upright. The new gallon bins make it easy to store even large containers in the door, keeping them accessible while freeing up shelf space.
Internal Water Dispenser	Seamlessly integrated water dispenser on the left side panel, providing cold, fresh water at any time. Thanks to the built-in filter, the water is always clean and ready to drink. Dispense manually or pre-set your favorites for your preferred glass or bottle size.
Spillproof Shelves	Spills and leaks are contained by the aluminum-framed glass shelves, preventing messes and making cleaning quick and easy. The shelves are height-adjustable and, depending on the model, available as full-width or split versions for flexible storage.
MaxLoad Hinge	Ensures safe storage of large amounts of food in the door shelves, while also offering flexible options for door panel materials.
FoodView	Up to four cameras inside the appliance capture images of key areas, including drawers, whenever doors are opened and closed. Viewable via the Miele app, these images help simplify shopping and reduce food waste.
Longlife AirClean Filter	For food storage in an odor-free environment. This innovative filter system combines an active charcoal filter integrated into the rear panel of the appliance's air circuit, effectively neutralizing odors. It is regenerable – cleanable up to five times in an oven – and only needs replacement every three years, hence reducing waste.
Freeze&Cool	Features a temperature range of +39.2° F to -0.4° F and 5 pre-set settings for maximum flexibility.
Dual IceMaker	Produce two different types of ice cubes (small and large) at the same time.
IceMaker	Always have daily, fresh ice cubes on hand. For ultimate convenience, use the included ice scoop.
MasterFresh Pro	Now standard in all models, MasterFresh Pro optimizes freshness by keeping food fresh up to 5× longer. It automatically adjusts humidity based on food type, ensuring ideal conditions and less waste.
DailyFresh ExtraCool	Fruit and vegetables stay fresh up to twice as long with the spacious and extra drawer. Featuring a temperature ExtraCool at approx. 35.6° F lower than the set refrigerator temperature – it's the perfect place for meat, fish and dairy products.
SlidingShelf	Store small items within easy reach without using much fridge space. Attached beneath a glass shelf, the sliding box keeps items organized and easily accessible without stacking.

MasterCool Refrigeration – 30" Bottom Mount

KFMC 3632 R



KFMC 3632 L



Model	Hinge	Material	UMRP
KFMC 3632 R 30" Premium Bottom Mount Fridge/Freezer	Right	12489450	\$12,499

KFMC 3632 L 30" Premium Bottom Mount Fridge/Freeze	Left	12489460	\$12,499
--	------	----------	----------

Specifications

Width	29 3/4 in (756 mm)
Height	83 9/16 – 85 1/2 in (2123 – 2171 mm)
Depth	24 in (610 mm)
Shipping Weight	472 lbs (214 kg)
Finish	Panel-ready

Features

- BrilliantLight
- M Touch Pro
- SmartLight
- Longlife AirClean System
- IceMaker
- MasterFresh Pro
- Miele@Home

Included Accessories

Ice scoop
Longlife AirClean filter
Water filter

Optional Accessories	Material	UMRP
KWF 2000 Water filter	11480330	\$189
KFP 3031 ed/cs Front Panel fridge 30"	12687730	\$749
KFP 3032 ed/cs Front Panel freezer 30"	12687750	\$399
KFK 3001 Frame set – 30" BM (For SS Proud Installation)	12687400	\$799
KTk 3030 ed Toe kick cover 30" Stainless steel	12687180	\$149
KHK 3002 Door direction change kit	12687710	\$399

MasterCool Refrigeration – 30" Bottom Mount

KFMC 3836 R



KFCM 3836 L



Model	Hinge	Material	UMRP
KFMC 3836 R Custom Panel 30" Prestige Bottom Mount Fridge/Freezer	Right	12489320	\$13,499
KFMC 3836 L Custom Panel 30" Prestige Bottom Mount Fridge/Freezer	Left	12489330	\$13,499
Specifications			
Width	29 3/4 in (756 mm)		
Height	83 9/16 – 85 1/2 in (2123 – 2171 mm)		
Depth	24 in (610 mm)		
Shipping Weight	472 lbs (214 kg)		
Finish	Panel-ready		
Features			
• FoodView • Longlife AirClean System • IceMaker • Water dispenser • BrilliantLight Pro • M Touch Pro • Miele@Home			

Optional Accessories	Material	UMRP
KWF 2000 Water filter	11480330	\$189
KFP 3031 ed/cs Front Panel fridge 30"	12687730	\$749
KFP 3032 ed/cs Front Panel freezer 30"	12687750	\$399
KFK 3001 Frame set – 30" BM (For SS Proud Installation)	12687400	\$799
KTk 3030ed Toe kick cover 30" Stainless steel	12687180	\$149
KHK 3002 Door direction change kit	12687710	\$399
KSK 3001 Merge Kit with a 30" BM	12686320	\$349
KSK 3002 Merge Kit with a 30" BM	12687090	\$349
KSK 3004 Merge Kit with a Column	12687140	\$649

MasterCool Refrigeration – 36" Bottom Mount

KFMC 3642 R



KFMC 3642 L



KFMC 3642 FD



Model	Hinge	Material	UMRP	Optional Accessories	Material	UMRP
KFMC 3642 R Custom Panel 36" Premium Bottom Mount Fridge/Freezer	Right	12489480	\$12,999	KWF 2000 Water filter	11480330	\$189
KFMC 3642 L Custom Panel 36" Premium Bottom Mount Fridge/Freezer	Left	12489490	\$12,999	KFP 3631 ed/cs Front Panel fridge 36"	12687780	\$899
KFMC 3642 FD Custom Panel 36" Premium Bottom Mount Fridge/Freezer	French Door	12489500	\$13,499	KFP 3632 ed/cs Front Panel freezer 36"	12687790	\$449
				KFP 3633 ed/cs* FD Front Panel fridge (lower BeltLine) 36" SS	12687800	\$499
				KFK 3601 Frame set – 36" (For SS Proud Installation)	12687420	\$849
				KTk 3630 ed Toe kick cover 36" Stainless steel	12687210	\$149
				KTT 3001 Trim kit (For traditional 36" and 42" openings)	12687150	\$249
				KHK 3002 Door direction change kit	12687710	\$399
				KSK 3002 Merge Kit with a 30" BM	12687090	\$349
				KSK 3003 Merge Kit with either a 36" or 42" BM	12687120	\$349
				KSK 3004 Merge Kit with a Column	12687140	\$649

Specifications

Width	35 1/4 in (895 mm)
Height	83 9/16 – 85 1/2 in (2123 – 2171 mm)
Depth	24 in (610 mm)
Shipping Weight	483 lbs (219 kg) – 499 lbs (226 kg)
Finish	Panel-ready

Features

- BrilliantLight
- M Touch Pro
- SmartLight
- Longlife AirClean System
- IceMaker
- MasterFresh Pro
- Miele@Home

*Two of these panels must be ordered separately for both refrigerator doors.

MasterCool Refrigeration – 36" Bottom Mount



Model	Hinge	Material	UMRP	Optional Accessories	Material	UMRP
KFCM 3846 R Custom Panel 36" Prestige Bottom Mount Fridge/Freezer	Right	12489400	\$14,499	KWF 2000 Water filter	11480330	\$189
KFCM 3846 L Custom Panel 36" Prestige Bottom Mount Fridge/Freezer	Left	12489410	\$14,499	KFP 3638 ed/cs Front Panel fridge 36" SS	12687810	\$899
KFCM 3846 FD Custom Panel 36" Prestige Bottom Mount Fridge/Freezer	French Door	12489430	\$14,999	KFP 3639 ed/cs Front Panel freezer, upper drawer 36" SS	12687830	\$249
				KFP 3636 ed/cs* Front Panel freezer, lower drawer 36" SS	12687840	\$429
				KFP 3637 ed/cs FD Front Panel fridge (Higher BeltLine) 36" SS	12687860	\$499
				KFK 3601 Frame set - 36" (For SS Proud Installation)	12687420	\$849
				KTK 3630 ed Toe kick cover 36" Stainless steel	12687210	\$149
				KTT 3001 Trim kit (For traditional 36" and 42" openings)	12687150	\$249
				KHK 3002 Door direction change kit	12687710	\$399
				KSK 3002 Merge Kit with a 30" BM	12687090	\$349
				KSK 3003 Merge Kit with either a 36" or 42" BM	12687120	\$349
				KSK 3004 Merge Kit with a Column	12687140	\$649

Specifications

Width	35 1/4 in (895 mm)
Height	83 9/16 – 85 1/2 in (2123 – 2171 mm)
Depth	24 in (610 mm)
Shipping Weight	488 lbs (221 kg) – 501 lbs (227 kg)
Finish	Panel-ready

Features

- FoodView
- Longlife AirClean System
- Freeze&Cool
- IceMaker
- Water dispenser
- BrilliantLight Pro
- M Touch Pro

*Two of these panels must be ordered separately for both refrigerator doors.

MasterCool Refrigeration – 42" Bottom Mount



Model	Hinge	Material	UMRP
KFMC 3858 FD	French	12489440	\$15,999
Custom Panel			
42" Prestige	Door		
Bottom Mount			
Fridge/Freezer			

Specifications

Width	41 1/4 in (1048 mm)
Height	83 9/16 – 85 1/2 in (2123 – 2171 mm)
Depth	24 in (610 mm)
Shipping Weight	563 lbs (255 kg)
Finish	Panel-ready

Features

- FoodView
- Longlife AirClean System
- Freeze&Cool
- Dual IceMaker
- Water dispenser
- BrilliantLight Pro
- M Touch Pro

Optional Accessories	Material	UMRP
KWF 2000 Water filter	11480330	\$189
KFP 4231 ed/cs FD Front panel fridge 42"	12687870	\$649
KFP 4232 ed/cs Front Panel freezer, upper drawer SS 42"	12687950	\$329
KFP 4233 ed/cs Front Panel freezer, lower drawer SS 42"	12687980	\$499
KFK 4201 Frame set – 42" (For SS Proud Installation)	12687430	\$899
KTK 4230 ed Toe kick cover 42" Stainless steel	12687220	\$149
KTT 3001 Trim kit (For traditional 36" and 42" openings)	12687150	\$249

Two of these panels must be ordered separately for both refrigerator doors.

MasterCool Refrigeration – 24" Columns

K2602 Vi



K2602 SF



Model	Hinge	Material	UMRP
K2602 Vi Custom Panel	Right	11501360	\$9,199
K2602 SF Clean Touch Steel™ w/ DS6708 ContourLine Handle	Right	11502570	\$9,499

Specifications

Width	23 3/4 in (604 mm)
Height	83 3/4 – 85 3/16 in (2127 – 2164 mm)
Depth	24 in (610 mm)
Refrigerator Capacity	12.96 cu.ft. (357 l)
Shipping Weight	346 lbs (157 kg)
Annual Energy Usage	254 kWh

Fridge Features

- Push2Open Door
- MasterFresh
- BrilliantLight
- MasterSensor Controls
- SoftClose Door
- Temperature Zones: 2
- Maximum Storage Capacity and Flexibility:
4 Door Bins, 3 Drawers, 2 Movable Shelves
- DynaCool
- MaxLoad Hinge
- Active AirClean Filter
- SuperCool
- Acoustic Door and Temperature Alarm
- Sabbath Mode
- CleanSteel Back Wall

Optional Accessories Vi	Material	UMRP
KFP 2405 24 in Clean Touch Steel™ Panel (No Logo, w/o handle)	1499070	\$1,099
KTk 2420 SS 24 in Toekick	10984070	\$199
KSK 2002 Merge Kit	10984130	\$1,499

Optional Accessories SF	Material	UMRP
KTF 1042 42 in Top Frame	10984920	\$399
KTF 1048 48 in Top Frame	12556870	\$399
KTF 1054 54 in Top Frame	12556860	\$399
KTF 1060 60 in Top Frame	1255685	\$399
KTF 1066 66 in Top Frame	12556810	\$399
KTF 1072 72 in Top Frame	12556830	\$399
KTk 2420 SS 24 in Toekick	10984070	\$199
KSK 2002 Merge Kit	10984130	\$1,499
DS 7308 GEN 7000 ContourLine Handle	12047020	\$185.90

MasterCool Refrigeration – 30" Columns

K2802 Vi



K2802 SF



Model	Hinge	Material	UMRP
K2802 Vi Custom Panel	Right	11502590	\$9,699
K2802 SF Clean Touch Steel™ w/ DS6708 ContourLine Handle	Right	11502700	\$10,499

Specifications

Width	29 3/4 in (756 mm)
Height	83 3/4 – 85 3/16 in (2127 – 2164 mm)
Depth	24 in (610 mm)
Refrigerator Capacity	16.77 cu.ft. (475 l)
Shipping Weight	395 lbs (179 kg)
Annual Energy Usage	279 kWh

Fridge Features

- Push2Open Door
- MasterFresh
- BrilliantLight
- MasterSensor Controls
- SoftClose Door
- Temperature Zones: 2
- Maximum Storage Capacity and Flexibility:
4 Door Bins, 3 Drawers, 2 Movable Shelves
- DynaCool
- MaxLoad Hinge
- Active AirClean Filter
- SuperCool
- Acoustic Door and Temperature Alarm
- Sabbath Mode
- CleanSteel Back Wall

Optional Accessories Vi	Material	UMRP
KFP 3005 30 in Clean Touch Steel™ Panel (No Logo, w/o handle)	11499080	\$1,149
KTK 3020 SS 30 in Toekick	10984090	\$199
KSK 2002 Merge Kit	10984130	\$1,499

Optional Accessories SF	Material	UMRP
KTF 1048 48 in Top Frame	12556870	\$399
KTF 1054 54 in Top Frame	12556860	\$399
KTF 1060 60 in Top Frame	12556850	\$399
KTF 1066 66 in Top Frame	12556810	\$399
KTF 1072 72 in Top Frame	12556830	\$399
KTK 3020 SS 30 in Toekick	10984090	\$199
KSK 2002 Merge Kit	10984130	\$1,499
DS 7308 GEN 7000 ContourLine Handle	12047020	\$185.90

MasterCool Refrigeration – 36" Columns



Model	Hinge	Material	UMRP	Optional Accessories Vi	Material	UMRP
K2902 Vi Custom Panel	Right	11502710	\$9,999	KFP 3605 36 in Clean Touch Steel™ Panel (No Logo, w/o handle)	11499100	\$1,199
K2902 SF Clean Touch Steel™ w/ DS6708 ContourLine Handle	Right	11502840	\$10,999	KTK 3620 SS 36 in Toekick	10984110	\$199
K2912 Vi Custom Panel	Left	11502720	\$9,999	KSK 2002 Merge Kit	10984130	\$1,499
Specifications				Optional Accessories SF	Material	UMRP
Width	35 3/4 in (908 mm)			KTF 1054 54 in Top Frame	12556860	\$399
Height	83 3/4 – 853/16 in (2127 – 2164 mm)			KTF 1060 60 in Top Frame	12556850	\$399
Depth	24 in (610 mm)			KTF 1066 66 in Top Frame	112556810	\$399
Refrigerator Capacity	20.55 cu.ft. (582 l)			KTF 1072 72 in Top Frame	12556830	\$399
Shipping Weight	435 lbs (197 kg)			KTK 3620 SS 36 in Toekick	10984110	\$199
Annual Energy Usage	312 kWh			KSK 2002 Merge Kit	10984130	\$1,499
Fridge Features				DS 7308 GEN 7000 ContourLine Handle	12047020	\$185.90
• Push2Open Door • MasterFresh • BrilliantLight • MasterSensor Controls • SoftClose Door • Temperature Zones: 2 • Maximum Storage Capacity and Flexibility: 4 Door Bins, 3 Drawers, 2 Movable Shelves • DynaCool • MaxLoad Hinge • Active AirClean Filter • SuperCool • Acoustic Door and Temperature Alarm • Sabbath Mode • CleanSteel Back Wall						

MasterCool Freezers – 18" Columns

F2412 Vi



F2412 SF



Model	Hinge	Material	UMRP
F2412 Vi Custom Panel	Left	11503300	\$8,799
F2412 SF Clean Touch Steel™ w/ DS6708 ContourLine Handle	Left	11503310	\$9,449

Specifications

Width	17 3/4 in (451 mm)
Height	83 3/4 – 85 3/16 in (2127 – 2164 mm)
Depth	24 in (610 mm)
Freezer Capacity	8.55 cu.ft. (242 l)
Shipping Weight	306 lbs (139 kg)
Annual Energy Usage	404 kWh

Freezer Features

- Push2Open Door
- BrilliantLight
- MasterSensor Controls
- SoftClose Door
- Temperature Zones: 1
- MaxLoad Hinge
- Acoustic Door and Temperature Alarm
- IceMaker w/ plumbed water connection
- Maximum Storage Capacity and Flexibility:
3 Shelves, 2 Drawers, 3 large Door baskets
- SuperCool
- Sabbath Mode
- CleanSteel Back Wall

Optional Accessories Vi	Material	UMRP
KFP 1805 18 in Clean Touch Steel™ Panel (No Logo, w/o handle)	11499020	\$989
KTK 1820 SS 18 in Toekick	10984060	\$199
KSK 2002 Merge Kit	10984130	\$1,499
KWF 2000 Water Filter 2.0 (MC 2xx2)	11480330	\$189

Optional Accessories SF	Material	UMRP
KTF 1042 42 in Top Frame	10984920	\$399
KTF 1048 48 in Top Frame	12556870	\$399
KTF 1054 54 in Top Frame	12556860	\$399
KTF 1060 60 in Top Frame	12556850	\$399
KTF 1066 66 in Top Frame	12556810	\$399
KTF 1072 72 in Top Frame	12556830	\$399
KTK 1820 SS 18 in Toekick	10984060	\$199
KSK 2002 Merge Kit	10984130	\$1,499
KWF 2000 Water Filter 2.0 (MC 2xx2) Handle	11480330	\$189
DS 7308 GEN 7000 ContourLine Handle	12047020	\$185.90

MasterCool Freezers – 18" Columns

F2462 Vi



F2472 Vi



F2472 SF



Model	Hinge	Material	UMRP
F2462 Vi Custom Panel	Right	11503420	\$8,799
F2472 Vi Custom Panel	Left	11503430	\$9,249
F2472 SF Clean Touch Steel™ w/ DS6708 ContourLine Handle	Left	11503530	\$9,499

Specifications

Width	17 3/4 in (451 mm)
Height	83 3/4 – 85 3/16 in (2127 – 2164 mm)
Depth	24 in (610 mm)
Freezer Capacity	7.73 cu.ft. (219 l)
Shipping Weight	328 lbs (149 kg)
Annual Energy Usage	428 kWh

Freezer Features

- Push2Open Door
- BrilliantLight
- MasterSensor Controls
- SoftClose Door
- Temperature Zones: 1
- MaxLoad Hinge
- Acoustic Door and Temperature Alarm
- Ice & Water Dispenser
- Maximum Storage Capacity and Flexibility:
3 Shelves, 2 Drawers
- SuperCool
- Sabbath Mode
- CleanSteel Back Wall

Optional Accessories Vi	Material	UMRP
KFP 1845 18 in Clean Touch Steel™ Panel (No Logo, w/o handle)	11499570	\$999
KTK 1820 SS 18 in Toekick	10984060	\$199
KSK 2002 Merge Kit	10984130	\$1,499
KWF 2000 Water Filter 2.0 (MC 2xx2)	11480330	\$189

Optional Accessories SF	Material	UMRP
KTF 1042 42 in Top Frame	10984920	\$399
KTF 1048 48 in Top Frame	12556870	\$399
KTF 1054 54 in Top Frame	12556860	\$399
KTF 1060 60 in Top Frame	12556850	\$399
KTF 1066 66 in Top Frame	12556810	\$399
KTF 1072 72 in Top Frame	12556830	\$399
KTK 1820 SS 18 in Toekick	10984060	\$199
KSK 2002 Merge Kit	10984130	\$1,499
KWF 2000 Water Filter 2.0 (MC 2xx2) Handle	11480330	\$189
DS 7308 GEN 7000 ContourLine Handle	12047020	\$185.90

MasterCool Freezers – 24" Columns



Model	Hinge	Material	UMRP
F2672 Vi Custom Panel	Left	11503550	\$9,849

Specifications

Width	23 3/4 in (604 mm)
Height	83 3/4 – 85 3/16 in (2127 – 2164 mm)
Depth	24 in (610 mm)
Freezer Capacity	11.23 cu.ft. (318 l)
Shipping Weight	375 lbs (170 kg)
Annual Energy Usage	454 kWh

Freezer Features

- Push2Open Door
- BrilliantLight
- MasterSensor Controls
- SoftClose Door
- Temperature Zones: 1
- MaxLoad Hinge
- Acoustic Door and Temperature Alarm
- Ice & Water Dispenser
- Maximum Storage Capacity and Flexibility:
3 Shelves, 2 Drawers
- SuperCool
- Sabbath Mode
- CleanSteel Back Wall

Optional Accessories Vi	Material	UMRP
KFP 2445 24 in Clean Touch Steel™ Panel (No Logo, w/o handle)	11499620	\$1,149

KTk 2420 SS 24 in Toekick	10984070	\$199
KSK 2002 Merge Kit	10984130	\$1,499
KWF 2000 Water Filter 2.0 (MC 2xx2)	11480330	\$189

Optional Accessories SF	Material	UMRP
KTF 1042 42 in Top Frame	10984920	\$399
KTF 1048 48 in Top Frame	12556870	\$399
KTF 1054 54 in Top Frame	12556860	\$399
KTF 1060 60 in Top Frame	1255685	\$399
KTF 1066 66 in Top Frame	12556810	\$399
KTF 1072 72 in Top Frame	12556830	\$399
KTk 2420 SS 24 in Toekick	10984070	\$199
KSK 2002 Merge Kit	10984130	\$1,499
DS 7308 GEN 7000 ContourLine Handle	12047020	\$185.90

MasterCool Freezers – 30" Columns



Model	Hinge	Material	UMRP	Optional Accessories Vi	Material	UMRP
F2802 Vi Custom Panel	Right	11503330	\$9,999	KFP 3005 30 in Clean Touch Steel™ Panel (No Logo, w/o handle)	11499080	\$1,149
F2812 Vi Custom Panel	Left	11503340	\$10,499	KTK 3020 SS 30 in Toekick	10984090	\$199
F2812 SF Clean Touch Steel™ w/ DS6708 ContourLine Handle	Left	11503350	\$11,549	KSK 2002 Merge Kit	10984130	\$1,499
Specifications				Optional Accessories SF	Material	UMRP
Width	29 3/4 in (756 mm)			KTF 1048 48 in Top Frame	12556870	\$399
Height	83 3/4 – 85 3/16 in (2127 – 2164 mm)			KTF 1054 54 in Top Frame	12556860	\$399
Depth	24 in (610 mm)			KTF 1060 60 in Top Frame	12556850	\$399
Freezer Capacity	15.75 cu.ft. (446 l)			KTF 1066 66 in Top Frame	12556810	\$399
Shipping Weight	395 lbs (179 kg)			KTF 1072 72 in Top Frame	12556830	\$399
Annual Energy Usage	479 kWh			KTK 3020 SS 30 in Toekick	10984090	\$199
Fridge Features				KSK 2002 Merge Kit	10984130	\$1,499
• Push2Open Door				KWF 2000 Water Filter 2.0 (MC 2xx2) Handle	11480330	\$189
• BrilliantLight				DS 7308 GEN 7000 ContourLine Handle	12047020	\$185.90
• MasterSensor Controls						
• SoftClose Door						
• Temperature Zones: 1						
• MaxLoad Hinge						
• Acoustic Door and Temperature Alarm						
• IceMaker w/ plumbed water connection						
• Maximum Storage Capacity and Flexibility: 3 Shelves, 2 Drawers, 1 small Door basket, 3 large Door baskets						
• SuperCool						
• Sabbath Mode						
• CleanSteel Back Wall						

MasterCool Freezers – 36" Columns



Model	Hinge	Material	UMRP	Optional Accessories Vi	Material	UMRP
F2902 Vi Custom Panel	Right	11503360	\$10,799	KFP 3605 36 in Clean Touch Steel™ Panel (No Logo, w/o handle)	11499100	\$1,199
F2912 Vi Custom Panel	Left	11503390	\$10,799	KTK 3620 SS 36 in Toekick	10984110	\$199
F2912 SF Clean Touch Steel™ w/ DS6708 ContourLine Handle	Left	11503410	\$11,549	KSK 2002 Merge Kit	10984130	\$1,499
				KWF 2000 Water Filter 2.0 (MC 2xx2)	11480330	\$189
Specifications				Optional Accessories SF	Material	UMRP
Width	35 3/4 in (908 mm)			KTF 1054 54 in Top Frame	12556860	\$399
Height	83 3/4 – 85 3/16 in (2127 – 2164 mm)			KTF 1060 60 in Top Frame	12556850	\$399
Depth	24 in (610 mm)			KTF 1066 66 in Top Frame	12556810	\$399
Freezer Capacity	19.39 cu.ft. (549 l)			KTF 1072 72 in Top Frame	12556830	\$399
Shipping Weight	462 lbs (210 kg)			KTK 3620 SS 36 in Toekick	10984110	\$199
Annual Energy Usage	528 kWh			KSK 2002 Merge Kit	10984130	\$1,499
Fridge Features				KWF 2000 Water Filter 2.0 (MC 2xx2) Handle	11480330	\$189
• Push2Open Door • BrilliantLight • MasterSensor Controls • SoftClose Door • Temperature Zones: 1 • MaxLoad Hinge • Acoustic Door and Temperature Alarm • IceMaker w/ plumbed water connection • Maximum Storage Capacity and Flexibility: 3 Shelves, 2 Drawers, 1 small Door basket, 3 large Door baskets • SuperCool • Sabbath Mode • CleanSteel Back Wall				DS 7308 GEN 7000 ContourLine Handle	12047020	\$185.90

Product Highlights — **MasterCool Wine Storage**

Feature	Description (see specific models for details)
MasterSensor Controls	Incredibly convenient: a whole range of settings can be controlled easily with the tap of a finger on the color touch display.
BrilliantLight	Each area of the unit is perfectly illuminated by many LED light strips strategically placed throughout.
Push2Open	For a handleless design, just apply slight pressure to the door to open.
SoftClose	With just a gentle touch, our dynamic doors close on their own. Integrates perfectly within a handleless kitchen.
Temperature Zones	Store up to three different types of wine with different temperature zones.
FlexiFrame Racks	Individual wooden slats can be easily moved to make room for larger wine bottles.
SommelierSet	Perfect for wine connoisseurs: prepare cooled wine glasses and wine for decanting. Drink perfectly conditioned wine even from opened bottles.
NoteBoard	Every bottle rack features a removable, magnetic strip for labeling bottles.
Miele@home/ Mobile Control	Access your appliance from your smart device for maximum convenience.

MasterCool Wine Storage – 24" Columns

KWT 2602 Vi



KWT 2602 SF



KWT 2612 Vi



KWT 2612 SF



Model	Hinge	Material	UMRP
KWT 2602 Vi Custom Panel	Right	11503590	\$9,449
KWT 2602 SF Clean Touch Steel™ w/ DS6708 ContourLine Handle	Right	11503620	\$10,099
KWT 2612 Vi Custom Panel	Left	11503610	\$9,449
KWT 2612 SF Clean Touch Steel™ w/ DS6708 ContourLine Handle	Left	11503640	\$10,099

Specifications

Width	23 3/4 in (604 mm)
Height	83 3/4 – 85 3/16 in (2127 – 2164 mm)
Depth	24 in (610 mm)
Shipping Weight	357 lbs (162 kg)
Annual Energy Usage	179 kWh

Features

- Push2Open Door
- BrilliantLight
- MasterSensor Controls
- SoftClose Door
- Temperature Zones: 3
- Maximum Storage Capacity and Flexibility:
104 x 0.75 l bottles
- DynaCool
- MaxLoad Hinge
- Acoustic Door and Temperature Alarm
- FlexiFrame Racks: 13
- UV Tinted Glass
- NoteBoard
- Sabbath Mode

Included Accessories

WSS2600
SommelierSet (Ships separate from unit)

Optional Accessories (Vi)	Material	UMRP
KFP 2455 Clean Touch Steel™ Panel (No Logo, w/o handle)	11499630	\$1,279
KTK 2420 SS 24 in Toekick	10984070	\$199
KSK 2002 Merge Kit	10984130	\$1,499


Optional Accessories (SF)	Material	UMRP
KTF 1042 42 in Top Frame	10984920	\$399
KTF 1048 48 in Top Frame	12556870	\$399
KTF 1054 54 in Top Frame	12556860	\$399
KTF 1060 60 in Top Frame	12556850	\$399
KTF 1066 66 in Top Frame	12556810	\$399
KTF 1072 72 in Top Frame	12556830	\$399
KTK 2420 SS 24 in Toekick	10984070	\$199
KSK 2002 Merge Kit	10984130	\$1,499
DS 7308 GEN 7000 ContourLine Handle	12047020	\$185.90

MasterCool Wine Storage – 24" Columns w/ SommelierSet

KWT 2662 ViS



KWT 2672 ViS



Model	Hinge	Material	UMRP
KWT 2662 ViS Custom Panel	Right	11503650	\$10,599
KWT 2672 ViS Custom Panel	Left	11503660	\$10,599

Specifications

Width	23 3/4 in (604 mm)
Height	83 3/4 – 85 3/16 in (2127 – 2164 mm)
Depth	24 in (610 mm)
Shipping Weight	357 lbs (162 kg)
Annual Energy Usage	179 kWh

Features

- Push2Open Door
- BrilliantLight
- MasterSensor Controls
- SoftClose Door
- Temperature Zones: 3
- Maximum Storage Capacity and Flexibility:
77 x 0.75 l bottles
- DynaCool
- MaxLoad Hinge
- Acoustic Door and Temperature Alarm
- FlexiFrame Racks: 9
- UV Tinted Glass
- SommelierSet
- NoteBoard
- Sabbath Mode

Included Accessories

WSS2600
SommelierSet (Ships separate from unit)

Optional Accessories	Material	UMRP
KFP 2455 Clean Touch Steel™ Panel (No Logo, w/o handle)	11499630	\$1,279
KTK 2420 SS 24 in Toekick	10984070	\$199
KSK 2002 Merge Kit	10984130	\$1,499

Handle Options

GEN 7000	MODEL	MATERIAL	TRIM / COLOR	HANDLE WIDTH	COOKING	VI DISH-WASHERS	VI COOLING	SF MASTER-COOL	UMRP
	DS 7000	11345890	PureLine Stainless steel ¹	15 3/4 in	•	•	•	—	\$164
	DS 7000	11345930	VitroLine Obsidian black ¹	15 3/4 in	•	•	•	—	\$340
	DS 7000	11345940	VitroLine Brilliant white ¹	15 3/4 in	•	•	•	—	\$340
	DS 7000	11345950	VitroLine Graphite grey ¹	15 3/4 in	•	•	•	—	\$340
	DS 7308	12047020	ContourLine Stainless steel standard handle	21 1/8 in	•	•	•	•	\$186
	DS 7708	12047000	ContourLine Stainless steel swiveling handle	21 1/8 in	•	•	•	•	\$230
	DS 7808	12047030	VitroLine Obsidian black	19 11/16 in	•	•	•	—	\$384
	DS 7808	12047050	VitroLine Graphite grey	19 11/16 in	•	•	•	—	\$384
	DS 7808	12047060	VitroLine Brilliant white	19 11/16 in	•	•	•	—	\$384
	DS 7808	12046910	PureLine Stainless steel	19 11/16 in	•	•	•	—	\$186



Miele, Inc.
9 Independence Way
Princeton, NJ 08540

mieleusa.com
1-800-843-7231

Find your nearest Miele Experience Center in:

Beverly Hills
Chicago
Coral Gables
Manhattan
Princeton
Seattle
Tysons Corner