

Miele

Cooking and Refrigeration Appliances Price List, New Zealand.

Effective 15.05.2024



Quality Ahead of its Time

Discovery 2000 Oven - 60 cm

H 2267-1 B



PureLine CLST

H 2267-1 BP



PureLine CLST

H 2861 B



PureLine CLST

H 2861 BP



PureLine CLST












Price	\$2,599	\$3,199	\$3,299	CLST \$4,199 Colour variant \$4,399
Item Number	11127690	11127700	12174510	CLST 12174530 OBSW 12174490 GRGR 12174500
Capacity	76 l	76 l	76 l	76 l
Display / Controls	EasyControl	EasyControl	EasyControl Plus	EasyControl Plus
Cooking Functions	9	9	10	11
Catalytic Liner / Pyrolytic Cleaning	YES / -	- / YES	YES / -	- / YES
Pyrofit Accessories	-	-	-	-
Door Construction	Triple Glazing	Quadruple Glazing	Triple Glazing	Quadruple Glazing
SoftOpen / SoftClose	-	-	YES / YES	YES / YES
Automatic Programmes	-	-	YES	YES
User Programmes	-	-	-	-
Moisture Plus	-	-	-	-
Crisp Function	-	-	-	-
TasteControl	-	-	-	-
Corded / Wireless Food Probe	-	-	-	-
FoodView	-	-	-	-
Miele@home ¹	-	-	YES	YES
SuperVision Display	-	-	-	-
MotionReact	-	-	-	-
Cavity Lighting	Halogen	Halogen	Halogen	Halogen
Baking Tray	1	1	1	1
Multi-Purpose Tray	1	1	1	1
Grilling and Roasting Insert	-	-	1	1
Wire Racks	2	2	2	2
FlexiClips	1	1	1	1
AirFry Tray	-	-	1	1

Exclusive to Miele. **Highlight** indicates difference from model to model within the appliance group. Colour variant codes: CLST = CleanSteel, OBSW = Obsidian Black, GRGR = Graphite Grey, BRWS = Brilliant White.

¹Miele@home is the umbrella term covering all aspects of connected Miele appliances, regardless whether their operation is via the Miele App, via voice control, or via full integration into existing SmartHome systems.

Generation 7000 Oven - 60 cm

	H 7260 BP	H 7264 BP	H 7464 BP	H 7860 BP
				
	PureLine CLST	PureLine CLST	PureLine CLST	PureLine CLST
			 	 
Price	\$4,999	CLST \$6,199 Colour variant \$6,399	CLST \$7,499 Colour variant \$7,699	CLST \$10,699 Colour variant \$10,899
Item Number	11128380	CLST 11128420 OBSW 11128400	CLST 11128470 OBSW 11128450 GRGR 11128460 BRWS 11128440 ▲	CLST 11128580 OBSW 11128560 GRGR 11128570
Capacity	76 l	76 l	76 l	76 l
Display / Controls	DirectSensor S	DirectSensor S	DirectSensor	M Touch
Cooking Functions	11	11	14	17
Catalytic Liner / Pyrolytic Cleaning	- / YES	- / YES	- / YES	- / YES
Pyrofit Accessories	-	-	YES	YES
Door Construction	Quadruple Glazing	Quadruple Glazing	Quadruple Glazing	Quadruple Glazing
SoftOpen / SoftClose	YES / YES	YES / YES	YES / YES	YES / YES
Automatic Programmes	YES	YES	YES	YES
User Programmes	-	-	YES	YES
Moisture Plus	-	YES	YES	YES
Crisp Function	-	-	YES	YES
TasteControl	-	-	YES	YES
Corded / Wireless Food Probe	-	-	Corded	Wireless
FoodView	-	-	-	YES
Miele@home¹	-	YES	YES	YES
SuperVision Display	-	-	-	YES
MotionReact	-	-	-	YES
Cavity Lighting	Halogen	Halogen	LED	LED
Baking Tray	1	1	1	1
Multi-Purpose Tray	1	1	1	1
Grilling and Roasting Insert	1	1	1	1
Wire Racks	2	2	2	2
FlexiClips	1	1	1	1
Available Design Line				
ArtLine - (Handleless)	-	-	\$7,899 OBSW 11128490 GRGR 11128500 BRWS 11128480 ▲	\$11,199 OBSW 11128600 GRGR 11128610

Exclusive to Miele. Highlight indicates difference from model to model within the appliance group. Colour variant codes: CLST = CleanSteel, OBSW = Obsidian Black, GRGR = Graphite Grey, BRWS = Brilliant White. ▲ Limited stock, only available while stocks last.

¹Miele@home is the umbrella term covering all aspects of connected Miele appliances, regardless whether their operation is via the Miele App, via voice control, or via full integration into existing SmartHome systems.

Generation 7000 Oven - 90 cm

H 2890 B



H 7890 BP



Price	\$10,699	\$20,199
Item Number	11127820	11127830
Capacity	90 l	90 l
Display / Controls	EasyControl	M Touch
Cooking Functions	8	17
Catalytic Liner / Pyrolytic Cleaning	YES / -	- / YES
Pyrofit Accessories	-	YES
Door Construction	Quadruple Glazing	Quadruple Glazing
SoftOpen / SoftClose	YES / YES	YES / YES
Automatic Programmes	-	YES
User Programmes	YES	YES
Moisture Plus	-	YES
Crisp Function	-	YES
TasteControl	-	-
Corded / Wireless Food Probe	-	Wireless
FoodView	-	YES
Miele@home ¹	-	YES
SuperVision Display	-	-
MotionReact	-	YES
Cavity Lighting	Halogen	Halogen
Baking Tray	1	1
Multi-Purpose Tray	1	1
Grilling and Roasting Insert	1	1
Wire Racks	2	2
FlexiClips	-	1

Highlight indicates difference from model to model within the appliance group. Colour variant codes: CLST = CleanSteel, OBSW = Obsidian Black, GRGR = Graphite Grey, BRWS = Brilliant White.

¹Miele@home is the umbrella term covering all aspects of connected Miele appliances, regardless whether their operation is via the Miele App, via voice control, or via full integration into existing SmartHome systems.

Dialog Oven - 60 cm

DO 7860



PureLine CLST



Price

CLST \$17,999
Colour variant \$17,999

Item Number	CLST 1137670 ▲ OBSW 1137650 ▲
Capacity	50 l
Display / Controls	M Touch
Interior Enamel	PerfectClean Enamel
Catalytic / Pyrolytic Cleaning	- / YES
PyroFit Accessories	YES
Door Construction	CoolTouch door
SoftOpen / SoftClose	YES / -
M Chef Technology	YES
M Chef Operating Modes (Cooking with Electromagnetic Waves and Conventional Heating Methods)	M Chef + Fan Plus M Chef + Conventional heat M Chef + Intensive Bake M Chef + Moisture Plus M Chef + Auto Roast M Chef + Full Grill M Chef + Fan Grill M Chef Menu
Gourmet Pro	YES
Gourmet Assistant	YES
Automatic Programmes	>100 programmes
User Programmes	20 programmes
Moisture Plus	YES
Crisp Function	YES
Corded Food Probe/Wireless Food Probe	YES / -
Miele@home ¹	YES
Halogen / BrilliantLight LED	- / YES
Baking Tray	x1
Multi-purpose Tray	x1
Wire Rack w / PyroFit	x1
Side Rails w / PyroFit	As standard in the oven

Highlight indicates difference from model to model within the appliance group. Colour variant codes: CLST = CleanSteel, OBSW = Obsidian Black, GRGR = Graphite Grey, BRWS = Brilliant White. ▲ Limited stock, only available while stocks last.

¹Miele@home is the umbrella term covering all aspects of connected Miele appliances, regardless whether their operation is via the Miele App, via voice control, or via full integration into existing SmartHome systems.

Straight Steam - 45 cm x 60 cm

DG 2840



PureLine CLST



DG 7440



PureLine CLST



Price

CLST \$4,299
Colour variant \$4,499

CLST \$5,699
Colour variant \$5,899

Item Number	CLST 11135390 OBSW 11135350	CLST 11135430 OBSW 11135410
Appliance Type	Straight Steam	Straight Steam
Display / Controls	EasySensor	DirectSensor
Oven Compartment Volume in l	40	40
Water Tank Capacity in l	1.5	1.5
Steam Delivery	DualSteam Technology	DualSteam Technology
Automatic Programmes	-	50
User Programmes	-	20
Cavity Finish	Stainless steel	Stainless steel
Auto Steam Reduction	YES	YES
SoftOpen / SoftClose	YES / YES	YES / YES
Plumbed Option	-	-
MotionReact	-	-
Appliance Networking	-	YES
SuperVision	-	-
Perforated Stainless Steel Containers	x2	x2
Solid Stainless Steel Containers	x1	x1
Wire Rack	x1	x1
Drip Tray	x1	x1

Exclusive to Miele. **Highlight** indicates difference from model to model within the appliance group. Colour variant codes: CLST = CleanSteel, OBSW = Obsidian Black, GRGR = Graphite Grey, BRWS = Brilliant White.

*Miele@home is the umbrella term covering all aspects of connected Miele appliances, regardless whether their operation is via the Miele App, via voice control, or via full integration into existing SmartHome systems.

2-in-1 Combi Steam Oven - 60 cm

DGC 7250



PureLine CLST

DGC 7450



PureLine CLST



Price

\$4,699

CLST \$5,399
Colour variant \$5,599

Item Number	12086520	CLST 11819160 OBSW 11819120
Appliance Type	2-in-1	2-in-1
Display / Controls	DirectSensor S	DirectSensor
Oven Compartment Volume in l	76	76
Steam Type with External Steam Generator (2.2 kW)	MonoSteam	MonoSteam
Oven Light	1x Halogen	1x LED
5 Shelf Levels with Removable Side Racks	YES	YES
CleanGlass Door with SoftOpen / SoftClose	YES	YES
Cooking Functions	11	16
Oven Temperature in °C	30 - 250	30 - 250
TasteControl (RapidCooling Function)	YES	YES
Crisp Function	-	YES
Moisture Plus	YES	YES
Automatic Programmes (Oven)	29	76
User Programmes	-	20
Steam Temperature in °C	70 - 100	70 - 100
Fresh Water - Volume in l (Drawn by Suction Rod)	1.0	1.0
Automatic Programmes (Steam)	15	144
Defrost	YES	YES
Soak Maintenance Programme	YES	YES
Oven Compartment Drying Programme	YES	YES
Automatic Descaling	YES	YES
Miele@home ¹	YES	YES
CoolTouch Door	YES	YES
Safety Switch-off	YES	YES
System Lock / Sensor Lock	YES	YES
FlexiClip Runners with PerfectClean	1 Pair	1 Pair
Universal Tray with PerfectClean	x1	x1
Baking Tray with PerfectClean	x1	x1
Wire Rack with PerfectClean	x1	x1
Removable Side Racks with PerfectClean	1 Pair	1 Pair
Perforated Stainless Steel Cooking Container	x1	x1
Solid Stainless Steel Cooking Container	x1	x1
Descaling Tablets	x2	x2

Exclusive to Miele. Highlight indicates difference from model to model within the appliance group. Colour variant codes: CLST = CleanSteel, OBSW = Obsidian Black, GRGR = Graphite Grey, BRWS = Brilliant White.

¹Miele@home is the umbrella term covering all aspects of connected Miele appliances, regardless whether their operation is via the Miele App, via voice control, or via full integration into existing SmartHome systems.

3-in-1 Pro Combi Steam Oven - 45 cm x 60 cm

DGC 7440 HC Pro



PureLine CLST



Price

CLST \$7,699
Colour variant \$7,899

Item Number	CLST 12087200 OBSW 12086870 GRGR 12087190 ▲
Display Type	DirectSensor
Oven Compartment Volume in l / No. of Shelf Levels	48 / 3
Quick Release Side Racks / Hinged Grill Element / CleanGlass Door	YES / YES / YES
SoftOpen / SoftClose / Touch2Open	YES / YES / -
External Steam Generator Performance (3.3 kW) / Steam Type	YES / DualSteam
Fresh Water Container Volume in l	1.4
Temperature Range: Oven / Steam (in °C)	30-230°C / 40-100°C
Oven Functions (Conventional, Steam & Combi Mode)	14
Automatic Programmes	75+
Crisp Function / GourmetRoast / Keeping Warm (15 mins) / Cakes Plus	YES / YES / YES / YES
Mix & Match (Gentle Cook & Reheat Crispy Heat & Reheat)	YES
Food Probe	-
Menu Cooking (Automatic & Manual) / Sous-vide / Defrost	YES / YES / YES
User Programmes	20
Sabbath Programme	YES
Miele@home ¹	YES
SuperVision / MotionReact	-
HydroClean	YES
Soak / Rinse / Maintenance Programmes	YES / YES / YES
Oven Compartment Drying Programme	YES
Automatic Descaling	YES
Appliance Cooling System and CoolTouch Door	YES
Safety Switch-off / System Lock / Sensor Lock	YES / YES / YES
1x Universal Tray with PerfectClean	YES
1x FlexiClip Runners with PerfectClean	-
1x Removable Side Racks	YES
Perforated Stainless Steel Cooking Containers / Solid Stainless Steel Cooking Containers	x1 / x1
Descaling Tablets	x2
HydroCleaner Detergent	x1
Available Design Line	
ArtLine - (Handleless)	\$8,099 OBSW 12087320 GRGR 12087340

Exclusive to Miele. Colour variant codes: CLST = CleanSteel, OBSW = Obsidian Black, GRGR = Graphite Grey, BRWS = Brilliant White.

▲ Limited stock, only available while stocks last.

¹Miele@home is the umbrella term covering all aspects of connected Miele appliances, regardless whether their operation is via the Miele App, via voice control, or via full integration into existing SmartHome systems.

3-in-1 Pro Combi Steam Oven - 45 cm x 60 cm

DGC 7840 HC Pro



PureLine CLST



DGC 7845 HC Pro



PureLine CLST



Price	CLST \$11,199 Colour variant \$11,399	CLST \$12,199 Colour variant \$12,399
Item Number	CLST 12087560 OBSW 12087530 GRGR 12087550	CLST 12087800 OBSW 12087700
Display Type	M Touch	M Touch
Oven Compartment Volume in l / No. of Shelf Levels	48 / 3	48 / 3
Quick Release Side Racks / Hinged Grill Element / CleanGlass Door	YES / YES / YES	YES / YES / YES
SoftOpen / SoftClose / Touch2Open	YES / YES / -	YES / YES / -
External Steam Generator Performance (3.3 kW) / Steam Type	YES / DualSteam	YES / DualSteam
Fresh Water Container Volume in l	1.4	1.4
Temperature Range: Oven / Steam (in °C)	30-230°C / 40-100°C	30-230°C / 40-100°C
Oven Functions (Conventional, Steam & Combi Mode)	14	14
Automatic Programmes	150+	150+
Crisp Function / GourmetRoast / Keeping Warm (15 mins) / Cakes Plus	YES / YES / YES / YES	YES / YES / YES / YES
Mix & Match (Gentle Cook & Reheat Crispy Heat & Reheat)	YES	YES
Food Probe	Wireless	Wireless
Menu Cooking (Automatic & Manual) / Sous-vide / Defrost	YES / YES / YES	YES / YES / YES
User Programmes	20	20
Sabbath Programme	YES	YES
Miele@home ¹	YES	YES
SuperVision / MotionReact	YES	YES
DirectWaterPlus	YES	YES
HydroClean	YES	YES
Soak / Rinse / Maintenance Programmes	YES / YES / YES	YES / YES / YES
Oven Compartment Drying Programme	YES	YES
Automatic Descaling	YES	YES
Appliance Cooling System and CoolTouch Door	YES	YES
Safety Switch-off / System Lock / Sensor Lock	YES / YES / YES	YES / YES / YES
1x Universal Tray with PerfectClean	YES	YES
1x FlexiClip Runners with PerfectClean	YES	YES
1x Removable Side Racks	YES	YES
Perforated Stainless Steel Cooking Containers / Solid Stainless Steel Cooking Containers	x2 / x1	x2 / x1
Descaling Tablets	x2	x2
HydroCleaner Detergent	x1	x1
Available Design Line		
ArtLine - (Handleless)	\$11,599 OBSW 12087620 GRGR 12087670 ▲	\$12,599 OBSW 12087840 GRGR 12087850

Exclusive to Miele. Colour variant codes: CLST = CleanSteel, OBSW = Obsidian Black, GRGR = Graphite Grey, BRWS = Brilliant White.

▲ Limited stock, only available while stocks last.

¹Miele@home is the umbrella term covering all aspects of connected Miele appliances, regardless whether their operation is via the Miele App, via voice control, or via full integration into existing SmartHome systems.

3-in-1 Pro Combi Steam Oven - 60 cm x 60 cm

DGC 7460 HC Pro



PureLine CLST



Price

CLST \$10,699
Colour variant \$10,899

Item Number	CLST 12087480 BRWS 12087450 ▲ OBSW 12087460 GRGR 12087470
Display Type	DirectSensor
Oven Compartment Volume in l / No. of Shelf Levels	68 / 4
Quick Release Side Racks / Hinged Grill Element / CleanGlass Door	YES / YES / YES
SoftOpen / SoftClose / Touch2Open	YES / YES / -
External Steam Generator Performance (3.3 kW) / Steam Type	YES / DualSteam
Fresh Water Container Volume in l	1.4
Temperature Range: Oven / Steam (in °C)	30-230°C / 40-100°C
Oven Functions (Conventional, Steam & Combi Mode)	14
Automatic Programmes	75+
Crisp Function / GourmetRoast / Keeping Warm (15 mins) / Cakes Plus	YES / YES / YES / YES
Mix & Match (Gentle Cook & Reheat Crispy Heat & Reheat)	YES
Food Probe	Cable
Menu Cooking (Automatic & Manual) / Sous-vide / Defrost	YES / YES / YES
User Programmes	20
Sabbath Programme	YES
Miele@home ¹	YES
SuperVision / MotionReact	-
HydroClean	YES
Soak / Rinse / Maintenance Programmes	YES / YES / YES
Oven Compartment Drying Programme	YES
Automatic Descaling	YES
Appliance Cooling System and CoolTouch Door	YES
Safety Switch-off / System Lock / Sensor Lock	YES / YES / YES
1x Universal Tray with PerfectClean	YES
1x FlexiClip Runners with PerfectClean	YES
1x Removable Side Racks	YES
Perforated Stainless Steel Cooking Containers / Solid Stainless Steel Cooking Containers	x1 / x1
Descaling Tablets	x2
HydroCleaner Detergent	x1

Exclusive to Miele. Colour variant codes: CLST = CleanSteel, OBSW = Obsidian Black, GRGR = Graphite Grey, BRWS = Brilliant White.

▲ Limited stock, only available while stocks last.

¹Miele@home is the umbrella term covering all aspects of connected Miele appliances, regardless whether their operation is via the Miele App, via voice control, or via full integration into existing SmartHome systems.

3-in-1 Pro Combi Steam Oven - 60 cm x 60 cm

DGC 7860 HC Pro



PureLine CLST



DGC 7865 HC Pro



PureLine CLST



Price

CLST \$14,199
Colour variant \$14,499

CLST \$15,299
Colour variant \$15,499

Item Number	CLST 12087900 OBSW 12087870	CLST 12087940 OBSW 12087920
Display Type	DirectSensor	DirectSensor
Oven Compartment Volume in l / No. of Shelf Levels	68 / 4	68 / 4
Quick Release Side Racks / Hinged Grill Element / CleanGlass Door	YES / YES / YES	YES / YES / YES
SoftOpen / SoftClose / Touch2Open	YES / YES / -	YES / YES / -
External Steam Generator Performance (3.3 kW) / Steam Type	YES / DualSteam	YES / DualSteam
Fresh Water Container Volume in l	1.4	1.4
Temperature Range: Oven / Steam (in °C)	30-230°C / 40-100°C	30-230°C / 40-100°C
Oven Functions (Conventional, Steam & Combi Mode)	14	14
Automatic Programmes	150+	150+
Crisp Function / GourmetRoast / Keeping Warm (15 mins) / Cakes Plus	YES / YES / YES / YES	YES / YES / YES / YES
Mix & Match (Gentle Cook & Reheat Crispy Heat & Reheat)	YES	YES
Food Probe	Wireless	Wireless
Menu Cooking (Automatic & Manual) / Sous-vide / Defrost	YES / YES / YES	YES / YES / YES
User Programmes	20	20
Sabbath Programme	YES	YES
Miele@home ¹	YES	YES
SuperVision / MotionReact	YES	YES
DirectWaterPlus	-	YES
HydroClean	YES	YES
Soak / Rinse / Maintenance Programmes	YES / YES / YES	YES / YES / YES
Oven Compartment Drying Programme	YES	YES
Automatic Descaling	YES	YES
Appliance Cooling System and CoolTouch Door	YES	YES
Safety Switch-off / System Lock / Sensor Lock	YES / YES / YES	YES / YES / YES
1x Universal Tray with PerfectClean	YES	YES
1x FlexiClip Runners with PerfectClean	YES	YES
1x Removable Side Racks	YES	YES
Perforated Stainless Steel Cooking Containers / Solid Stainless Steel Cooking Containers	x2 / x1	x2 / x1
Descaling Tablets	x2	x2
HydroCleaner Detergent	x1	x1

Exclusive to Miele. **Highlight** indicates difference from model to model within the appliance group. Colour variant codes: CLST = CleanSteel, OBSW = Obsidian Black, GRGR = Graphite Grey, BRWS = Brilliant White.

¹Miele@home is the umbrella term covering all aspects of connected Miele appliances, regardless whether their operation is via the Miele App, via voice control, or via full integration into existing SmartHome systems.

Steam and Microwave Combination - 45 cm x 60 cm

DGM 7440



PureLine CLST



Price

CLST \$6,199
Colour variant \$6,449

Item Number	CLST 11135500 OBSW 11135480
Appliance Type	Steam & Microwave Combination
Display / Controls	DirectSensor
Oven Compartment Volume in l	40
Water Tank Capacity in l	1.5
Steam Delivery	DualSteam Technology
Automatic Programmes	50+
User Programmes	20
Cavity Finish	Stainless Steel Linen Finish
Auto Steam Reduction	YES
Microwave Technology	Inverter
Microwave Wattage	80 - 1000
Popcorn Function	YES
SoftOpen / SoftClose	YES / YES
MotionReact	-
Miele@home ¹	YES
SuperVision	-
Glass Tray	1
Perforated Stainless Steel Container	2
Solid Stainless Steel Container	1
Deep Solid Stainless Steel Container	-
Wire Rack	1

Colour variant codes: CLST = CleanSteel, OBSW = Obsidian Black, GRGR = Graphite Grey, BRWS = Brilliant White.

¹Miele@home is the umbrella term covering all aspects of connected Miele appliances, regardless whether their operation is via the Miele App, via voice control, or via full integration into existing SmartHome systems.

Microwave - 45 cm x 60 cm

M 7244 TC



PureLine CLST



Price

CLST \$3,699
Colour variant \$3,899

Item Number	CLST 11134160 OBSW 1134140 GRGR 1134150
Appliance Type	Straight Microwave
Capacity	46 l
Display / Controls	DirectSensor S
Microwave Wattage	80 - 900 W
Popcorn Function	YES
Quartz Grill	YES
SoftOpen / SoftClose	YES / YES
Stainless Steel Oven Compartment	YES
Cavity Lighting	LED
Grilling Rack	1
Gourmet Plate	1

Speed Oven - 45 cm x 60 cm

H 7440 BM



PureLine CLST



H 7840 BM



PureLine CLST



Price

CLST \$5,899
Colour variant \$6,099

CLST \$7,999
Colour variant \$8,199

Item Number	CLST 1128230 OBSW 11128210 GRGR 11128220 ▲ BRWS 11128200 ▲	CLST 1128320 OBSW 1128300
Capacity	43 l	43 l
Display / Controls	DirectSensor	M Touch
Cooking Functions	11	15
Interior Enamel	PerfectClean Enamel	PerfectClean Enamel
Catalytic Liner / Pyrolytic Cleaning	Stainless Steel	Stainless Steel
Pyrofit Accessories	-	-
Door Construction	Quadruple Glazing	Quadruple Glazing
SoftOpen / SoftClose	YES / YES	YES / YES
Automatic Programmes	YES	YES
User Programmes	-	-
Moisture Plus	-	-
Crisp Function	YES	YES
TasteControl	-	-
Corded / Wireless Food Probe	Corded	Corded
FoodView	-	-
Miele@home ¹	YES	YES
SuperVision Display	-	-
MotionReact	YES	YES
Cavity Lighting	LED	LED
Baking Tray	1	1
Glass Tray	1	1
Available Design Line		
ArtLine - (Handleless)	\$6,299 OBSW 11128270	\$8,399 OBSW 11128340 GRGR 11128350 ▲

Highlight indicates difference from model to model within the appliance group. Colour variant codes: CLST = CleanSteel, OBSW = Obsidian Black, GRGR = Graphite Grey, BRWS = Brilliant White. ▲ Limited stock, only available while stocks last.

¹Miele@home is the umbrella term covering all aspects of connected Miele appliances, regardless whether their operation is via the Miele App, via voice control, or via full integration into existing SmartHome systems.

Cooking

Benchtop coffee machines

Item no.	Product	Description	NZD
11555710	CM 5310 Obsidian Black	Full touch DirectSensor controls, 18+ beverage varieties, AromaticSystem brew unit, OneTouch for Two	1,799
11594700	CM 6160 Obsidian Black	Full touch DirectSensor controls, 26+ beverage varieties, 4 user profiles, AromaticSystem brew unit, OneTouch for Two, MilkPerfection double milk frothing, WiFi Conn@ct mobile control	2,399
11594730	CM 6360 Obsidian Black	Full touch DirectSensor controls, 26+ beverage varieties, 8 user profiles, AromaticSystem brew unit, OneTouch for Two, MilkPerfection double milk frothing, WiFi Conn@ct mobile control, heated cup rest	2,499
11025480	CM 7750 Obsidian Black	CM Touch display, CoffeeSelect – 3 separate bean containers, 28+ beverage varieties, 10 user profiles, AromaticSystemFresh brew unit, OneTouch for Two, CupSensor, AutoDescale, WiFi Conn@ct mobile control, heated cup rest	4,699

Built-in coffee machines

11165380	CVA 7440 PureLine CleanSteel	Full touch DirectSensor controls, EasyClick milk flask, CupSensor, 24+ beverage varieties, OneTouch for Two, WiFiConn@ct, MobileControl	7,299
11165360		Colour variant: VitroLine Obsidian Black	7,499
11165390	CVA 7840 PureLine CleanSteel	M Touch controls, CoffeeSelect - 3 separate bean containers, AutoClean, AutoDescale, EasyClick milk flask, CupSensor, 24+ beverage varieties, OneTouch for Two, WiFiConn@ct, MobileControl, MotionReact	8,799
11165430	CVA 7845 PureLine CleanSteel	M Touch controls, CoffeeSelect - 3 separate bean containers, AutoClean, AutoDescale, EasyClick milk flask, CupSensor, 24+ beverage varieties, OneTouch for Two, WiFiConn@ct, MobileControl, MotionReact, DirectWater	9,399
11165410		Colour variant: VitroLine Obsidian Black	9,599

Warming drawers

11135170	ESW 7010 Obsidian Black	Handleless design with Push2Open, 14 cm tall, Touch controls, capacity for 6 complete place settings, 4 operating modes incl food-warming and slow cooking functions, WiFiConn@ct	2,699
11135160	Brilliant White ▲		2,699
11135190	Graphite Grey ▲		2,699
11135240	ESW 7020 PureLine CleanSteel	Handleless design with Push2Open, 29 cm tall, Touch controls, capacity for 12 complete place settings, 4 operating modes incl food-warming and slow cooking functions, WiFiConn@ct	3,099
11135210		Colour variants: VitroLine Obsidian Black	3,099
11135220		VitroLine Graphite Grey	3,099

Vacuum sealing drawers

11159260	EVS 7010 Obsidian Black	Handleless design with Push2Open, 14 cm tall, Touch controls, 3 vacuum-sealing settings, fully telescopic runners for easy loading and unloading	5,999
----------	------------------------------------	--	--------------

Benchtop microwave oven

09546330	M 6012 CleanSteel	Benchtop microwave with grill, 26 l capacity, stainless steel cavity, 800 W microwave, quartz grill, Automatic Programmes, 3-stage memory, left-hinged door	1,699
----------	------------------------------	---	--------------

Induction cooktops

12399760	KM 7360 FL	62 cm wide, 3 cooking zones, frameless design for flush or proud benchtop installation, ComfortSelect sensor controls, Con@ctivity-enabled, Miele@home	2,699
11230350	KM 7464 FL	62 cm wide, 4 zone PowerFlex induction cooktop with TwinBoost, frameless design for flush or proud benchtop installation, ComfortSelect sensor controls with timers and Stop&Go, 3-in-1 PowerFlex area can be used as two separate, one large or a casserole zone, Con@ctivity-enabled	3,999
11230370	KM 7564 FL	62 cm wide, 4 zone dual PowerFlex induction cooktop with TwinBoost, frameless design for flush or proud benchtop installation, SmartSelect sensor controls with timers and Stop&Go, two 3-in-1 PowerFlex area can be used as two separate, one large or a casserole zone, Con@ctivity-enabled	4,599

Cooking

Induction cooktops (continued)

Item no.	Product	Description	NZD
11230380	KM 7574 FL	80 cm wide, 4 zone PowerFlex induction cooktop with TwinBoost, frameless design for flush or proud benchtop installation, SmartSelect sensor controls with timers and Stop&Go, 3-in-1 PowerFlex area can be used as two separate, one large or a casserole zone, Con@ctivity-enabled	5,499
12187600	KM 7575-2 FL	80 cm wide, 6 zone triple PowerFlex Induction cooktop with TwinBoost, frameless design for flush or proud benchtop installation, SmartSelect sensor controls with timers and Stop&Go, three 3-in-1 PowerFlex areas can each be used as two separate, one large or a casserole zone, Con@ctivity-enabled	5,999
12187610	KM 7678-2 FL	80 cm wide, full-surface Induction cooktop with TwinBoost, frameless design for flush or proud benchtop installation, SmartSelect sensor controls with timers and Stop&Go, Con@ctivity-enabled	6,599
11230310	KM 7684 FL	91.6 cm wide, 4 zone panoramic design PowerFlex induction cooktop with TwinBoost, frameless design for flush or proud benchtop installation, SmartSelect sensor controls with timers and Stop&Go, two 3-in-1 PowerFlex areas, Con@ctivity-enabled	6,499
12187590	KM 7594-2 FL	93.6 cm wide, five-zone dual PowerFlex Induction cooktop with TwinBoost, frameless design for flush or proud benchtop installation, SmartSelect sensor controls with timers and Stop&Go, two 3-in-1 PowerFlex areas can each be used as two separate, one large or a casserole zone, Con@ctivity-enabled	7,199
12187620	KM 7897-2 FL Diamond	93.6 cm wide, full-surface Induction cooktop with diamond finish coating. TwinBoost, frameless design for flush or proud benchtop installation, SmartSelect White sensor controls with timers and Stop&Go, Con@ctivity-enabled	8,799

Cooktop with integrated extractor

11503460	KMDA 7634 FL	Induction cooktop with flush fit integrated downdraught extractor, 80 cm wide, 4 zone PowerFlex Induction cooktop with TwinBoost, suitable for flush or frameless proud installation, SmartSelect sensor controls with timer and Stop & Go, 3-in-1 PowerFlex areas can be used as two separate, one large or a casserole zone, Integrated downdraught extractor, air flow up to 570 m ³ /h* in programmable booster setting, Con@ctivity enabled, supplied for ducted installation, recirculation operation will require DUU 1000-2 conversion kit	7,899
----------	---------------------	---	--------------

SmartLine CombiSet cooktops

11402680	CS 7101-1 FL	Gas wok burner, 37.8 cm wide, GasStop safety, frameless for flush or proud installation	3,499
11402690	CS 7102-1 FL	2 burner gas cooktop, 37.8 cm wide, GasStop safety, frameless for flush or proud installation	3,699
10787010	CS 7612 FL	Induction cooktop, 37.8 cm wide, 2 cooking zones with integrated TwinBooster and food-warming function, 'on', 'residual heat' and 'booster' indicator lights, frameless for flush or proud installation	3,699

Stainless steel gas cooktops

07111200	KM 2012 G	65 cm wide, 4 burners including wok burner (14.5 MJ/h), stainless steel	1,899
06540270	KM 362-1 G	58.5 cm wide, 4 burners including wok burner (14.4 MJ/h), stainless steel	2,099
09594410	KM 2334 G	77 cm wide, 5 burners including mono wok burner (15.5 MJ/h), solid metal dials, ComfortClean dishwasher safe trivets, flat-fit stainless steel trough design	3,199
09323230	KM 2354 G	88.8 cm wide, low profile design, solid metal dials, 5 burners including dual wok burner (16.0 MJ/h), solid metal knobs, ComfortClean dishwasher safe trivets, flat-fit stainless steel trough design	3,999

Cooking

Ceramic gas cooktops

Item no.	Product	Description	NZD
09209870	KM 3014	62.6 cm wide, 3 burners including high-output dual wok burner (17.0 MJ/h), electro-mechanical controls, ceramic glass with compact stainless steel frame, ComfortClean dishwasher-safe trivets	3,299
10939820	KM 3034-1	80.6 cm wide, 5 burners including centrally positioned high-output dual wok burner (17.0 MJ/h), electronic controls with rapid ignition and switch-off, automatic reignition and minute minder, ceramic glass with raised stainless steel frame, ComfortClean dishwasher-safe trivets	4,299
10939890	KM 3054-1	94.2 cm wide, 5 burners including off-set high-output dual wok burner (17.0 MJ/h), electronic controls with rapid ignition and switch-off, automatic reignition and minute minder, ceramic glass with raised stainless steel frame, ComfortClean dishwasher-safe trivets	4,999

Gas conversion kits**

12285980	CSUG 7101	Gas conversion kit suitable for CS 7101-1
12286020	CSUG 7102	Gas conversion kit suitable for CS 7102-1
12285940	KMUG 2000	Gas conversion kit suitable for KM 2012, KM 2054
12285950	KMUG 2300	Gas conversion kit suitable for KM 2312, KM 2334, KM 2354, KM 2357-1
12285960	KMUG 3000	Gas conversion kit suitable for KM 3014, KM 3034-1, KM 3054-1
12285970	KMUG 362	Gas conversion kit suitable for KM 362-1

Slimline rangehoods

11878390	DAS 2620	60 cm wide, EasySwitch pushbuttons, LED lighting, air flow up to 925 m³/h* in booster setting, Stainless steel	1,599
11878410	DAS 4620	60 cm wide, EasySwitch pushbuttons, Con@activity 3.0, LED lighting, air flow up to 925 m³/h* in programmable booster setting, Stainless steel	2,099
11878420	DAS 4920	90 cm wide, EasySwitch pushbuttons, Con@activity 3.0, LED lighting, air flow up to 925 m³/h* in programmable booster setting, Stainless steel	2,399

Built-in rangehoods

10539540	DA 2360	60 cm wide, extra-slim design, light-touch controls with LEDs, 2 x 3 W LED lights, air flow up to 600 m³/h* in booster setting	2,299
10539550	DA 2390	90 cm wide, extra-slim design, light-touch controls with LEDs, 4 x 3 W LED lights, air flow up to 600 m³/h* in booster setting	2,899
10539530	DA 2450 ▲	53 cm wide, rotary dial controls, 2 x 3 W LED lights, air flow up to 590 m³/h* in booster setting	1,249
12350340	DA 2450-1	53 cm wide, rotary dial controls, 2 x 3 W LED lights, air flow up to 590 m³/h* in booster setting	1,249
10868940	DA 2578	70 cm wide, light-touch electronic controls with LEDs, 2 x 3 W LED lights, air flow up to 600 m³/h* in programmable booster setting, programmable filter saturation indicator	2,499
10868930	DA 2518	110 cm wide, light-touch electronic controls with LEDs, 4 x 3 W LED lights, air flow up to 785 m³/h* in programmable booster setting, programmable filter saturation indicator	4,299
10868970	DA 2668	60 cm wide, extra-slim design, light-touch electronic controls with LEDs, ECO package, 2 x 4.5 W LED lights, stainless steel edge extraction, air flow up to 750 m³/h* in programmable booster setting	3,999
10868980	DA 2698	90 cm wide, extra-slim design, light-touch electronic controls with LEDs, ECO package, 4 x 3 W LED lights, stainless steel edge extraction, air flow up to 890 m³/h* in programmable booster setting	4,899

▲ Limited stock, only available while stocks last.

* Performance data tested under European Standard EN 61591 at the end of a specified ducting run.

**Special order only via online shop or spare parts.

Cooking

Downdraught extractor

Item no.	Product	Description	NZD
12440730	DAD 4941	93.6 cm wide, Intuitive SmartControl touch controls, Hood in motion, Con@tivity, LED lighting, air flow up to 640 m³/h* in booster setting, automatic run-on time, filter saturation indicator	5,699

Wall-mounted décor hoods

10456810	PUR 98 W	90 cm wide, stainless steel casing, light-touch electronic controls with LEDs, 3 x 3 W LED lights, air flow up to 790 m³/h* in programmable booster setting	3,199
----------	-----------------	---	--------------

Island décor hoods

10869030	DA 4248 V	120 cm wide, stainless steel casing, motorised height adjustment, light-touch electronic controls with LEDs, ECO package, Silence package, 4 x 3 W LED lights, air flow up to 820 m³/h* in programmable booster setting, programmable filter saturation indicator	9,799
07377410	DDB 150 *	Ceiling installation spacer, to bridge up to 300 mm of void in suspended ceilings, suitable for DA 4248 V D	299

Control modules

11839890	DSM 408 *	Control module for select rangehoods. Suitable for DAS 2620, 4620, 4920, DA 2578, 2518, 2668, 2698, DA 4248V	252
----------	------------------	--	------------

Oven accessories

10314270	HUB 5001-M	Medium gourmet oven dish, Induction compatible, suits H 2000/H 6000/H 7000 appliances with 76 l oven capacity and DGC 7000 combi steam ovens with 48 l oven capacity (save \$100 when purchased with oven)	508
10314310	HUB 5001-XL	Large oven dish, suits H 2000/H 6000/H 7000 appliances with 76 l oven capacity and DGC 7000 combi steam ovens with 48 l oven capacity (save \$100 when purchased with oven)	738
09520650	HFC 70	1 pair chrome FlexiClip fully telescopic runners, suits 60 cm wide 76 l capacity ovens and Generation 6000 and 7000 Combi steam ovens (save \$100 when purchased with oven)	426
09520660	HFC 71	1 pair PerfectClean FlexiClip fully telescopic runners, suits 60 cm wide 76 l capacity ovens and Generation 6000 and 7000 Combi steam ovens (save \$100 when purchased with oven)	480
09520670	HFC 72	1 pair PyroFit FlexiClip fully telescopic runners, suits 60 cm wide 76 l capacity Pyrolytic ovens (save \$100 when purchased with oven)	555
05136950	HBD 60-22	Stainless steel lid for medium gourmet oven dish, suits HUB 5000 M, HUB 5001 M and HUB 62-22	230
05136960	HBD 60-35	Stainless steel lid for large gourmet oven dish suits HUB 61-35 and HUB 5001 XL	248
05165170	HKL 60 *	Black decor strip, 60 cm wide, suits installation of Microwave, Speed, Steam or Steam combination oven above 60 cm wide H 6000 series Oven	79
07114780	HKL 60 *	CleanSteel décor strip, 60 cm wide, suits installation of Microwave, Speed, Steam or Steam combination oven above 60 cm wide H 6000 series Oven	79
09632220	EBA 6767 *	70 cm built-in adaptor to accommodate a 60 cm wide full-size Oven in a 70 cm wide niche	499
11345870	DS 7003 *	Set of 3 x CleanSteel H 7000 series oven handles, for installation to kitchen cabinet doors or other furniture	320
09520710	HFC 92	1 pair PyroFit FlexiClip fully telescopic runners, suits 90 cm wide H 6000 and H 7000 series Ovens (save \$100 when purchased with oven)	555
11344390	HAL 90 *	90 cm Obsidian Black spacer bar, required for underbench installation of H 2890 B and H 7890 BP	231
11345930	DS 7000 VitroLine Obsidian Black *	Glass inlay H 7000 series oven handle for installation to kitchen cabinet doors or other furniture	425
11345950		Colour variants: VitroLine Graphite Grey *	
11345940		VitroLine Brilliant White *	

* Product available to special order only, estimated delivery time 3 months from date of order.

* Performance data tested under European Standard EN 61591 at the end of a specified ducting run.

Cooking

Rangehood accessories

Item no.	Product	Description	NZD
04623230	DAS 150	Aluminium vent hose for ducting, 60 cm long, 150 mm diameter, supplied in 5 metre pack. Suitable with all Miele rangehoods	230
11258630	DMK 150-1	Wall vent kit for extracting rangehoods, 150 mm, stainless steel grill. Suitable for all Miele rangehoods and KMDA's	399
04623200	DDF 150 *	Roof vent for extraction, for tiled roof with min 22° pitch, stainless steel casing. Suitable for all Miele rangehoods and KMDA's	692
03915292	DKS 150 *	Condensate trap, prevents condensation from re-entering rangehood canopy. Suitable for all Miele rangehoods and KMDA's	195
07294230	DUU 151 Conv. kit for air recirculation	Recirculation box for installation in cupboards, Suitable for DA 2360, 2390, 2450, 2578, 2518, 2668, 2698, 2628	184
11762580	DKF12-P Active charcoal filter	Recirculation filter- suitable for PUR 98 W, DA 399-7, DA 6698 W	160
11762550	DKF15-P Active charcoal filter	Recirculation filter - Suitable for DA 2450, 2578, 2518, 7189 W	206
11762560	DKF19-P Active charcoal filter	Recirculation filter - Suitable for DA 2360, 2390, 2668, 2628	160
11662790	DKF 30-P Active AirClean filter	Filter for DAD 4941	253
11662830	DKF 30-R Longlife AirClean filter	Filter for DAD 4941	772
11793450	DKF31-P Active charcoal filter	Recirculation filter - Suitable for DAS 2620, 4620, 4920, 4630, 4930	172
06264790	DUW20 Conv. kit	Recirculation conversion kit for wall rangehood	126
12185620	DWL80	Strip for downdraft extractors DAD 4941	135
11207310	DUU1000-2 Conv. kit for air recirculation	Recirculation box for installation in plinths	923
Naber Compair rectangular steel ducting [^] Suitable for all Miele Rangehoods and KMDA's			
99501354	SF-VRO 150 *	Flat duct ventilation pipe. 1000 mm length and can be shortened, connection dimensions 216 w x 83 h mm with seal. Comes with 2 SF profile seals, pre-assembled	201
99501362	SF-VRO 150 support *	Support bar for insertion into flat duct SF-VRO 150 for laying in the floor structure, 2 support bars needed for SF-VRO 150. Standing load 100 kg	77
99501356	SF-UR 150 *	Deflector 90°, suitable for flat ducts SF-VRO	139
99501357	SF-RBV 150 *	Pipe bend vertical 90°. With air deflector, suitable for flat ducts SF-VRO	95
99501358	SF-RBH 150 *	Pipe bend horizontal 90°. With air deflector, suitable for flat ducts SF-VRO	107
99501360	SF 150 *	Pipe set for downdraft ventilation. Space-saving arrangement of the exhaust pipes for extractor hoods with downdraft or downdraft ventilation, connection dimensions (222 x 89 mm) for direct connection to the ventilation system, guide direction (left / right) can be varied by repositioning, suitable for flat ducts SF-VRO	224
99501361	SF-VEST 150 *	Offset end piece. Ø 148 mm (connection dimension inside), use when connecting downdraft hoods, suitable for flat ducts SF-VRO	210
99501359	SF-RVB 150 *	Pipe connector. Connector for flat duct pipes, suitable for flat ducts SF-VRO	87
99501355	SF-EST 150 *	End piece. Transition from flat to round, suitable for flat ducts SF-VRO	99
99501405	SF-Profile Seal *	SF profile seal can be adapted to SF-VRO flat duct pipes as well as to the hood connection of the SF-150 pipe set for cooktop extractors	53

* Product available to special order only, estimated delivery time 3 months from date of order.

[^] Naber Compair Steel flow duct components must only be connected to each other or to original Miele rangehood accessories, but never to any other type/ form of ducting, including other types of Naber or other rectangular ducting.

Cooking

Slimline rangehood accessories

Item no.	Product	Description	NZD
11839970	DML 2000 *	Installation set furniture frame. Suitable for DAS 2620, DAS 4620, DAS 4920	172
12185620	DWL 80 *	New angle trim for downdraft extractors - two screws on the angle trim make it easy to adjust the height of the hob to match the downdraft extractor. Suitable for DAD 4840, DAD 4940	135

Wall-mounted décor hood accessories

06847210	DATK 1-760 *	Stainless steel chimney extension for DA 399-7, PUR 98 W, décor hoods, 760 mm long	399
06847220	DATK 2-1000 *	Stainless steel chimney extension for DA 399-7, PUR 98 W, décor hoods, 1,000 mm long	399
12140580	DACW 895 *	Stainless steel chimney extension, ceiling height 600–895 mm. Suitable for PUR 98 W	461
12140570	DACW 1645/1775 *	Stainless steel chimney extension 1325 -1645 mm. Suitable for PUR 98 W	732
12140560	DACW 1325/1455 *	Stainless steel chimney extension, ceiling height 1005-1325 mm. Suitable for PUR 98 W	633

Cooktop accessories

10009310	GGRP	Gourmet griddle plate for a unique grilling experience on Miele Induction cooktops. Ideal for cooktops with PowerFlex. High-quality non-stick coating. Not suitable for gas and electric cooktops	572
11555900	KMTY	Gourmet Tepan Yaki multi-layer stainless-steel plate for preparing light and healthy dishes. Ideal for Miele cooktops with PowerFlex and full-surface induction. Not suitable for gas or electric cooktops	620
11945190	KMTS 5704-2	Fiskars All Steel cookware starter set - is ideal for professional home chefs who appreciate the best tools in the kitchen. Set of 4 pans with satin finish exclusively made for Miele Contents: • Frying pan Ø 28 cm • Saucepan Ø 16 cm, capacity: 1.5 l • Casserole pan Ø 18 cm, capacity 2.5 l • Casserole pan Ø 20 cm, capacity 4.0 l Perfect on Miele induction cooktops. Also suitable for conventional electric and gas cooktops Purchase with any induction cooktop and save \$100	747

CombiSet cooktop accessories

10690630	CSZL 7000 *	SmartLine CombiSet connecting rail for installation of side-by-side units	137
07806500	CSAD 1400 *	Decorative and protective lid for use on 38.8 cm wide CombiSets	726

Refrigeration

Item no.	Product	Description	NZD
Freestanding refrigerators			
11949490	KS 4383 ED edt/cs	CleanSteel, 399 l total volume, DailyFresh freshness system, DynaCool, SuperCool, SideOpen, audible door alarm, ComfortClean, SensorTouch electronic controls, 6 star energy rating, 185 cm h x 60 cm w, suitable side-by-side partner for FNS 4382 E edt/CS	3,199
11949580	KS 4783 ED etc/cs	CleanSteel, 399 l total volume, DailyFresh freshness system, DynaCool, SuperCool, EasyOpen lever handle, audible door alarm, SoftClose, ComfortClean, chrome bottle rack, WiFiConn@ct, SensorTouch electronic controls, 6 star energy rating, 185 cm h x 60 cm w, suitable side-by-side partner for FNS 4782 E edt/CS	3,499
Freestanding freezers			
11953080	FNS 4382 E edt/cs	CleanSteel, 278 l total volume, NoFrost, SuperFreeze, SideOpen, audible door alarm, ComfortClean, SensorTouch electronic controls, 5.5 star energy rating, 185 cm h x 60 cm w, suitable side-by-side partner for KS 4383 ED edt/cs	3,199
11953250	FNS 4782 E edt/cs	CleanSteel, 278 l total volume, NoFrost, SuperFreeze, EasyOpen lever handle, audible door alarm, SoftClose, ComfortClean, WiFiConn@ct, SensorTouch electronic controls, 5.5 star energy rating, 185 cm h x 60 cm w, suitable side-by-side partner for KS 4783 ED etc/cs	3,499
Freestanding fridge / freezer combination			
11949890	KFN 4375 DD edt/cs	CleanSteel, bottom mount freezer, 330 l total volume, DailyFresh freshness system, DuplexCool, DynaCool, SuperCool, SuperFreeze, SideOpen, audible door and temperature alarm, NoFrost, ComfortClean, SensorTouch electronic controls, 185 cm h x 60 cm w, 6 star energy rating, not suitable for side-by-side installation	3,199
Freestanding wine conditioning unit			
09472250	KWT 6831 SG *	Stainless steel model with tinted, tempered glass door, 3 separate temperature zones, 5° - 20° C, 178 bottle capacity, 10 flexible wooden shelves, DynamicCooling, Active charcoal air filter	12,499
Built-under wine conditioning unit			
09850180	KWT 6321 UG	Under bench wine model with tinted tempered glass door, 2 separate zones, 5° - 20° C, 34 bottle capacity, DynaCool, Active AirClean, 3 telescopic wood shelves, LED dimmable lights. KSK 6300 kits required if side-by-side placement	6,249
Wine conditioning unit accessories			
09799630	KSK 6300 *	Side-by-side installation kit required when installing two (or more) built-under Wine conditioning units side-by-side with no gap between units	139
Integrated refrigerators			
11738400	KS 7743 E Fridge	Fully integrated refrigerator, for 178 cm cabinet niche height, 294 l total volume, PerfectFresh Pro, DynaCool, SuperCool, LED lighting, ComfortClean, WiFiConn@ct, SensorTouch electronic controls, White plastic dry wall, 5.5 star energy rating, right hinged (convertible), freely combinable with any K 7000 model	3,499
11738410	KS 7793 D Fridge	Fully integrated refrigerator, for 178 cm cabinet niche height, 294 l total volume, PerfectFresh Active, DynaCool, SuperCool, FlexiLight 2.0 lighting, FlexiTray, SoftClose, ComfortClean, WiFiConn@ct, FreshTouch electronic controls, CleanSteel dry wall, 5.5 star energy rating, right hinged (convertible), freely combinable with any K 7000 model	5,699
Integrated freezers			
11738280	FNS 7740 F Freezer	Fully integrated freezer, for 178 cm cabinet niche height, 213 l total volume, SuperFreeze, NoFrost, WiFiConn@ct, SensorTouch electronic controls, 4 star energy rating, left hinged (convertible), freely combinable with any K 7000 model	3,499
11738290	FNS 7794 E Freezer	Fully integrated freezer, for 178 cm cabinet niche height, 213 l total volume, IceMaker with mains water connection, LED lighting, SuperFreeze, NoFrost, SoftClose, WiFiConn@ct, FreshTouch electronic controls, 4 star energy rating, left hinged (convertible), freely combinable with any K 7000 model	5,699
Integrated fridge / freezer combinations			
12426100	KFNS 7734 D	Fully integrated fridge / freezer, for 178 cm cabinet niche height, 253 l volume, 183 l refrigerator / 70 l freezer, SensorTouch Controls, DailyFresh DynaCool, SuperCool, SuperFreeze, LED Lighting, VarioRoom, white plastic dry wall, 5.5 star energy rating, freely combinable with any K 7000 and K 30000 model, Miele@home	3,799
11738320	KFNS 7784 D	Fully integrated fridge / freezer, for 178 cm cabinet niche height, 254 l total gross volume, 184 l refrigerator / 69 l freezer, FreshTouch Controls, DailyFresh DynaCool, SuperCool, SuperFreeze, FlexiLight 2.0, VarioRoom, SoftClose / SelfClose, FlexiTray, 5.5 star energy rating, freely combinable with any K 7000 and K 30000 model	5,199
11738340	KFNS 7785 D	Fully integrated fridge / freezer, for 178 cm cabinet niche height, 255 l total gross volume, 184 l refrigerator / 70 l freezer, FreshTouch Controls, DailyFresh, DynaCool, SuperCool, SuperFreeze, NoFrost, FlexiLight 2.0, VarioRoom, SoftClose / SelfClose, MyIce with water container, FlexiTray, 5.5 star energy rating, freely combinable with any K 7000 and K 30000 model	5,799
11738390	KFNS 7795 D	Fully integrated fridge / freezer, for 178 cm cabinet niche height, 246 l total gross volume, 175 l refrigerator / 70 l freezer, FreshTouch Controls, PerfectFresh Active, DynaCool, SuperCool, SuperFreeze, NoFrost, FlexiLight 2.0, VarioRoom, SoftClose / SelfClose, IceMaker with mains water connection, FlexiTray, 5.5 star energy rating, freely combinable with any K 7000 and K 30000 model	6,199

* Product available to special order only, estimated delivery time 3 months from date of order.

Refrigeration

Item no.	Product	Description	NZD
MasterCool refrigerators			
10746150	K 2601 Vi *	For 60 cm w x 213.4 cm h cabinet niche, 422 l total volume, Push2open, Pull2open, MasterFresh, BrilliantLight, Drop&Lock shelving, MasterSensor touch controls, DynaCool, 3.5 star energy rating, suitable in side-by-side combination with any MasterCool unit with the use of the KSK 2001 side-by-side installation kit	18,199
12253660	K 2802 Vi *	75 cm w x 213.4 cm h cabinet niche, 467 l total volume, Push2open, Pull2open, MasterFresh, BrilliantLight, Drop&Lock shelving, MasterSensor touch controls, DynaCool, 4.5 star energy rating, suitable in side-by-side combination with any MasterCool unit with the use of the KSK 2001 side-by-side installation kit, Miele@home	18,999
MasterCool freezers			
10746200	F 2671 Vi *	For 213.4 cm cabinet niche, 359 l total volume, Push2open, Pull2open, through-the-door ice and water dispenser, BrilliantLight, Drop&Lock shelving, MasterSensor touch controls, NoFrost, 3 star energy rating, suitable in side-by-side combination with any MasterCool unit with the use of the KSK 2001 side-by-side installation kit	19,249
MasterCool fridge / freezer combinations			
10746490	KF 2981 Vi *	For 213.4 cm cabinet niche, 633 l total volume, FrenchDoor design, Push2open, Pull2open, MasterFresh, BrilliantLight, Drop&Lock shelving, DynaCool, NoFrost, internal ice maker, MasterSensor touch controls, 3.5 star energy rating, suitable in side-by-side combination with any MasterCool unit with the use of the KSK 2001 side-by-side installation kit	20,349
MasterCool wine conditioner			
12253670	KWT 2672 ViS *	For 213.4 cm cabinet niche, 633 l total volume, FrenchDoor design, Push2open, Pull2open, MasterFresh, BrilliantLight, Drop&Lock shelving, DynaCool, NoFrost, internal ice maker, MasterSensor touch controls, 3.5 star energy rating, suitable in side-by-side combination with any MasterCool unit with the use of the KSK 2001 side-by-side installation kit	19,499
MasterCool accessories			
10984120	KSK 2001 *	Side-by-side installation kit required when installing two (or more) MasterCool units side-by-side with a gap of less than 160 mm	1,119
11499620	KFP 2445 ed CS *	CleanSteel panel suitable for F 2671 Vi with provision for ice and water	1,739
10982770	KFP 2404 ed CS *	CleanSteel panel suitable for K 2601 Vi	1,599
11153850	KFP 3634 ed CS L *	CleanSteel panel suitable for KF 2981 Vi - Left door	1,099
10982930	KFP 3634 ed CS R *	CleanSteel panel suitable for KF 2981 Vi - Right door	1,099
10982850	KFP 3624 ed CS *	CleanSteel panel suitable for KF 2981 Vi - Freezer	1,099
11499080	KFP 3005 ed/cs W *	CleanSteel panel suitable for K 2802 Vi	1,799
11499630	KFP 2455 ed/cs W *	CleanSteel panel suitable for KWT 2672 ViS	2,099

Head office

8 College Hill
Freemans Bay, Auckland, 1011

Miele Experience Centre Auckland

8 College Hill
Freemans Bay, Auckland, 1011

Miele Experience Centre Wellington

183 Featherston Street
Wellington, 6011

Miele Experience Centre Christchurch

2 Cathedral Square
Christchurch, 8011

Telephone

0800 4 MIELE (0800 464 353)

www.miele.co.nz

Trading Conditions: Sales transactions are made between Miele New Zealand Ltd. and the end consumer.

Terms and conditions of sale are outlined on the official GST tax invoice.

The Miele Chartered Agent acts on behalf of Miele New Zealand Ltd.

For further information about our products and services please visit our website: www.miele.co.nz

This price list is valid throughout New Zealand as from 15 May 2024.

All prices quoted are in New Zealand Dollars, inclusive of GST. Product availability and prices are subject to change without prior notice.

