

**Miele**

## Dishwasher and Laundry Appliances Price List, New Zealand.

Effective 01.08.2024



Once a Miele,  
**Always a Miele.**

## Washing Machine Specifications

|                                             | WCA 020                                                                           | WWD 164                                                                           | WWD 320                                                                             | WWD 660                                                                             |
|---------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|                                             |  |  |  |  |
| Price                                       | \$1,899                                                                           | \$2,599                                                                           | \$2,599                                                                             | \$2,599                                                                             |
| Item Number                                 | 11636040                                                                          | 12144850                                                                          | 11407240                                                                            | 11621240                                                                            |
| Load Capacity                               | 7 kg                                                                              | 9 kg                                                                              | 8 kg                                                                                | 8 kg                                                                                |
| Door Design                                 | White / Black                                                                     | White / Black                                                                     | White / Black                                                                       | White / Black                                                                       |
| Display Type                                | EasyControl Yellow / 7-segment                                                    | 7 segment DirectSensor Yellow                                                     | 7 segment DirectSensor Yellow                                                       | 7 segment DirectSensor Yellow                                                       |
| Fascia Type                                 | Straight                                                                          | 5° angle                                                                          | 5° angle                                                                            | 5° angle                                                                            |
| Front Panel Construction                    | Co-Laminate                                                                       | Enamel                                                                            | Enamel                                                                              | Enamel                                                                              |
| Installation: Built-Under                   | YES                                                                               | -                                                                                 | -                                                                                   | -                                                                                   |
| Built-Under Kit                             | UBS W1/G                                                                          | -                                                                                 | -                                                                                   | -                                                                                   |
| Water Connection                            | Cold Connection                                                                   | Cold Connection                                                                   | Cold Connection                                                                     | Cold Connection                                                                     |
| Water Protection System                     | WCS <sup>1</sup>                                                                  | WCS <sup>1</sup>                                                                  | WCS <sup>1</sup>                                                                    | WCS <sup>1</sup>                                                                    |
| Wash Programmes                             | 12                                                                                | 12                                                                                | 12                                                                                  | 12                                                                                  |
| Spin Speed                                  | 1400rpm                                                                           | 1400rpm                                                                           | 1400rpm                                                                             | 1400rpm                                                                             |
| CapDosing                                   | YES                                                                               | YES                                                                               | YES                                                                                 | YES                                                                                 |
| TwinDos Automatic Detergent Dispensing      | -                                                                                 | -                                                                                 | -                                                                                   | YES                                                                                 |
| QuickPowerWash Programme (4 kg)             | -                                                                                 | -                                                                                 | YES                                                                                 | -                                                                                   |
| SingleWash                                  | -                                                                                 | -                                                                                 | -                                                                                   | -                                                                                   |
| Stains                                      | -                                                                                 | -                                                                                 | -                                                                                   | -                                                                                   |
| Soak Option                                 | -                                                                                 | -                                                                                 | -                                                                                   | -                                                                                   |
| Extra Quiet Option                          | -                                                                                 | -                                                                                 | -                                                                                   | -                                                                                   |
| Honeycomb Drum                              | YES                                                                               | YES                                                                               | YES                                                                                 | YES                                                                                 |
| SteamCare                                   | -                                                                                 | -                                                                                 | -                                                                                   | -                                                                                   |
| AddLoad                                     | YES                                                                               | YES                                                                               | YES                                                                                 | YES                                                                                 |
| Pre-Ironing                                 | -                                                                                 | YES                                                                               | YES                                                                                 | YES                                                                                 |
| 24 h Delay Start                            | YES                                                                               | YES                                                                               | YES                                                                                 | YES                                                                                 |
| LED Drum Lighting                           | -                                                                                 | -                                                                                 | -                                                                                   | -                                                                                   |
| MultiLingua                                 | -                                                                                 | -                                                                                 | -                                                                                   | -                                                                                   |
| Energy / WELS Star Rating Test Programme    | 4.0 / 4.0<br>Eco 40-60                                                            | 4.5 / 4.5<br>Eco 40-60                                                            | 4.5 / 4.5<br>Cottons <40°C                                                          | 4.5 / 4.5<br>Eco 40-60                                                              |
| WELS Registration Number                    | C01942                                                                            | C02179                                                                            | C01823                                                                              | C01917                                                                              |
| Water l / Wash                              | 68                                                                                | 76                                                                                | 67                                                                                  | 63                                                                                  |
| ECOFeedback                                 | -                                                                                 | -                                                                                 | -                                                                                   | -                                                                                   |
| Miele@home                                  | -                                                                                 | YES                                                                               | -                                                                                   | YES                                                                                 |
| UltraPhase 1 and 2 Included <sup>3</sup>    | -                                                                                 | -                                                                                 | -                                                                                   | YES                                                                                 |
| 6 Months' Supply of UltraPhase <sup>4</sup> | -                                                                                 | -                                                                                 | -                                                                                   | YES                                                                                 |
| CapDos Sample <sup>5</sup>                  | -                                                                                 | -                                                                                 | -                                                                                   | -                                                                                   |

## Matching Tumble Dryers



Highlight indicates difference from model to model within the appliance group. <sup>1</sup>Watercontrol system, <sup>2</sup>Waterproof system. <sup>3</sup>1 supply equals x1 UltraPhase cartridge 1 and x1 UltraPhase cartridge 2 supplied with appliance. <sup>4</sup>6 months' supply UltraPhase voucher redeemable at [www.shop.miele.co.nz](http://www.shop.miele.co.nz). <sup>5</sup>CapDos sample includes WoolCare, Sport, Fabric Softener, supplied with appliance.



## Washing Machine Specifications

|                                             | WWH 860                                                                           | WWI 860                                                                           | WWR 860 WPS                                                                         | WWV 980 WPS                                                                         |
|---------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|                                             |  |  |  |  |
| Price                                       | \$3,399                                                                           | \$3,799                                                                           | \$4,899                                                                             | \$5,699                                                                             |
| Item Number                                 | 11902450                                                                          | 11407370                                                                          | 11420470                                                                            | 11006000                                                                            |
| Load Capacity                               | 8 kg                                                                              | 9 kg                                                                              | 9 kg                                                                                | 9 kg                                                                                |
| Door Design                                 | Chrome / Black                                                                    | Chrome / Black                                                                    | Chrome / White                                                                      | Chrome / Alu Silver                                                                 |
| Display Type                                | ComfortSensor / 1-line, White                                                     | 1 line DirectSensor White                                                         | M Touch                                                                             | M Touch                                                                             |
| Fascia Type                                 | 5° angle                                                                          | 5° angle                                                                          | 5° angle                                                                            | 5° angle                                                                            |
| Front Panel Construction                    | Enamel                                                                            | Enamel                                                                            | Enamel                                                                              | Enamel                                                                              |
| Installation: Built-Under                   | -                                                                                 | -                                                                                 | -                                                                                   | -                                                                                   |
| Built-Under Kit                             | -                                                                                 | -                                                                                 | -                                                                                   | -                                                                                   |
| Water Connection                            | Hot and Cold Connect                                                              | Hot and Cold Connection                                                           | Hot and Cold Connection                                                             | Hot and Cold Connection                                                             |
| Water Protection System                     | WCS <sup>1</sup>                                                                  | WCS <sup>1</sup>                                                                  | WPS <sup>2</sup>                                                                    | WPS <sup>2</sup>                                                                    |
| Wash Programmes                             | 12                                                                                | 22                                                                                | 26                                                                                  | 28                                                                                  |
| Spin Speed                                  | 1400rpm                                                                           | 1600rpm                                                                           | 1600rpm                                                                             | 1600rpm                                                                             |
| CapDosing                                   | YES                                                                               | YES                                                                               | YES                                                                                 | YES                                                                                 |
| TwinDos Automatic Detergent Dispensing      | YES                                                                               | YES                                                                               | YES                                                                                 | YES                                                                                 |
| QuickPowerWash Programme (4 kg)             | YES                                                                               | YES                                                                               | YES                                                                                 | YES                                                                                 |
| SingleWash                                  | YES                                                                               | YES                                                                               | YES                                                                                 | YES                                                                                 |
| Stains                                      | YES                                                                               | YES                                                                               | YES                                                                                 | YES                                                                                 |
| Soak Option                                 | YES                                                                               | YES                                                                               | YES                                                                                 | YES                                                                                 |
| Extra Quiet Option                          | YES                                                                               | YES                                                                               | YES                                                                                 | YES                                                                                 |
| Honeycomb Drum                              | YES                                                                               | YES                                                                               | YES                                                                                 | YES                                                                                 |
| SteamCare                                   | -                                                                                 | -                                                                                 | -                                                                                   | YES                                                                                 |
| AddLoad                                     | YES                                                                               | YES                                                                               | YES                                                                                 | YES                                                                                 |
| Pre-Ironing                                 | YES                                                                               | YES                                                                               | YES                                                                                 | YES                                                                                 |
| 24 h Delay Start                            | YES                                                                               | YES                                                                               | YES                                                                                 | YES                                                                                 |
| LED Drum Lighting                           | -                                                                                 | -                                                                                 | YES                                                                                 | YES                                                                                 |
| MultiLingua                                 | YES                                                                               | YES                                                                               | YES                                                                                 | YES                                                                                 |
| Energy / WELS Star Rating Test Programme    | 4.5 / 4.5<br>ECO 40-60                                                            | 4.5 / 4.5<br>Cottons <40°C                                                        | 5.0 / 5.0<br>Cottons <40°C                                                          | 5.0 / 5.0<br>Cottons <40°C                                                          |
| WELS Registration Number                    | C02037                                                                            | C01821                                                                            | C01765                                                                              | C01667                                                                              |
| Water I / Wash                              | 67                                                                                | 76                                                                                | 76                                                                                  | 76                                                                                  |
| ECOFeedback                                 | -                                                                                 | YES                                                                               | YES                                                                                 | YES                                                                                 |
| Miele@home                                  | YES                                                                               | YES                                                                               | YES                                                                                 | YES                                                                                 |
| UltraPhase 1 and 2 Included <sup>3</sup>    | YES                                                                               | YES                                                                               | YES                                                                                 | YES                                                                                 |
| 6 Months' Supply of UltraPhase <sup>4</sup> | YES                                                                               | YES                                                                               | YES                                                                                 | YES                                                                                 |
| CapDos Sample <sup>5</sup>                  | YES                                                                               | YES                                                                               | YES                                                                                 | YES                                                                                 |

## Matching Tumble Dryers

TWF 720 WP / TWH 780 WP



TWL 780 WP



TWR 780 WP



TWV 780 WP



Highlight indicates difference from model to model within the appliance group. <sup>1</sup>Watercontrol system, <sup>2</sup>Waterproof system. <sup>3</sup>1 supply equals x1 UltraPhase cartridge 1 and x1 UltraPhase cartridge 2 supplied with appliance. <sup>4</sup>6 months' supply UltraPhase voucher redeemable at [www.shop.miele.co.nz](http://www.shop.miele.co.nz). <sup>5</sup>CapDos sample includes WoolCare, Sport, Fabric Softener, supplied with appliance.

## Tumble Dryer Specifications

|                                        | TCA 220 WP                                                                        | TCB 140 WP                                                                        | TWD 364 WP                                                                          | TWD 660 WP                                                                          |
|----------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|                                        |  |  |  |  |
| Price                                  | \$1,999 ■                                                                         | \$2,099 ▲                                                                         | \$2,699                                                                             | \$2,599                                                                             |
| Item Number                            | 12388960                                                                          | 11420330                                                                          | 12210550                                                                            | 11621390                                                                            |
| Load Capacity                          | 7 kg                                                                              | 7 kg                                                                              | 9 kg                                                                                | 8 kg                                                                                |
| Door Design                            | EasyControl yellow / 7-segment                                                    | White solid door, straight front                                                  | White / Black                                                                       | Black / White                                                                       |
| Display Type                           | 7 segment DirectSensor Yellow                                                     | 7 segment DirectSensor Yellow                                                     | 7 segment DirectSensor Yellow                                                       | 7 segment DirectSensor Yellow                                                       |
| Fascia                                 | Straight                                                                          | Straight                                                                          | 5° angle                                                                            | 5° angle                                                                            |
| Front Panel Construction               | Enamel                                                                            | Enamel                                                                            | Enamel                                                                              | Enamel                                                                              |
| SilenceDrum                            | -                                                                                 | -                                                                                 | -                                                                                   | -                                                                                   |
| Installation: Built-Under              | -                                                                                 | YES                                                                               | -                                                                                   | -                                                                                   |
| Reversible Door Hinge                  | -                                                                                 | -                                                                                 | YES                                                                                 | YES                                                                                 |
| Stacking Kit Slim <sup>1</sup>         | WTV 502                                                                           | WTV 501                                                                           | WTV 502                                                                             | WTV 502                                                                             |
| Stacking Kit Drawer <sup>1</sup>       | WTV 511                                                                           | WTV 511                                                                           | WTV 512                                                                             | WTV 512                                                                             |
| ProfiEco Motor                         | -                                                                                 | -                                                                                 | YES                                                                                 | YES                                                                                 |
| Drying Programmes                      | 12                                                                                | 12                                                                                | 12                                                                                  | 12                                                                                  |
| Wash2Dry                               | -                                                                                 | -                                                                                 | YES                                                                                 | YES                                                                                 |
| DryCare 40                             | -                                                                                 | -                                                                                 | -                                                                                   | -                                                                                   |
| HygieneDry                             | -                                                                                 | -                                                                                 | -                                                                                   | -                                                                                   |
| SteamFinish / PowerFresh               | - / -                                                                             | - / -                                                                             | - / -                                                                               | - / -                                                                               |
| DryFresh                               | -                                                                                 | -                                                                                 | -                                                                                   | -                                                                                   |
| AddLoad                                | YES                                                                               | -                                                                                 | YES                                                                                 | YES                                                                                 |
| Pre-Ironing                            | YES                                                                               | YES                                                                               | YES                                                                                 | YES                                                                                 |
| Delay Start                            | YES                                                                               | YES                                                                               | YES                                                                                 | YES                                                                                 |
| Freshen Up Option                      | -                                                                                 | -                                                                                 | -                                                                                   | -                                                                                   |
| Bed Linen Programme                    | YES                                                                               | YES                                                                               | YES                                                                                 | YES                                                                                 |
| FragranceDos                           | Single                                                                            | Single                                                                            | Single                                                                              | Single                                                                              |
| Energy Star Rating                     | 9                                                                                 | 9                                                                                 | 9                                                                                   | 9                                                                                   |
| EcoFeedback                            | -                                                                                 | -                                                                                 | -                                                                                   | -                                                                                   |
| ECO Option                             | -                                                                                 | -                                                                                 | -                                                                                   | -                                                                                   |
| Miele@home                             | -                                                                                 | -                                                                                 | YES                                                                                 | YES                                                                                 |
| Fragrance Flacon Included <sup>2</sup> | YES                                                                               | YES                                                                               | YES                                                                                 | YES                                                                                 |
| Drying Basket Included <sup>3</sup>    | -                                                                                 | -                                                                                 | -                                                                                   | -                                                                                   |

## Matching Washing Machines

| WCA 020                                                                             | WCA 020                                                                             | WWD 164                                                                               | WWD 320 / WWD 660                                                                     |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|  |  |  |  |

Highlight indicates difference from model to model within the appliance group. ■ New model, check availability. ▲ Limited stock, only available while stocks last.

<sup>1</sup>Stacking kit for matching washing machine. <sup>2</sup>1 supply of Aqua Fragrance Flacon with appliance. <sup>3</sup>Supply of TRK 555 with appliance.

## Tumble Dryer Specifications

|                                              | TWF 720 WP                                                                        | TWH 780 WP                                                                        | TWL 780 WP                                                                         | TWR 780 WP                                                                          | TWV 780 WP                                                                          |
|----------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|                                              |  |  |  |  |  |
| <b>Price</b>                                 | <b>\$3,399</b>                                                                    | <b>\$3,599</b>                                                                    | <b>\$4,199</b>                                                                     | <b>\$5,399</b>                                                                      | <b>\$5,799</b>                                                                      |
| <b>Item Number</b>                           | 11493720                                                                          | 11905900                                                                          | 11905910                                                                           | 11905920                                                                            | 11905930                                                                            |
| <b>Load Capacity</b>                         | 8 kg                                                                              | 9 kg                                                                              | 9 kg                                                                               | 9 kg                                                                                | 9 kg                                                                                |
| <b>Door Design</b>                           | Chrome / Black                                                                    | Chrome, inner ring Black                                                          | Chrome, inner ring Black                                                           | Outer ring high-gloss chrome, inner ring White                                      | Outer ring high-gloss chrome, inner ring Silver                                     |
| <b>Display Type</b>                          | 7 segment DirectSensor White                                                      | 7 segment DirectSensor White                                                      | 1 line ComfortSensor White                                                         | M Touch                                                                             | M Touch                                                                             |
| <b>Fascia</b>                                | 5° angle                                                                          | 5° angle                                                                          | 5° angle                                                                           | 5° angle                                                                            | 5° angle                                                                            |
| <b>Front Panel Construction</b>              | Enamel                                                                            | Enamel                                                                            | Enamel                                                                             | Enamel                                                                              | Enamel                                                                              |
| <b>SilenceDrum</b>                           | -                                                                                 | YES                                                                               | YES                                                                                | YES                                                                                 | YES                                                                                 |
| <b>Installation: Built-Under</b>             | -                                                                                 | -                                                                                 | -                                                                                  | -                                                                                   | -                                                                                   |
| <b>Reversible Door Hinge</b>                 | YES                                                                               | YES                                                                               | YES                                                                                | YES                                                                                 | YES                                                                                 |
| <b>Stacking Kit Slim<sup>1</sup></b>         | WTV 502                                                                           | WTV 502                                                                           | WTV 502                                                                            | WTV 502                                                                             | WTV 502                                                                             |
| <b>Stacking Kit Drawer<sup>1</sup></b>       | WTV 512                                                                           | WTV 512                                                                           | WTV 512                                                                            | WTV 512                                                                             | WTV 512                                                                             |
| <b>ProfiEco Motor</b>                        | YES                                                                               | YES                                                                               | YES                                                                                | YES                                                                                 | YES                                                                                 |
| <b>Drying Programmes</b>                     | 12                                                                                | 12                                                                                | 22                                                                                 | 22                                                                                  | 23                                                                                  |
| <b>Wash2Dry</b>                              | -                                                                                 | YES                                                                               | YES                                                                                | YES                                                                                 | YES                                                                                 |
| <b>DryCare 40</b>                            | -                                                                                 | YES                                                                               | YES                                                                                | YES                                                                                 | YES                                                                                 |
| <b>HygieneDry</b>                            | -                                                                                 | YES                                                                               | YES                                                                                | YES                                                                                 | YES                                                                                 |
| <b>SteamFinish / PowerFresh</b>              | - / -                                                                             | - / -                                                                             | YES / YES                                                                          | YES / YES                                                                           | YES / YES                                                                           |
| <b>DryFresh</b>                              | -                                                                                 | YES                                                                               | YES                                                                                | YES                                                                                 | YES                                                                                 |
| <b>AddLoad</b>                               | YES                                                                               | YES                                                                               | YES                                                                                | YES                                                                                 | YES                                                                                 |
| <b>Pre-Ironing</b>                           | YES                                                                               | YES                                                                               | YES                                                                                | YES                                                                                 | YES                                                                                 |
| <b>Delay Start</b>                           | YES                                                                               | YES                                                                               | YES                                                                                | YES                                                                                 | YES                                                                                 |
| <b>Freshen Up Option</b>                     | -                                                                                 | -                                                                                 | -                                                                                  | YES                                                                                 | YES                                                                                 |
| <b>Bed Linen Programme</b>                   | YES                                                                               | YES                                                                               | YES                                                                                | YES                                                                                 | YES                                                                                 |
| <b>FragranceDos</b>                          | Double                                                                            | Double                                                                            | Double                                                                             | Double                                                                              | Double                                                                              |
| <b>Energy Star Rating</b>                    | 10                                                                                | 10                                                                                | 10                                                                                 | 10                                                                                  | 10                                                                                  |
| <b>EcoFeedback</b>                           | -                                                                                 | YES                                                                               | YES                                                                                | YES                                                                                 | YES                                                                                 |
| <b>ECO Option</b>                            | -                                                                                 | -                                                                                 | -                                                                                  | -                                                                                   | YES                                                                                 |
| <b>Miele@home</b>                            | -                                                                                 | YES                                                                               | YES                                                                                | YES                                                                                 | YES                                                                                 |
| <b>Fragrance Flacon Included<sup>2</sup></b> | YES                                                                               | YES                                                                               | YES                                                                                | YES                                                                                 | YES                                                                                 |
| <b>Drying Basket Included<sup>3</sup></b>    | -                                                                                 | -                                                                                 | -                                                                                  | -                                                                                   | YES                                                                                 |

## Matching Washing Machines



Highlight indicates difference from model to model within the appliance group. <sup>1</sup>Stacking kit for matching washing machine. <sup>2</sup>1 supply of Aqua Fragrance Flacon with appliance. <sup>3</sup>Supply of TRK 555 with appliance.

# Miele

Package Prices - **Save \$200** when any Miele washing machine and dryer are bought as a package.<sup>1</sup>

## Package 1



WCA 020 + TCA 220 WP

**Save \$200**

**Now \$3,698**

## Package 2



WCA 020 + TCB 140 WP

**Save \$200**

**Now \$3,798**

## Package 3



WWD 164 + TWD 364 WP

**Save \$200**

**Now \$5,098**

## Package 4



WWD 320 + TWD 660 WP

**Save \$200**

**Now \$4,998**

## Package 5



WWD 660 + TWD 660 WP

**Save \$200**

**Now \$4,998**

## Package 6



WWH 860 + TWF 720 WP

**Save \$200**

**Now \$6,598**

## Package 7



WWH 860 + TWH 780 WP

**Save \$200**

**Now \$6,798**

## Package 8



WWI 860 + TWL 780 WP

**Save \$200**

**Now \$7,798**

## Package 9



WWR 860 + TWR 780 WP

**Save \$200**

**Now \$10,098**

## Package 10



WWV 980 + TWV 780 WP

**Save \$200**

**Now \$11,298**

<sup>1</sup>Effective from 1 August 2024. Customers have up to 90 days from date of purchase of their washing machine to purchase the matching tumble dryer at the package price saving. Saving applies to tumble dryer model purchased. Non-matching Miele washing machine and tumble dryer packages can be purchased.

## Washer Dryer Specifications

WTD 160 WCS



WTR 870 WPM



WTW 870 WPM



|                                                            |                                   |                                                         |                                                         |
|------------------------------------------------------------|-----------------------------------|---------------------------------------------------------|---------------------------------------------------------|
| Price                                                      | \$3,699                           | \$4,899                                                 | \$5,399 ▲                                               |
| Item Number                                                | 11679820                          | 11679830                                                | 11679840                                                |
| Load Capacity                                              | 8 kg Washing / 4 kg Drying        | 8 kg Washing / 4 kg Drying                              | 9 kg Washing / 5 kg Drying                              |
| Installation: Built-Under (82 cm) / Slot-in / Stackable    | YES / YES / YES                   | - / YES / YES                                           | - / - / -                                               |
| Door Design                                                | White / Graphite Grey PearlFinish | White / Chrome                                          | White / Chrome                                          |
| Fascia Type                                                | Straight                          | Slanted                                                 | Slanted                                                 |
| Display Type                                               | DirectSensor White                | M Touch                                                 | M Touch                                                 |
| Stainless Steel Suds Container                             | YES                               | YES                                                     | YES                                                     |
| ProfiEco Motor                                             | YES                               | YES                                                     | YES                                                     |
| Enamel Front Panel Coating                                 | YES                               | YES                                                     | YES                                                     |
| Water Protection System                                    | WCS <sup>1</sup>                  | WPM <sup>2</sup>                                        | WPM <sup>2</sup>                                        |
| Wash Programmes                                            | 11                                | 29                                                      | 29                                                      |
| Drying Programmes                                          | 8                                 | 21                                                      | 21                                                      |
| Spin Speed                                                 | 1500rpm                           | 1600rpm                                                 | 1600rpm                                                 |
| CapDosing                                                  | -                                 | YES                                                     | YES                                                     |
| Single Wash&Dry                                            | -                                 | YES                                                     | YES                                                     |
| QuickPower (4 kg Capacity)                                 | -                                 | Wash (49 min) / Dry <sup>3</sup> / Wash&Dry (2h 59 min) | Wash (49 min) / Dry <sup>3</sup> / Wash&Dry (2h 59 min) |
| TwinDos Automatic Detergent Dispensing                     | -                                 | YES                                                     | YES                                                     |
| Honeycomb Drum                                             | YES                               | YES                                                     | YES                                                     |
| SteamCare / Anti-Crease                                    | - / YES                           | YES / YES                                               | YES / YES                                               |
| AddLoad (Washing ONLY)                                     | YES                               | YES                                                     | YES                                                     |
| 24 hr Delay Start / Countdown Indicator / Buzzer           | YES / YES / -                     | YES / YES / YES                                         | YES / YES / YES                                         |
| Time of Day Display / LED Drum Lighting                    | - / -                             | YES / YES                                               | YES / YES                                               |
| Load indicator (3D Sensor)                                 | -                                 | -                                                       | YES                                                     |
| WashDry Assistant                                          | -                                 | YES                                                     | YES                                                     |
| PerfectCare Technology                                     | YES                               | YES                                                     | YES                                                     |
| Energy Star Rating - Washing / Energy Star Rating - Drying | 4.5 / 4.0                         | 4.5 / 4.5                                               | 5.0 / 4.5                                               |
| WELS Star Rating                                           | 4.5                               | 4.5                                                     | 4.5                                                     |
| WELS Registration Number                                   | C02014                            | C02013                                                  | C02018                                                  |
| Test Programme                                             | Eco 40-60 Programme               | Eco 40-60 Programme                                     | Eco 40-60 Programme                                     |
| Water Consumption in l / Wash                              | 67                                | 67                                                      | 76                                                      |
| Additional Water Used for Drying                           | 21                                | 21                                                      | 25                                                      |
| Dryer Type                                                 | Condenser                         | Condenser                                               | Condenser                                               |
| Miele@home                                                 | YES                               | YES                                                     | YES                                                     |
| UltraPhase 1 and 2 Included <sup>4</sup>                   | -                                 | YES                                                     | YES                                                     |
| 6 Months' Supply of UltraPhase <sup>5</sup>                | -                                 | YES                                                     | YES                                                     |
| CapDos Sample <sup>6</sup>                                 | -                                 | YES                                                     | YES                                                     |

Highlight indicates difference from model to model within the appliance group. ▲ Limited stock, only available while stocks last. <sup>1</sup>Watercontrol system, <sup>2</sup>Waterproof metal.

<sup>3</sup>QuickPower Dry programme can follow any wash programme, therefore the timing will vary depending on residual moisture content of load. <sup>4</sup>UltraPhase 1 and 2 included.

<sup>5</sup>6 months' supply of UltraPhase. <sup>6</sup>CapDos Sample.

## FashionMaster and Laundry Accessories

### Steam ironing system

| Item no. | Product                     | Description                                                                                                                                                                                                             | NZD          |
|----------|-----------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------|
| 11977970 | <b>B 4847 FashionMaster</b> | Steam iron with Honeycomb soleplate, Single line display, Steam Jet, 4 Bar steam pressure, Active ironing table, 1-2 Lift system, Infinite Height adjustment to 102 cm, Large ironing table with Comfort Zone, Auto-Off | <b>3,499</b> |

### Washing machine and tumble dryer accessories

| Laundry accessories |                      |                                                                                                                                                    |              |
|---------------------|----------------------|----------------------------------------------------------------------------------------------------------------------------------------------------|--------------|
| 09709940            | <b>UBS W1/G</b>      | Built-under kit, suits WCA, WCD and WCG washing machine models                                                                                     | <b>145</b>   |
| 09710050            | <b>UBS T1/G</b>      | Built-under kit, suits TCB, TCD tumble dryer models                                                                                                | <b>145</b>   |
| 09256130            | <b>WTV 501</b>       | Slim stacking kit (2.5 cm) suits washing machines and tumble dryers as per below table                                                             | <b>159</b>   |
| 09256140            | <b>WTV 502</b>       | Slim stacking kit (2.5 cm) for use with washing machines and tumble dryers as per table below                                                      | <b>159</b>   |
| 06667550            | <b>WTV 412</b>       | Stacking kit, without drawer, suits washing machines and tumble dryers as per below table                                                          | <b>159</b>   |
| 09351780            | <b>WTV 511</b>       | Stacking kit (12 cm), suits washing machines and tumble dryers as per table below, with push-pull drawer and non-slip liner for additional storage | <b>319</b>   |
| 09351790            | <b>WTV 512</b>       | Stacking kit with drawer (12 cm) for use with washing machines and tumble dryers as per table below                                                | <b>319</b>   |
| 09614800            | <b>TRK 555</b>       | Dryer basket for T1 series dryers to facilitate drying of textiles and items that tolerate drying but not tumbling action                          | <b>145</b>   |
| 10223070            | <b>UP1 cartridge</b> | Empty cartridge for TwinDos washing machines for use with Miele or conventional liquid detergent or fabric softener                                | <b>40.45</b> |
| 10223120            | <b>UP2 cartridge</b> | Empty cartridge for TwinDos washing machines for use with Miele or conventional liquid detergent or fabric softener                                | <b>40.45</b> |

### Stacking kit compatibility chart

|                                                                                                                                                                                                                                      |                                                                                                                                                                   | Tumble Dryers                                                                    |           |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------|-----------|
|                                                                                                                                                                                                                                      |                                                                                                                                                                   | T1 and T1 Classic                                                                | T Classic |
| <b>Washing Machines</b>                                                                                                                                                                                                              | <b>T1 Series</b><br>TWB 140 / TWD 440 / TWF 720<br>TWJ 660 / TWR 860 / TMV 840<br>TMR 840 / TWV 680 / TWD 660<br>TWC 220 / TWH 780 / TWL 780<br>TWR 780 / TWV 780 | TDB 130 / TDD 130<br>TCE 630 / TCJ 690<br>TCR 870 / TCB 140<br>TEA 235 / TCA 220 | TDA 150 C |
| <b>W1 Series</b><br>WMV 960 / WMR 861<br>WWV 980<br><br><b>W1 and W1 Classic</b><br>WWD 320<br>WWI 860 / WWR 860<br>WCE 330 / WCE 670<br>WCI 670 / WDB 030<br>WDD 030 / WCR 870<br>WCR 890 / WCA 020<br>WWD 660 / WCD 660<br>WWH 860 | WTV 502<br>WTV 512                                                                                                                                                | WTV 501<br>WTV 511                                                               | WTV 412   |



## Dishwasher Specifications - Freestanding

**G 5000 SC CLST**



**G 5210 SC CLST**



**G 7130 SC CLST**



|                                                                                                   |                              |                             |                             |
|---------------------------------------------------------------------------------------------------|------------------------------|-----------------------------|-----------------------------|
| <b>Price</b>                                                                                      | <b>\$1,899</b>               | <b>\$2,199</b>              | <b>\$2,799 ■</b>            |
| <b>Item Number</b>                                                                                | 11587510                     | 11587590                    | 12531610                    |
| <b>Colour</b>                                                                                     | CleanSteel                   | CleanSteel                  | CleanSteel                  |
| <b>Place Settings</b>                                                                             | 14                           | 14                          | 14                          |
| <b>Basket Design</b>                                                                              | Comfort Baskets              | Comfort Baskets             | ExtraComfort                |
| <b>Cutlery Basket (BK)</b>                                                                        | -                            | -                           | -                           |
| <b>Cutlery Tray (SC)</b>                                                                          | Fixed cutlery tray           | 3D MultiFlex Tray           | 3D MultiFlex Tray           |
| <b>Wash Programmes</b>                                                                            | 5                            | 5                           | 8                           |
| <b>Display Type</b>                                                                               | 7-segment<br>Yellow display) | 7-segment<br>Yellow display | 1-line text display         |
| <b>AutoDos Automatic Detergent Dispensing</b>                                                     | -                            | -                           | YES                         |
| <b>AutoStart Function</b>                                                                         | -                            | -                           | YES                         |
| <b>Delay Start</b>                                                                                | -                            | -                           | YES                         |
| <b>EcoFeedback</b>                                                                                | -                            | -                           | YES                         |
| <b>AutoOpen Drying</b>                                                                            | -                            | YES                         | YES                         |
| <b>AutoClose</b>                                                                                  | -                            | -                           | -                           |
| <b>Brilliant LED Light</b>                                                                        | -                            | -                           | -                           |
| <b>Knock2Open (K2O)</b>                                                                           | -                            | -                           | -                           |
| <b>Operation Noise</b>                                                                            | 46 (db)                      | 46 (db)                     | 43 (db)                     |
| <b>Wash Extras / Options:<br/>Express / ExtraClean / ExtraDry /<br/>IntenseZone / Bottle Wash</b> | YES / YES / YES / - / -      | YES / YES / YES / - / -     | YES / YES / YES / YES / YES |
| <b>MultiLingua</b>                                                                                | -                            | -                           | YES                         |
| <b>Triple Spray Arms / Alternating Action</b>                                                     | YES                          | YES                         | YES                         |
| <b>QuickPowerWash</b>                                                                             | YES                          | YES                         | YES                         |
| <b>Brilliant GlassCare</b>                                                                        | -                            | YES                         | YES                         |
| <b>EcoPower Technology</b>                                                                        | YES                          | YES                         | YES                         |
| <b>Energy Star Rating</b>                                                                         | 4                            | 4                           | 4.5                         |
| <b>WELS Star Rating</b>                                                                           | 6                            | 6                           | 6                           |
| <b>WELS Registration Number</b>                                                                   | D02487                       | D02491                      | D02879                      |
| <b>Water Consumption in l / Wash</b>                                                              | 9.2                          | 9.2                         | 9.3                         |
| <b>Test Programme Used</b>                                                                        | ECO                          | ECO                         | ECO                         |
| <b>Miele@home</b>                                                                                 | -                            | -                           | YES                         |
| <b>1 Month Supply of UltraTabs All in 1<sup>1</sup></b>                                           | YES                          | YES                         | -                           |
| <b>1 Month Supply of PowerDisk<sup>2</sup></b>                                                    | -                            | -                           | YES                         |
| <b>6 Months Supply of PowerDisk<sup>3</sup></b>                                                   | -                            | -                           | YES                         |

Highlight indicates difference from model to model within the appliance group. ■ New model, check availability. <sup>1</sup>1 month supply equals 20 UltraTab All-in-1 tablets. <sup>2</sup>1 month supply equals 1 PowerDisk cartridge. <sup>3</sup>6 months' supply PowerDisk voucher redeemable at [www.shop.miele.co.nz](http://www.shop.miele.co.nz).

## Dishwasher Specifications - Built-Under

**G 5000 SCU CLST**



**G 5210 SCU CLST**



|                                                                                                   |                             |                             |
|---------------------------------------------------------------------------------------------------|-----------------------------|-----------------------------|
| <b>Price</b>                                                                                      | <b>\$1,999</b>              | <b>\$2,499</b>              |
| <b>Item Number</b>                                                                                | 11587530                    | 11587610                    |
| <b>Colour</b>                                                                                     | CleanSteel                  | CleanSteel                  |
| <b>Place Settings</b>                                                                             | 14                          | 14                          |
| <b>Basket Design</b>                                                                              | Comfort Baskets             | Comfort Baskets             |
| <b>Cutlery Basket (BK)</b>                                                                        | YES                         | -                           |
| <b>Cutlery Tray (SC)</b>                                                                          | -                           | 3D MultiFlex Tray           |
| <b>Wash Programmes</b>                                                                            | 5                           | 5                           |
| <b>Display Type</b>                                                                               | 7-segment<br>Yellow display | 7-segment<br>Yellow display |
| <b>AutoDos Automatic Detergent Dispensing</b>                                                     | -                           | -                           |
| <b>AutoStart Function</b>                                                                         | -                           | -                           |
| <b>Delay Start</b>                                                                                | -                           | -                           |
| <b>EcoFeedback</b>                                                                                | -                           | -                           |
| <b>AutoOpen Drying</b>                                                                            | -                           | YES                         |
| <b>AutoClose</b>                                                                                  | -                           | -                           |
| <b>Brilliant LED Light</b>                                                                        | -                           | -                           |
| <b>Knock2Open (K2O)</b>                                                                           | -                           | -                           |
| <b>Operation Noise</b>                                                                            | 46 (db)                     | 46 (db)                     |
| <b>Wash Extras / Options:<br/>Express / ExtraClean / ExtraDry /<br/>IntenseZone / Bottle Wash</b> | YES / YES / YES / - / -     | YES / YES / YES / - / -     |
| <b>MultiLingua</b>                                                                                | -                           | -                           |
| <b>Triple Spray Arms / Alternating Action</b>                                                     | YES                         | YES                         |
| <b>QuickPowerWash</b>                                                                             | YES                         | YES                         |
| <b>Brilliant GlassCare</b>                                                                        | -                           | YES                         |
| <b>EcoPower Technology</b>                                                                        | YES                         | YES                         |
| <b>Energy Star Rating</b>                                                                         | 4                           | 4                           |
| <b>WELS Star Rating</b>                                                                           | 6                           | 6                           |
| <b>WELS Registration Number</b>                                                                   | D02488                      | D02492                      |
| <b>Water Consumption in l / Wash</b>                                                              | 9.2                         | 9.2                         |
| <b>Test Programme Used</b>                                                                        | ECO                         | ECO                         |
| <b>Miele@home</b>                                                                                 | -                           | -                           |
| <b>1 Month Supply of UltraTabs All in 1<sup>1</sup></b>                                           | YES                         | YES                         |
| <b>1 Month Supply of PowerDisk<sup>2</sup></b>                                                    | -                           | -                           |
| <b>6 Months Supply of PowerDisk<sup>3</sup></b>                                                   | -                           | -                           |

## Dishwasher Specifications - Built-Under

G 7130 SCU CLST



G 7604 SCU CLST



G 7609 SCU XXL CLST



|                                                                                    |                             |                                       |                                       |
|------------------------------------------------------------------------------------|-----------------------------|---------------------------------------|---------------------------------------|
| Price                                                                              | \$2,999 ■                   | \$3,199 ■                             | \$3,499 ■                             |
| Item Number                                                                        | 12531620                    | 12531670                              | 12531680                              |
| Colour                                                                             | CleanSteel                  | CleanSteel with Obsidian Black Fascia | CleanSteel with Obsidian Black Fascia |
| Place Settings                                                                     | 14                          | 14                                    | 15                                    |
| Basket Design                                                                      | ExtraComfort                | ExtraComfort                          | ExtraComfort                          |
| Cutlery Basket (BK)                                                                | -                           | -                                     | -                                     |
| Cutlery Tray (SC)                                                                  | 3D MultiFlex Tray           | 3D MultiFlex Tray                     | 3D MultiFlex Tray                     |
| Wash Programmes                                                                    | 8                           | 10                                    | 10                                    |
| Display Type                                                                       | 1-line text display         | 1-line text display                   | 1-line text display                   |
| AutoDos Automatic Detergent Dispensing                                             | YES                         | YES                                   | YES                                   |
| AutoStart Function                                                                 | YES                         | YES                                   | YES                                   |
| Delay Start                                                                        | YES                         | YES                                   | YES                                   |
| EcoFeedback                                                                        | YES                         | YES                                   | YES                                   |
| AutoOpen Drying                                                                    | YES                         | YES                                   | YES                                   |
| AutoClose                                                                          | -                           | -                                     | -                                     |
| Brilliant LED Light                                                                | -                           | -                                     | -                                     |
| Knock2Open (K2O)                                                                   | -                           | -                                     | -                                     |
| Operation Noise                                                                    | 43 (db)                     | 42 (db)                               | 42 (db)                               |
| Wash Extras / Options: Express / ExtraClean / ExtraDry / IntenseZone / Bottle Wash | YES / YES / YES / YES / YES | YES / YES / YES / YES / YES           | YES / YES / YES / YES / YES           |
| MultiLingua                                                                        | YES                         | YES                                   | YES                                   |
| Triple Spray Arms / Alternating Action                                             | YES                         | YES                                   | YES                                   |
| QuickPowerWash                                                                     | YES                         | YES                                   | YES                                   |
| Brilliant GlassCare                                                                | YES                         | YES                                   | YES                                   |
| EcoPower Technology                                                                | YES                         | YES                                   | YES                                   |
| Energy Star Rating                                                                 | 4.5                         | 4.5                                   | 4.5                                   |
| WELS Star Rating                                                                   | 6                           | 6                                     | 6                                     |
| WELS Registration Number                                                           | D02880                      | D02883                                | D02885                                |
| Water Consumption in l / Wash                                                      | 9.3                         | 9.3                                   | 9.6                                   |
| Test Programme Used                                                                | ECO                         | ECO                                   | ECO                                   |
| Miele@home                                                                         | YES                         | YES                                   | YES                                   |
| 1 Month Supply of UltraTabs All in 1 <sup>1</sup>                                  | -                           | -                                     | -                                     |
| 1 Month Supply of PowerDisk <sup>2</sup>                                           | YES                         | YES                                   | YES                                   |
| 6 Months Supply of PowerDisk <sup>3</sup>                                          | YES                         | YES                                   | YES                                   |

Highlight indicates difference from model to model within the appliance group. ■ New model, check availability. <sup>1</sup>1 month supply equals 20 UltraTab All-in-1 tablets. <sup>2</sup>1 month supply equals 1 PowerDisk cartridge. <sup>3</sup>6 months' supply PowerDisk voucher redeemable at [www.shop.miele.co.nz](http://www.shop.miele.co.nz).

## Dishwasher Specifications - Integrated

G 7130 SCi CLST



G 7609 SCi XXL



G 7719 SCi XXL



|                                                                                          |                             |                                       |                             |
|------------------------------------------------------------------------------------------|-----------------------------|---------------------------------------|-----------------------------|
| Price                                                                                    | \$2,999 ■                   | \$3,499 ■                             | \$3,999 ■                   |
| Item Number                                                                              | 12531640                    | 12531690                              | 12531710                    |
| Colour                                                                                   | CleanSteel Fascia           | CleanSteel with Obsidian Black Fascia | Obsidian Black Fascia       |
| Place Settings                                                                           | 14                          | 15                                    | 15                          |
| Basket Design                                                                            | ExtraComfort                | ExtraComfort                          | MaxiComfort                 |
| Cutlery Basket (BK)                                                                      | -                           | -                                     | -                           |
| Cutlery Tray (SC)                                                                        | 3D MultiFlex Tray           | 3D MultiFlex Tray                     | 3D MultiFlex Tray           |
| Wash Programmes                                                                          | 8                           | 10                                    | 13                          |
| Display Type                                                                             | 1-line text display         | 1-line text display                   | 1-line text display         |
| AutoDos Automatic Detergent Dispensing                                                   | YES                         | YES                                   | YES                         |
| AutoStart Function                                                                       | YES                         | YES                                   | YES                         |
| Delay Start                                                                              | YES                         | YES                                   | YES                         |
| EcoFeedback                                                                              | YES                         | YES                                   | YES                         |
| AutoOpen Drying                                                                          | YES                         | YES                                   | YES                         |
| AutoClose                                                                                | -                           | -                                     | -                           |
| Brilliant LED Light                                                                      | -                           | -                                     | YES                         |
| Knock2Open (K2O)                                                                         | -                           | -                                     | -                           |
| Operation Noise                                                                          | 43 (db)                     | 42 (db)                               | 42 (db)                     |
| Wash Extras / Options:<br>Express / ExtraClean / ExtraDry /<br>IntenseZone / Bottle Wash | YES / YES / YES / YES / YES | YES / YES / YES / YES / YES           | YES / YES / YES / YES / YES |
| Multilingual                                                                             | YES                         | YES                                   | YES                         |
| Triple Spray Arms / Alternating Action                                                   | YES                         | YES                                   | YES                         |
| QuickPowerWash                                                                           | YES                         | YES                                   | YES                         |
| Brilliant GlassCare                                                                      | YES                         | YES                                   | YES                         |
| EcoPower Technology                                                                      | YES                         | YES                                   | YES                         |
| Energy Star Rating                                                                       | 4.5                         | 4.5                                   | 4.5                         |
| WELS Star Rating                                                                         | 6                           | 6                                     | 6                           |
| WELS Registration Number                                                                 | D02881                      | D02886                                | D02888                      |
| Water Consumption in l / Wash                                                            | 9.3                         | 9.6                                   | 9.6                         |
| Test Programme Used                                                                      | ECO                         | ECO                                   | ECO                         |
| Miele@home                                                                               | YES                         | YES                                   | YES                         |
| 1 Month Supply of UltraTabs All in 1 <sup>1</sup>                                        | -                           | -                                     | -                           |
| 1 Month Supply of PowerDisk <sup>2</sup>                                                 | YES                         | YES                                   | YES                         |
| 6 Months Supply of PowerDisk <sup>3</sup>                                                | YES                         | YES                                   | YES                         |

Highlight indicates difference from model to model within the appliance group. ■ New model, check availability. <sup>1</sup>1 month supply equals 20 UltraTab All-in-1 tablets.

<sup>2</sup>1 month supply equals 1 PowerDisk cartridge. <sup>3</sup>6 months' supply PowerDisk voucher redeemable at [www.shop.miele.co.nz](http://www.shop.miele.co.nz).



## Dishwasher Specifications - Fully Integrated

**G 5481 SCVi  
(45 cm model)**



**G 5263 SCVi BK**



**G 7180 SCVi**



|                                                                                                   |                             |                             |                                |
|---------------------------------------------------------------------------------------------------|-----------------------------|-----------------------------|--------------------------------|
| <b>Price</b>                                                                                      | <b>\$2,399</b>              | <b>\$2,699</b>              | <b>\$3,299 ■</b>               |
| <b>Item Number</b>                                                                                | 11587660                    | 11587640                    | 12531650                       |
| <b>Colour</b>                                                                                     | CleanSteel                  | CleanSteel                  | CleanSteel                     |
| <b>Place Settings</b>                                                                             | 10                          | 14                          | 14                             |
| <b>Basket Design</b>                                                                              | Comfort Baskets             | Comfort Baskets             | ExtraComfort                   |
| <b>Cutlery Basket (BK)</b>                                                                        | -                           | YES                         | -                              |
| <b>Cutlery Tray (SC)</b>                                                                          | Fixed Cutlery Tray          | 3D MultiFlex Tray           | 3D MultiFlex Tray              |
| <b>Wash Programmes</b>                                                                            | 5                           | 5                           | 8                              |
| <b>Display Type</b>                                                                               | 7-segment<br>Yellow display | 7-segment<br>Yellow display | 1-line text display            |
| <b>AutoDos Automatic<br/>Detergent Dispensing</b>                                                 | -                           | -                           | YES                            |
| <b>AutoStart Function</b>                                                                         | -                           | -                           | YES                            |
| <b>Delay Start</b>                                                                                | -                           | -                           | YES                            |
| <b>EcoFeedback</b>                                                                                | -                           | -                           | YES                            |
| <b>AutoOpen Drying</b>                                                                            | -                           | YES                         | YES                            |
| <b>AutoClose</b>                                                                                  | -                           | -                           | -                              |
| <b>Brilliant LED Light</b>                                                                        | -                           | -                           | -                              |
| <b>Knock2Open (K2O)</b>                                                                           | -                           | -                           | -                              |
| <b>Operation Noise</b>                                                                            | 46 (db)                     | 46 (db)                     | 43 (db)                        |
| <b>Wash Extras / Options:<br/>Express / ExtraClean / ExtraDry /<br/>IntenseZone / Bottle Wash</b> | YES / YES / YES / - / -     | YES / YES / YES / - / -     | YES / YES / YES /<br>YES / YES |
| <b>MultiLingua</b>                                                                                | -                           | -                           | YES                            |
| <b>Triple Spray Arms / Alternating Action</b>                                                     | YES                         | YES                         | YES                            |
| <b>QuickPowerWash</b>                                                                             | YES                         | YES                         | YES                            |
| <b>Brilliant GlassCare</b>                                                                        | -                           | YES                         | YES                            |
| <b>EcoPower Technology</b>                                                                        | YES                         | YES                         | YES                            |
| <b>Energy Star Rating</b>                                                                         | 3.5                         | 4                           | 4.5                            |
| <b>WELS Star Rating</b>                                                                           | 4.5                         | 6                           | 6                              |
| <b>WELS Registration Number</b>                                                                   | D02486                      | D02494                      | D02882                         |
| <b>Water Consumption in l / Wash</b>                                                              | 9.0                         | 9.2                         | 9.3                            |
| <b>Test Programme Used</b>                                                                        | ECO                         | ECO                         | ECO                            |
| <b>Miele@home</b>                                                                                 | -                           | -                           | YES                            |
| <b>1 Month Supply of UltraTabs All in 1<sup>1</sup></b>                                           | YES                         | YES                         | -                              |
| <b>1 Month Supply of PowerDisk<sup>2</sup></b>                                                    | -                           | -                           | YES                            |
| <b>6 Months Supply of PowerDisk<sup>3</sup></b>                                                   | -                           | -                           | YES                            |

Highlight indicates difference from model to model within the appliance group. ■ New model, check availability. <sup>1</sup>1 month supply equals 20 UltraTab All-in-1 tablets. <sup>2</sup>1 month supply equals 1 PowerDisk cartridge. <sup>3</sup>6 months' supply PowerDisk voucher redeemable at [www.shop.miele.co.nz](http://www.shop.miele.co.nz).

## Dishwasher Specifications - Fully Integrated

G 7659 SCVi XXL



G 7799 SCVi XXL K2O



G 7989 SCVi XXL K2O



|                                                                                          |                                |                                |                                |
|------------------------------------------------------------------------------------------|--------------------------------|--------------------------------|--------------------------------|
| Price                                                                                    | \$3,899 ■                      | \$4,999 ■                      | \$5,399 ■                      |
| Item Number                                                                              | 12531700                       | 12531720                       | 12531740                       |
| Colour                                                                                   | Obsidian Black Fascia          | Obsidian Black Fascia          | Obsidian Black Fascia          |
| Place Settings                                                                           | 15                             | 15                             | 15                             |
| Basket Design                                                                            | ExtraComfort                   | MaxiComfort                    | MaxiComfort                    |
| Cutlery Basket (BK)                                                                      | -                              | -                              | -                              |
| Cutlery Tray (SC)                                                                        | 3D MultiFlex Tray              | 3D MultiFlex Tray              | 3D MultiFlex Tray              |
| Wash Programmes                                                                          | 10                             | 13                             | 13                             |
| Display Type                                                                             | 1-line text display            | 1-line text display            | M Touch Vi                     |
| AutoDos Automatic Detergent Dispensing                                                   | YES                            | YES                            | YES                            |
| AutoStart Function                                                                       | YES                            | YES                            | YES                            |
| Delay Start                                                                              | YES                            | YES                            | YES                            |
| EcoFeedback                                                                              | YES                            | YES                            | YES                            |
| AutoOpen Drying                                                                          | YES                            | YES                            | YES                            |
| AutoClose                                                                                | -                              | YES                            | YES                            |
| Brilliant LED Light                                                                      | -                              | YES                            | YES                            |
| Knock2Open (K2O)                                                                         | -                              | YES                            | YES                            |
| Operation Noise                                                                          | 42 (db)                        | 42 (db)                        | 42 (db)                        |
| Wash Extras / Options:<br>Express / ExtraClean / ExtraDry /<br>IntenseZone / Bottle Wash | YES / YES / YES /<br>YES / YES | YES / YES / YES /<br>YES / YES | YES / YES / YES /<br>YES / YES |
| MultiLingua                                                                              | YES                            | YES                            | YES                            |
| Triple Spray Arms / Alternating Action                                                   | YES                            | YES                            | YES                            |
| QuickPowerWash                                                                           | YES                            | YES                            | YES                            |
| Brilliant GlassCare                                                                      | YES                            | YES                            | YES                            |
| EcoPower Technology                                                                      | YES                            | YES                            | YES                            |
| Energy Star Rating                                                                       | 4.5                            | 4.5                            | 4.5                            |
| WELS Star Rating                                                                         | 6                              | 6                              | 6                              |
| WELS Registration Number                                                                 | D02887                         | D02889                         | D02891                         |
| Water Consumption in l / Wash                                                            | 9.6                            | 9.6                            | 9.6                            |
| Test Programme Used                                                                      | ECO                            | ECO                            | ECO                            |
| Miele@home                                                                               | YES                            | YES                            | YES                            |
| 1 Month Supply of UltraTabs All in 1 <sup>1</sup>                                        | -                              | -                              | -                              |
| 1 Month Supply of PowerDisk <sup>2</sup>                                                 | YES                            | YES                            | YES                            |
| 6 Months Supply of PowerDisk <sup>3</sup>                                                | YES                            | YES                            | YES                            |

Highlight indicates difference from model to model within the appliance group. ■ New model, check availability. <sup>1</sup>1 month supply equals 20 UltraTab All-in-1 tablets. <sup>2</sup>1 month supply equals 1 PowerDisk cartridge. <sup>3</sup>6 months' supply PowerDisk voucher redeemable at [www.shop.miele.co.nz](http://www.shop.miele.co.nz).

## Dishwasher Accessories

| Item no.                                          | Product                | Description                                                                                                                                            | NZD        |
|---------------------------------------------------|------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|------------|
| <b>Suitable for G 5000 and G 7000 dishwashers</b> |                        |                                                                                                                                                        |            |
| 9614020                                           | <b>GBU 5000 *</b>      | Cutlery basket to fit all G 7000 and G 5000 models                                                                                                     | <b>139</b> |
| 10986710                                          | <b>GFV 60/57-7 *</b>   | 60 cm wide CleanSteel door panel, suits all 60 cm wide semi-integrated models with the intention to keep the spacer strips installed                   | <b>425</b> |
| 10986720                                          | <b>GFV 60/60-7 *</b>   | 60 cm wide CleanSteel door panel, suits all 60 cm wide semi-integrated models with the intention to remove the spacer strips                           | <b>425</b> |
| 11526970                                          | <b>GFVi 453/72-7 *</b> | CleanSteel door panel, not pre-drilled, supplied without handle (for use with custom handles), suits all 45 cm wide G 5000, fully integrated models    | <b>510</b> |
| 10986760                                          | <b>GFVi 702/72 *</b>   | 60 cm wide CleanSteel door panel, with H 7000 PureLine oven handle, suits all 60 cm wide fully integrated models                                       | <b>510</b> |
| 10986740                                          | <b>GFVi 701/72 *</b>   | 60 cm wide CleanSteel door panel, not pre-drilled, supplied without handle (for use with custom handles), suits all 60 cm wide fully integrated models | <b>510</b> |

---

**Head office**

8 College Hill  
Freemans Bay, Auckland, 1011

**Miele Experience Centre Auckland**

8 College Hill  
Freemans Bay, Auckland, 1011

**Miele Experience Centre Wellington**

183 Featherston Street  
Wellington, 6011

**Miele Experience Centre Christchurch**

2 Cathedral Square  
Christchurch, 8011

**Telephone**

0800 4 MIELE (0800 464 353)

[www.miele.co.nz](http://www.miele.co.nz)

Trading Conditions: Sales transactions are made between Miele New Zealand Ltd. and the end consumer.

Terms and conditions of sale are outlined on the official GST tax invoice.

The Miele Chartered Agent acts on behalf of Miele New Zealand Ltd.

For further information about our products and services please visit our website:  
[www.miele.co.nz](http://www.miele.co.nz)

This price list is valid throughout New Zealand as from 1 August 2024.

All prices quoted are in New Zealand Dollars, inclusive of GST. Product availability and prices are subject to change without prior notice.