

## Cooker hoods order form customized island hoods

### Basic information

- Model:  PUR 98D  DA 4208D  DA 6698D
- Standard colour:  Stainless steel  Brilliant white  Obsidian black
- Operation mode:  Vented  Recirculation

### Chimney

#### Variant 1 Extension


- Vented: 990 – 1290 mm
- Recirculation: 1050 – 1360 mm

#### Variant 2 Extension

- Vented: 1290 – 1590 mm
- Recirculation: 1350 – 1660 mm

#### Variant 3 Shortening

- Vented: 600 – 900 mm



- Hole on the side:**  left  right  back

- Layout:  for 150mm round hose (with connection)
- square, dimensions: \_\_\_\_\_ (H) x \_\_\_\_\_ (W) mm

- Position:  flush with ceiling (with „35“-mm-base: „Top edge chimney – Center cut-out“: 110mm)
- not flush with ceiling: Dimension „Top edge chimney – Lower edge cut-out“: \_\_\_\_ mm (Minimum lower edge hood – Lower edge hole on the side: 700mm\*)

ATTENTION: Hole on the side only possible with variant 1 and 2 extension. Slanted is no longer possible!

\*725mm at DA 6698D

### RAL colour\*

- Colour of DA and chimney: \_\_\_\_\_

ATTENTION: DA and chimney will get same colour. Customized chimney can also be ordered in same RAL colour!

\*Not possible for DA 6698D