

## Cooker hoods order form customized wall hoods

### Basic information

Model:  PUR 68 W  PUR 98 W  DA 5798 W  DA 4228 W  
 DA 4288 W  DA 4298 W  DA 6698 W

Standard colour:  Stainless steel  Brilliant white  Obsidian black

Operation mode:  Vented  Recirculation

### Chimney

#### Variant 1 Extension


- Vented: 1005 – 1325 mm
- Recirculation: 1135 – 1455 mm

#### Variant 2 Extension

- Vented: 1325 – 1645 mm
- Recirculation: 1455 – 1775 mm

#### Variant 3 Shortening

- Vented: 600 – 895 mm



Hole on the side:  left  right

Layout:  for 150mm round hose (with connection)  
 square, dimensions: \_\_\_\_\_ (H) x \_\_\_\_\_ (W) mm


Position:  flush with ceiling (with „35“mm-base: „Top edge chimney – Center cut-out“: 110mm)  
 not flush with ceiling: Dimension „Top edge chimney – Lower edge cut-out“: \_\_\_mm  
 (Minimum lower edge hood – Lower edge hole on the side: 700mm\*)

ATTENTION: Hole on the side only possible with variant 1 and 2 extension.


\* ATTENTION: Exact dimensions in special table!

## Slanted:

Example: left = higher side



Example: front = higher side



„Higher“ side:

left

right

front

Grade:

\_\_\_\_\_ ° (e)

Total height:

\_\_\_\_\_ mm („Middle“ „A1“) OR \_\_\_\_\_ mm („back“, to wall „A2“)

ATTENTION: Slanted only possible with variant 1 and 2 extension. Min. height shorter side: 600mm

## RAL colour\*

Colour of DA and chimney: \_\_\_\_\_

ATTENTION: DA and chimney will get same colour. Customized chimney can also be ordered in same RAL colour!

\*Not possible for DA 6698W