

Cooker hoods order form customized chimney DADC 6000

Basic information

Model: DA 60x6 W DA 64x8 W DA 679x W DA 699x W

Standard colour: Stainless steel Brilliant white Obsidian black Graphite grey

Operation mode: Vented


Chimney

Variant 1 Extension

Vented: 660 – 955 mm

Variant 2 Extension

Vented: 955 – 1250 mm



Hole on the side: left right


Layout: for 150mm round hose (with connection)
 square, dimensions: _____ (H) x _____ (W) mm

Position: flush with ceiling (with „35“mm-base: „Top edge chimney – Center cut-out“: 110mm)
 not flush with ceiling: Dimension „Top edge chimney – Lower edge cut-out“: ___ mm
 (Minimum lower edge hood – Lower edge hole on the side: 922-949mm*)


* ATTENTION: Exact dimensions in special table!

Abschrägung:

Example: left = higher side



Example: front = higher side



„Higher“ side:

left

right

front

Grade:

_____ ° (e)

Total height:

_____ mm („Middle“ „A1“) OR _____ mm („back“, to wall „A2“)

RAL colour*

Chimney:

Brilliant white

Obsidian black

Graphite grey

*ATTENTION: Only above colours for customized chimneys possible!