

Cooker hoods order form customized wall hoods

Basic information

Model: PUR 68 W PUR 98 W DA 5798 W DA 4228 W
 DA 4288 W DA 4298 W DA 6698 W

Standard colour: Stainless steel Brilliant white Obsidian black

Operation mode: Vented Recirculation

Chimney

Variant 1 Extension


- Vented: 1005 – 1325 mm
- Recirculation: 1135 – 1455 mm

Variant 2 Extension

- Vented: 1325 – 1645 mm
- Recirculation: 1455 – 1775 mm

Variant 3 Shortening

- Vented: 600 – 895 mm



Hole on the side: left right

Layout: for 150mm round hose (with connection)
 square, dimensions: _____ (H) x _____ (W) mm


Position: flush with ceiling (with „35“mm-base: „Top edge chimney – Center cut-out“: 110mm)
 not flush with ceiling: Dimension „Top edge chimney – Lower edge cut-out“: ___mm
 (Minimum lower edge hood – Lower edge hole on the side: 700mm*)

ATTENTION: Hole on the side only possible with variant 1 and 2 extension.


* ATTENTION: Exact dimensions in special table!

Slanted:

Example: left = higher side



Example: front = higher side



„Higher“ side:

left

right

front

Grade:

_____ ° (e)

Total height:

_____ mm („Middle“ „A1“) OR _____ mm („back“, to wall „A2“)

ATTENTION: Slanted only possible with variant 1 and 2 extension. Min. height shorter side: 600mm

RAL colour*

Colour of DA and chimney: _____

ATTENTION: DA and chimney will get same colour. Customized chimney can also be ordered in same RAL colour!

*Not possible for DA 6698W