

Cooker hoods order form customized island hoods

Basic information

Model: PUR 98D DA 4208D DA 6698D

Standard colour: Stainless steel Brilliant white Obsidian black

Operation mode: Vented Recirculation

Chimney

Variant 1 Extension

Vented: 990 – 1290 mm

Recirculation: 1050 – 1360 mm


Variant 2 Extension

Vented: 1290 – 1590 mm

Recirculation: 1350 – 1660 mm

Variant 3 Shortening

Vented: 600 – 900 mm



Hole on the side: left right back

Layout: for 150mm round hose (with connection)

square, dimensions: _____ (H) x _____ (W) mm

Position: flush with ceiling (with „35“-mm-base: „Top edge chimney – Center cut-out“: 110mm)

not flush with ceiling: Dimension „Top edge chimney – Lower edge cut-out“: ____ mm
(Minimum lower edge hood – Lower edge hole on the side: 700mm*)

ATTENTION: Hole on the side only possible with variant 1 and 2 extension. Slanted is no longer possible!

*725mm at DA 6698D

RAL colour*

Colour of DA and chimney: _____

ATTENTION: DA and chimney will get same colour. Customized chimney can also be ordered in same RAL colour!

*Not possible for DA 6698D